

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331477-927

Luminaire Tested: **S122DIW-S290D970U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331477-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4101.3 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25				
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22				
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	25	24	19				
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16				
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14				
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16	12				
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11				
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.1
10°-20°	129.6	3.2
20°-30°	188.1	4.6
30°-40°	198.5	4.8
40°-50°	175.8	4.3
50°-60°	140.3	3.4
60°-70°	95.4	2.3
70°-80°	48.9	1.2
80°-90°	14.4	0.4
90°-100°	34.9	0.9
100°-110°	128.0	3.1
110°-120°	342.1	8.3
120°-130°	564.7	13.8
130°-140°	600.5	14.6
140°-150°	558.1	13.6
150°-160°	448.7	10.9
160°-170°	289.2	7.1
170°-180°	99.5	2.4
0°-30°	362.4	8.8
0°-40°	560.9	13.7
0°-60°	877.0	21.4
0°-90°	1035.6	25.3
90°-120°	504.9	12.3
90°-150°	2228.2	54.3
90°-180°	3066.0	74.8
0°-180°	4101.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	20	1	20	1	20	9
95°	33	49	33	49	33	30
105°	58	230	58	230	58	60
115°	62	435	62	435	62	155
125°	647	615	647	615	647	560
135°	786	762	786	762	786	606
145°	897	883	897	883	897	561
155°	973	973	973	973	973	449
165°	1023	1025	1023	1025	1023	289
175°	1042	1048	1042	1048	1042	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	7.8	7.8	7.8	7.6	7.5	7.6	7.4	7.1	7.1	7.1	7.0
90°	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8	16.0	15.1	13.8
92.5°	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5	18.0	17.6	16.9
95°	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2	30.3	29.5	28.4
97.5°	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9	40.2	39.5	36.8
100°	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9	44.5	43.2	40.3
102.5°	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8	46.1	44.4	68.3
105°	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9	48.0	46.2	92.1
107.5°	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8	62.7	64.6	119.7
110°	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8	115.7	132.5	181.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4	272.7	334.1	346.1
115°	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2	389.1	467.1	462.9
117.5°	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6	498.4	517.3	514.4
120°	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9	556.9	554.8	551.8
122.5°	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0	591.8	590.6	587.2
125°	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0	640.8	639.6	636.4
127.5°	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3	685.6	683.8	681.4
130°	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0	714.2	712.3	710.4
132.5°	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9	742.4	740.8	738.9
135°	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8	782.1	780.5	778.9
137.5°	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8	819.2	817.5	815.8
140°	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8	843.3	841.8	839.9
142.5°	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9	865.5	864.1	862.1
145°	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9	896.7	895.5	892.6
147.5°	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8	923.9	923.1	920.2
150°	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4	940.4	939.4	936.7
152.5°	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6	955.5	954.5	952.0
155°	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0	976.0	974.9	973.0
157.5°	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2	993.1	991.9	990.5
160°	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2	1003.2	1002.2	1001.2
162.5°	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6	1012.4	1011.3	1010.4
165°	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6	1022.2
167.5°	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5	1033.3	1032.2	1031.7
170°	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4	1038.2	1037.0	1036.7
172.5°	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0	1041.9	1040.7	1040.3
175°	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9	1045.8	1044.6	1044.3
177.5°	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4	1046.5	1045.5	1045.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	6.8	6.6	6.3	6.3	5.5	5.1	4.1	3.3	3.6	3.8	3.9
90°	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3	15.1	15.0	14.8
95°	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2	43.6	38.1	32.6
97.5°	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7	82.0	66.4	50.7
100°	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0	110.9	87.9	64.9
102.5°	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0	169.1	164.2	159.3
105°	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1	235.2	240.2	245.3
107.5°	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1	298.3	302.3	306.3
110°	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3	338.9	342.4	345.9



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1	377.2	380.3	383.5
115°	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2	438.1	441.0	443.9
117.5°	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9	493.1	496.3	499.5
120°	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9	532.4	534.9	537.4
122.5°	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8	566.4	569.1	571.7
125°	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4	617.6	619.8	621.9
127.5°	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2	664.6	667.0	669.5
130°	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9	694.6	697.3	699.9
132.5°	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2	724.5	726.7	729.0
135°	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5	764.2	766.9	769.6
137.5°	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3	803.2	805.1	807.0
140°	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4	828.7	830.0	831.4
142.5°	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1	850.3	851.6	852.8
145°	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4	883.2	883.0	882.9
147.5°	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2	912.5	911.9	911.2
150°	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6	931.4	930.2	929.1
152.5°	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0	947.6	946.3	945.0
155°	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7	971.1	969.6	968.1
157.5°	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3	990.1	988.7	987.5
160°	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1001.2	1000.2	999.2
162.5°	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9	1010.9	1009.9	1008.8
165°	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9	1023.9	1022.9	1021.9
167.5°	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6	1033.6	1032.6	1031.6
170°	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1	1039.0	1038.1	1037.0
172.5°	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7	1042.7	1041.6	1040.7
175°	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4	1047.2	1046.0	1044.9
177.5°	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2	1048.2	1047.3	1046.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	4.0	4.3	4.4	4.7	4.8	4.9	4.9	5.1	5.2	5.1	5.2
90°	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8	17.7	18.5	19.1
92.5°	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5	18.9	19.3	19.6
95°	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2	32.1	32.9	33.2
97.5°	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9	41.5	42.2	42.6
100°	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9	47.2	48.6	49.4
102.5°	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8	49.6	51.3	52.4
105°	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9	51.7	53.6	54.8
107.5°	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8	59.0	57.1	56.5
110°	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8	82.0	65.2	57.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4	150.0	88.6	58.2
115°	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2	233.4	155.5	110.5
117.5°	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6	460.8	442.0	412.6
120°	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9	560.9	562.9	552.5
122.5°	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0	594.2	595.4	593.8
125°	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0	643.2	644.4	645.2
127.5°	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3	689.0	690.7	691.6
130°	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0	717.9	719.7	720.6
132.5°	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9	745.5	747.1	747.8
135°	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8	785.4	787.1	787.8
137.5°	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8	822.4	824.1	824.7
140°	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8	846.3	847.8	848.1
142.5°	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9	868.3	869.7	869.9
145°	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9	899.0	900.2	900.4
147.5°	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8	925.7	926.5	926.6
150°	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4	942.4	943.4	943.5
152.5°	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6	957.5	958.5	958.5
155°	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0	977.9	979.0	978.8
157.5°	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2	995.4	996.5	996.4
160°	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2	1005.2	1006.2	1006.2
162.5°	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6	1014.7	1015.9	1015.7
165°	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4
167.5°	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5	1035.7	1036.9	1036.7
170°	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4	1040.5	1041.7	1041.6
172.5°	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0	1044.2	1045.4	1045.2
175°	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9	1048.1	1049.3	1049.1
177.5°	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4	1048.3	1049.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	5.3	5.2	5.3	5.2	5.3	5.2	5.3	5.2	5.1	5.2	5.1
90°	19.4	19.7	20.1	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8
92.5°	19.8	20.0	20.2	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5
95°	33.0	32.9	32.7	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2
97.5°	42.9	43.0	43.3	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9
100°	49.7	50.1	50.4	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9
102.5°	52.9	53.4	53.9	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8
105°	55.5	56.2	56.9	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9
107.5°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8
110°	57.8	58.5	59.1	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	58.8	59.3	59.9	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4
115°	98.4	86.3	74.1	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2
117.5°	372.8	333.0	293.3	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6
120°	529.9	507.2	484.4	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9
122.5°	589.4	585.0	580.6	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0
125°	645.7	646.2	646.7	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0
127.5°	691.7	691.8	691.9	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3
130°	720.3	720.2	720.0	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0
132.5°	747.6	747.4	747.3	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9
135°	787.5	787.1	786.8	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8
137.5°	824.1	823.5	822.9	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8
140°	847.3	846.4	845.6	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8
142.5°	869.1	868.2	867.4	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9
145°	899.5	898.7	897.9	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9
147.5°	925.9	925.2	924.5	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8
150°	942.7	941.8	941.0	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4
152.5°	957.4	956.3	955.2	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6
155°	977.5	976.1	974.8	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0
157.5°	995.1	993.8	992.4	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2
160°	1005.0	1003.8	1002.7	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2
162.5°	1014.2	1012.8	1011.4	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6
165°	1026.2	1025.0	1023.8	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0
167.5°	1035.2	1033.7	1032.2	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5
170°	1040.1	1038.6	1037.0	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4
172.5°	1043.7	1042.2	1040.7	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0
175°	1047.3	1045.7	1044.0	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9
177.5°	1047.9	1046.7	1045.5	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	4.9	4.9	4.8	4.7	4.4	4.3	4.0	3.9	3.8	3.6	3.3
90°	16.0	15.1	13.8	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8
92.5°	18.0	17.6	16.9	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3
95°	30.3	29.5	28.4	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2
97.5°	40.2	39.5	36.8	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7
100°	44.5	43.2	40.3	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0
102.5°	46.1	44.4	68.3	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0
105°	48.0	46.2	92.1	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1
107.5°	62.7	64.6	119.7	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1
110°	115.7	132.5	181.1	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.7	334.1	346.1	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1
115°	389.1	467.1	462.9	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2
117.5°	498.4	517.3	514.4	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9
120°	556.9	554.8	551.8	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9
122.5°	591.8	590.6	587.2	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8
125°	640.8	639.6	636.4	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4
127.5°	685.6	683.8	681.4	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2
130°	714.2	712.3	710.4	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9
132.5°	742.4	740.8	738.9	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2
135°	782.1	780.5	778.9	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5
137.5°	819.2	817.5	815.8	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3
140°	843.3	841.8	839.9	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4
142.5°	865.5	864.1	862.1	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1
145°	896.7	895.5	892.6	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4
147.5°	923.9	923.1	920.2	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2
150°	940.4	939.4	936.7	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6
152.5°	955.5	954.5	952.0	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0
155°	976.0	974.9	973.0	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7
157.5°	993.1	991.9	990.5	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3
160°	1003.2	1002.2	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2
162.5°	1012.4	1011.3	1010.4	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9
165°	1023.8	1022.6	1022.2	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9
167.5°	1033.3	1032.2	1031.7	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6
170°	1038.2	1037.0	1036.7	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1
172.5°	1041.9	1040.7	1040.3	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7
175°	1045.8	1044.6	1044.3	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4
177.5°	1046.5	1045.5	1045.4	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.1	5.1	5.5	6.3	6.3	6.6	6.8	7.0	7.1	7.1	7.1
90°	2.6	4.4	6.3	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8
92.5°	15.1	15.0	14.8	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5
95°	43.6	38.1	32.6	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2
97.5°	82.0	66.4	50.7	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9
100°	110.9	87.9	64.9	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9
102.5°	169.1	164.2	159.3	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8
105°	235.2	240.2	245.3	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9
107.5°	298.3	302.3	306.3	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8
110°	338.9	342.4	345.9	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	377.2	380.3	383.5	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4
115°	438.1	441.0	443.9	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2
117.5°	493.1	496.3	499.5	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6
120°	532.4	534.9	537.4	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9
122.5°	566.4	569.1	571.7	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0
125°	617.6	619.8	621.9	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0
127.5°	664.6	667.0	669.5	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3
130°	694.6	697.3	699.9	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0
132.5°	724.5	726.7	729.0	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9
135°	764.2	766.9	769.6	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8
137.5°	803.2	805.1	807.0	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8
140°	828.7	830.0	831.4	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8
142.5°	850.3	851.6	852.8	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9
145°	883.2	883.0	882.9	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9
147.5°	912.5	911.9	911.2	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8
150°	931.4	930.2	929.1	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4
152.5°	947.6	946.3	945.0	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6
155°	971.1	969.6	968.1	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0
157.5°	990.1	988.7	987.5	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2
160°	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2
162.5°	1010.9	1009.9	1008.8	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6
165°	1023.9	1022.9	1021.9	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0
167.5°	1033.6	1032.6	1031.6	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5
170°	1039.0	1038.1	1037.0	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4
172.5°	1042.7	1041.6	1040.7	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0
175°	1047.2	1046.0	1044.9	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9
177.5°	1048.2	1047.3	1046.3	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	7.4	7.6	7.5	7.6	7.8	7.8	7.8
90°	17.7	18.5	19.1	19.4	19.7	20.1	20.4
92.5°	18.9	19.3	19.6	19.8	20.0	20.2	20.4
95°	32.1	32.9	33.2	33.0	32.9	32.7	32.6
97.5°	41.5	42.2	42.6	42.9	43.0	43.3	43.4
100°	47.2	48.6	49.4	49.7	50.1	50.4	50.7
102.5°	49.6	51.3	52.4	52.9	53.4	53.9	54.3
105°	51.7	53.6	54.8	55.5	56.2	56.9	57.5
107.5°	59.0	57.1	56.5	57.2	57.8	58.5	59.2
110°	82.0	65.2	57.1	57.8	58.5	59.1	59.8



TEST NUMBER: P331477-927

CATALOG NUMBER: S122DIW-S290D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	150.0	88.6	58.2	58.8	59.3	59.9	60.4
115°	233.4	155.5	110.5	98.4	86.3	74.1	62.1
117.5°	460.8	442.0	412.6	372.8	333.0	293.3	253.4
120°	560.9	562.9	552.5	529.9	507.2	484.4	461.8
122.5°	594.2	595.4	593.8	589.4	585.0	580.6	576.2
125°	643.2	644.4	645.2	645.7	646.2	646.7	647.2
127.5°	689.0	690.7	691.6	691.7	691.8	691.9	692.0
130°	717.9	719.7	720.6	720.3	720.2	720.0	719.9
132.5°	745.5	747.1	747.8	747.6	747.4	747.3	747.1
135°	785.4	787.1	787.8	787.5	787.1	786.8	786.5
137.5°	822.4	824.1	824.7	824.1	823.5	822.9	822.4
140°	846.3	847.8	848.1	847.3	846.4	845.6	844.8
142.5°	868.3	869.7	869.9	869.1	868.2	867.4	866.6
145°	899.0	900.2	900.4	899.5	898.7	897.9	897.0
147.5°	925.7	926.5	926.6	925.9	925.2	924.5	923.8
150°	942.4	943.4	943.5	942.7	941.8	941.0	940.2
152.5°	957.5	958.5	958.5	957.4	956.3	955.2	954.1
155°	977.9	979.0	978.8	977.5	976.1	974.8	973.4
157.5°	995.4	996.5	996.4	995.1	993.8	992.4	991.2
160°	1005.2	1006.2	1006.2	1005.0	1003.8	1002.7	1001.5
162.5°	1014.7	1015.9	1015.7	1014.2	1012.8	1011.4	1010.0
165°	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6
167.5°	1035.7	1036.9	1036.7	1035.2	1033.7	1032.2	1030.7
170°	1040.5	1041.7	1041.6	1040.1	1038.6	1037.0	1035.5
172.5°	1044.2	1045.4	1045.2	1043.7	1042.2	1040.7	1039.2
175°	1048.1	1049.3	1049.1	1047.3	1045.7	1044.0	1042.4
177.5°	1048.3	1049.2	1049.2	1047.9	1046.7	1045.5	1044.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1

(END OF REPORT)