

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331783-930

Luminaire Tested: **S122RDIW-S290D1440U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331783-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D1440U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5541.9 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	64	64	64	43	43	43	24	24	24	15
1	90	86	82	79	79	76	73	70	56	54	52	38	37	36	22	21	21	13
2	82	75	70	65	72	66	62	58	49	46	44	34	32	30	19	18	18	11
3	75	66	59	54	65	58	53	48	43	40	37	30	28	26	17	16	15	10
4	68	58	51	46	60	52	45	41	39	34	31	27	24	22	15	14	13	8
5	63	52	44	39	55	46	40	35	34	30	27	24	21	19	14	12	11	7
6	58	46	39	33	50	41	35	30	31	27	23	21	19	17	13	11	10	7
7	53	42	34	29	47	37	31	26	28	24	20	19	17	15	11	10	9	6
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	10	9	8	5
9	46	34	27	22	40	30	24	20	23	19	16	16	13	12	10	8	7	5
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	0.7
10°-20°	105.2	1.9
20°-30°	147.7	2.7
30°-40°	161.1	2.9
40°-50°	148.1	2.7
50°-60°	116.3	2.1
60°-70°	75.8	1.4
70°-80°	39.1	0.7
80°-90°	14.1	0.3
90°-100°	53.5	1.0
100°-110°	196.0	3.5
110°-120°	524.0	9.5
120°-130°	865.0	15.6
130°-140°	919.9	16.6
140°-150°	855.0	15.4
150°-160°	687.4	12.4
160°-170°	443.0	8.0
170°-180°	152.5	2.8
0°-30°	291.2	5.3
0°-40°	452.3	8.2
0°-60°	716.7	12.9
0°-90°	845.7	15.3
90°-120°	773.5	14.0
90°-150°	3413.3	61.6
90°-180°	4696.0	84.7
0°-180°	5541.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	14	23	29	31	4
95°	75	40	45	51	50	92
105°	352	368	71	83	88	377
115°	667	687	715	204	95	656
125°	943	958	980	988	991	840
135°	1166	1185	1196	1206	1205	901
145°	1353	1353	1372	1379	1374	846
155°	1490	1481	1494	1500	1491	686
165°	1570	1564	1566	1574	1566	443
175°	1606	1598	1600	1607	1597	153
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	5.0	5.0	5.1	5.1	5.1	5.4	5.8	6.2	6.6	7.0	7.2
90°	1.1	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5
92.5°	23.4	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6
95°	75.3	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5
97.5°	149.6	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6
100°	205.2	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2
102.5°	266.4	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6
105°	352.5	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5
107.5°	450.6	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1
110°	513.7	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2



TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	573.1	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8
115°	666.8	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1
117.5°	750.5	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6
120°	811.7	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0
122.5°	863.6	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5
125°	942.7	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6
127.5°	1014.4	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2
130°	1059.8	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0
132.5°	1106.2	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2
135°	1166.5	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1
137.5°	1227.5	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8
140°	1267.4	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8
142.5°	1300.8	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8
145°	1353.2	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5
147.5°	1398.9	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3
150°	1428.6	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6
152.5°	1453.6	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7
155°	1490.0	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0
157.5°	1518.6	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3
160°	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8
162.5°	1550.0	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9
165°	1570.0	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4
167.5°	1584.9	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0
170°	1593.3	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4
172.5°	1598.8	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9
175°	1606.0	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0
177.5°	1607.1	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	7.4	7.6	7.7	7.9	8.0	8.2	8.2	8.3
90°	25.8	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.2	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	47.8	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	62.6	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	70.2	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	73.3	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	76.4	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	93.3	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	151.4	125.6	99.9	87.5	88.5	89.5	90.6	91.6





TEST NUMBER: P331783-930

CATALOG NUMBER: S122RDIW-S290D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	323.8	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	476.9	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	734.7	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	856.1	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	908.4	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	983.4	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1052.8	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1096.8	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1139.5	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1200.6	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1257.4	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1294.0	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1328.0	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1375.3	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1416.7	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1442.1	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1465.3	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1496.6	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1523.0	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1538.3	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1552.7	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1584.8	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1592.2	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1597.7	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1603.8	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1604.4	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)