

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331767-930

Luminaire Tested: **S122RDIW-S290D435U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331767-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D435U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2254.2 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	18	16	14	12
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.7
10°-20°	105.2	4.7
20°-30°	147.7	6.6
30°-40°	161.1	7.1
40°-50°	148.1	6.6
50°-60°	116.3	5.2
60°-70°	75.8	3.4
70°-80°	39.1	1.7
80°-90°	11.3	0.5
90°-100°	16.1	0.7
100°-110°	58.9	2.6
110°-120°	157.5	7.0
120°-130°	259.9	11.5
130°-140°	276.4	12.3
140°-150°	256.9	11.4
150°-160°	206.6	9.2
160°-170°	133.1	5.9
170°-180°	45.8	2.0
0°-30°	291.2	12.9
0°-40°	452.3	20.1
0°-60°	716.7	31.8
0°-90°	842.9	37.4
90°-120°	232.4	10.3
90°-150°	1025.8	45.5
90°-180°	1411.0	62.6
0°-180°	2254.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	0	4	7	9	9	2
95°	23	12	14	15	15	28
105°	106	110	21	25	26	113
115°	200	206	215	61	28	197
125°	283	288	294	297	298	252
135°	351	356	359	362	362	271
145°	407	407	412	414	413	254
155°	448	445	449	451	448	206
165°	472	470	471	473	471	133
175°	483	480	481	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.8	4.5	4.1	3.8	3.4	3.3	3.4	3.5	3.7	3.8	3.8
90°	0.3	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3
92.5°	7.0	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3
95°	22.7	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9
97.5°	44.9	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5
100°	61.7	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5
102.5°	80.1	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2
105°	105.9	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1
107.5°	135.4	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9
110°	154.3	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2



TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.2	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6
115°	200.4	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1
117.5°	225.5	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5
120°	243.9	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3
122.5°	259.5	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5
125°	283.3	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0
127.5°	304.8	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6
130°	318.5	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7
132.5°	332.5	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8
135°	350.6	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0
137.5°	368.9	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1
140°	380.9	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2
142.5°	390.9	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4
145°	406.7	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8
147.5°	420.4	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3
150°	429.3	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9
152.5°	436.8	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9
155°	447.8	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3
157.5°	456.3	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1
160°	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9
162.5°	465.9	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1
165°	471.8	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3
167.5°	476.3	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7
170°	478.8	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9
172.5°	480.5	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6
175°	482.7	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4
177.5°	483.0	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	3.8	3.8	3.8	3.8	3.8	3.9	3.9	4.0
90°	7.7	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.5	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.3	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	18.8	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.1	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.0	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.0	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	28.0	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	45.5	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331767-930

CATALOG NUMBER: S122RDIW-S290D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	97.3	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	143.3	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	220.8	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	257.3	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.0	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	295.5	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	316.4	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	329.6	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	342.5	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	360.9	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	377.9	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	388.9	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.1	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.4	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	425.7	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.4	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.3	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	449.8	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	457.7	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.3	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	466.6	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.3	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	478.5	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.1	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.0	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.2	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)