

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331513-927

Luminaire Tested: **S122DIW-S485D1240U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331513-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D1240U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5626.3 lumens  
Efficiency: N/A  
Efficacy: 104.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.3	1.3
10°-20°	213.1	3.8
20°-30°	309.3	5.5
30°-40°	326.4	5.8
40°-50°	289.0	5.1
50°-60°	230.6	4.1
60°-70°	156.8	2.8
70°-80°	80.4	1.4
80°-90°	22.7	0.4
90°-100°	44.7	0.8
100°-110°	163.8	2.9
110°-120°	437.9	7.8
120°-130°	722.9	12.8
130°-140°	768.8	13.7
140°-150°	714.5	12.7
150°-160°	574.5	10.2
160°-170°	370.2	6.6
170°-180°	127.4	2.3
0°-30°	595.8	10.6
0°-40°	922.2	16.4
0°-60°	1441.8	25.6
0°-90°	1701.6	30.2
90°-120°	646.4	11.5
90°-150°	2852.5	50.7
90°-180°	3925.0	69.8
0°-180°	5626.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	26	1	26	1	26	12
95°	42	63	42	63	42	39
105°	74	295	74	295	74	77
115°	80	557	80	557	80	199
125°	828	788	828	788	828	717
135°	1007	975	1007	975	1007	776
145°	1148	1131	1148	1131	1148	718
155°	1246	1245	1246	1245	1246	575
165°	1309	1312	1309	1312	1309	370
175°	1334	1342	1334	1342	1334	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	11.4	11.3	11.5	11.1	11.0	11.1	10.9	10.5	10.5	10.5	10.4
90°	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5	20.4	19.4	17.7
92.5°	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6	23.1	22.5	21.6
95°	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9	38.9	37.8	36.3
97.5°	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3	51.4	50.6	47.1
100°	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7	57.0	55.2	51.6
102.5°	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2	59.0	56.8	87.4
105°	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8	61.5	59.1	117.9
107.5°	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0	80.3	82.8	153.3
110°	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5	148.1	169.6	231.8



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6	349.2	427.7	443.1
115°	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5	498.2	597.9	592.6
117.5°	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0	638.1	662.3	658.5
120°	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5	712.9	710.3	706.5
122.5°	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1	757.6	756.1	751.9
125°	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9	820.4	818.9	814.8
127.5°	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8	877.7	875.4	872.4
130°	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6	914.3	911.9	909.5
132.5°	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4	950.3	948.3	945.9
135°	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4	1001.2	999.1	997.1
137.5°	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8	1048.7	1046.6	1044.3
140°	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5	1079.5	1077.6	1075.2
142.5°	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8	1108.0	1106.3	1103.5
145°	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4	1147.9	1146.4	1142.7
147.5°	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9	1182.8	1181.6	1178.1
150°	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1	1203.9	1202.6	1199.1
152.5°	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6	1223.3	1221.9	1218.7
155°	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7	1249.4	1248.2	1245.5
157.5°	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8	1271.3	1269.9	1268.0
160°	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6	1284.3	1283.0	1281.8
162.5°	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6	1296.1	1294.7	1293.6
165°	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2	1308.5
167.5°	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4	1322.9	1321.4	1320.8
170°	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6	1329.1	1327.6	1327.1
172.5°	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2	1333.7	1332.2	1331.8
175°	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3	1338.8	1337.3	1336.9
177.5°	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8	1339.7	1338.5	1338.2
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	10.3	10.0	9.6	9.7	8.5	8.0	6.6	5.4	5.6	5.9	5.9
90°	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6	19.3	19.2	18.9
95°	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0	55.8	48.8	41.7
97.5°	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0	105.0	84.9	65.0
100°	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5	142.0	112.5	83.0
102.5°	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7	216.4	210.2	204.0
105°	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6	301.0	307.5	313.9
107.5°	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6	381.8	387.0	392.2
110°	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3	433.8	438.3	442.8





TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9	482.9	486.9	490.9
115°	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2	560.9	564.5	568.2
117.5°	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2	631.3	635.3	639.4
120°	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3	681.6	684.8	688.0
122.5°	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8	725.2	728.6	732.0
125°	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8	790.6	793.4	796.2
127.5°	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7	850.8	853.9	857.1
130°	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7	889.1	892.6	896.0
132.5°	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5	927.4	930.3	933.3
135°	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9	978.3	981.8	985.2
137.5°	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8	1028.3	1030.6	1033.1
140°	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1	1060.9	1062.6	1064.3
142.5°	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1	1088.6	1090.2	1091.7
145°	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8	1130.7	1130.4	1130.2
147.5°	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0	1168.2	1167.4	1166.6
150°	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9	1192.4	1190.9	1189.3
152.5°	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8	1213.1	1211.4	1209.7
155°	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2	1243.3	1241.3	1239.4
157.5°	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1	1267.4	1265.7	1264.2
160°	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1281.8	1280.4	1279.1
162.5°	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5	1294.1	1292.8	1291.6
165°	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1	1310.8	1309.5	1308.2
167.5°	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5	1323.2	1321.9	1320.6
170°	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5	1330.2	1328.9	1327.6
172.5°	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1	1334.8	1333.6	1332.2
175°	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1	1340.6	1339.1	1337.6
177.5°	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1	1341.9	1340.7	1339.5
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	6.1	6.3	6.4	6.7	6.8	7.0	7.0	7.1	7.4	7.1	7.3
90°	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5	22.6	23.7	24.5
92.5°	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6	24.2	24.7	25.1
95°	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9	41.0	42.1	42.5
97.5°	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3	53.2	54.0	54.6
100°	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7	60.4	62.1	63.2
102.5°	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2	63.5	65.8	67.2
105°	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8	66.2	68.6	70.2
107.5°	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0	75.5	73.1	72.3
110°	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5	105.0	83.4	73.1



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6	192.1	113.5	74.5
115°	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5	298.8	199.1	141.5
117.5°	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0	589.9	565.8	528.2
120°	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5	718.0	720.6	707.4
122.5°	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1	760.7	762.2	760.2
125°	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9	823.4	824.9	825.9
127.5°	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8	882.0	884.2	885.4
130°	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6	919.0	921.3	922.4
132.5°	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4	954.3	956.4	957.3
135°	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4	1005.5	1007.7	1008.5
137.5°	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8	1052.9	1055.0	1055.7
140°	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5	1083.4	1085.4	1085.8
142.5°	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8	1111.6	1113.3	1113.6
145°	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4	1150.9	1152.4	1152.6
147.5°	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9	1185.0	1186.1	1186.2
150°	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1	1206.5	1207.8	1207.8
152.5°	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6	1225.8	1227.2	1227.1
155°	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7	1252.0	1253.3	1253.1
157.5°	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8	1274.2	1275.7	1275.6
160°	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6	1286.9	1288.2	1288.1
162.5°	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6	1299.0	1300.5	1300.3
165°	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2
167.5°	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4	1325.9	1327.4	1327.2
170°	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6	1332.1	1333.6	1333.4
172.5°	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2	1336.7	1338.2	1338.1
175°	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3	1341.8	1343.3	1343.0
177.5°	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8	1342.0	1343.3	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	7.4	7.2	7.3	7.1	7.3	7.2	7.4	7.3	7.1	7.4	7.1
90°	24.9	25.3	25.7	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5
92.5°	25.3	25.7	25.9	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6
95°	42.3	42.1	41.9	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9
97.5°	54.8	55.1	55.4	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3
100°	63.6	64.1	64.5	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7
102.5°	67.7	68.4	69.0	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2
105°	71.1	71.9	72.8	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8
107.5°	73.2	74.1	74.9	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0
110°	74.0	74.9	75.7	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	75.3	76.0	76.6	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6
115°	126.0	110.5	95.0	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5
117.5°	477.3	426.4	375.4	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0
120°	678.3	649.3	620.2	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5
122.5°	754.6	748.9	743.3	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1
125°	826.6	827.3	827.9	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9
127.5°	885.5	885.7	885.7	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8
130°	922.2	922.0	921.8	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6
132.5°	957.1	956.9	956.6	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4
135°	1008.1	1007.7	1007.3	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4
137.5°	1054.9	1054.2	1053.5	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8
140°	1084.7	1083.6	1082.5	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5
142.5°	1112.6	1111.5	1110.4	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8
145°	1151.5	1150.5	1149.4	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4
147.5°	1185.3	1184.4	1183.5	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9
150°	1206.8	1205.7	1204.6	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1
152.5°	1225.7	1224.2	1222.8	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6
155°	1251.3	1249.7	1247.9	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7
157.5°	1273.9	1272.2	1270.6	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8
160°	1286.6	1285.1	1283.6	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6
162.5°	1298.5	1296.6	1294.7	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6
165°	1313.7	1312.2	1310.7	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2
167.5°	1325.2	1323.3	1321.4	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4
170°	1331.5	1329.5	1327.6	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6
172.5°	1336.1	1334.2	1332.2	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2
175°	1340.8	1338.7	1336.5	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3
177.5°	1341.6	1340.0	1338.5	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	7.0	7.0	6.8	6.7	6.4	6.3	6.1	5.9	5.9	5.6	5.4
90°	20.4	19.4	17.7	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0
92.5°	23.1	22.5	21.6	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6
95°	38.9	37.8	36.3	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0
97.5°	51.4	50.6	47.1	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0
100°	57.0	55.2	51.6	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5
102.5°	59.0	56.8	87.4	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7
105°	61.5	59.1	117.9	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6
107.5°	80.3	82.8	153.3	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6
110°	148.1	169.6	231.8	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.2	427.7	443.1	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9
115°	498.2	597.9	592.6	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2
117.5°	638.1	662.3	658.5	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2
120°	712.9	710.3	706.5	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3
122.5°	757.6	756.1	751.9	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8
125°	820.4	818.9	814.8	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8
127.5°	877.7	875.4	872.4	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7
130°	914.3	911.9	909.5	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7
132.5°	950.3	948.3	945.9	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5
135°	1001.2	999.1	997.1	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9
137.5°	1048.7	1046.6	1044.3	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8
140°	1079.5	1077.6	1075.2	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1
142.5°	1108.0	1106.3	1103.5	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1
145°	1147.9	1146.4	1142.7	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8
147.5°	1182.8	1181.6	1178.1	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0
150°	1203.9	1202.6	1199.1	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9
152.5°	1223.3	1221.9	1218.7	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8
155°	1249.4	1248.2	1245.5	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2
157.5°	1271.3	1269.9	1268.0	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1
160°	1284.3	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0
162.5°	1296.1	1294.7	1293.6	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5
165°	1310.7	1309.2	1308.5	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1
167.5°	1322.9	1321.4	1320.8	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5
170°	1329.1	1327.6	1327.1	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5
172.5°	1333.7	1332.2	1331.8	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1
175°	1338.8	1337.3	1336.9	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1
177.5°	1339.7	1338.5	1338.2	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.6	8.0	8.5	9.7	9.6	10.0	10.3	10.4	10.5	10.5	10.5
90°	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5
92.5°	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6
95°	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9
97.5°	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3
100°	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7
102.5°	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2
105°	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8
107.5°	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0
110°	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5





TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6
115°	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5
117.5°	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0
120°	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5
122.5°	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1
125°	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9
127.5°	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8
130°	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6
132.5°	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4
135°	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4
137.5°	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8
140°	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5
142.5°	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8
145°	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4
147.5°	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9
150°	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1
152.5°	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6
155°	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7
157.5°	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8
160°	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6
162.5°	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6
165°	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2
167.5°	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4
170°	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6
172.5°	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2
175°	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3
177.5°	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	10.9	11.1	11.0	11.1	11.5	11.3	11.4
90°	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	105.0	83.4	73.1	74.0	74.9	75.7	76.5



TEST NUMBER: P331513-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)