

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331520-927

Luminaire Tested: **S122DIW-S485D1440U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331520-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1440U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5661.1 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	26				
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	22				
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19				
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17				
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15				
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13				
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12				
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	11				
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10				
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.3
10°-20°	213.1	3.8
20°-30°	309.3	5.5
30°-40°	326.4	5.8
40°-50°	289.0	5.1
50°-60°	230.6	4.1
60°-70°	156.8	2.8
70°-80°	80.4	1.4
80°-90°	25.0	0.4
90°-100°	89.7	1.6
100°-110°	278.5	4.9
110°-120°	476.1	8.4
120°-130°	626.1	11.1
130°-140°	702.7	12.4
140°-150°	689.0	12.2
150°-160°	577.9	10.2
160°-170°	383.3	6.8
170°-180°	134.0	2.4
0°-30°	595.8	10.5
0°-40°	922.2	16.3
0°-60°	1441.8	25.5
0°-90°	1704.0	30.1
90°-120°	844.3	14.9
90°-150°	2862.0	50.6
90°-180°	3957.0	69.9
0°-180°	5661.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	19
90°	41	1	41	1	41	18
95°	74	62	74	62	74	83
105°	265	257	265	257	265	279
115°	478	478	478	478	478	472
125°	697	695	697	695	697	622
135°	910	899	910	899	910	700
145°	1104	1092	1104	1092	1104	689
155°	1258	1248	1258	1248	1258	579
165°	1359	1358	1359	1358	1359	383
175°	1408	1413	1408	1413	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	14.3	14.3	14.4	14.1	14.1	14.3	14.4	14.3	14.7	15.0	14.0
90°	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7	41.3	41.8	36.0
92.5°	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2	38.1	37.9	36.6
95°	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4	76.4	76.4	75.9
97.5°	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5	128.5	128.5	127.5
100°	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8	164.8	164.8	164.0
102.5°	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4	204.2	204.0	203.0
105°	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8	263.2	262.8	262.2
107.5°	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9	327.6	327.5	327.5
110°	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0	415.7	416.3	416.5
115°	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0	482.2	482.5	483.0
117.5°	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7	547.3	548.0	549.4
120°	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9	589.9	589.9	592.1
122.5°	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5	635.2	635.8	637.3
125°	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6	701.4	702.2	703.1
127.5°	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8	765.7	766.8	767.7
130°	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7	809.2	809.7	810.2
132.5°	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4	852.5	853.7	853.6
135°	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3	914.6	914.8	914.3
137.5°	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5	974.8	975.0	974.3
140°	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1	1015.1	1015.1	1013.8
142.5°	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9	1051.6	1051.5	1050.5
145°	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6	1107.3	1107.1	1105.5
147.5°	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5	1156.0	1155.3	1154.3
150°	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9	1184.9
152.5°	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5	1215.2
155°	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8	1256.5	1255.1	1254.3
157.5°	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1	1292.3	1290.5	1290.1
160°	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7	1314.1	1312.5	1312.2
162.5°	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2	1333.4	1331.6	1331.3
165°	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4	1358.5	1356.7	1356.7
167.5°	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2	1379.3	1377.4	1377.5
170°	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7	1390.8	1388.9	1389.2
172.5°	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2	1399.4	1397.5	1397.8
175°	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6	1408.7	1406.8	1407.4
177.5°	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3	1412.8
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	13.2	12.0	10.8	10.4	9.0	8.4	6.8	5.5	5.9	6.3	6.4
90°	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2	4.4	7.5	10.8
92.5°	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2	23.6	25.9	28.3
95°	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1	64.7	67.4	70.0
97.5°	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4	115.8	118.1	120.5
100°	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7	153.8	155.9	158.0
102.5°	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8	193.5	195.2	196.9
105°	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7	257.5	258.3	259.1
107.5°	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2	323.4	324.6	325.7
110°	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2	365.8	367.4	369.0



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1	411.7	413.3	414.9
115°	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7	479.3	480.9	482.5
117.5°	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1	547.2	549.3	551.4
120°	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	592.1	594.2	596.4
122.5°	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1	633.6	636.1	638.7
125°	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1	697.4	699.8	702.2
127.5°	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4	760.4	763.4	766.5
130°	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5	800.0	803.5	806.9
132.5°	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5	843.4	846.1	849.0
135°	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3	902.2	905.1	908.0
137.5°	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2	963.5	965.9	968.3
140°	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4	1000.8	1003.2	1005.6
142.5°	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6	1039.0	1041.4	1043.8
145°	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5	1093.4	1095.3	1097.1
147.5°	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5	1142.7	1144.9	1147.2
150°	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9	1175.5	1177.2	1178.8
152.5°	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6	1205.1	1206.7	1208.3
155°	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0	1248.8	1249.6	1250.4
157.5°	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9	1286.5	1287.1	1287.6
160°	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9	1309.5	1310.0	1310.5
162.5°	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9	1330.1	1330.2	1330.2
165°	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9	1357.6	1357.3	1357.1
167.5°	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2	1380.5	1379.7	1378.9
170°	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7	1392.9	1392.1	1391.3
172.5°	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3	1401.5	1400.7	1399.9
175°	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8	1412.0	1411.2	1410.4
177.5°	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1	1416.5	1415.9	1415.2
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	6.8	7.4	8.4	9.6	10.5	11.4	11.1	11.0	10.9	10.3	10.3
90°	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7	40.2	39.7	39.5
92.5°	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2	38.3	38.4	38.5
95°	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4	76.4	76.4	76.1
97.5°	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5	128.5	128.5	128.5
100°	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8	164.8	164.8	164.7
102.5°	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4	204.6	204.9	204.8
105°	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8	264.4	264.8	265.1
107.5°	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9	328.1	328.3	327.8
110°	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.0



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0	414.4	413.8	413.1
115°	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0	481.6	481.4	480.9
117.5°	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7	546.1	545.4	544.6
120°	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9	589.9	589.9	589.5
122.5°	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5	633.9	633.3	632.6
125°	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6	699.8	699.0	698.5
127.5°	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8	763.8	762.9	762.0
130°	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7	808.1	807.6	806.8
132.5°	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4	850.2	849.0	848.0
135°	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3	914.0	913.8	913.2
137.5°	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5	974.4	974.1	973.5
140°	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1	1015.1	1015.1	1014.6
142.5°	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9	1052.1	1052.3	1051.9
145°	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6	1107.9	1108.1	1107.7
147.5°	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5	1157.1	1157.7	1157.5
150°	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1
152.5°	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5
155°	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8	1259.2	1260.4	1260.8
157.5°	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1	1295.9	1297.8	1298.0
160°	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7	1317.2	1318.8	1319.1
162.5°	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2	1337.0	1338.8	1339.1
165°	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4	1362.2	1364.1	1364.4
167.5°	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2	1383.1	1384.9	1385.1
170°	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7	1394.5	1396.4	1396.5
172.5°	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2	1403.1	1404.9	1405.1
175°	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6	1412.4	1414.3	1414.4
177.5°	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	10.3	10.1	10.2	10.0	10.2	10.1	10.3	10.3	10.3	10.9	11.0
90°	39.8	40.1	40.3	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7
92.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2
95°	75.7	75.1	74.5	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4
97.5°	128.4	128.3	128.3	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5
100°	164.4	164.1	163.9	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8
102.5°	204.5	204.3	204.0	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4
105°	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8
107.5°	326.6	325.3	324.2	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9
110°	370.2	369.4	368.6	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.6	412.0	411.4	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0
115°	480.1	479.3	478.5	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0
117.5°	543.8	543.0	542.2	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7
120°	588.7	588.0	587.2	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9
122.5°	632.1	631.5	630.9	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5
125°	698.2	698.0	697.8	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6
127.5°	761.1	760.3	759.5	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8
130°	805.7	804.7	803.6	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7
132.5°	847.2	846.3	845.4	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4
135°	912.4	911.6	910.9	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3
137.5°	972.5	971.4	970.3	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5
140°	1013.5	1012.5	1011.4	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1
142.5°	1050.8	1049.7	1048.7	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9
145°	1106.7	1105.6	1104.5	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6
147.5°	1156.4	1155.4	1154.4	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5
150°	1188.3	1187.5	1186.7	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5
152.5°	1219.5	1218.5	1217.5	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5
155°	1260.0	1259.2	1258.4	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8
157.5°	1296.7	1295.5	1294.2	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1
160°	1318.0	1317.0	1316.0	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7
162.5°	1337.8	1336.6	1335.3	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2
165°	1363.0	1361.8	1360.4	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4
167.5°	1383.8	1382.4	1381.0	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2
170°	1394.9	1393.3	1391.7	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7
172.5°	1403.5	1401.9	1400.3	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2
175°	1412.8	1411.2	1409.6	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6
177.5°	1416.2	1414.9	1413.6	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	11.1	11.4	10.5	9.6	8.4	7.4	6.8	6.4	6.3	5.9	5.5
90°	41.3	41.8	36.0	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2
92.5°	38.1	37.9	36.6	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2
95°	76.4	76.4	75.9	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1
97.5°	128.5	128.5	127.5	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4
100°	164.8	164.8	164.0	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7
102.5°	204.2	204.0	203.0	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8
105°	263.2	262.8	262.2	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7
107.5°	327.6	327.5	327.5	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2
110°	371.5	371.5	371.5	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.7	416.3	416.5	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1
115°	482.2	482.5	483.0	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7
117.5°	547.3	548.0	549.4	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1
120°	589.9	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9
122.5°	635.2	635.8	637.3	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1
125°	701.4	702.2	703.1	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1
127.5°	765.7	766.8	767.7	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4
130°	809.2	809.7	810.2	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5
132.5°	852.5	853.7	853.6	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5
135°	914.6	914.8	914.3	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3
137.5°	974.8	975.0	974.3	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2
140°	1015.1	1015.1	1013.8	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4
142.5°	1051.6	1051.5	1050.5	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6
145°	1107.3	1107.1	1105.5	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5
147.5°	1156.0	1155.3	1154.3	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5
150°	1186.7	1185.9	1184.9	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9
152.5°	1217.5	1216.5	1215.2	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6
155°	1256.5	1255.1	1254.3	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0
157.5°	1292.3	1290.5	1290.1	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9
160°	1314.1	1312.5	1312.2	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9
162.5°	1333.4	1331.6	1331.3	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9
165°	1358.5	1356.7	1356.7	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9
167.5°	1379.3	1377.4	1377.5	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2
170°	1390.8	1388.9	1389.2	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7
172.5°	1399.4	1397.5	1397.8	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3
175°	1408.7	1406.8	1407.4	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8
177.5°	1413.6	1412.3	1412.8	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.8	8.4	9.0	10.4	10.8	12.0	13.2	14.0	15.0	14.7	14.3
90°	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7
92.5°	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2
95°	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4
97.5°	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5
100°	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8
102.5°	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4
105°	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8
107.5°	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9
110°	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0
115°	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0
117.5°	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7
120°	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9
122.5°	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5
125°	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6
127.5°	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8
130°	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7
132.5°	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4
135°	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3
137.5°	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5
140°	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1
142.5°	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9
145°	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6
147.5°	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5
150°	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5
152.5°	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5
155°	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8
157.5°	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1
160°	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7
162.5°	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2
165°	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4
167.5°	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2
170°	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7
172.5°	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2
175°	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6
177.5°	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	14.4	14.3	14.1	14.1	14.4	14.3	14.3
90°	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.0	370.2	369.4	368.6	367.8



TEST NUMBER: P331520-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)