

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331772-930

Luminaire Tested: **S122RDIW-S290D710U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331772-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2849.2 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	93	89	86	82	84	80	77	75	63	61	59	48	47	45	33	33	32	25
2	85	78	73	68	76	71	66	62	56	52	50	42	40	38	30	29	27	22
3	78	69	62	57	70	62	56	52	49	45	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	16
5	66	55	47	41	59	49	43	38	39	35	31	30	27	24	22	20	18	14
6	60	49	41	36	54	44	38	33	36	31	27	27	24	22	20	18	16	13
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14	11
8	52	40	33	28	46	36	30	25	29	25	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.3
10°-20°	105.2	3.7
20°-30°	147.7	5.2
30°-40°	161.1	5.7
40°-50°	148.1	5.2
50°-60°	116.3	4.1
60°-70°	75.8	2.7
70°-80°	39.1	1.4
80°-90°	13.0	0.5
90°-100°	45.4	1.6
100°-110°	141.1	5.0
110°-120°	241.2	8.5
120°-130°	317.1	11.1
130°-140°	356.0	12.5
140°-150°	349.0	12.2
150°-160°	292.8	10.3
160°-170°	194.2	6.8
170°-180°	67.9	2.4
0°-30°	291.2	10.2
0°-40°	452.3	15.9
0°-60°	716.7	25.2
0°-90°	844.6	29.6
90°-120°	427.7	15.0
90°-150°	1449.8	50.9
90°-180°	2005.0	70.4
0°-180°	2849.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	8	21	20	20	2
95°	32	37	39	39	38	36
105°	130	132	133	134	134	137
115°	242	245	244	244	242	239
125°	352	357	356	354	353	315
135°	456	462	463	463	461	352
145°	553	557	561	561	559	345
155°	632	634	636	639	637	291
165°	688	687	687	691	688	194
175°	716	714	713	716	713	68
180°	717	717	717	717	717	



TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.9	4.6	4.5	4.2	4.1	4.2	4.8	5.5	6.0	6.6	6.5
90°	0.6	2.2	3.8	5.5	7.1	9.4	12.3	15.2	18.2	21.2	20.9
92.5°	10.8	12.0	13.1	14.3	15.5	16.5	17.1	17.9	18.5	19.2	19.3
95°	31.5	32.8	34.2	35.5	36.9	37.7	37.9	38.2	38.5	38.7	38.7
97.5°	57.5	58.6	59.8	61.0	62.2	63.0	63.6	64.1	64.6	65.1	65.1
100°	76.8	77.9	79.0	80.1	81.1	81.9	82.3	82.7	83.1	83.5	83.5
102.5°	97.2	98.0	98.9	99.7	100.6	101.3	101.8	102.3	102.8	103.3	103.5
105°	130.0	130.4	130.9	131.3	131.7	132.0	132.3	132.6	132.8	133.1	133.4
107.5°	163.2	163.8	164.4	165.0	165.6	165.9	165.9	165.9	165.9	165.9	166.0
110°	184.5	185.3	186.1	186.9	187.8	188.2	188.2	188.2	188.2	188.2	188.2



TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	207.7	208.6	209.4	210.2	211.0	211.3	211.2	211.1	211.0	210.9	210.6
115°	242.0	242.8	243.6	244.4	245.2	245.5	245.2	244.9	244.7	244.4	244.3
117.5°	276.1	277.2	278.3	279.3	280.4	280.5	279.8	279.1	278.3	277.6	277.3
120°	298.9	299.9	301.0	302.1	303.1	303.1	302.1	301.0	299.9	298.9	298.9
122.5°	319.7	321.0	322.3	323.5	324.8	325.1	324.3	323.6	322.9	322.1	321.8
125°	352.1	353.4	354.5	355.7	356.9	357.3	356.9	356.5	356.1	355.7	355.3
127.5°	383.7	385.2	386.8	388.2	389.8	390.4	389.9	389.4	388.9	388.4	387.9
130°	403.5	405.3	407.0	408.8	410.5	411.2	411.0	410.7	410.4	410.2	409.9
132.5°	425.8	427.2	428.7	430.1	431.5	432.3	432.3	432.4	432.4	432.4	431.9
135°	455.6	457.1	458.5	460.0	461.5	462.4	462.6	462.9	463.2	463.4	463.3
137.5°	486.9	488.1	489.3	490.6	491.7	492.5	492.8	493.3	493.6	493.9	493.8
140°	505.8	507.0	508.2	509.4	510.6	511.5	512.3	512.9	513.6	514.2	514.2
142.5°	525.1	526.4	527.6	528.8	529.9	530.8	531.2	531.7	532.1	532.6	532.7
145°	552.9	553.9	554.8	555.8	556.8	557.6	558.4	559.2	560.0	560.8	560.9
147.5°	577.8	578.9	580.0	581.1	582.3	583.1	583.7	584.2	584.7	585.3	585.5
150°	594.7	595.5	596.3	597.1	597.9	598.6	599.2	599.7	600.2	600.8	601.2
152.5°	609.7	610.5	611.3	612.1	612.9	613.7	614.3	615.0	615.6	616.3	616.8
155°	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.4	635.9	636.5
157.5°	651.4	651.8	652.0	652.2	652.6	652.8	653.1	653.3	653.5	653.8	654.7
160°	663.1	663.3	663.6	663.9	664.1	664.4	664.5	664.6	664.7	664.9	665.7
162.5°	673.7	673.8	673.8	673.8	673.9	674.0	674.2	674.3	674.4	674.6	675.5
165°	687.9	687.7	687.6	687.5	687.4	687.3	687.3	687.3	687.3	687.3	688.2
167.5°	699.8	699.4	699.0	698.5	698.1	697.9	697.9	697.8	697.8	697.8	698.7
170°	706.0	705.6	705.2	704.8	704.4	704.2	704.0	703.8	703.8	703.6	704.6
172.5°	710.4	710.0	709.6	709.1	708.7	708.5	708.3	708.3	708.1	707.9	708.9
175°	715.7	715.3	714.9	714.5	714.1	713.8	713.5	713.2	713.0	712.7	713.6
177.5°	717.9	717.5	717.2	716.9	716.6	716.3	716.1	715.9	715.7	715.4	716.1
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9



TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	6.4	6.3	6.1	6.1	6.1	6.1	6.2	6.2
90°	20.6	20.4	20.1	20.1	20.1	20.3	20.5	20.5
92.5°	19.3	19.4	19.5	19.5	19.5	19.6	19.6	19.6
95°	38.7	38.7	38.7	38.6	38.3	38.1	37.7	37.5
97.5°	65.1	65.1	65.1	65.1	65.1	65.1	65.0	65.0
100°	83.5	83.5	83.5	83.4	83.3	83.2	83.0	82.9
102.5°	103.5	103.6	103.8	103.8	103.6	103.5	103.4	103.2
105°	133.6	133.9	134.2	134.3	134.3	134.3	134.3	134.3
107.5°	166.1	166.2	166.3	166.1	165.4	164.9	164.2	163.6
110°	188.2	188.2	188.2	187.9	187.5	187.1	186.7	186.4



TEST NUMBER: P331772-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	209.9	209.6	209.3	209.0	208.7	208.4	208.1
115°	244.2	244.0	243.9	243.6	243.2	242.8	242.4	242.0
117.5°	277.0	276.6	276.3	275.9	275.5	275.1	274.7	274.3
120°	298.9	298.9	298.9	298.6	298.2	297.8	297.4	297.0
122.5°	321.5	321.1	320.8	320.5	320.2	319.9	319.6	319.4
125°	354.9	354.5	354.1	353.8	353.8	353.6	353.4	353.4
127.5°	387.4	386.9	386.5	386.0	385.6	385.1	384.7	384.3
130°	409.7	409.4	409.1	408.7	408.1	407.6	407.1	406.6
132.5°	431.3	430.6	430.1	429.6	429.2	428.7	428.3	427.9
135°	463.2	463.0	462.9	462.6	462.2	461.8	461.4	461.0
137.5°	493.7	493.6	493.5	493.2	492.6	492.1	491.5	491.0
140°	514.2	514.2	514.2	514.0	513.5	512.9	512.3	511.8
142.5°	532.9	533.0	533.0	532.9	532.3	531.7	531.2	530.7
145°	561.1	561.3	561.3	561.2	560.6	560.1	559.5	559.1
147.5°	585.9	586.1	586.4	586.4	585.9	585.3	584.8	584.3
150°	601.5	601.9	602.3	602.3	601.9	601.5	601.2	600.8
152.5°	617.3	617.8	618.3	618.3	617.8	617.3	616.8	616.3
155°	637.2	637.9	638.5	638.7	638.3	637.9	637.5	637.1
157.5°	655.6	656.5	657.4	657.5	656.9	656.2	655.6	654.9
160°	666.5	667.3	668.1	668.2	667.7	667.2	666.7	666.1
162.5°	676.4	677.4	678.2	678.3	677.7	677.1	676.5	675.8
165°	689.2	690.1	691.0	691.2	690.5	689.8	689.2	688.5
167.5°	699.7	700.6	701.6	701.6	701.0	700.3	699.6	698.9
170°	705.5	706.5	707.4	707.4	706.6	705.8	705.0	704.2
172.5°	709.9	710.8	711.8	711.8	711.0	710.2	709.4	708.6
175°	714.5	715.5	716.5	716.5	715.7	714.9	714.1	713.3
177.5°	716.7	717.4	718.0	718.0	717.4	716.7	716.1	715.4
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9

(END OF REPORT)