

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331523-927

Luminaire Tested: **S122DIW-S485D1440U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331523-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1440U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6132.3 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22				
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18				
3	77	68	61	55	68	60	54	50	47	43	40	35	32	30	23	22	20	15				
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17	13				
5	64	53	45	39	57	48	41	36	37	32	29	28	24	22	19	17	15	11				
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10				
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12	9				
8	50	38	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8				
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9	7				
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9935	9935	9935
5°	9972	9828	9887
10°	9914	9729	9778
15°	9790	9603	9593
20°	9617	9414	9402
25°	9444	9180	9180
30°	9221	8968	8889
35°	9014	8712	8584
40°	8753	8456	8292
45°	8499	8200	7996
50°	8219	7935	7654
55°	7927	7626	7344
60°	7601	7259	6991
65°	7255	6896	6575
70°	6812	6453	6146
75°	6201	5939	5795
80°	5504	5337	5058
85°	4483	4279	3835



TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	0.9
10°-20°	162.8	2.7
20°-30°	239.3	3.9
30°-40°	278.0	4.5
40°-50°	277.7	4.5
50°-60°	242.1	3.9
60°-70°	179.0	2.9
70°-80°	101.4	1.7
80°-90°	31.1	0.5
90°-100°	51.9	0.8
100°-110°	190.5	3.1
110°-120°	509.1	8.3
120°-130°	840.4	13.7
130°-140°	893.8	14.6
140°-150°	830.7	13.5
150°-160°	667.9	10.9
160°-170°	430.4	7.0
170°-180°	148.2	2.4
0°-30°	459.9	7.5
0°-40°	737.9	12.0
0°-60°	1257.7	20.5
0°-90°	1569.2	25.6
90°-120°	751.5	12.3
90°-150°	3316.5	54.1
90°-180°	4563.0	74.4
0°-180°	6132.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	615	613	606	611	610	58
15°	586	582	574	577	574	165
25°	530	525	515	516	515	244
35°	457	451	442	438	436	285
45°	372	368	359	353	350	287
55°	282	278	271	264	261	252
65°	190	186	180	175	172	188
75°	99	98	95	92	93	106
85°	24	24	23	21	21	28
90°	1	13	22	28	30	5
95°	73	39	44	49	48	90
105°	342	357	69	81	86	366
115°	648	668	695	198	92	638
125°	916	931	952	960	963	816
135°	1134	1151	1162	1172	1171	875
145°	1315	1315	1333	1340	1335	822
155°	1448	1439	1451	1457	1449	667
165°	1526	1519	1522	1529	1522	431
175°	1560	1553	1555	1562	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	618.1	617.6	617.1	616.6	616.0	615.2	614.0	612.9	611.7	610.5	611.6
5°	615.3	614.7	614.3	613.7	613.2	612.2	610.8	609.3	607.8	606.4	607.4
7.5°	609.8	609.0	608.2	607.4	606.6	605.5	604.0	602.5	601.0	599.5	600.6
10°	604.7	603.7	602.8	601.9	600.9	599.7	598.1	596.6	595.0	593.4	594.5
12.5°	597.5	596.8	595.9	595.1	594.3	593.1	591.5	589.9	588.4	586.8	587.5
15°	585.7	584.9	584.2	583.4	582.6	581.3	579.6	577.9	576.2	574.5	575.0
17.5°	570.5	569.8	569.0	568.2	567.4	566.2	564.4	562.7	560.9	559.2	559.8
20°	559.7	558.9	558.1	557.3	556.5	555.2	553.3	551.5	549.7	547.9	548.3
22.5°	548.8	547.7	546.6	545.5	544.4	543.0	541.2	539.5	537.7	536.0	536.1
25°	530.1	529.0	528.0	527.0	525.9	524.3	522.0	519.8	517.5	515.3	515.6
27.5°	508.8	507.9	506.9	506.0	505.0	503.7	501.9	500.1	498.4	496.6	496.2
30°	494.6	493.5	492.5	491.5	490.4	488.9	486.9	485.0	483.0	481.0	480.6
32.5°	479.4	478.6	477.8	476.9	476.1	474.6	472.5	470.5	468.4	466.4	465.6
35°	457.3	456.0	454.7	453.4	452.1	450.4	448.3	446.2	444.0	442.0	441.2
37.5°	432.4	431.2	430.1	428.9	427.7	426.1	424.0	421.9	419.8	417.7	416.7
40°	415.3	414.2	413.2	412.2	411.1	409.6	407.4	405.4	403.2	401.2	400.0
42.5°	398.8	397.7	396.6	395.6	394.6	393.0	390.9	388.8	386.7	384.5	383.3
45°	372.2	371.2	370.3	369.4	368.4	367.0	365.0	363.1	361.1	359.1	357.7
47.5°	345.6	344.8	343.9	343.0	342.1	340.7	338.7	336.6	334.5	332.5	331.0
50°	327.2	326.5	325.8	325.2	324.6	323.3	321.5	319.6	317.7	315.9	314.1
52.5°	309.2	308.3	307.4	306.6	305.7	304.4	302.7	301.0	299.2	297.5	296.0
55°	281.6	280.8	280.0	279.2	278.5	277.3	275.7	274.1	272.5	270.9	269.4
57.5°	253.9	253.3	252.6	252.1	251.4	250.3	248.5	246.8	245.0	243.3	241.7
60°	235.4	235.0	234.4	233.9	233.4	232.2	230.4	228.5	226.6	224.8	223.4
62.5°	217.5	216.7	215.8	214.9	214.1	213.0	211.6	210.2	208.7	207.3	206.0
65°	189.9	189.1	188.3	187.5	186.8	185.7	184.4	183.1	181.7	180.5	179.3
67.5°	161.8	161.2	160.6	159.9	159.3	158.4	157.2	156.1	154.9	153.7	152.8
70°	144.3	143.9	143.3	142.8	142.3	141.4	140.2	139.0	137.8	136.7	135.8
72.5°	126.4	125.9	125.3	124.8	124.3	123.7	122.9	122.1	121.4	120.6	119.6
75°	99.4	99.1	98.9	98.6	98.3	97.9	97.2	96.6	95.9	95.2	94.4
77.5°	75.3	74.8	74.4	73.9	73.4	73.1	72.9	72.6	72.3	72.1	71.7
80°	59.2	59.0	58.9	58.8	58.6	58.5	58.1	57.9	57.7	57.4	57.0
82.5°	44.0	44.0	44.0	44.0	43.9	43.8	43.6	43.5	43.3	43.2	42.7
85°	24.2	24.2	24.0	23.8	23.8	23.6	23.4	23.4	23.2	23.1	22.7
87.5°	8.7	9.1	9.4	9.7	10.1	10.4	10.5	10.8	10.9	11.2	11.1
90°	1.1	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8
92.5°	22.7	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8
95°	73.2	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2
97.5°	145.4	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8
100°	199.4	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2
102.5°	258.9	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6
105°	342.5	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5
107.5°	437.8	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4
110°	499.2	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1



TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.8	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0
115°	647.8	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2
117.5°	729.2	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0
120°	788.7	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9
122.5°	839.2	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8
125°	916.0	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8
127.5°	985.6	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4
130°	1029.8	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0
132.5°	1074.8	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9
135°	1133.5	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1
137.5°	1192.7	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2
140°	1231.4	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1
142.5°	1263.9	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2
145°	1314.9	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6
147.5°	1359.2	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1
150°	1388.1	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7
152.5°	1412.4	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2
155°	1447.8	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6
157.5°	1475.5	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1
160°	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2
162.5°	1506.1	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0
165°	1525.5	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9
167.5°	1539.9	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1
170°	1548.1	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3
172.5°	1553.5	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7
175°	1560.4	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6
177.5°	1561.5	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	612.7	613.7	614.7	615.2	615.0	614.7	614.6	614.3
5°	608.6	609.6	610.6	611.0	610.8	610.5	610.2	610.0
7.5°	601.7	602.7	603.8	604.1	603.9	603.6	603.2	603.0
10°	595.5	596.6	597.6	597.9	597.5	597.1	596.8	596.4
12.5°	588.3	589.0	589.7	589.9	589.6	589.4	589.1	588.7
15°	575.5	576.1	576.6	576.5	575.8	575.2	574.6	573.9
17.5°	560.4	561.0	561.7	561.6	560.9	560.4	559.8	559.1
20°	548.7	549.1	549.5	549.4	548.8	548.3	547.8	547.2
22.5°	536.1	536.2	536.3	536.2	535.9	535.6	535.3	535.0
25°	515.9	516.1	516.3	516.3	516.1	515.9	515.6	515.3
27.5°	495.8	495.4	495.0	494.6	493.9	493.3	492.7	492.0
30°	480.2	479.8	479.4	479.0	478.4	477.9	477.4	476.8
32.5°	464.9	464.2	463.5	462.9	462.3	461.8	461.3	460.7
35°	440.4	439.6	438.8	438.1	437.4	436.7	436.1	435.5
37.5°	415.7	414.8	413.8	413.0	412.3	411.7	411.1	410.5
40°	398.8	397.6	396.4	395.5	395.0	394.5	394.0	393.4
42.5°	382.0	380.7	379.4	378.4	377.6	376.9	376.2	375.4
45°	356.2	354.8	353.3	352.4	351.8	351.3	350.8	350.2
47.5°	329.5	327.9	326.4	325.3	324.5	323.8	323.0	322.2
50°	312.3	310.4	308.6	307.3	306.7	306.0	305.3	304.7
52.5°	294.5	292.9	291.4	290.2	289.3	288.4	287.6	286.7
55°	267.8	266.3	264.7	263.6	262.8	262.2	261.6	260.9
57.5°	240.2	238.6	237.1	236.1	235.5	235.0	234.6	234.0
60°	221.9	220.5	219.0	218.1	217.7	217.3	216.9	216.5
62.5°	204.6	203.3	201.9	201.1	200.5	200.0	199.6	199.0
65°	178.1	176.9	175.7	174.8	174.1	173.5	172.9	172.1
67.5°	151.9	150.9	150.0	149.3	148.8	148.2	147.7	147.2
70°	134.8	133.9	133.0	132.3	131.7	131.2	130.7	130.2
72.5°	118.7	117.8	116.9	116.2	115.8	115.3	114.9	114.5
75°	93.6	92.9	92.1	91.8	92.1	92.4	92.6	92.9
77.5°	71.3	70.9	70.5	70.1	69.7	69.4	69.0	68.6
80°	56.6	56.2	55.8	55.5	55.2	55.0	54.7	54.4
82.5°	42.2	41.7	41.2	40.9	40.9	40.8	40.7	40.7
85°	22.3	21.9	21.5	21.2	21.1	21.0	20.8	20.7
87.5°	11.0	10.9	10.9	10.9	10.9	10.9	10.9	10.9
90°	25.0	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	27.4	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	46.4	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	60.8	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	68.2	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	71.2	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	74.2	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	90.6	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	147.1	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331523-927

CATALOG NUMBER: S122DIW-S485D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	314.7	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	463.3	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	713.9	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	831.9	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	882.6	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	955.5	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1022.9	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1065.7	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1107.2	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1166.6	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1221.7	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1257.4	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1290.3	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1376.5	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1401.2	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1423.7	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1454.1	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1479.8	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1494.7	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1508.6	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1539.8	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1547.1	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1552.4	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1558.3	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1558.9	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)