

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331803-930

Luminaire Tested: **S122RDIW-S485D1440U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331803-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D1440U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6084.0 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	34	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	39	34	31	29	22	21	20	14
4	70	60	53	47	62	54	47	42	41	37	34	30	27	25	20	18	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	16	15	13	10
7	55	43	35	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	17	19	16	13	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10863	10863	10863
5°	10904	10728	10786
10°	10822	10552	10462
15°	10696	10238	9944
20°	10524	9792	9301
25°	10349	9285	8678
30°	10103	8764	7879
35°	9865	8198	7177
40°	9624	7611	6365
45°	9344	6951	5631
50°	9053	6285	4908
55°	8757	5571	4217
60°	8415	4818	3500
65°	8027	4046	3186
70°	7558	3333	2932
75°	6987	3038	2739
80°	6174	2715	2492
85°	4854	2149	2149



TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.0	1.0
10°-20°	172.9	2.8
20°-30°	242.8	4.0
30°-40°	264.8	4.4
40°-50°	243.5	4.0
50°-60°	191.2	3.1
60°-70°	124.7	2.0
70°-80°	64.3	1.1
80°-90°	20.6	0.3
90°-100°	53.5	0.9
100°-110°	196.0	3.2
110°-120°	524.0	8.6
120°-130°	865.0	14.2
130°-140°	919.9	15.1
140°-150°	855.0	14.1
150°-160°	687.4	11.3
160°-170°	443.0	7.3
170°-180°	152.5	2.5
0°-30°	478.7	7.9
0°-40°	743.5	12.2
0°-60°	1178.2	19.4
0°-90°	1387.8	22.8
90°-120°	773.5	12.7
90°-150°	3413.3	56.1
90°-180°	4696.0	77.2
0°-180°	6084.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	673	670	662	667	666	64
15°	640	632	612	601	595	180
25°	581	560	521	497	487	267
35°	500	468	416	379	364	313
45°	409	367	304	263	247	316
55°	311	263	198	163	150	278
65°	210	160	106	86	83	208
75°	112	71	49	45	44	119
85°	26	14	12	12	12	31
90°	1	14	23	29	31	5
95°	75	40	45	51	50	92
105°	352	368	71	83	88	377
115°	667	687	715	204	95	656
125°	943	958	980	988	991	840
135°	1166	1185	1196	1206	1205	901
145°	1353	1353	1372	1379	1374	846
155°	1490	1481	1494	1500	1491	686
165°	1570	1564	1566	1574	1566	443
175°	1606	1598	1600	1607	1597	153
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	675.2	674.7	674.2	673.6	673.1	672.2	671.1	669.8	668.6	667.5	668.5
5°	672.8	672.1	671.5	670.8	670.1	668.9	667.2	665.4	663.7	661.9	663.1
7.5°	665.9	665.0	664.2	663.3	662.5	661.0	659.0	657.0	654.9	652.9	653.2
10°	660.1	659.1	658.1	657.2	656.2	654.4	651.8	649.0	646.3	643.6	643.2
12.5°	652.7	651.6	650.4	649.2	648.1	645.8	642.3	638.9	635.4	631.9	631.2
15°	639.9	638.5	637.0	635.4	634.0	631.0	626.3	621.7	617.2	612.5	610.0
17.5°	624.3	622.0	619.7	617.4	615.1	611.1	605.2	599.2	593.4	587.4	584.4
20°	612.5	609.8	607.2	604.5	601.7	597.0	590.2	583.4	576.7	569.9	566.6
22.5°	599.9	596.9	593.8	590.8	587.7	582.4	574.8	567.1	559.5	551.9	547.6
25°	580.9	576.6	572.3	567.9	563.5	556.9	548.0	539.1	530.1	521.2	515.7
27.5°	558.0	553.3	548.5	543.9	539.2	531.7	521.7	511.6	501.6	491.5	485.0
30°	541.9	536.8	531.7	526.5	521.4	513.4	502.6	491.7	480.9	470.1	463.2
32.5°	526.4	520.3	514.3	508.3	502.3	493.7	482.7	471.7	460.6	449.6	441.7
35°	500.5	493.6	486.7	479.8	472.9	463.5	451.6	439.7	427.8	415.9	407.3
37.5°	474.7	467.1	459.5	451.9	444.4	434.2	421.6	408.9	396.2	383.5	374.1
40°	456.6	448.6	440.4	432.4	424.2	413.6	400.5	387.3	374.2	361.1	351.5
42.5°	438.1	429.6	421.0	412.5	404.0	392.9	379.4	365.7	352.2	338.7	328.7
45°	409.2	400.1	391.0	382.0	372.9	361.3	347.1	332.9	318.6	304.4	294.8
47.5°	380.9	371.3	361.7	352.1	342.5	330.4	315.7	301.0	286.3	271.7	262.1
50°	360.4	350.8	341.3	331.7	322.0	309.8	294.9	280.1	265.1	250.2	240.9
52.5°	340.5	330.4	320.4	310.4	300.4	288.0	273.5	258.9	244.3	229.8	220.8
55°	311.1	300.6	290.0	279.5	269.0	256.3	241.7	227.1	212.5	197.9	189.8
57.5°	281.0	270.3	259.4	248.6	237.7	225.3	211.3	197.2	183.2	169.2	161.7
60°	260.6	249.8	239.0	228.1	217.3	205.0	191.0	177.1	163.1	149.2	142.3
62.5°	240.6	229.8	219.0	208.1	197.3	185.3	172.0	158.7	145.4	132.2	125.6
65°	210.1	199.1	188.2	177.2	166.2	154.7	142.5	130.3	118.1	105.9	101.3
67.5°	180.6	169.7	158.8	148.0	137.1	126.1	115.2	104.3	93.3	82.3	80.2
70°	160.1	149.6	139.0	128.5	117.9	107.9	98.7	89.3	80.0	70.6	69.3
72.5°	140.6	130.5	120.4	110.3	100.2	91.4	83.9	76.4	68.9	61.4	60.3
75°	112.0	102.6	93.1	83.6	74.1	67.1	62.5	57.9	53.3	48.7	47.8
77.5°	83.9	75.6	67.3	58.9	50.7	45.4	43.2	41.0	38.7	36.5	36.0
80°	66.4	59.4	52.6	45.7	38.7	34.7	33.3	32.0	30.6	29.2	28.7
82.5°	50.3	44.9	39.5	34.2	28.8	25.6	24.7	23.7	22.8	21.9	21.6
85°	26.2	23.3	20.5	17.7	14.8	13.2	12.8	12.4	12.0	11.6	11.6
87.5°	8.0	7.7	7.4	7.1	6.8	6.8	7.3	7.7	8.2	8.6	8.7
90°	1.1	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5
92.5°	23.4	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6
95°	75.3	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5
97.5°	149.6	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6
100°	205.2	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2
102.5°	266.4	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6
105°	352.5	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5
107.5°	450.6	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1
110°	513.7	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2



TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	573.1	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8
115°	666.8	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1
117.5°	750.5	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6
120°	811.7	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0
122.5°	863.6	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5
125°	942.7	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6
127.5°	1014.4	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2
130°	1059.8	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0
132.5°	1106.2	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2
135°	1166.5	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1
137.5°	1227.5	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8
140°	1267.4	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8
142.5°	1300.8	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8
145°	1353.2	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5
147.5°	1398.9	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3
150°	1428.6	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6
152.5°	1453.6	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7
155°	1490.0	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0
157.5°	1518.6	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3
160°	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8
162.5°	1550.0	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9
165°	1570.0	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4
167.5°	1584.9	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0
170°	1593.3	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4
172.5°	1598.8	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9
175°	1606.0	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0
177.5°	1607.1	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	669.6	670.7	671.8	672.2	672.1	671.8	671.6	671.4
5°	664.3	665.5	666.8	667.2	666.8	666.3	665.9	665.5
7.5°	653.5	653.9	654.3	654.1	653.4	652.6	652.0	651.3
10°	642.8	642.4	642.0	641.4	640.6	639.8	639.0	638.1
12.5°	630.5	629.7	629.0	627.9	626.6	625.3	623.9	622.6
15°	607.4	604.9	602.3	600.3	598.9	597.6	596.2	594.9
17.5°	581.3	578.3	575.2	572.5	570.2	567.9	565.6	563.2
20°	563.1	559.8	556.4	553.2	550.2	547.2	544.3	541.3
22.5°	543.2	538.8	534.5	531.2	529.0	526.8	524.6	522.3
25°	510.1	504.6	499.0	495.2	493.2	491.1	489.2	487.1
27.5°	478.6	472.1	465.6	460.8	457.5	454.4	451.1	447.9
30°	456.2	449.4	442.5	437.2	433.5	429.9	426.2	422.6
32.5°	433.8	426.0	418.1	412.5	409.0	405.6	402.1	398.7
35°	398.8	390.3	381.8	376.0	373.1	370.1	367.1	364.1
37.5°	364.7	355.3	345.9	339.5	336.1	332.7	329.3	325.9
40°	341.9	332.2	322.6	316.1	312.6	309.1	305.5	302.0
42.5°	318.8	308.8	299.0	292.3	288.9	285.4	282.0	278.6
45°	285.2	275.7	266.0	259.6	256.3	253.1	249.8	246.6
47.5°	252.6	243.0	233.5	227.2	224.3	221.4	218.3	215.4
50°	231.5	222.3	212.9	206.8	204.0	201.1	198.3	195.4
52.5°	211.7	202.8	193.7	187.9	185.3	182.7	180.0	177.4
55°	181.6	173.5	165.4	160.0	157.5	154.9	152.4	149.8
57.5°	154.3	146.8	139.4	134.6	132.4	130.3	128.1	125.9
60°	135.3	128.5	121.6	117.1	114.9	112.7	110.6	108.4
62.5°	119.0	112.4	105.8	101.9	100.6	99.3	98.0	96.7
65°	96.8	92.1	87.6	85.0	84.6	84.2	83.8	83.4
67.5°	78.1	76.0	73.9	72.6	72.2	71.7	71.3	70.8
70°	67.9	66.6	65.2	64.2	63.8	63.2	62.6	62.1
72.5°	59.1	58.0	56.8	56.1	55.8	55.4	55.1	54.8
75°	46.8	45.9	44.9	44.4	44.3	44.1	43.9	43.9
77.5°	35.5	34.9	34.4	34.0	33.8	33.6	33.3	33.1
80°	28.1	27.6	27.1	26.8	26.8	26.8	26.8	26.8
82.5°	21.3	21.0	20.6	20.5	20.5	20.5	20.5	20.5
85°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
87.5°	8.8	9.0	9.1	9.3	9.4	9.5	9.5	9.7
90°	25.8	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.2	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	47.8	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	62.6	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	70.2	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	73.3	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	76.4	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	93.3	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	151.4	125.6	99.9	87.5	88.5	89.5	90.6	91.6





TEST NUMBER: P331803-930

CATALOG NUMBER: S122RDIW-S485D1440U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	323.8	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	476.9	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	734.7	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	856.1	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	908.4	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	983.4	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1052.8	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1096.8	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1139.5	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1200.6	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1257.4	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1294.0	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1328.0	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1375.3	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1416.7	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1442.1	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1465.3	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1496.6	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1523.0	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1538.3	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1552.7	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1584.8	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1592.2	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1597.7	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1603.8	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1604.4	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)