

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331500-927

Luminaire Tested: **S122DIW-S485D435U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331500-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D435U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2756.3 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57																			
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48																			
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40																			
3	83	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34																			
4	76	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29																			
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25																			
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	31	28	25	22																			
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20																			
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18																			
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16																			
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9935	9935	9935
5°	9972	9828	9887
10°	9914	9729	9778
15°	9790	9603	9593
20°	9617	9414	9402
25°	9444	9180	9180
30°	9221	8968	8889
35°	9014	8712	8584
40°	8753	8456	8292
45°	8499	8200	7996
50°	8219	7935	7654
55°	7927	7626	7344
60°	7601	7259	6991
65°	7255	6896	6575
70°	6812	6453	6146
75°	6201	5939	5795
80°	5504	5337	5058
85°	4483	4279	3835



TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.9	2.1
10°-20°	162.8	5.9
20°-30°	239.3	8.7
30°-40°	278.0	10.1
40°-50°	277.7	10.1
50°-60°	242.1	8.8
60°-70°	179.0	6.5
70°-80°	101.4	3.7
80°-90°	29.0	1.1
90°-100°	27.0	1.0
100°-110°	83.7	3.0
110°-120°	143.1	5.2
120°-130°	188.1	6.8
130°-140°	211.2	7.7
140°-150°	207.1	7.5
150°-160°	173.7	6.3
160°-170°	115.2	4.2
170°-180°	40.3	1.5
0°-30°	459.9	16.7
0°-40°	737.9	26.8
0°-60°	1257.7	45.6
0°-90°	1567.1	56.9
90°-120°	253.7	9.2
90°-150°	860.1	31.2
90°-180°	1189.0	43.1
0°-180°	2756.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	615	613	606	611	610	58
15°	586	582	574	577	574	165
25°	530	525	515	516	515	244
35°	457	451	442	438	436	285
45°	372	368	359	353	350	287
55°	282	278	271	264	261	252
65°	190	186	180	175	172	188
75°	99	98	95	92	93	106
85°	24	24	23	21	21	28
90°	0	5	13	12	12	2
95°	19	22	23	23	22	21
105°	77	78	79	80	80	82
115°	144	146	145	145	144	142
125°	209	212	211	210	210	187
135°	270	274	275	274	274	209
145°	328	331	333	333	332	205
155°	375	376	377	379	378	173
165°	408	408	408	410	408	115
175°	425	424	423	425	423	40
180°	425	425	425	425	425	



TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	618.1	617.6	617.1	616.6	616.0	615.2	614.0	612.9	611.7	610.5	611.6
5°	615.3	614.7	614.3	613.7	613.2	612.2	610.8	609.3	607.8	606.4	607.4
7.5°	609.8	609.0	608.2	607.4	606.6	605.5	604.0	602.5	601.0	599.5	600.6
10°	604.7	603.7	602.8	601.9	600.9	599.7	598.1	596.6	595.0	593.4	594.5
12.5°	597.5	596.8	595.9	595.1	594.3	593.1	591.5	589.9	588.4	586.8	587.5
15°	585.7	584.9	584.2	583.4	582.6	581.3	579.6	577.9	576.2	574.5	575.0
17.5°	570.5	569.8	569.0	568.2	567.4	566.2	564.4	562.7	560.9	559.2	559.8
20°	559.7	558.9	558.1	557.3	556.5	555.2	553.3	551.5	549.7	547.9	548.3
22.5°	548.8	547.7	546.6	545.5	544.4	543.0	541.2	539.5	537.7	536.0	536.1
25°	530.1	529.0	528.0	527.0	525.9	524.3	522.0	519.8	517.5	515.3	515.6
27.5°	508.8	507.9	506.9	506.0	505.0	503.7	501.9	500.1	498.4	496.6	496.2
30°	494.6	493.5	492.5	491.5	490.4	488.9	486.9	485.0	483.0	481.0	480.6
32.5°	479.4	478.6	477.8	476.9	476.1	474.6	472.5	470.5	468.4	466.4	465.6
35°	457.3	456.0	454.7	453.4	452.1	450.4	448.3	446.2	444.0	442.0	441.2
37.5°	432.4	431.2	430.1	428.9	427.7	426.1	424.0	421.9	419.8	417.7	416.7
40°	415.3	414.2	413.2	412.2	411.1	409.6	407.4	405.4	403.2	401.2	400.0
42.5°	398.8	397.7	396.6	395.6	394.6	393.0	390.9	388.8	386.7	384.5	383.3
45°	372.2	371.2	370.3	369.4	368.4	367.0	365.0	363.1	361.1	359.1	357.7
47.5°	345.6	344.8	343.9	343.0	342.1	340.7	338.7	336.6	334.5	332.5	331.0
50°	327.2	326.5	325.8	325.2	324.6	323.3	321.5	319.6	317.7	315.9	314.1
52.5°	309.2	308.3	307.4	306.6	305.7	304.4	302.7	301.0	299.2	297.5	296.0
55°	281.6	280.8	280.0	279.2	278.5	277.3	275.7	274.1	272.5	270.9	269.4
57.5°	253.9	253.3	252.6	252.1	251.4	250.3	248.5	246.8	245.0	243.3	241.7
60°	235.4	235.0	234.4	233.9	233.4	232.2	230.4	228.5	226.6	224.8	223.4
62.5°	217.5	216.7	215.8	214.9	214.1	213.0	211.6	210.2	208.7	207.3	206.0
65°	189.9	189.1	188.3	187.5	186.8	185.7	184.4	183.1	181.7	180.5	179.3
67.5°	161.8	161.2	160.6	159.9	159.3	158.4	157.2	156.1	154.9	153.7	152.8
70°	144.3	143.9	143.3	142.8	142.3	141.4	140.2	139.0	137.8	136.7	135.8
72.5°	126.4	125.9	125.3	124.8	124.3	123.7	122.9	122.1	121.4	120.6	119.6
75°	99.4	99.1	98.9	98.6	98.3	97.9	97.2	96.6	95.9	95.2	94.4
77.5°	75.3	74.8	74.4	73.9	73.4	73.1	72.9	72.6	72.3	72.1	71.7
80°	59.2	59.0	58.9	58.8	58.6	58.5	58.1	57.9	57.7	57.4	57.0
82.5°	44.0	44.0	44.0	44.0	43.9	43.8	43.6	43.5	43.3	43.2	42.7
85°	24.2	24.2	24.0	23.8	23.8	23.6	23.4	23.4	23.2	23.1	22.7
87.5°	8.6	8.6	8.6	8.6	8.5	8.6	8.7	8.9	9.0	9.1	8.8
90°	0.4	1.3	2.3	3.2	4.2	5.5	7.3	9.0	10.8	12.6	12.4
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.6	11.0	11.4	11.4
95°	18.7	19.5	20.3	21.1	21.9	22.3	22.5	22.7	22.8	23.0	23.0
97.5°	34.1	34.8	35.5	36.2	36.9	37.4	37.7	38.0	38.3	38.6	38.6
100°	45.6	46.2	46.8	47.5	48.2	48.6	48.8	49.0	49.3	49.5	49.5
102.5°	57.7	58.1	58.6	59.2	59.7	60.1	60.4	60.7	61.0	61.3	61.4
105°	77.2	77.4	77.6	77.9	78.1	78.3	78.5	78.7	78.8	79.0	79.1
107.5°	96.8	97.2	97.5	97.9	98.2	98.4	98.4	98.4	98.4	98.4	98.5
110°	109.5	110.0	110.4	110.9	111.4	111.6	111.6	111.6	111.6	111.6	111.6



TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.3	123.7	124.2	124.7	125.2	125.4	125.3	125.2	125.2	125.1	124.9
115°	143.5	144.0	144.5	145.0	145.4	145.6	145.4	145.3	145.1	145.0	144.9
117.5°	163.8	164.5	165.1	165.7	166.4	166.4	166.0	165.6	165.1	164.7	164.5
120°	177.3	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.3
122.5°	189.6	190.4	191.2	191.9	192.7	192.9	192.4	191.9	191.5	191.1	190.9
125°	208.9	209.6	210.3	211.0	211.8	212.0	211.8	211.5	211.3	211.0	210.8
127.5°	227.6	228.5	229.4	230.4	231.2	231.6	231.3	231.0	230.7	230.4	230.1
130°	239.4	240.4	241.5	242.5	243.5	244.0	243.8	243.7	243.5	243.4	243.2
132.5°	252.6	253.4	254.3	255.2	256.0	256.4	256.4	256.5	256.5	256.5	256.2
135°	270.3	271.2	272.0	272.9	273.8	274.3	274.4	274.6	274.7	274.9	274.8
137.5°	288.8	289.5	290.3	291.0	291.7	292.2	292.4	292.6	292.8	293.0	292.9
140°	300.1	300.8	301.5	302.2	302.9	303.5	303.9	304.3	304.7	305.1	305.1
142.5°	311.6	312.3	313.0	313.7	314.4	314.9	315.1	315.4	315.7	316.0	316.1
145°	328.0	328.6	329.2	329.7	330.3	330.8	331.3	331.8	332.2	332.7	332.8
147.5°	342.8	343.4	344.1	344.8	345.5	345.9	346.3	346.6	346.9	347.2	347.4
150°	352.8	353.3	353.8	354.3	354.7	355.1	355.5	355.8	356.1	356.4	356.6
152.5°	361.7	362.2	362.7	363.1	363.6	364.1	364.4	364.8	365.2	365.6	365.9
155°	375.0	375.3	375.5	375.8	376.0	376.3	376.5	376.8	377.0	377.2	377.6
157.5°	386.5	386.7	386.8	387.0	387.1	387.2	387.4	387.5	387.7	387.9	388.4
160°	393.4	393.6	393.7	393.9	394.0	394.1	394.2	394.3	394.3	394.4	394.9
162.5°	399.7	399.7	399.7	399.7	399.8	399.9	400.0	400.1	400.1	400.2	400.7
165°	408.1	408.0	407.9	407.8	407.7	407.7	407.7	407.7	407.7	407.7	408.3
167.5°	415.1	414.9	414.6	414.4	414.2	414.0	414.0	414.0	414.0	414.0	414.5
170°	418.8	418.6	418.4	418.1	417.9	417.7	417.6	417.6	417.5	417.4	418.0
172.5°	421.4	421.2	421.0	420.7	420.5	420.3	420.3	420.2	420.1	420.0	420.6
175°	424.6	424.4	424.1	423.9	423.7	423.4	423.3	423.1	422.9	422.8	423.3
177.5°	425.9	425.7	425.5	425.3	425.1	424.9	424.8	424.7	424.5	424.5	424.8
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	612.7	613.7	614.7	615.2	615.0	614.7	614.6	614.3
5°	608.6	609.6	610.6	611.0	610.8	610.5	610.2	610.0
7.5°	601.7	602.7	603.8	604.1	603.9	603.6	603.2	603.0
10°	595.5	596.6	597.6	597.9	597.5	597.1	596.8	596.4
12.5°	588.3	589.0	589.7	589.9	589.6	589.4	589.1	588.7
15°	575.5	576.1	576.6	576.5	575.8	575.2	574.6	573.9
17.5°	560.4	561.0	561.7	561.6	560.9	560.4	559.8	559.1
20°	548.7	549.1	549.5	549.4	548.8	548.3	547.8	547.2
22.5°	536.1	536.2	536.3	536.2	535.9	535.6	535.3	535.0
25°	515.9	516.1	516.3	516.3	516.1	515.9	515.6	515.3
27.5°	495.8	495.4	495.0	494.6	493.9	493.3	492.7	492.0
30°	480.2	479.8	479.4	479.0	478.4	477.9	477.4	476.8
32.5°	464.9	464.2	463.5	462.9	462.3	461.8	461.3	460.7
35°	440.4	439.6	438.8	438.1	437.4	436.7	436.1	435.5
37.5°	415.7	414.8	413.8	413.0	412.3	411.7	411.1	410.5
40°	398.8	397.6	396.4	395.5	395.0	394.5	394.0	393.4
42.5°	382.0	380.7	379.4	378.4	377.6	376.9	376.2	375.4
45°	356.2	354.8	353.3	352.4	351.8	351.3	350.8	350.2
47.5°	329.5	327.9	326.4	325.3	324.5	323.8	323.0	322.2
50°	312.3	310.4	308.6	307.3	306.7	306.0	305.3	304.7
52.5°	294.5	292.9	291.4	290.2	289.3	288.4	287.6	286.7
55°	267.8	266.3	264.7	263.6	262.8	262.2	261.6	260.9
57.5°	240.2	238.6	237.1	236.1	235.5	235.0	234.6	234.0
60°	221.9	220.5	219.0	218.1	217.7	217.3	216.9	216.5
62.5°	204.6	203.3	201.9	201.1	200.5	200.0	199.6	199.0
65°	178.1	176.9	175.7	174.8	174.1	173.5	172.9	172.1
67.5°	151.9	150.9	150.0	149.3	148.8	148.2	147.7	147.2
70°	134.8	133.9	133.0	132.3	131.7	131.2	130.7	130.2
72.5°	118.7	117.8	116.9	116.2	115.8	115.3	114.9	114.5
75°	93.6	92.9	92.1	91.8	92.1	92.4	92.6	92.9
77.5°	71.3	70.9	70.5	70.1	69.7	69.4	69.0	68.6
80°	56.6	56.2	55.8	55.5	55.2	55.0	54.7	54.4
82.5°	42.2	41.7	41.2	40.9	40.9	40.8	40.7	40.7
85°	22.3	21.9	21.5	21.2	21.1	21.0	20.8	20.7
87.5°	8.5	8.1	7.8	7.5	7.4	7.4	7.3	7.2
90°	12.3	12.1	12.0	11.9	12.0	12.0	12.1	12.2
92.5°	11.5	11.5	11.6	11.6	11.6	11.6	11.6	11.6
95°	23.0	23.0	23.0	22.9	22.7	22.6	22.4	22.3
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.5	49.5	49.5	49.5	49.4	49.4	49.3	49.2
102.5°	61.4	61.5	61.6	61.6	61.5	61.4	61.3	61.2
105°	79.3	79.5	79.6	79.7	79.7	79.7	79.7	79.7
107.5°	98.5	98.6	98.7	98.5	98.2	97.8	97.4	97.0
110°	111.6	111.6	111.6	111.5	111.2	111.0	110.7	110.5





TEST NUMBER: P331500-927

CATALOG NUMBER: S122DIW-S485D435U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.8	124.5	124.4	124.1	124.0	123.8	123.7	123.5
115°	144.8	144.7	144.7	144.5	144.3	144.0	143.8	143.5
117.5°	164.3	164.1	163.9	163.7	163.4	163.2	163.0	162.7
120°	177.3	177.3	177.3	177.2	177.0	176.7	176.5	176.3
122.5°	190.7	190.5	190.3	190.1	190.0	189.8	189.6	189.4
125°	210.6	210.3	210.1	209.9	209.8	209.8	209.7	209.6
127.5°	229.8	229.6	229.3	229.0	228.7	228.5	228.2	228.0
130°	243.0	242.9	242.7	242.5	242.2	241.9	241.5	241.2
132.5°	255.9	255.5	255.2	254.8	254.6	254.3	254.1	253.8
135°	274.7	274.6	274.6	274.4	274.2	273.9	273.7	273.5
137.5°	292.9	292.8	292.8	292.6	292.2	291.9	291.6	291.3
140°	305.1	305.1	305.1	304.9	304.6	304.3	304.0	303.6
142.5°	316.1	316.2	316.2	316.1	315.8	315.4	315.1	314.8
145°	332.9	333.0	333.0	332.9	332.6	332.2	331.9	331.6
147.5°	347.5	347.8	347.9	347.8	347.5	347.2	346.9	346.7
150°	356.9	357.1	357.4	357.4	357.1	356.9	356.6	356.4
152.5°	366.1	366.5	366.8	366.8	366.5	366.1	365.9	365.6
155°	378.0	378.4	378.8	378.9	378.7	378.4	378.2	378.0
157.5°	388.9	389.4	390.0	390.1	389.7	389.3	389.0	388.6
160°	395.4	395.9	396.3	396.4	396.1	395.8	395.5	395.1
162.5°	401.2	401.8	402.3	402.4	402.0	401.6	401.2	400.9
165°	408.8	409.4	410.0	410.0	409.6	409.2	408.8	408.4
167.5°	415.1	415.7	416.2	416.3	415.8	415.4	415.0	414.6
170°	418.5	419.1	419.6	419.7	419.2	418.7	418.3	417.8
172.5°	421.1	421.7	422.2	422.2	421.8	421.3	420.8	420.3
175°	423.9	424.5	425.0	425.1	424.6	424.1	423.7	423.2
177.5°	425.2	425.6	426.0	426.0	425.6	425.2	424.8	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3

(END OF REPORT)