

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331785-930

Luminaire Tested: **S122RDIW-S485D435U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331785-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D435U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2926.8 lumens  
Efficiency: N/A  
Efficacy: 96.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	91	84	78	73	84	78	73	69	67	63	60	57	54	52	47	45	44	39
3	83	75	68	62	77	69	63	59	60	55	52	51	48	45	42	40	38	34
4	77	67	59	53	71	62	56	51	54	49	45	46	42	39	39	36	34	30
5	71	60	52	46	66	56	49	44	49	43	39	42	38	35	35	32	30	27
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	24
7	61	49	42	36	56	46	39	35	40	35	31	35	31	28	30	27	24	22
8	57	45	38	32	53	42	36	31	37	32	28	32	28	25	28	25	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	26	23	20	18
10	50	38	31	27	46	36	30	25	32	27	23	28	24	21	24	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.1	2.8
10°-20°	231.5	7.9
20°-30°	298.2	10.2
30°-40°	283.4	9.7
40°-50°	242.8	8.3
50°-60°	184.9	6.3
60°-70°	116.9	4.0
70°-80°	58.4	2.0
80°-90°	16.4	0.6
90°-100°	16.1	0.5
100°-110°	58.9	2.0
110°-120°	157.5	5.4
120°-130°	259.9	8.9
130°-140°	276.4	9.4
140°-150°	256.9	8.8
150°-160°	206.6	7.1
160°-170°	133.1	4.5
170°-180°	45.8	1.6
0°-30°	612.8	20.9
0°-40°	896.2	30.6
0°-60°	1323.9	45.2
0°-90°	1515.5	51.8
90°-120°	232.4	7.9
90°-150°	1025.8	35.0
90°-180°	1411.0	48.2
0°-180°	2926.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	9	0	9	0	9	5
95°	15	23	15	23	15	14
105°	26	106	26	106	26	28
115°	28	200	28	200	28	72
125°	298	283	298	283	298	258
135°	362	351	362	351	362	279
145°	413	407	413	407	413	258
155°	448	448	448	448	448	207
165°	471	472	471	472	471	133
175°	480	483	480	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	5.8	6.0	6.0	6.0	5.9	5.9	5.8	6.0	5.6	5.8	5.4
90°	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7	7.3	6.9	6.4
92.5°	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5	8.3	8.1	7.7
95°	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3	13.9	13.6	13.0
97.5°	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8	18.5	18.2	17.0
100°	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1	20.5	19.9	18.5
102.5°	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0	21.2	20.4	31.5
105°	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0	22.1	21.3	42.4
107.5°	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0	28.9	29.8	55.1
110°	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5	53.2	61.0	83.3



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3	125.6	153.8	159.3
115°	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3	179.1	215.0	213.0
117.5°	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8	229.5	238.1	236.8
120°	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3	256.3	255.4	254.0
122.5°	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0	272.5	271.9	270.4
125°	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5	295.0	294.5	293.0
127.5°	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4	315.6	314.8	313.7
130°	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6	328.7	327.9	327.1
132.5°	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5	341.8	341.0	340.1
135°	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9	360.0	359.3	358.6
137.5°	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9	377.1	376.3	375.5
140°	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9	388.2	387.5	386.6
142.5°	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1	398.4	397.8	396.8
145°	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4	412.8	412.2	410.9
147.5°	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7	425.3	424.9	423.6
150°	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4	432.9	432.4	431.2
152.5°	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3	439.9	439.4	438.2
155°	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8	449.3	448.8	447.9
157.5°	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7	457.1	456.6	456.0
160°	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3	461.9	461.4	460.9
162.5°	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6	466.1	465.5	465.1
165°	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8	470.6
167.5°	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3	475.7	475.2	475.0
170°	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5	477.9	477.4	477.3
172.5°	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1	479.6	479.1	478.9
175°	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0	481.4	480.9	480.7
177.5°	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2	481.8	481.3	481.3
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	5.3	5.4	5.3	4.9	5.0	5.1	6.1	7.1	6.4	5.8	5.5
90°	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3	1.2	2.0	2.9
92.5°	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0	6.9	6.8	6.8
95°	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7	20.1	17.5	15.0
97.5°	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9	37.7	30.6	23.3
100°	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7	51.0	40.4	29.8
102.5°	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1	77.9	75.6	73.4
105°	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9	108.3	110.6	112.9
107.5°	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4	137.3	139.2	141.0
110°	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3	156.0	157.6	159.2





TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2	173.7	175.1	176.5
115°	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4	201.7	203.0	204.3
117.5°	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5	227.0	228.4	229.9
120°	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9	245.1	246.2	247.4
122.5°	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5	260.7	262.0	263.2
125°	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3	284.3	285.4	286.3
127.5°	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8	306.0	307.0	308.2
130°	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5	319.8	321.0	322.2
132.5°	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5	333.5	334.5	335.6
135°	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6	351.8	353.0	354.2
137.5°	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9	369.7	370.6	371.5
140°	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9	381.5	382.1	382.7
142.5°	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9	391.5	392.0	392.6
145°	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7	406.6	406.5	406.4
147.5°	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4	420.1	419.8	419.6
150°	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3	428.8	428.2	427.7
152.5°	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8	436.3	435.6	435.0
155°	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8	447.1	446.4	445.7
157.5°	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3	455.8	455.2	454.6
160°	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	460.9	460.5	460.0
162.5°	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9	465.4	464.9	464.5
165°	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8	471.4	470.9	470.4
167.5°	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3	475.8	475.4	474.9
170°	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8	478.3	477.8	477.4
172.5°	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5	480.0	479.6	479.1
175°	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7	482.1	481.5	481.0
177.5°	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0	482.6	482.1	481.7
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	5.4	5.3	4.9	5.1	5.1	5.1	5.1	5.0	5.1	5.1	4.9
90°	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7	8.2	8.5	8.8
92.5°	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5	8.7	8.9	9.0
95°	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3	14.8	15.2	15.3
97.5°	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8	19.2	19.4	19.6
100°	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1	21.7	22.3	22.7
102.5°	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0	22.8	23.6	24.1
105°	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0	23.8	24.7	25.3
107.5°	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0	27.1	26.3	26.0
110°	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5	37.7	30.0	26.3



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3	69.1	40.8	26.8
115°	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3	107.5	71.6	50.9
117.5°	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8	212.1	203.4	190.0
120°	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3	258.2	259.2	254.4
122.5°	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0	273.5	274.1	273.4
125°	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5	296.1	296.6	297.0
127.5°	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4	317.2	318.0	318.4
130°	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6	330.4	331.3	331.7
132.5°	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5	343.2	343.9	344.2
135°	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9	361.6	362.4	362.6
137.5°	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9	378.6	379.4	379.6
140°	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9	389.6	390.3	390.4
142.5°	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1	399.7	400.4	400.5
145°	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4	413.8	414.4	414.5
147.5°	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7	426.2	426.6	426.6
150°	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4	433.8	434.3	434.4
152.5°	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3	440.8	441.3	441.2
155°	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8	450.2	450.7	450.6
157.5°	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7	458.2	458.8	458.7
160°	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3	462.8	463.3	463.2
162.5°	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6	467.2	467.7	467.6
165°	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9	472.4	473.0	473.0
167.5°	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3	476.8	477.4	477.3
170°	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5	479.1	479.6	479.5
172.5°	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1	480.7	481.3	481.2
175°	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0	482.5	483.1	483.0
177.5°	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2	482.6	483.1	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	5.0	4.7	5.1	4.8	5.1	4.7	5.0	4.9	5.1	5.1	5.0
90°	9.0	9.1	9.3	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7
92.5°	9.1	9.2	9.3	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5
95°	15.2	15.2	15.1	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3
97.5°	19.7	19.8	19.9	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8
100°	22.9	23.1	23.2	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1
102.5°	24.4	24.6	24.8	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0
105°	25.5	25.8	26.2	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0
107.5°	26.3	26.7	26.9	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0
110°	26.6	26.9	27.2	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	27.1	27.3	27.6	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3
115°	45.3	39.7	34.2	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3
117.5°	171.6	153.3	135.0	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8
120°	243.9	233.5	223.0	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3
122.5°	271.3	269.3	267.3	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0
125°	297.3	297.5	297.7	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5
127.5°	318.5	318.5	318.5	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4
130°	331.7	331.6	331.5	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6
132.5°	344.1	344.1	344.1	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5
135°	362.6	362.4	362.2	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9
137.5°	379.4	379.1	378.9	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9
140°	390.0	389.6	389.3	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9
142.5°	400.1	399.7	399.3	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1
145°	414.1	413.7	413.4	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4
147.5°	426.2	425.9	425.6	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7
150°	434.0	433.6	433.2	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4
152.5°	440.8	440.3	439.7	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3
155°	450.0	449.4	448.7	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8
157.5°	458.1	457.5	456.9	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7
160°	462.7	462.1	461.5	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3
162.5°	466.9	466.3	465.6	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6
165°	472.4	471.9	471.3	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9
167.5°	476.5	475.9	475.2	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3
170°	478.8	478.1	477.4	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5
172.5°	480.5	479.8	479.1	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1
175°	482.2	481.4	480.6	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0
177.5°	482.4	481.8	481.3	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	5.1	5.1	5.1	5.1	4.9	5.3	5.4	5.5	5.8	6.4	7.1
90°	7.3	6.9	6.4	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3
92.5°	8.3	8.1	7.7	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0
95°	13.9	13.6	13.0	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7
97.5°	18.5	18.2	17.0	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9
100°	20.5	19.9	18.5	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7
102.5°	21.2	20.4	31.5	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1
105°	22.1	21.3	42.4	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9
107.5°	28.9	29.8	55.1	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4
110°	53.2	61.0	83.3	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	125.6	153.8	159.3	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2
115°	179.1	215.0	213.0	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4
117.5°	229.5	238.1	236.8	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5
120°	256.3	255.4	254.0	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9
122.5°	272.5	271.9	270.4	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5
125°	295.0	294.5	293.0	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3
127.5°	315.6	314.8	313.7	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8
130°	328.7	327.9	327.1	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5
132.5°	341.8	341.0	340.1	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5
135°	360.0	359.3	358.6	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6
137.5°	377.1	376.3	375.5	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9
140°	388.2	387.5	386.6	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9
142.5°	398.4	397.8	396.8	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9
145°	412.8	412.2	410.9	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7
147.5°	425.3	424.9	423.6	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4
150°	432.9	432.4	431.2	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3
152.5°	439.9	439.4	438.2	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8
155°	449.3	448.8	447.9	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8
157.5°	457.1	456.6	456.0	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3
160°	461.9	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4
162.5°	466.1	465.5	465.1	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9
165°	471.3	470.8	470.6	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8
167.5°	475.7	475.2	475.0	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3
170°	477.9	477.4	477.3	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8
172.5°	479.6	479.1	478.9	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5
175°	481.4	480.9	480.7	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7
177.5°	481.8	481.3	481.3	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.1	5.1	5.0	4.9	5.3	5.4	5.3	5.4	5.8	5.6	6.0
90°	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7
92.5°	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5
95°	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3
97.5°	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8
100°	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1
102.5°	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0
105°	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0
107.5°	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0
110°	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5





TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3
115°	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3
117.5°	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8
120°	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3
122.5°	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0
125°	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5
127.5°	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4
130°	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6
132.5°	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5
135°	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9
137.5°	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9
140°	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9
142.5°	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1
145°	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4
147.5°	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7
150°	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4
152.5°	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3
155°	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8
157.5°	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7
160°	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3
162.5°	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6
165°	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9
167.5°	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3
170°	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5
172.5°	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1
175°	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0
177.5°	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	5.8	5.9	5.9	6.0	6.0	6.0	5.8
90°	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331785-930

CATALOG NUMBER: S122RDIW-S485D435U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)