

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331501-927

Luminaire Tested: **S122DIW-S485D710U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331501-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3946.2 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.9
10°-20°	213.1	5.4
20°-30°	309.3	7.8
30°-40°	326.4	8.3
40°-50°	289.0	7.3
50°-60°	230.6	5.8
60°-70°	156.8	4.0
70°-80°	80.4	2.0
80°-90°	21.3	0.5
90°-100°	25.6	0.6
100°-110°	93.8	2.4
110°-120°	250.6	6.4
120°-130°	413.7	10.5
130°-140°	440.0	11.1
140°-150°	408.9	10.4
150°-160°	328.8	8.3
160°-170°	211.9	5.4
170°-180°	72.9	1.8
0°-30°	595.8	15.1
0°-40°	922.2	23.4
0°-60°	1441.8	36.5
0°-90°	1700.2	43.1
90°-120°	369.9	9.4
90°-150°	1632.5	41.4
90°-180°	2246.0	56.9
0°-180°	3946.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	15	1	15	1	15	7
95°	24	36	24	36	24	22
105°	42	169	42	169	42	44
115°	46	319	46	319	46	114
125°	474	451	474	451	474	410
135°	576	558	576	558	576	444
145°	657	647	657	647	657	411
155°	713	713	713	713	713	329
165°	749	751	749	751	749	212
175°	764	768	764	768	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	9.1	9.1	9.3	9.0	9.0	9.1	9.0	8.6	8.7	8.9	8.9
90°	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4	11.7	11.1	10.1
92.5°	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5	13.2	12.8	12.4
95°	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9	22.3	21.6	20.8
97.5°	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9	29.5	28.9	26.9
100°	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6	32.6	31.6	29.5
102.5°	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1	33.7	32.5	50.0
105°	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5	35.2	33.8	67.5
107.5°	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6	45.9	47.4	87.7
110°	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4	84.8	97.0	132.7



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9	199.9	244.8	253.6
115°	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1	285.1	342.1	339.1
117.5°	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4	365.2	379.0	376.8
120°	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5	408.0	406.5	404.3
122.5°	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4	433.6	432.7	430.2
125°	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3	469.4	468.6	466.3
127.5°	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5	502.2	501.0	499.2
130°	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6	523.2	521.9	520.5
132.5°	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0	543.8	542.7	541.4
135°	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3	573.0	571.8	570.7
137.5°	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3	600.2	599.0	597.7
140°	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9	617.8	616.7	615.3
142.5°	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1	634.1	633.1	631.5
145°	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7	657.0	656.1	653.9
147.5°	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6	676.9	676.2	674.1
150°	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7	689.0	688.2	686.3
152.5°	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8	700.1	699.3	697.4
155°	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7	715.0	714.3	712.8
157.5°	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4	727.5	726.7	725.6
160°	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7	735.0	734.3	733.5
162.5°	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6	741.7	740.9	740.3
165°	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2	748.8
167.5°	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0	757.1	756.2	755.9
170°	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5	760.7	759.8	759.5
172.5°	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1	763.3	762.4	762.2
175°	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1	766.2	765.3	765.1
177.5°	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4	766.7	766.0	765.9
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	9.0	8.7	8.6	8.8	7.8	7.5	6.3	5.3	5.4	5.4	5.1
90°	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6	1.9	3.2	4.6
92.5°	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2	11.1	10.9	10.9
95°	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0	32.0	27.9	23.8
97.5°	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5	60.0	48.6	37.2
100°	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2	81.3	64.4	47.5
102.5°	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5	123.9	120.3	116.7
105°	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6	172.3	176.0	179.7
107.5°	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5	218.5	221.5	224.4
110°	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7	248.3	250.9	253.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1	276.4	278.7	280.9
115°	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9	321.0	323.1	325.2
117.5°	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9	361.2	363.6	365.9
120°	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2	390.1	391.9	393.7
122.5°	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0	415.0	416.9	418.9
125°	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8	452.5	454.1	455.7
127.5°	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1	486.9	488.7	490.4
130°	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8	508.8	510.8	512.8
132.5°	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1	530.8	532.4	534.1
135°	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9	559.8	561.8	563.8
137.5°	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1	588.4	589.9	591.2
140°	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2	607.1	608.1	609.1
142.5°	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1	623.0	623.9	624.8
145°	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2	647.1	647.0	646.8
147.5°	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0	668.6	668.1	667.7
150°	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3	682.4	681.5	680.6
152.5°	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2	694.3	693.3	692.3
155°	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6	711.5	710.4	709.3
157.5°	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3	725.3	724.4	723.4
160°	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	733.5	732.8	732.1
162.5°	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3	740.6	739.9	739.1
165°	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9	750.1	749.4	748.7
167.5°	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0	757.2	756.5	755.7
170°	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0	761.2	760.5	759.8
172.5°	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6	763.9	763.2	762.4
175°	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1	767.2	766.4	765.5
177.5°	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7	767.9	767.2	766.6
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	5.2	5.2	5.1	5.4	5.3	5.3	5.1	5.3	5.5	5.1	5.1
90°	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4	12.9	13.5	14.0
92.5°	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5	13.9	14.2	14.4
95°	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9	23.4	24.1	24.3
97.5°	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9	30.4	30.9	31.2
100°	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6	34.5	35.6	36.2
102.5°	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1	36.4	37.6	38.4
105°	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5	37.9	39.2	40.2
107.5°	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6	43.3	41.8	41.4
110°	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4	60.0	47.8	41.8



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9	110.0	65.0	42.7
115°	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1	171.0	113.9	81.0
117.5°	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4	337.5	323.8	302.3
120°	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5	410.9	412.4	404.8
122.5°	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4	435.3	436.3	435.1
125°	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3	471.2	472.1	472.7
127.5°	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5	504.8	506.0	506.7
130°	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6	525.9	527.3	527.9
132.5°	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0	546.2	547.3	547.9
135°	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3	575.4	576.7	577.2
137.5°	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3	602.5	603.8	604.2
140°	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9	620.0	621.2	621.4
142.5°	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1	636.1	637.2	637.3
145°	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7	658.6	659.5	659.7
147.5°	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6	678.2	678.8	678.9
150°	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7	690.5	691.2	691.3
152.5°	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8	701.6	702.3	702.3
155°	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7	716.5	717.2	717.1
157.5°	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4	729.2	730.1	730.0
160°	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7	736.5	737.2	737.1
162.5°	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6	743.4	744.3	744.2
165°	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0	751.8	752.7	752.7
167.5°	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0	758.8	759.6	759.5
170°	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5	762.3	763.2	763.1
172.5°	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1	765.0	765.9	765.7
175°	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1	767.9	768.7	768.6
177.5°	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4	768.0	768.7	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	5.2	5.0	5.1	4.9	5.1	5.0	5.2	5.1	5.1	5.5	5.3
90°	14.3	14.5	14.7	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4
92.5°	14.5	14.7	14.8	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5
95°	24.2	24.1	24.0	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9
97.5°	31.4	31.5	31.7	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9
100°	36.4	36.7	36.9	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6
102.5°	38.8	39.1	39.5	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1
105°	40.6	41.2	41.7	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5
107.5°	41.9	42.4	42.9	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6
110°	42.3	42.9	43.3	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	43.1	43.5	43.9	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9
115°	72.1	63.2	54.3	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1
117.5°	273.1	244.0	214.8	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4
120°	388.2	371.5	354.9	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5
122.5°	431.8	428.6	425.4	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4
125°	473.0	473.4	473.8	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3
127.5°	506.8	506.8	506.9	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5
130°	527.8	527.7	527.5	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6
132.5°	547.7	547.6	547.5	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0
135°	576.9	576.7	576.5	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3
137.5°	603.7	603.3	602.9	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3
140°	620.8	620.1	619.5	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9
142.5°	636.8	636.1	635.5	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1
145°	659.0	658.4	657.7	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7
147.5°	678.3	677.9	677.3	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6
150°	690.6	690.0	689.4	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7
152.5°	701.4	700.6	699.8	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8
155°	716.1	715.2	714.2	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7
157.5°	729.0	728.1	727.1	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4
160°	736.3	735.4	734.6	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7
162.5°	743.1	742.0	740.9	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6
165°	751.8	751.0	750.1	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0
167.5°	758.4	757.3	756.2	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0
170°	762.0	760.9	759.8	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5
172.5°	764.6	763.5	762.4	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1
175°	767.3	766.1	764.9	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1
177.5°	767.8	766.8	766.0	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	5.1	5.3	5.3	5.4	5.1	5.2	5.2	5.1	5.4	5.4	5.3
90°	11.7	11.1	10.1	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6
92.5°	13.2	12.8	12.4	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2
95°	22.3	21.6	20.8	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0
97.5°	29.5	28.9	26.9	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5
100°	32.6	31.6	29.5	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2
102.5°	33.7	32.5	50.0	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5
105°	35.2	33.8	67.5	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6
107.5°	45.9	47.4	87.7	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5
110°	84.8	97.0	132.7	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	199.9	244.8	253.6	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1
115°	285.1	342.1	339.1	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9
117.5°	365.2	379.0	376.8	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9
120°	408.0	406.5	404.3	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2
122.5°	433.6	432.7	430.2	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0
125°	469.4	468.6	466.3	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8
127.5°	502.2	501.0	499.2	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1
130°	523.2	521.9	520.5	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8
132.5°	543.8	542.7	541.4	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1
135°	573.0	571.8	570.7	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9
137.5°	600.2	599.0	597.7	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1
140°	617.8	616.7	615.3	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2
142.5°	634.1	633.1	631.5	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1
145°	657.0	656.1	653.9	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2
147.5°	676.9	676.2	674.1	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0
150°	689.0	688.2	686.3	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3
152.5°	700.1	699.3	697.4	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2
155°	715.0	714.3	712.8	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6
157.5°	727.5	726.7	725.6	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3
160°	735.0	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3
162.5°	741.7	740.9	740.3	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3
165°	750.1	749.2	748.8	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9
167.5°	757.1	756.2	755.9	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0
170°	760.7	759.8	759.5	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0
172.5°	763.3	762.4	762.2	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6
175°	766.2	765.3	765.1	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1
177.5°	766.7	766.0	765.9	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.3	7.5	7.8	8.8	8.6	8.7	9.0	8.9	8.9	8.7	8.6
90°	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4
92.5°	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5
95°	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9
97.5°	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9
100°	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6
102.5°	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1
105°	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5
107.5°	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6
110°	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9
115°	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1
117.5°	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4
120°	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5
122.5°	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4
125°	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3
127.5°	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5
130°	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6
132.5°	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0
135°	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3
137.5°	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3
140°	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9
142.5°	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1
145°	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7
147.5°	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6
150°	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7
152.5°	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8
155°	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7
157.5°	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4
160°	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7
162.5°	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6
165°	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0
167.5°	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0
170°	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5
172.5°	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1
175°	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1
177.5°	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	9.0	9.1	9.0	9.0	9.3	9.1	9.1
90°	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	60.0	47.8	41.8	42.3	42.9	43.3	43.8



TEST NUMBER: P331501-927

CATALOG NUMBER: S122DIW-S485D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)