

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331543-927

Luminaire Tested: **S122DIW-S675D1240U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331543-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6249.4 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	42	35	34	33	27				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14				
8	53	41	34	29	48	38	31	27	31	26	23	26	22	19	20	17	15	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	18	16	14	12				
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	1.6
10°-20°	291.3	4.7
20°-30°	422.8	6.8
30°-40°	446.2	7.1
40°-50°	395.0	6.3
50°-60°	315.3	5.0
60°-70°	214.3	3.4
70°-80°	109.9	1.8
80°-90°	29.8	0.5
90°-100°	44.7	0.7
100°-110°	163.8	2.6
110°-120°	437.9	7.0
120°-130°	722.9	11.6
130°-140°	768.8	12.3
140°-150°	714.5	11.4
150°-160°	574.5	9.2
160°-170°	370.2	5.9
170°-180°	127.4	2.0
0°-30°	814.3	13.0
0°-40°	1260.5	20.2
0°-60°	1970.8	31.5
0°-90°	2324.7	37.2
90°-120°	646.4	10.3
90°-150°	2852.5	45.6
90°-180°	3925.0	62.8
0°-180°	6249.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	25
90°	26	1	26	1	26	13
95°	42	63	42	63	42	39
105°	74	295	74	295	74	77
115°	80	557	80	557	80	199
125°	828	788	828	788	828	717
135°	1007	975	1007	975	1007	776
145°	1148	1131	1148	1131	1148	718
155°	1246	1245	1246	1245	1246	575
165°	1309	1312	1309	1312	1309	370
175°	1334	1342	1334	1342	1334	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	13.6	13.5	13.8	13.4	13.3	13.5	13.2	12.8	12.8	12.9	12.9
90°	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5	20.4	19.4	17.7
92.5°	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6	23.1	22.5	21.6
95°	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9	38.9	37.8	36.3
97.5°	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3	51.4	50.6	47.1
100°	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7	57.0	55.2	51.6
102.5°	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2	59.0	56.8	87.4
105°	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8	61.5	59.1	117.9
107.5°	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0	80.3	82.8	153.3
110°	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5	148.1	169.6	231.8



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6	349.2	427.7	443.1
115°	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5	498.2	597.9	592.6
117.5°	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0	638.1	662.3	658.5
120°	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5	712.9	710.3	706.5
122.5°	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1	757.6	756.1	751.9
125°	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9	820.4	818.9	814.8
127.5°	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8	877.7	875.4	872.4
130°	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6	914.3	911.9	909.5
132.5°	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4	950.3	948.3	945.9
135°	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4	1001.2	999.1	997.1
137.5°	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8	1048.7	1046.6	1044.3
140°	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5	1079.5	1077.6	1075.2
142.5°	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8	1108.0	1106.3	1103.5
145°	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4	1147.9	1146.4	1142.7
147.5°	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9	1182.8	1181.6	1178.1
150°	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1	1203.9	1202.6	1199.1
152.5°	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6	1223.3	1221.9	1218.7
155°	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7	1249.4	1248.2	1245.5
157.5°	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8	1271.3	1269.9	1268.0
160°	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6	1284.3	1283.0	1281.8
162.5°	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6	1296.1	1294.7	1293.6
165°	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2	1308.5
167.5°	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4	1322.9	1321.4	1320.8
170°	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6	1329.1	1327.6	1327.1
172.5°	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2	1333.7	1332.2	1331.8
175°	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3	1338.8	1337.3	1336.9
177.5°	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8	1339.7	1338.5	1338.2
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	12.9	12.5	12.2	12.4	11.0	10.5	8.8	7.3	7.4	7.6	7.4
90°	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6	19.3	19.2	18.9
95°	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0	55.8	48.8	41.7
97.5°	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0	105.0	84.9	65.0
100°	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5	142.0	112.5	83.0
102.5°	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7	216.4	210.2	204.0
105°	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6	301.0	307.5	313.9
107.5°	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6	381.8	387.0	392.2
110°	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3	433.8	438.3	442.8



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9	482.9	486.9	490.9
115°	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2	560.9	564.5	568.2
117.5°	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2	631.3	635.3	639.4
120°	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3	681.6	684.8	688.0
122.5°	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8	725.2	728.6	732.0
125°	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8	790.6	793.4	796.2
127.5°	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7	850.8	853.9	857.1
130°	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7	889.1	892.6	896.0
132.5°	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5	927.4	930.3	933.3
135°	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9	978.3	981.8	985.2
137.5°	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8	1028.3	1030.6	1033.1
140°	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1	1060.9	1062.6	1064.3
142.5°	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1	1088.6	1090.2	1091.7
145°	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8	1130.7	1130.4	1130.2
147.5°	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0	1168.2	1167.4	1166.6
150°	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9	1192.4	1190.9	1189.3
152.5°	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8	1213.1	1211.4	1209.7
155°	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2	1243.3	1241.3	1239.4
157.5°	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1	1267.4	1265.7	1264.2
160°	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1281.8	1280.4	1279.1
162.5°	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5	1294.1	1292.8	1291.6
165°	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1	1310.8	1309.5	1308.2
167.5°	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5	1323.2	1321.9	1320.6
170°	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5	1330.2	1328.9	1327.6
172.5°	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1	1334.8	1333.6	1332.2
175°	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1	1340.6	1339.1	1337.6
177.5°	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1	1341.9	1340.7	1339.5
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	7.6	7.7	7.7	8.0	8.1	8.1	8.0	8.2	8.4	8.0	8.2
90°	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5	22.6	23.7	24.5
92.5°	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6	24.2	24.7	25.1
95°	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9	41.0	42.1	42.5
97.5°	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3	53.2	54.0	54.6
100°	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7	60.4	62.1	63.2
102.5°	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2	63.5	65.8	67.2
105°	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8	66.2	68.6	70.2
107.5°	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0	75.5	73.1	72.3
110°	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5	105.0	83.4	73.1



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6	192.1	113.5	74.5
115°	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5	298.8	199.1	141.5
117.5°	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0	589.9	565.8	528.2
120°	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5	718.0	720.6	707.4
122.5°	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1	760.7	762.2	760.2
125°	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9	823.4	824.9	825.9
127.5°	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8	882.0	884.2	885.4
130°	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6	919.0	921.3	922.4
132.5°	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4	954.3	956.4	957.3
135°	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4	1005.5	1007.7	1008.5
137.5°	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8	1052.9	1055.0	1055.7
140°	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5	1083.4	1085.4	1085.8
142.5°	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8	1111.6	1113.3	1113.6
145°	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4	1150.9	1152.4	1152.6
147.5°	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9	1185.0	1186.1	1186.2
150°	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1	1206.5	1207.8	1207.8
152.5°	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6	1225.8	1227.2	1227.1
155°	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7	1252.0	1253.3	1253.1
157.5°	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8	1274.2	1275.7	1275.6
160°	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6	1286.9	1288.2	1288.1
162.5°	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6	1299.0	1300.5	1300.3
165°	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2
167.5°	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4	1325.9	1327.4	1327.2
170°	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6	1332.1	1333.6	1333.4
172.5°	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2	1336.7	1338.2	1338.1
175°	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3	1341.8	1343.3	1343.0
177.5°	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8	1342.0	1343.3	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	8.2	8.0	8.1	7.8	8.1	8.0	8.2	8.2	8.0	8.4	8.2
90°	24.9	25.3	25.7	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5
92.5°	25.3	25.7	25.9	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6
95°	42.3	42.1	41.9	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9
97.5°	54.8	55.1	55.4	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3
100°	63.6	64.1	64.5	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7
102.5°	67.7	68.4	69.0	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2
105°	71.1	71.9	72.8	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8
107.5°	73.2	74.1	74.9	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0
110°	74.0	74.9	75.7	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	75.3	76.0	76.6	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6
115°	126.0	110.5	95.0	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5
117.5°	477.3	426.4	375.4	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0
120°	678.3	649.3	620.2	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5
122.5°	754.6	748.9	743.3	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1
125°	826.6	827.3	827.9	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9
127.5°	885.5	885.7	885.7	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8
130°	922.2	922.0	921.8	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6
132.5°	957.1	956.9	956.6	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4
135°	1008.1	1007.7	1007.3	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4
137.5°	1054.9	1054.2	1053.5	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8
140°	1084.7	1083.6	1082.5	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5
142.5°	1112.6	1111.5	1110.4	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8
145°	1151.5	1150.5	1149.4	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4
147.5°	1185.3	1184.4	1183.5	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9
150°	1206.8	1205.7	1204.6	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1
152.5°	1225.7	1224.2	1222.8	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6
155°	1251.3	1249.7	1247.9	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7
157.5°	1273.9	1272.2	1270.6	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8
160°	1286.6	1285.1	1283.6	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6
162.5°	1298.5	1296.6	1294.7	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6
165°	1313.7	1312.2	1310.7	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2
167.5°	1325.2	1323.3	1321.4	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4
170°	1331.5	1329.5	1327.6	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6
172.5°	1336.1	1334.2	1332.2	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2
175°	1340.8	1338.7	1336.5	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3
177.5°	1341.6	1340.0	1338.5	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	8.0	8.1	8.1	8.0	7.7	7.7	7.6	7.4	7.6	7.4	7.3
90°	20.4	19.4	17.7	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0
92.5°	23.1	22.5	21.6	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6
95°	38.9	37.8	36.3	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0
97.5°	51.4	50.6	47.1	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0
100°	57.0	55.2	51.6	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5
102.5°	59.0	56.8	87.4	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7
105°	61.5	59.1	117.9	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6
107.5°	80.3	82.8	153.3	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6
110°	148.1	169.6	231.8	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.2	427.7	443.1	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9
115°	498.2	597.9	592.6	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2
117.5°	638.1	662.3	658.5	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2
120°	712.9	710.3	706.5	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3
122.5°	757.6	756.1	751.9	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8
125°	820.4	818.9	814.8	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8
127.5°	877.7	875.4	872.4	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7
130°	914.3	911.9	909.5	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7
132.5°	950.3	948.3	945.9	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5
135°	1001.2	999.1	997.1	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9
137.5°	1048.7	1046.6	1044.3	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8
140°	1079.5	1077.6	1075.2	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1
142.5°	1108.0	1106.3	1103.5	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1
145°	1147.9	1146.4	1142.7	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8
147.5°	1182.8	1181.6	1178.1	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0
150°	1203.9	1202.6	1199.1	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9
152.5°	1223.3	1221.9	1218.7	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8
155°	1249.4	1248.2	1245.5	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2
157.5°	1271.3	1269.9	1268.0	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1
160°	1284.3	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0
162.5°	1296.1	1294.7	1293.6	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5
165°	1310.7	1309.2	1308.5	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1
167.5°	1322.9	1321.4	1320.8	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5
170°	1329.1	1327.6	1327.1	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5
172.5°	1333.7	1332.2	1331.8	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1
175°	1338.8	1337.3	1336.9	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1
177.5°	1339.7	1338.5	1338.2	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.8	10.5	11.0	12.4	12.2	12.5	12.9	12.9	12.9	12.8	12.8
90°	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5
92.5°	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6
95°	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9
97.5°	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3
100°	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7
102.5°	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2
105°	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8
107.5°	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0
110°	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6
115°	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5
117.5°	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0
120°	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5
122.5°	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1
125°	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9
127.5°	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8
130°	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6
132.5°	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4
135°	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4
137.5°	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8
140°	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5
142.5°	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8
145°	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4
147.5°	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9
150°	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1
152.5°	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6
155°	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7
157.5°	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8
160°	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6
162.5°	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6
165°	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2
167.5°	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4
170°	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6
172.5°	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2
175°	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3
177.5°	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	13.2	13.5	13.3	13.4	13.8	13.5	13.6
90°	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	105.0	83.4	73.1	74.0	74.9	75.7	76.5



TEST NUMBER: P331543-927

CATALOG NUMBER: S122DIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)