

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331793-930

Luminaire Tested: **S122RDIW-S485D970U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331793-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D970U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4672.1 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32				
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	35	35	28				
2	86	79	74	69	78	72	67	63	58	54	51	45	42	41	32	31	30	25				
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	29	28	26	21				
4	73	62	55	50	65	57	50	46	46	41	38	36	33	30	26	25	23	19				
5	67	56	48	43	60	51	44	39	41	37	33	32	29	27	24	22	20	17				
6	62	50	43	37	55	46	39	34	37	33	29	29	26	24	22	20	18	15				
7	57	45	38	33	51	42	35	30	34	29	26	27	24	21	20	18	16	14				
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12				
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	15	14	11				
10	46	35	28	23	42	32	26	22	26	22	19	21	18	16	16	14	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.1	1.8
10°-20°	231.5	5.0
20°-30°	298.2	6.4
30°-40°	283.4	6.1
40°-50°	242.8	5.2
50°-60°	184.9	4.0
60°-70°	116.9	2.5
70°-80°	58.4	1.2
80°-90°	17.8	0.4
90°-100°	35.9	0.8
100°-110°	131.7	2.8
110°-120°	352.0	7.5
120°-130°	581.1	12.4
130°-140°	618.0	13.2
140°-150°	574.4	12.3
150°-160°	461.8	9.9
160°-170°	297.6	6.4
170°-180°	102.4	2.2
0°-30°	612.8	13.1
0°-40°	896.2	19.2
0°-60°	1323.9	28.3
0°-90°	1517.0	32.5
90°-120°	519.7	11.1
90°-150°	2293.2	49.1
90°-180°	3155.0	67.5
0°-180°	4672.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	21	1	21	1	21	10
95°	34	51	34	51	34	31
105°	59	237	59	237	59	62
115°	64	448	64	448	64	160
125°	666	633	666	633	666	576
135°	809	784	809	784	809	624
145°	923	909	923	909	923	577
155°	1002	1001	1002	1001	1002	462
165°	1052	1055	1052	1055	1052	297
175°	1073	1079	1073	1079	1073	102
180°	1077	1077	1077	1077	1077	



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	8.1	8.3	8.2	8.2	8.1	8.0	7.7	7.8	7.4	7.5	7.0
90°	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3	16.5	15.6	14.2
92.5°	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0	18.5	18.1	17.4
95°	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1	31.2	30.4	29.2
97.5°	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1	41.3	40.7	37.8
100°	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2	45.8	44.4	41.5
102.5°	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2	47.5	45.7	40.3
105°	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4	49.4	47.5	44.8
107.5°	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6	64.6	66.5	123.2
110°	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7	119.0	136.3	186.4



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5	280.7	343.9	356.2
115°	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3	400.5	480.7	476.4
117.5°	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6	513.0	532.4	529.5
120°	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2	573.2	571.0	567.9
122.5°	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3	609.0	607.8	604.4
125°	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7	659.5	658.3	655.0
127.5°	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4	705.6	703.8	701.3
130°	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9	735.0	733.1	731.2
132.5°	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6	764.0	762.4	760.4
135°	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7	804.9	803.2	801.6
137.5°	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7	843.1	841.4	839.6
140°	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4	867.9	866.3	864.4
142.5°	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2	890.8	889.3	887.2
145°	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1	922.8	921.6	918.7
147.5°	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8	950.9	950.0	947.1
150°	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9	967.8	966.8	964.0
152.5°	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5	983.4	982.4	979.7
155°	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5	1004.4	1003.4	1001.4
157.5°	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2	1022.1	1020.8	1019.4
160°	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6	1032.5	1031.4	1030.5
162.5°	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2	1042.0	1040.8	1039.9
165°	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5	1052.0
167.5°	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7	1063.5	1062.3	1061.8
170°	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8	1068.5	1067.3	1067.0
172.5°	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4	1072.3	1071.1	1070.7
175°	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5	1076.3	1075.1	1074.7
177.5°	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0	1077.0	1076.0	1075.9
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	6.7	6.7	6.4	5.8	5.7	5.5	6.4	7.3	6.6	6.3	6.2
90°	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7	15.6	15.4	15.2
95°	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6	44.9	39.2	33.5
97.5°	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5	84.4	68.3	52.2
100°	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9	114.1	90.4	66.8
102.5°	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0	174.0	169.0	164.0
105°	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8	242.1	247.2	252.4
107.5°	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7	307.0	311.1	315.3
110°	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1	348.8	352.4	356.0





TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0	388.2	391.4	394.7
115°	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9	450.9	453.9	456.8
117.5°	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2	507.5	510.8	514.0
120°	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4	548.0	550.5	553.1
122.5°	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2	582.9	585.7	588.4
125°	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3	635.6	637.9	640.1
127.5°	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5	684.0	686.5	689.0
130°	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1	714.9	717.6	720.3
132.5°	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2	745.6	748.0	750.2
135°	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7	786.5	789.3	792.1
137.5°	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7	826.6	828.6	830.5
140°	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5	852.9	854.3	855.7
142.5°	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9	875.1	876.4	877.7
145°	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1	909.0	908.8	908.7
147.5°	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9	939.1	938.5	937.8
150°	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8	958.5	957.3	956.2
152.5°	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6	975.3	973.9	972.6
155°	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1	999.5	997.9	996.4
157.5°	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3	1019.0	1017.6	1016.3
160°	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1030.5	1029.4	1028.3
162.5°	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5	1040.4	1039.3	1038.3
165°	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8	1053.8	1052.7	1051.7
167.5°	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8	1063.7	1062.7	1061.7
170°	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4	1069.3	1068.4	1067.3
172.5°	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2	1073.1	1072.0	1071.1
175°	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0	1077.7	1076.5	1075.4
177.5°	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8	1078.8	1077.8	1076.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	6.3	6.4	6.2	6.4	6.8	6.8	6.9	6.8	7.0	7.3	7.1
90°	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3	18.2	19.1	19.6
92.5°	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0	19.4	19.9	20.2
95°	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1	33.0	33.8	34.2
97.5°	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1	42.7	43.5	43.9
100°	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2	48.6	50.0	50.8
102.5°	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2	51.0	52.8	54.0
105°	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4	53.2	55.1	56.4
107.5°	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6	60.7	58.8	58.1
110°	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7	84.4	67.1	58.8



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5	154.4	91.2	59.9
115°	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3	240.2	160.0	113.7
117.5°	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6	474.3	454.9	424.7
120°	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2	577.2	579.4	568.7
122.5°	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3	611.6	612.8	611.1
125°	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7	661.9	663.2	664.0
127.5°	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4	709.1	710.9	711.8
130°	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9	738.8	740.7	741.6
132.5°	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6	767.3	768.9	769.6
135°	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7	808.4	810.1	810.8
137.5°	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7	846.4	848.2	848.7
140°	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4	871.0	872.5	872.9
142.5°	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2	893.6	895.0	895.3
145°	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1	925.3	926.4	926.7
147.5°	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8	952.7	953.6	953.7
150°	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9	969.9	970.9	971.0
152.5°	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5	985.5	986.5	986.5
155°	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5	1006.5	1007.5	1007.4
157.5°	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2	1024.4	1025.6	1025.5
160°	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6	1034.5	1035.6	1035.5
162.5°	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2	1044.3	1045.5	1045.4
165°	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4
167.5°	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7	1065.9	1067.1	1067.0
170°	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8	1070.9	1072.1	1072.0
172.5°	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4	1074.6	1075.9	1075.7
175°	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5	1078.7	1079.9	1079.7
177.5°	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0	1078.9	1079.9	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	7.2	7.0	7.3	7.1	7.3	7.0	7.2	7.1	7.3	7.0	6.8
90°	20.0	20.3	20.7	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3
92.5°	20.4	20.6	20.8	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0
95°	34.0	33.8	33.7	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1
97.5°	44.1	44.3	44.5	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1
100°	51.1	51.5	51.9	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2
102.5°	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2
105°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4
107.5°	58.9	59.5	60.3	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6
110°	59.4	60.2	60.8	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	60.5	61.1	61.6	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5
115°	101.3	88.8	76.3	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3
117.5°	383.7	342.8	301.8	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6
120°	545.4	522.0	498.6	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2
122.5°	606.6	602.1	597.5	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3
125°	664.6	665.0	665.5	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7
127.5°	711.9	712.0	712.1	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4
130°	741.4	741.2	741.0	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9
132.5°	769.4	769.2	769.1	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6
135°	810.5	810.1	809.8	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7
137.5°	848.2	847.5	846.9	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7
140°	872.0	871.1	870.3	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4
142.5°	894.5	893.6	892.8	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2
145°	925.8	924.9	924.1	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1
147.5°	952.9	952.2	951.5	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8
150°	970.2	969.3	968.4	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9
152.5°	985.4	984.2	983.1	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5
155°	1006.0	1004.6	1003.2	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5
157.5°	1024.1	1022.8	1021.4	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2
160°	1034.3	1033.1	1031.9	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6
162.5°	1043.8	1042.4	1040.9	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2
165°	1056.1	1054.9	1053.7	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9
167.5°	1065.4	1063.9	1062.3	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7
170°	1070.4	1068.9	1067.3	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8
172.5°	1074.2	1072.6	1071.1	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4
175°	1077.9	1076.2	1074.5	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5
177.5°	1078.5	1077.3	1076.0	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	6.9	6.8	6.8	6.4	6.2	6.4	6.3	6.2	6.3	6.6	7.3
90°	16.5	15.6	14.2	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8
92.5°	18.5	18.1	17.4	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7
95°	31.2	30.4	29.2	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6
97.5°	41.3	40.7	37.8	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5
100°	45.8	44.4	41.5	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9
102.5°	47.5	45.7	70.3	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0
105°	49.4	47.5	94.8	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8
107.5°	64.6	66.5	123.2	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7
110°	119.0	136.3	186.4	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.7	343.9	356.2	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0
115°	400.5	480.7	476.4	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9
117.5°	513.0	532.4	529.5	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2
120°	573.2	571.0	567.9	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4
122.5°	609.0	607.8	604.4	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2
125°	659.5	658.3	655.0	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3
127.5°	705.6	703.8	701.3	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5
130°	735.0	733.1	731.2	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1
132.5°	764.0	762.4	760.4	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2
135°	804.9	803.2	801.6	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7
137.5°	843.1	841.4	839.6	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7
140°	867.9	866.3	864.4	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5
142.5°	890.8	889.3	887.2	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9
145°	922.8	921.6	918.7	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1
147.5°	950.9	950.0	947.1	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9
150°	967.8	966.8	964.0	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8
152.5°	983.4	982.4	979.7	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6
155°	1004.4	1003.4	1001.4	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1
157.5°	1022.1	1020.8	1019.4	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3
160°	1032.5	1031.4	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4
162.5°	1042.0	1040.8	1039.9	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5
165°	1053.7	1052.5	1052.0	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8
167.5°	1063.5	1062.3	1061.8	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8
170°	1068.5	1067.3	1067.0	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4
172.5°	1072.3	1071.1	1070.7	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2
175°	1076.3	1075.1	1074.7	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0
177.5°	1077.0	1076.0	1075.9	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.4	5.5	5.7	5.8	6.4	6.7	6.7	7.0	7.5	7.4	7.8
90°	2.7	4.6	6.5	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3
92.5°	15.6	15.4	15.2	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0
95°	44.9	39.2	33.5	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1
97.5°	84.4	68.3	52.2	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1
100°	114.1	90.4	66.8	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2
102.5°	174.0	169.0	164.0	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2
105°	242.1	247.2	252.4	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4
107.5°	307.0	311.1	315.3	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6
110°	348.8	352.4	356.0	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7





TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	388.2	391.4	394.7	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5
115°	450.9	453.9	456.8	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3
117.5°	507.5	510.8	514.0	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6
120°	548.0	550.5	553.1	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2
122.5°	582.9	585.7	588.4	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3
125°	635.6	637.9	640.1	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7
127.5°	684.0	686.5	689.0	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4
130°	714.9	717.6	720.3	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9
132.5°	745.6	748.0	750.2	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6
135°	786.5	789.3	792.1	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7
137.5°	826.6	828.6	830.5	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7
140°	852.9	854.3	855.7	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4
142.5°	875.1	876.4	877.7	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2
145°	909.0	908.8	908.7	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1
147.5°	939.1	938.5	937.8	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8
150°	958.5	957.3	956.2	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9
152.5°	975.3	973.9	972.6	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5
155°	999.5	997.9	996.4	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5
157.5°	1019.0	1017.6	1016.3	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2
160°	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6
162.5°	1040.4	1039.3	1038.3	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2
165°	1053.8	1052.7	1051.7	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9
167.5°	1063.7	1062.7	1061.7	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7
170°	1069.3	1068.4	1067.3	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8
172.5°	1073.1	1072.0	1071.1	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4
175°	1077.7	1076.5	1075.4	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5
177.5°	1078.8	1077.8	1076.8	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	7.7	8.0	8.1	8.2	8.2	8.3	8.1
90°	18.2	19.1	19.6	20.0	20.3	20.7	21.0
92.5°	19.4	19.9	20.2	20.4	20.6	20.8	21.0
95°	33.0	33.8	34.2	34.0	33.8	33.7	33.5
97.5°	42.7	43.5	43.9	44.1	44.3	44.5	44.7
100°	48.6	50.0	50.8	51.1	51.5	51.9	52.2
102.5°	51.0	52.8	54.0	54.5	55.0	55.4	55.9
105°	53.2	55.1	56.4	57.2	57.8	58.5	59.2
107.5°	60.7	58.8	58.1	58.9	59.5	60.3	60.9
110°	84.4	67.1	58.8	59.4	60.2	60.8	61.6



TEST NUMBER: P331793-930

CATALOG NUMBER: S122RDIW-S485D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	154.4	91.2	59.9	60.5	61.1	61.6	62.2
115°	240.2	160.0	113.7	101.3	88.8	76.3	63.9
117.5°	474.3	454.9	424.7	383.7	342.8	301.8	260.8
120°	577.2	579.4	568.7	545.4	522.0	498.6	475.2
122.5°	611.6	612.8	611.1	606.6	602.1	597.5	593.0
125°	661.9	663.2	664.0	664.6	665.0	665.5	666.1
127.5°	709.1	710.9	711.8	711.9	712.0	712.1	712.2
130°	738.8	740.7	741.6	741.4	741.2	741.0	740.9
132.5°	767.3	768.9	769.6	769.4	769.2	769.1	768.9
135°	808.4	810.1	810.8	810.5	810.1	809.8	809.4
137.5°	846.4	848.2	848.7	848.2	847.5	846.9	846.4
140°	871.0	872.5	872.9	872.0	871.1	870.3	869.4
142.5°	893.6	895.0	895.3	894.5	893.6	892.8	891.9
145°	925.3	926.4	926.7	925.8	924.9	924.1	923.2
147.5°	952.7	953.6	953.7	952.9	952.2	951.5	950.7
150°	969.9	970.9	971.0	970.2	969.3	968.4	967.6
152.5°	985.5	986.5	986.5	985.4	984.2	983.1	981.9
155°	1006.5	1007.5	1007.4	1006.0	1004.6	1003.2	1001.8
157.5°	1024.4	1025.6	1025.5	1024.1	1022.8	1021.4	1020.1
160°	1034.5	1035.6	1035.5	1034.3	1033.1	1031.9	1030.7
162.5°	1044.3	1045.5	1045.4	1043.8	1042.4	1040.9	1039.4
165°	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5
167.5°	1065.9	1067.1	1067.0	1065.4	1063.9	1062.3	1060.8
170°	1070.9	1072.1	1072.0	1070.4	1068.9	1067.3	1065.8
172.5°	1074.6	1075.9	1075.7	1074.2	1072.6	1071.1	1069.5
175°	1078.7	1079.9	1079.7	1077.9	1076.2	1074.5	1072.8
177.5°	1078.9	1079.9	1079.8	1078.5	1077.3	1076.0	1074.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6

(END OF REPORT)