

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331553-927

Luminaire Tested: **S122DIW-S675D1440U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331553-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6706.6 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.2
10°-20°	222.5	3.3
20°-30°	327.1	4.9
30°-40°	379.9	5.7
40°-50°	379.5	5.7
50°-60°	331.0	4.9
60°-70°	244.7	3.6
70°-80°	138.6	2.1
80°-90°	41.1	0.6
90°-100°	51.9	0.8
100°-110°	190.5	2.8
110°-120°	509.1	7.6
120°-130°	840.4	12.5
130°-140°	893.8	13.3
140°-150°	830.7	12.4
150°-160°	667.9	10.0
160°-170°	430.4	6.4
170°-180°	148.2	2.2
0°-30°	628.7	9.4
0°-40°	1008.6	15.0
0°-60°	1719.1	25.6
0°-90°	2143.6	32.0
90°-120°	751.5	11.2
90°-150°	3316.5	49.5
90°-180°	4563.0	68.0
0°-180°	6706.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	1	13	22	28	30	5
95°	73	39	44	49	48	90
105°	342	357	69	81	86	366
115°	648	668	695	198	92	638
125°	916	931	952	960	963	816
135°	1134	1151	1162	1172	1171	875
145°	1315	1315	1333	1340	1335	822
155°	1448	1439	1451	1457	1449	667
165°	1526	1519	1522	1529	1522	431
175°	1560	1553	1555	1562	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.9	12.1	12.4	12.7	12.9	13.2	13.2	13.3	13.5	13.5	13.4
90°	1.1	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8
92.5°	22.7	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8
95°	73.2	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2
97.5°	145.4	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8
100°	199.4	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2
102.5°	258.9	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6
105°	342.5	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5
107.5°	437.8	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4
110°	499.2	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1



TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.8	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0
115°	647.8	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2
117.5°	729.2	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0
120°	788.7	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9
122.5°	839.2	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8
125°	916.0	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8
127.5°	985.6	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4
130°	1029.8	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0
132.5°	1074.8	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9
135°	1133.5	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1
137.5°	1192.7	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2
140°	1231.4	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1
142.5°	1263.9	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2
145°	1314.9	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6
147.5°	1359.2	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1
150°	1388.1	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7
152.5°	1412.4	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2
155°	1447.8	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6
157.5°	1475.5	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1
160°	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2
162.5°	1506.1	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0
165°	1525.5	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9
167.5°	1539.9	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1
170°	1548.1	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3
172.5°	1553.5	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7
175°	1560.4	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6
177.5°	1561.5	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	13.2	13.0	12.8	12.8	12.7	12.7	12.6	12.5
90°	25.0	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	27.4	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	46.4	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	60.8	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	68.2	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	71.2	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	74.2	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	90.6	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	147.1	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331553-927

CATALOG NUMBER: S122DIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	314.7	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	463.3	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	713.9	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	831.9	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	882.6	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	955.5	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1022.9	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1065.7	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1107.2	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1166.6	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1221.7	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1257.4	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1290.3	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1376.5	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1401.2	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1423.7	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1454.1	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1479.8	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1494.7	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1508.6	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1539.8	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1547.1	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1552.4	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1558.3	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1558.9	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)