

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331529-927

Luminaire Tested: **S122DIW-S675D435U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331529-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3512.2 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	59	57	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.3
10°-20°	222.5	6.3
20°-30°	327.1	9.3
30°-40°	379.9	10.8
40°-50°	379.5	10.8
50°-60°	331.0	9.4
60°-70°	244.7	7.0
70°-80°	138.6	3.9
80°-90°	38.4	1.1
90°-100°	15.6	0.4
100°-110°	57.2	1.6
110°-120°	153.0	4.4
120°-130°	252.6	7.2
130°-140°	268.6	7.6
140°-150°	249.7	7.1
150°-160°	200.7	5.7
160°-170°	129.3	3.7
170°-180°	44.5	1.3
0°-30°	628.7	17.9
0°-40°	1008.6	28.7
0°-60°	1719.1	48.9
0°-90°	2140.9	61.0
90°-120°	225.9	6.4
90°-150°	996.7	28.4
90°-180°	1371.0	39.0
0°-180°	3512.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	0	4	7	8	9	3
95°	22	12	13	15	15	27
105°	103	107	21	24	26	110
115°	195	201	209	60	28	192
125°	275	280	286	288	290	245
135°	341	346	349	352	352	263
145°	395	395	400	403	401	247
155°	435	432	436	438	436	200
165°	458	457	457	460	457	129
175°	469	467	467	469	466	45
180°	468	468	468	468	468	



TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.7	11.6	11.5	11.3	11.2	11.1	10.9	10.8	10.6	10.4	10.1
90°	0.3	1.2	2.0	2.9	3.6	4.4	5.0	5.5	6.2	6.7	7.1
92.5°	6.8	6.7	6.7	6.6	6.6	6.7	7.0	7.3	7.5	7.8	8.1
95°	22.0	19.5	17.0	14.6	12.0	11.1	11.6	12.1	12.7	13.2	13.5
97.5°	43.6	36.7	29.7	22.7	15.7	12.8	14.0	15.2	16.5	17.7	18.0
100°	60.0	49.6	39.3	29.0	18.7	14.2	15.4	16.7	18.0	19.3	19.9
102.5°	77.8	75.7	73.4	71.3	69.1	62.7	52.0	41.3	30.6	19.8	20.6
105°	102.9	105.2	107.4	109.7	111.9	102.8	82.3	61.7	41.2	20.7	21.5
107.5°	131.6	133.4	135.2	137.0	138.9	127.5	102.8	78.2	53.6	28.9	28.0
110°	150.0	151.5	153.1	154.7	156.3	146.2	124.5	102.7	81.0	59.3	51.7



TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.3	168.7	170.2	171.5	172.9	171.0	165.6	160.2	154.8	149.5	122.0
115°	194.7	196.0	197.3	198.5	199.8	201.4	203.3	205.2	207.0	208.9	174.0
117.5°	219.1	220.5	222.0	223.4	224.8	226.2	227.5	228.8	230.1	231.4	223.0
120°	237.0	238.1	239.2	240.4	241.5	242.8	244.2	245.5	246.8	248.2	249.1
122.5°	252.2	253.3	254.5	255.7	256.9	258.3	259.8	261.2	262.7	264.2	264.7
125°	275.3	276.2	277.3	278.2	279.2	280.4	281.9	283.3	284.7	286.1	286.6
127.5°	296.2	297.3	298.3	299.4	300.6	301.6	302.7	303.7	304.8	305.9	306.7
130°	309.5	310.7	311.9	313.1	314.3	315.3	316.2	317.0	317.8	318.6	319.4
132.5°	323.1	324.0	325.0	326.1	327.1	328.0	328.8	329.7	330.5	331.4	332.1
135°	340.6	341.8	343.0	344.2	345.5	346.3	347.1	347.8	348.4	349.1	349.8
137.5°	358.5	359.3	360.1	361.0	361.8	362.6	363.4	364.2	364.9	365.7	366.4
140°	370.1	370.7	371.3	371.9	372.5	373.2	374.1	374.9	375.7	376.5	377.2
142.5°	379.9	380.4	380.9	381.4	382.0	382.8	383.7	384.6	385.6	386.5	387.1
145°	395.1	395.1	395.0	394.9	394.8	395.5	396.7	398.0	399.3	400.5	401.1
147.5°	408.4	408.2	407.9	407.7	407.3	407.8	409.1	410.4	411.6	412.9	413.3
150°	417.2	416.6	416.1	415.6	415.0	415.3	416.6	417.8	419.0	420.2	420.6
152.5°	424.5	423.9	423.3	422.7	422.1	422.4	423.5	424.7	425.8	427.0	427.4
155°	435.1	434.4	433.7	433.1	432.4	432.5	433.4	434.3	435.2	436.1	436.6
157.5°	443.4	442.8	442.3	441.7	441.2	441.2	441.8	442.4	443.1	443.7	444.2
160°	448.3	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	448.8
162.5°	452.7	452.2	451.7	451.3	450.8	450.8	451.1	451.5	451.9	452.3	452.9
165°	458.4	458.0	457.6	457.1	456.6	456.5	456.8	457.0	457.2	457.4	458.0
167.5°	462.8	462.3	461.9	461.4	461.0	460.9	461.1	461.3	461.5	461.7	462.2
170°	465.2	464.8	464.3	463.9	463.4	463.3	463.4	463.6	463.7	463.9	464.4
172.5°	466.8	466.4	466.0	465.5	465.0	464.9	465.0	465.2	465.3	465.5	466.0
175°	469.0	468.4	467.9	467.4	466.8	466.7	466.8	467.0	467.1	467.2	467.8
177.5°	469.3	468.9	468.4	468.0	467.6	467.4	467.5	467.5	467.6	467.6	468.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	9.7	9.3	9.0	8.7	8.6	8.6	8.4	8.3
90°	7.5	7.9	8.2	8.6	8.7	8.9	9.0	9.1
92.5°	8.2	8.5	8.6	8.8	8.9	9.0	9.0	9.1
95°	13.9	14.3	14.7	14.9	14.8	14.7	14.7	14.6
97.5°	18.3	18.6	18.9	19.1	19.2	19.3	19.3	19.4
100°	20.5	21.1	21.7	22.1	22.3	22.4	22.5	22.7
102.5°	21.4	22.2	23.0	23.4	23.7	23.9	24.1	24.3
105°	22.3	23.1	24.0	24.6	24.8	25.1	25.4	25.7
107.5°	27.3	26.4	25.5	25.3	25.6	25.9	26.1	26.5
110°	44.2	36.7	29.2	25.5	25.8	26.1	26.5	26.8



TEST NUMBER: P331529-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	94.6	67.1	39.7	26.1	26.3	26.5	26.8	27.0
115°	139.3	104.4	69.6	49.4	44.0	38.6	33.2	27.7
117.5°	214.5	206.1	197.6	184.6	166.8	148.9	131.2	113.4
120°	250.0	250.9	251.8	247.2	237.0	226.9	216.7	206.5
122.5°	265.2	265.8	266.3	265.6	263.6	261.7	259.7	257.7
125°	287.2	287.7	288.2	288.6	288.8	289.1	289.3	289.5
127.5°	307.4	308.2	309.0	309.3	309.4	309.4	309.5	309.5
130°	320.3	321.1	321.9	322.3	322.3	322.2	322.1	322.0
132.5°	332.8	333.4	334.1	334.5	334.4	334.3	334.3	334.2
135°	350.6	351.3	352.1	352.4	352.3	352.1	352.0	351.8
137.5°	367.2	367.9	368.6	368.8	368.6	368.4	368.1	367.8
140°	377.9	378.6	379.2	379.4	379.0	378.6	378.3	377.9
142.5°	387.8	388.4	389.0	389.1	388.7	388.4	388.0	387.6
145°	401.6	402.1	402.7	402.7	402.3	402.0	401.6	401.2
147.5°	413.7	414.1	414.5	414.5	414.2	413.8	413.5	413.2
150°	421.1	421.5	422.0	422.1	421.7	421.3	420.9	420.6
152.5°	427.9	428.3	428.8	428.7	428.3	427.8	427.2	426.7
155°	437.0	437.4	437.9	437.8	437.2	436.7	436.0	435.5
157.5°	444.7	445.2	445.8	445.7	445.1	444.5	443.9	443.4
160°	449.2	449.6	450.1	450.0	449.6	449.0	448.5	448.0
162.5°	453.4	453.9	454.4	454.3	453.7	453.0	452.4	451.8
165°	458.5	459.0	459.5	459.5	459.0	458.5	458.0	457.4
167.5°	462.8	463.3	463.8	463.7	463.0	462.4	461.7	461.1
170°	464.9	465.5	466.0	465.9	465.2	464.5	463.9	463.2
172.5°	466.5	467.1	467.6	467.5	466.8	466.2	465.5	464.9
175°	468.3	468.8	469.4	469.3	468.5	467.8	467.0	466.3
177.5°	468.5	468.9	469.4	469.3	468.7	468.2	467.6	467.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9

(END OF REPORT)