

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331812-930

Luminaire Tested: **S122RDIW-S675D710U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331812-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D710U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3899.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49					49			
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	49	48	47	42					42			
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	40	36					36			
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	39	37	35	31					31			
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	31	27					27			
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24					24			
6	64	52	44	39	59	49	42	36	42	36	32	35	31	28	29	26	24	21					21			
7	59	47	39	34	54	44	37	32	38	32	29	32	28	25	27	24	21	19					19			
8	55	43	35	30	51	40	33	29	35	29	25	30	25	22	25	22	19	17					17			
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15					15			
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14					14			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	2.2
10°-20°	236.4	6.1
20°-30°	331.9	8.5
30°-40°	361.9	9.3
40°-50°	332.8	8.5
50°-60°	261.4	6.7
60°-70°	170.4	4.4
70°-80°	87.9	2.3
80°-90°	25.7	0.7
90°-100°	45.4	1.2
100°-110°	141.1	3.6
110°-120°	241.2	6.2
120°-130°	317.1	8.1
130°-140°	356.0	9.1
140°-150°	349.0	9.0
150°-160°	292.8	7.5
160°-170°	194.2	5.0
170°-180°	67.9	1.7
0°-30°	654.4	16.8
0°-40°	1016.3	26.1
0°-60°	1610.5	41.3
0°-90°	1894.4	48.6
90°-120°	427.7	11.0
90°-150°	1449.8	37.2
90°-180°	2005.0	51.4
0°-180°	3899.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	8	21	20	20	3
95°	32	37	39	39	38	36
105°	130	132	133	134	134	137
115°	242	245	244	244	242	239
125°	352	357	356	354	353	315
135°	456	462	463	463	461	352
145°	553	557	561	561	559	345
155°	632	634	636	639	637	291
165°	688	687	687	691	688	194
175°	716	714	713	716	713	68
180°	717	717	717	717	717	



TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.9	9.0	8.2	7.3	7.2	7.8	8.4	9.0	9.5	9.4
90°	0.6	2.2	3.8	5.5	7.1	9.4	12.3	15.2	18.2	21.2	20.9
92.5°	10.8	12.0	13.1	14.3	15.5	16.5	17.1	17.9	18.5	19.2	19.3
95°	31.5	32.8	34.2	35.5	36.9	37.7	37.9	38.2	38.5	38.7	38.7
97.5°	57.5	58.6	59.8	61.0	62.2	63.0	63.6	64.1	64.6	65.1	65.1
100°	76.8	77.9	79.0	80.1	81.1	81.9	82.3	82.7	83.1	83.5	83.5
102.5°	97.2	98.0	98.9	99.7	100.6	101.3	101.8	102.3	102.8	103.3	103.5
105°	130.0	130.4	130.9	131.3	131.7	132.0	132.3	132.6	132.8	133.1	133.4
107.5°	163.2	163.8	164.4	165.0	165.6	165.9	165.9	165.9	165.9	165.9	166.0
110°	184.5	185.3	186.1	186.9	187.8	188.2	188.2	188.2	188.2	188.2	188.2



TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	207.7	208.6	209.4	210.2	211.0	211.3	211.2	211.1	211.0	210.9	210.6
115°	242.0	242.8	243.6	244.4	245.2	245.5	245.2	244.9	244.7	244.4	244.3
117.5°	276.1	277.2	278.3	279.3	280.4	280.5	279.8	279.1	278.3	277.6	277.3
120°	298.9	299.9	301.0	302.1	303.1	303.1	302.1	301.0	299.9	298.9	298.9
122.5°	319.7	321.0	322.3	323.5	324.8	325.1	324.3	323.6	322.9	322.1	321.8
125°	352.1	353.4	354.5	355.7	356.9	357.3	356.9	356.5	356.1	355.7	355.3
127.5°	383.7	385.2	386.8	388.2	389.8	390.4	389.9	389.4	388.9	388.4	387.9
130°	403.5	405.3	407.0	408.8	410.5	411.2	411.0	410.7	410.4	410.2	409.9
132.5°	425.8	427.2	428.7	430.1	431.5	432.3	432.3	432.4	432.4	432.4	431.9
135°	455.6	457.1	458.5	460.0	461.5	462.4	462.6	462.9	463.2	463.4	463.3
137.5°	486.9	488.1	489.3	490.6	491.7	492.5	492.8	493.3	493.6	493.9	493.8
140°	505.8	507.0	508.2	509.4	510.6	511.5	512.3	512.9	513.6	514.2	514.2
142.5°	525.1	526.4	527.6	528.8	529.9	530.8	531.2	531.7	532.1	532.6	532.7
145°	552.9	553.9	554.8	555.8	556.8	557.6	558.4	559.2	560.0	560.8	560.9
147.5°	577.8	578.9	580.0	581.1	582.3	583.1	583.7	584.2	584.7	585.3	585.5
150°	594.7	595.5	596.3	597.1	597.9	598.6	599.2	599.7	600.2	600.8	601.2
152.5°	609.7	610.5	611.3	612.1	612.9	613.7	614.3	615.0	615.6	616.3	616.8
155°	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.4	635.9	636.5
157.5°	651.4	651.8	652.0	652.2	652.6	652.8	653.1	653.3	653.5	653.8	654.7
160°	663.1	663.3	663.6	663.9	664.1	664.4	664.5	664.6	664.7	664.9	665.7
162.5°	673.7	673.8	673.8	673.8	673.9	674.0	674.2	674.3	674.4	674.6	675.5
165°	687.9	687.7	687.6	687.5	687.4	687.3	687.3	687.3	687.3	687.3	688.2
167.5°	699.8	699.4	699.0	698.5	698.1	697.9	697.9	697.8	697.8	697.8	698.7
170°	706.0	705.6	705.2	704.8	704.4	704.2	704.0	703.8	703.8	703.6	704.6
172.5°	710.4	710.0	709.6	709.1	708.7	708.5	708.3	708.3	708.1	707.9	708.9
175°	715.7	715.3	714.9	714.5	714.1	713.8	713.5	713.2	713.0	712.7	713.6
177.5°	717.9	717.5	717.2	716.9	716.6	716.3	716.1	715.9	715.7	715.4	716.1
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9



TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	9.1	9.0	8.7	8.6	8.7	8.7	8.7	8.8
90°	20.6	20.4	20.1	20.1	20.1	20.3	20.5	20.5
92.5°	19.3	19.4	19.5	19.5	19.5	19.6	19.6	19.6
95°	38.7	38.7	38.7	38.6	38.3	38.1	37.7	37.5
97.5°	65.1	65.1	65.1	65.1	65.1	65.1	65.0	65.0
100°	83.5	83.5	83.5	83.4	83.3	83.2	83.0	82.9
102.5°	103.5	103.6	103.8	103.8	103.6	103.5	103.4	103.2
105°	133.6	133.9	134.2	134.3	134.3	134.3	134.3	134.3
107.5°	166.1	166.2	166.3	166.1	165.4	164.9	164.2	163.6
110°	188.2	188.2	188.2	187.9	187.5	187.1	186.7	186.4



TEST NUMBER: P331812-930

CATALOG NUMBER: S122RDIW-S675D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	209.9	209.6	209.3	209.0	208.7	208.4	208.1
115°	244.2	244.0	243.9	243.6	243.2	242.8	242.4	242.0
117.5°	277.0	276.6	276.3	275.9	275.5	275.1	274.7	274.3
120°	298.9	298.9	298.9	298.6	298.2	297.8	297.4	297.0
122.5°	321.5	321.1	320.8	320.5	320.2	319.9	319.6	319.4
125°	354.9	354.5	354.1	353.8	353.8	353.6	353.4	353.4
127.5°	387.4	386.9	386.5	386.0	385.6	385.1	384.7	384.3
130°	409.7	409.4	409.1	408.7	408.1	407.6	407.1	406.6
132.5°	431.3	430.6	430.1	429.6	429.2	428.7	428.3	427.9
135°	463.2	463.0	462.9	462.6	462.2	461.8	461.4	461.0
137.5°	493.7	493.6	493.5	493.2	492.6	492.1	491.5	491.0
140°	514.2	514.2	514.2	514.0	513.5	512.9	512.3	511.8
142.5°	532.9	533.0	533.0	532.9	532.3	531.7	531.2	530.7
145°	561.1	561.3	561.3	561.2	560.6	560.1	559.5	559.1
147.5°	585.9	586.1	586.4	586.4	585.9	585.3	584.8	584.3
150°	601.5	601.9	602.3	602.3	601.9	601.5	601.2	600.8
152.5°	617.3	617.8	618.3	618.3	617.8	617.3	616.8	616.3
155°	637.2	637.9	638.5	638.7	638.3	637.9	637.5	637.1
157.5°	655.6	656.5	657.4	657.5	656.9	656.2	655.6	654.9
160°	666.5	667.3	668.1	668.2	667.7	667.2	666.7	666.1
162.5°	676.4	677.4	678.2	678.3	677.7	677.1	676.5	675.8
165°	689.2	690.1	691.0	691.2	690.5	689.8	689.2	688.5
167.5°	699.7	700.6	701.6	701.6	701.0	700.3	699.6	698.9
170°	705.5	706.5	707.4	707.4	706.6	705.8	705.0	704.2
172.5°	709.9	710.8	711.8	711.8	711.0	710.2	709.4	708.6
175°	714.5	715.5	716.5	716.5	715.7	714.9	714.1	713.3
177.5°	716.7	717.4	718.0	718.0	717.4	716.7	716.1	715.4
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9

(END OF REPORT)