

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331530-927

Luminaire Tested: **S122DIW-S675D435U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331530-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3330.7 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75	70	68	67	61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	40	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.4
10°-20°	222.5	6.7
20°-30°	327.1	9.8
30°-40°	379.9	11.4
40°-50°	379.5	11.4
50°-60°	331.0	9.9
60°-70°	244.7	7.3
70°-80°	138.6	4.2
80°-90°	39.0	1.2
90°-100°	27.0	0.8
100°-110°	83.7	2.5
110°-120°	143.1	4.3
120°-130°	188.1	5.6
130°-140°	211.2	6.3
140°-150°	207.1	6.2
150°-160°	173.7	5.2
160°-170°	115.2	3.5
170°-180°	40.3	1.2
0°-30°	628.7	18.9
0°-40°	1008.6	30.3
0°-60°	1719.1	51.6
0°-90°	2141.5	64.3
90°-120°	253.7	7.6
90°-150°	860.1	25.8
90°-180°	1189.0	35.7
0°-180°	3330.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	0	5	13	12	12	3
95°	19	22	23	23	22	21
105°	77	78	79	80	80	82
115°	144	146	145	145	144	142
125°	209	212	211	210	210	187
135°	270	274	275	274	274	209
145°	328	331	333	333	332	205
155°	375	376	377	379	378	173
165°	408	408	408	410	408	115
175°	425	424	423	425	423	40
180°	425	425	425	425	425	



TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.7	11.6	11.5	11.4	11.3	11.3	11.4	11.4	11.5	11.6	11.1
90°	0.4	1.3	2.3	3.2	4.2	5.5	7.3	9.0	10.8	12.6	12.4
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.6	11.0	11.4	11.4
95°	18.7	19.5	20.3	21.1	21.9	22.3	22.5	22.7	22.8	23.0	23.0
97.5°	34.1	34.8	35.5	36.2	36.9	37.4	37.7	38.0	38.3	38.6	38.6
100°	45.6	46.2	46.8	47.5	48.2	48.6	48.8	49.0	49.3	49.5	49.5
102.5°	57.7	58.1	58.6	59.2	59.7	60.1	60.4	60.7	61.0	61.3	61.4
105°	77.2	77.4	77.6	77.9	78.1	78.3	78.5	78.7	78.8	79.0	79.1
107.5°	96.8	97.2	97.5	97.9	98.2	98.4	98.4	98.4	98.4	98.4	98.5
110°	109.5	110.0	110.4	110.9	111.4	111.6	111.6	111.6	111.6	111.6	111.6



TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.3	123.7	124.2	124.7	125.2	125.4	125.3	125.2	125.2	125.1	124.9
115°	143.5	144.0	144.5	145.0	145.4	145.6	145.4	145.3	145.1	145.0	144.9
117.5°	163.8	164.5	165.1	165.7	166.4	166.4	166.0	165.6	165.1	164.7	164.5
120°	177.3	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.3
122.5°	189.6	190.4	191.2	191.9	192.7	192.9	192.4	191.9	191.5	191.1	190.9
125°	208.9	209.6	210.3	211.0	211.8	212.0	211.8	211.5	211.3	211.0	210.8
127.5°	227.6	228.5	229.4	230.4	231.2	231.6	231.3	231.0	230.7	230.4	230.1
130°	239.4	240.4	241.5	242.5	243.5	244.0	243.8	243.7	243.5	243.4	243.2
132.5°	252.6	253.4	254.3	255.2	256.0	256.4	256.4	256.5	256.5	256.5	256.2
135°	270.3	271.2	272.0	272.9	273.8	274.3	274.4	274.6	274.7	274.9	274.8
137.5°	288.8	289.5	290.3	291.0	291.7	292.2	292.4	292.6	292.8	293.0	292.9
140°	300.1	300.8	301.5	302.2	302.9	303.5	303.9	304.3	304.7	305.1	305.1
142.5°	311.6	312.3	313.0	313.7	314.4	314.9	315.1	315.4	315.7	316.0	316.1
145°	328.0	328.6	329.2	329.7	330.3	330.8	331.3	331.8	332.2	332.7	332.8
147.5°	342.8	343.4	344.1	344.8	345.5	345.9	346.3	346.6	346.9	347.2	347.4
150°	352.8	353.3	353.8	354.3	354.7	355.1	355.5	355.8	356.1	356.4	356.6
152.5°	361.7	362.2	362.7	363.1	363.6	364.1	364.4	364.8	365.2	365.6	365.9
155°	375.0	375.3	375.5	375.8	376.0	376.3	376.5	376.8	377.0	377.2	377.6
157.5°	386.5	386.7	386.8	387.0	387.1	387.2	387.4	387.5	387.7	387.9	388.4
160°	393.4	393.6	393.7	393.9	394.0	394.1	394.2	394.3	394.3	394.4	394.9
162.5°	399.7	399.7	399.7	399.7	399.8	399.9	400.0	400.1	400.1	400.2	400.7
165°	408.1	408.0	407.9	407.8	407.7	407.7	407.7	407.7	407.7	407.7	408.3
167.5°	415.1	414.9	414.6	414.4	414.2	414.0	414.0	414.0	414.0	414.0	414.5
170°	418.8	418.6	418.4	418.1	417.9	417.7	417.6	417.6	417.5	417.4	418.0
172.5°	421.4	421.2	421.0	420.7	420.5	420.3	420.3	420.2	420.1	420.0	420.6
175°	424.6	424.4	424.1	423.9	423.7	423.4	423.3	423.1	422.9	422.8	423.3
177.5°	425.9	425.7	425.5	425.3	425.1	424.9	424.8	424.7	424.5	424.5	424.8
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	10.6	10.2	9.7	9.4	9.3	9.2	9.0	8.9
90°	12.3	12.1	12.0	11.9	12.0	12.0	12.1	12.2
92.5°	11.5	11.5	11.6	11.6	11.6	11.6	11.6	11.6
95°	23.0	23.0	23.0	22.9	22.7	22.6	22.4	22.3
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.5	49.5	49.5	49.5	49.4	49.4	49.3	49.2
102.5°	61.4	61.5	61.6	61.6	61.5	61.4	61.3	61.2
105°	79.3	79.5	79.6	79.7	79.7	79.7	79.7	79.7
107.5°	98.5	98.6	98.7	98.5	98.2	97.8	97.4	97.0
110°	111.6	111.6	111.6	111.5	111.2	111.0	110.7	110.5



TEST NUMBER: P331530-927

CATALOG NUMBER: S122DIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.8	124.5	124.4	124.1	124.0	123.8	123.7	123.5
115°	144.8	144.7	144.7	144.5	144.3	144.0	143.8	143.5
117.5°	164.3	164.1	163.9	163.7	163.4	163.2	163.0	162.7
120°	177.3	177.3	177.3	177.2	177.0	176.7	176.5	176.3
122.5°	190.7	190.5	190.3	190.1	190.0	189.8	189.6	189.4
125°	210.6	210.3	210.1	209.9	209.8	209.8	209.7	209.6
127.5°	229.8	229.6	229.3	229.0	228.7	228.5	228.2	228.0
130°	243.0	242.9	242.7	242.5	242.2	241.9	241.5	241.2
132.5°	255.9	255.5	255.2	254.8	254.6	254.3	254.1	253.8
135°	274.7	274.6	274.6	274.4	274.2	273.9	273.7	273.5
137.5°	292.9	292.8	292.8	292.6	292.2	291.9	291.6	291.3
140°	305.1	305.1	305.1	304.9	304.6	304.3	304.0	303.6
142.5°	316.1	316.2	316.2	316.1	315.8	315.4	315.1	314.8
145°	332.9	333.0	333.0	332.9	332.6	332.2	331.9	331.6
147.5°	347.5	347.8	347.9	347.8	347.5	347.2	346.9	346.7
150°	356.9	357.1	357.4	357.4	357.1	356.9	356.6	356.4
152.5°	366.1	366.5	366.8	366.8	366.5	366.1	365.9	365.6
155°	378.0	378.4	378.8	378.9	378.7	378.4	378.2	378.0
157.5°	388.9	389.4	390.0	390.1	389.7	389.3	389.0	388.6
160°	395.4	395.9	396.3	396.4	396.1	395.8	395.5	395.1
162.5°	401.2	401.8	402.3	402.4	402.0	401.6	401.2	400.9
165°	408.8	409.4	410.0	410.0	409.6	409.2	408.8	408.4
167.5°	415.1	415.7	416.2	416.3	415.8	415.4	415.0	414.6
170°	418.5	419.1	419.6	419.7	419.2	418.7	418.3	417.8
172.5°	421.1	421.7	422.2	422.2	421.8	421.3	420.8	420.3
175°	423.9	424.5	425.0	425.1	424.6	424.1	423.7	423.2
177.5°	425.2	425.6	426.0	426.0	425.6	425.2	424.8	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3

(END OF REPORT)