

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331813-930

Luminaire Tested: **S122RDIW-S675D970U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331813-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5227.7 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19339	19339	19339	19339
5°	21598	19460	17253	19460
10°	23963	19323	14955	19323
15°	25142	19041	11784	19041
20°	21795	18620	10198	18620
25°	14295	18045	9103	18045
30°	9622	17350	8240	17350
35°	7792	16472	7433	16472
40°	6930	15517	6877	15517
45°	6272	14397	6140	14397
50°	5707	13288	5687	13288
55°	5365	12056	5295	12056
60°	4489	10924	4434	10924
65°	3786	9922	4290	9922
70°	3498	8861	4050	8861
75°	3269	7711	3737	7711
80°	3013	6341	3329	6341
85°	2779	5020	2927	5020



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	2.2
10°-20°	316.4	6.1
20°-30°	407.7	7.8
30°-40°	387.4	7.4
40°-50°	331.9	6.3
50°-60°	252.7	4.8
60°-70°	159.8	3.1
70°-80°	79.8	1.5
80°-90°	23.4	0.4
90°-100°	35.9	0.7
100°-110°	131.7	2.5
110°-120°	352.0	6.7
120°-130°	581.1	11.1
130°-140°	618.0	11.8
140°-150°	574.4	11.0
150°-160°	461.8	8.8
160°-170°	297.6	5.7
170°-180°	102.4	2.0
0°-30°	837.6	16.0
0°-40°	1225.0	23.4
0°-60°	1809.6	34.6
0°-90°	2072.6	39.6
90°-120°	519.7	9.9
90°-150°	2293.2	43.9
90°-180°	3155.0	60.4
0°-180°	5227.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1198	1198	1198	1198	1198	
5°	1333	1201	1064	1201	1333	132
15°	1504	1139	705	1139	1504	406
25°	802	1013	511	1013	802	381
35°	395	836	377	836	395	253
45°	275	630	269	630	275	213
55°	191	428	188	428	191	167
65°	99	260	112	260	99	101
75°	52	124	60	124	52	56
85°	15	27	16	27	15	17
90°	21	1	21	1	21	10
95°	34	51	34	51	34	31
105°	59	237	59	237	59	62
115°	64	448	64	448	64	160
125°	666	633	666	633	666	576
135°	809	784	809	784	809	624
145°	923	909	923	909	923	577
155°	1002	1001	1002	1001	1002	462
165°	1052	1055	1052	1055	1052	297
175°	1073	1079	1073	1079	1073	102
180°	1077	1077	1077	1077	1077	



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1246.3	1247.3	1248.4	1246.0	1246.0	1244.0	1239.7	1236.4	1227.0	1225.7	1225.7
5°	1332.6	1331.7	1333.4	1328.0	1320.5	1318.8	1310.9	1300.6	1289.7	1277.7	1275.1
7.5°	1418.3	1417.1	1413.7	1412.8	1407.0	1394.5	1381.8	1368.2	1350.2	1332.7	1323.9
10°	1461.6	1475.4	1467.0	1452.5	1455.4	1435.8	1425.4	1407.5	1392.5	1366.3	1360.5
12.5°	1504.2	1509.6	1507.0	1498.7	1494.9	1481.4	1467.4	1451.8	1424.2	1400.6	1380.1
15°	1504.1	1512.0	1514.0	1511.6	1513.6	1512.8	1505.3	1492.4	1468.3	1442.4	1420.0
17.5°	1393.0	1398.5	1412.2	1421.4	1433.1	1457.7	1469.8	1474.6	1471.0	1456.3	1440.5
20°	1268.5	1259.3	1297.6	1317.2	1333.8	1375.4	1411.2	1425.0	1447.0	1446.6	1442.4
22.5°	1092.0	1094.2	1130.5	1153.7	1202.3	1243.9	1284.7	1336.4	1379.1	1407.3	1423.8
25°	802.4	818.2	854.4	886.1	940.1	1017.6	1087.9	1169.5	1246.4	1307.2	1365.1
27.5°	602.6	603.8	632.5	661.7	693.8	757.2	845.8	943.2	1053.0	1143.5	1247.7
30°	516.1	513.6	525.6	543.6	571.0	620.1	686.6	782.4	891.9	1028.3	1149.9
32.5°	454.8	454.9	464.1	477.3	500.1	533.2	578.8	656.6	760.0	894.2	1036.7
35°	395.3	394.9	401.6	411.2	420.8	442.0	473.2	514.0	585.1	710.4	856.1
37.5°	352.8	354.6	357.8	363.8	374.4	386.2	405.0	432.4	483.0	557.1	679.6
40°	328.8	329.6	334.2	339.2	345.4	354.6	370.0	392.0	429.1	488.2	577.6
42.5°	306.8	307.6	310.9	315.5	320.4	329.6	342.3	361.4	391.4	437.6	511.4
45°	274.7	274.7	277.6	279.6	285.1	293.4	303.8	319.6	340.5	374.5	423.6
47.5°	244.5	244.6	246.5	250.1	253.6	260.0	270.3	283.2	298.3	324.7	366.6
50°	227.2	227.6	228.9	231.8	233.9	239.7	247.6	258.9	274.7	295.1	330.0
52.5°	213.3	213.0	214.6	215.8	217.3	221.4	227.3	237.3	251.4	269.1	298.1
55°	190.6	188.9	191.4	193.6	194.8	196.4	199.7	206.0	218.1	233.1	254.7
57.5°	162.3	161.7	163.4	165.3	169.3	173.7	176.5	180.5	186.8	197.5	219.0
60°	139.0	139.0	142.8	144.0	148.5	154.4	160.2	163.5	169.8	176.8	192.7
62.5°	118.4	118.7	120.4	121.7	124.3	131.4	139.6	146.9	152.8	159.6	170.1
65°	99.1	99.9	99.9	100.7	102.4	104.0	107.4	113.2	123.6	133.1	141.0
67.5°	84.1	84.3	84.5	85.4	85.9	87.6	88.9	91.6	94.0	103.1	112.8
70°	74.1	75.3	74.9	75.7	76.1	77.0	78.7	79.9	83.6	85.8	91.6
72.5°	64.7	65.6	65.6	66.1	67.2	67.3	68.6	70.0	72.3	74.1	77.2
75°	52.4	52.0	52.4	53.2	53.6	54.1	54.1	55.8	57.0	58.7	60.7
77.5°	40.4	40.8	40.8	40.8	40.9	41.7	41.6	42.4	43.6	44.4	45.4
80°	32.4	32.9	32.4	32.9	33.3	33.7	33.3	33.7	35.0	35.8	35.8
82.5°	25.1	25.2	25.4	25.5	25.6	25.7	26.3	26.4	27.3	27.1	27.5
85°	15.0	14.6	14.6	14.6	15.0	15.4	15.0	15.0	15.4	15.4	15.4
87.5°	9.5	9.8	9.7	9.6	9.6	9.5	9.3	9.5	9.0	9.1	8.5
90°	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3	16.5	15.6	14.2
92.5°	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0	18.5	18.1	17.4
95°	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1	31.2	30.4	29.2
97.5°	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1	41.3	40.7	37.8
100°	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2	45.8	44.4	41.5
102.5°	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2	47.5	45.7	40.3
105°	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4	49.4	47.5	44.8
107.5°	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6	64.6	66.5	123.2
110°	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7	119.0	136.3	186.4



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5	280.7	343.9	356.2
115°	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3	400.5	480.7	476.4
117.5°	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6	513.0	532.4	529.5
120°	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2	573.2	571.0	567.9
122.5°	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3	609.0	607.8	604.4
125°	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7	659.5	658.3	655.0
127.5°	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4	705.6	703.8	701.3
130°	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9	735.0	733.1	731.2
132.5°	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6	764.0	762.4	760.4
135°	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7	804.9	803.2	801.6
137.5°	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7	843.1	841.4	839.6
140°	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4	867.9	866.3	864.4
142.5°	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2	890.8	889.3	887.2
145°	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1	922.8	921.6	918.7
147.5°	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8	950.9	950.0	947.1
150°	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9	967.8	966.8	964.0
152.5°	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5	983.4	982.4	979.7
155°	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5	1004.4	1003.4	1001.4
157.5°	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2	1022.1	1020.8	1019.4
160°	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6	1032.5	1031.4	1030.5
162.5°	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2	1042.0	1040.8	1039.9
165°	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5	1052.0
167.5°	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7	1063.5	1062.3	1061.8
170°	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8	1068.5	1067.3	1067.0
172.5°	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4	1072.3	1071.1	1070.7
175°	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5	1076.3	1075.1	1074.7
177.5°	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0	1077.0	1076.0	1075.9
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1226.4	1223.7	1221.4	1215.4	1212.4	1205.7	1204.8	1204.4	1195.7	1187.4	1185.1
5°	1268.5	1261.8	1251.8	1240.2	1228.1	1215.6	1207.3	1200.7	1184.0	1168.2	1159.0
7.5°	1310.9	1296.7	1279.4	1257.4	1238.9	1218.3	1203.0	1189.3	1165.6	1143.0	1127.7
10°	1342.6	1319.2	1296.4	1266.0	1242.3	1219.0	1197.3	1178.6	1151.9	1122.0	1100.7
12.5°	1362.2	1336.6	1305.0	1275.3	1244.6	1215.0	1186.0	1162.0	1130.7	1099.7	1074.5
15°	1388.8	1361.3	1323.0	1280.6	1241.0	1202.3	1169.1	1139.1	1098.3	1061.3	1030.5
17.5°	1410.5	1372.7	1331.5	1282.5	1236.7	1187.5	1144.6	1106.4	1060.9	1016.3	980.0
20°	1417.5	1380.1	1332.6	1283.4	1229.4	1171.5	1125.4	1083.7	1035.0	986.3	944.7
22.5°	1413.2	1384.1	1331.2	1272.5	1217.1	1156.5	1104.3	1056.1	1002.1	952.4	904.1
25°	1383.8	1373.8	1323.9	1259.7	1196.5	1126.2	1065.8	1012.9	951.4	898.1	845.6
27.5°	1315.2	1336.8	1305.9	1237.6	1167.3	1091.8	1024.0	963.8	899.9	840.0	787.7
30°	1249.4	1298.9	1285.6	1222.3	1143.6	1069.6	993.4	930.6	862.3	800.7	749.1
32.5°	1159.1	1241.0	1253.9	1201.0	1119.7	1038.3	958.5	895.9	824.7	759.8	709.5
35°	1015.5	1137.8	1194.0	1160.3	1078.7	990.9	908.5	835.7	764.1	700.0	650.0
37.5°	844.1	1010.7	1104.3	1106.8	1031.8	940.5	850.8	778.5	705.2	642.3	588.3
40°	732.9	913.5	1035.4	1062.5	999.2	900.6	809.8	736.2	664.6	603.0	541.0
42.5°	633.0	812.9	962.9	1009.9	959.6	861.6	770.6	693.6	624.0	565.7	502.4
45°	511.9	669.2	834.5	918.5	890.6	799.9	703.8	630.5	565.2	514.8	454.0
47.5°	431.8	542.7	702.5	816.3	815.8	733.0	638.4	568.3	507.7	460.5	411.2
50°	386.2	482.7	618.0	747.1	757.8	688.4	598.4	529.0	472.4	422.8	383.3
52.5°	345.3	424.9	546.4	670.1	700.9	640.7	553.5	489.3	434.4	388.9	355.0
55°	291.7	353.4	445.7	561.4	608.1	565.6	488.2	428.3	383.7	345.4	316.3
57.5°	246.8	293.0	367.1	460.3	514.5	487.9	424.0	375.3	337.2	302.6	279.6
60°	218.5	256.3	319.2	397.1	457.0	438.2	383.7	338.3	305.9	275.9	254.3
62.5°	191.8	224.4	278.3	341.4	396.4	388.7	344.1	306.1	277.6	250.3	232.0
65°	154.4	178.1	220.1	269.7	313.8	317.6	285.5	259.7	234.3	212.6	196.4
67.5°	122.9	138.4	168.0	209.8	242.8	254.6	235.1	215.3	195.2	178.5	164.4
70°	103.6	116.1	137.8	171.5	201.9	214.3	203.1	187.7	170.2	156.5	144.4
72.5°	84.0	96.1	112.1	136.8	162.9	176.3	172.4	161.4	147.2	135.8	124.4
75°	63.3	67.0	77.9	94.5	114.9	126.5	129.5	123.6	112.3	103.6	96.9
77.5°	46.8	49.0	54.2	62.9	76.2	86.7	90.9	90.3	82.5	77.4	71.2
80°	37.4	38.7	41.2	44.9	55.0	65.3	68.2	68.2	62.9	60.7	54.5
82.5°	28.5	29.4	30.9	32.9	37.6	46.7	50.0	50.6	47.2	44.4	39.5
85°	16.2	15.8	16.6	17.9	18.8	21.2	26.3	27.1	26.3	22.9	21.6
87.5°	8.2	8.3	8.0	7.3	7.3	7.3	8.6	9.8	8.9	8.2	8.0
90°	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7	15.6	15.4	15.2
95°	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6	44.9	39.2	33.5
97.5°	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5	84.4	68.3	52.2
100°	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9	114.1	90.4	66.8
102.5°	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0	174.0	169.0	164.0
105°	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8	242.1	247.2	252.4
107.5°	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7	307.0	311.1	315.3
110°	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1	348.8	352.4	356.0



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0	388.2	391.4	394.7
115°	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9	450.9	453.9	456.8
117.5°	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2	507.5	510.8	514.0
120°	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4	548.0	550.5	553.1
122.5°	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2	582.9	585.7	588.4
125°	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3	635.6	637.9	640.1
127.5°	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5	684.0	686.5	689.0
130°	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1	714.9	717.6	720.3
132.5°	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2	745.6	748.0	750.2
135°	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7	786.5	789.3	792.1
137.5°	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7	826.6	828.6	830.5
140°	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5	852.9	854.3	855.7
142.5°	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9	875.1	876.4	877.7
145°	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1	909.0	908.8	908.7
147.5°	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9	939.1	938.5	937.8
150°	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8	958.5	957.3	956.2
152.5°	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6	975.3	973.9	972.6
155°	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1	999.5	997.9	996.4
157.5°	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3	1019.0	1017.6	1016.3
160°	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1030.5	1029.4	1028.3
162.5°	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5	1040.4	1039.3	1038.3
165°	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8	1053.8	1052.7	1051.7
167.5°	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8	1063.7	1062.7	1061.7
170°	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4	1069.3	1068.4	1067.3
172.5°	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2	1073.1	1072.0	1071.1
175°	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0	1077.7	1076.5	1075.4
177.5°	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8	1078.8	1077.8	1076.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1180.8	1178.4	1174.1	1167.4	1163.4	1156.4	1151.8	1154.5	1155.1	1154.5	1153.8
5°	1149.1	1140.3	1128.2	1116.6	1105.8	1094.1	1087.4	1084.5	1078.7	1075.4	1073.7
7.5°	1110.7	1095.6	1078.6	1058.3	1041.0	1023.0	1013.7	1009.1	997.2	990.8	985.0
10°	1082.1	1058.3	1041.3	1014.6	998.4	974.7	958.5	958.9	942.6	933.4	926.8
12.5°	1050.4	1024.3	996.0	972.0	949.4	930.4	910.9	902.9	885.7	876.9	858.9
15°	998.0	967.6	937.7	905.1	882.3	852.7	824.4	789.9	762.0	737.8	731.2
17.5°	940.7	903.1	873.0	834.9	795.7	746.0	713.2	693.2	676.4	663.7	654.1
20°	901.4	863.2	831.1	773.6	720.8	687.1	663.0	647.6	630.1	616.4	608.9
22.5°	860.1	820.2	776.5	712.4	671.2	644.2	622.6	605.0	593.1	582.4	575.6
25°	801.5	757.8	685.8	641.7	608.5	580.2	565.2	554.3	541.8	527.3	520.7
27.5°	739.6	670.1	618.4	585.6	553.8	535.4	522.0	505.8	494.6	488.1	481.2
30°	693.3	623.9	583.5	547.7	525.2	504.8	489.0	479.9	469.0	457.8	453.2
32.5°	641.7	586.2	547.6	517.7	494.9	477.5	465.0	450.2	442.4	435.5	425.9
35°	577.6	535.7	500.3	476.1	454.4	440.3	425.7	417.0	402.8	397.1	393.3
37.5°	523.3	486.9	460.6	435.0	417.9	402.3	393.4	379.4	373.3	365.3	357.3
40°	492.8	457.0	431.5	410.7	391.6	379.9	368.8	357.5	348.3	344.6	335.0
42.5°	461.5	432.4	406.9	384.1	371.3	359.0	344.8	336.6	327.0	321.0	315.0
45°	418.2	392.5	370.8	352.0	337.9	325.1	315.8	302.1	296.8	284.6	279.6
47.5°	380.3	356.3	335.7	317.9	304.0	295.6	282.3	271.5	262.9	255.4	249.1
50°	353.4	333.4	313.4	297.6	285.1	273.0	259.3	253.9	240.5	236.8	233.1
52.5°	328.7	309.7	291.4	275.9	263.4	251.7	239.6	232.5	223.6	219.8	217.1
55°	294.2	275.9	258.4	244.7	232.2	220.1	212.6	203.9	199.7	196.8	193.6
57.5°	259.6	243.1	229.8	215.8	203.3	193.7	185.0	179.8	175.5	171.6	167.6
60°	237.7	221.8	209.8	196.8	183.9	176.0	169.4	163.1	158.2	152.3	150.7
62.5°	214.3	200.5	189.5	176.8	165.7	158.4	152.1	146.2	140.1	131.7	129.3
65°	182.3	171.5	159.8	149.4	139.4	132.3	123.2	116.5	114.1	113.2	112.8
67.5°	153.4	143.1	133.1	122.5	113.3	106.8	102.2	101.1	99.4	98.9	97.8
70°	134.0	124.4	114.5	104.4	95.7	94.5	92.8	91.2	89.0	88.2	87.4
72.5°	116.7	106.8	96.8	88.8	85.0	83.5	81.9	80.1	78.8	77.9	77.4
75°	89.4	80.3	73.7	70.8	68.6	67.4	64.9	63.7	62.9	61.6	61.1
77.5°	64.4	59.3	56.2	54.4	52.2	50.9	49.4	48.2	47.3	47.0	46.4
80°	49.1	46.6	44.5	42.1	41.2	39.5	39.1	37.9	38.3	37.0	37.0
82.5°	38.2	35.0	33.2	32.0	31.2	29.9	29.4	28.9	28.9	28.0	28.0
85°	19.6	18.8	17.9	17.0	17.0	15.8	16.2	15.8	15.8	15.0	14.6
87.5°	8.0	8.0	7.6	7.9	8.2	8.1	8.3	8.2	8.3	8.5	8.2
90°	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3	18.2	19.1	19.6
92.5°	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0	19.4	19.9	20.2
95°	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1	33.0	33.8	34.2
97.5°	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1	42.7	43.5	43.9
100°	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2	48.6	50.0	50.8
102.5°	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2	51.0	52.8	54.0
105°	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4	53.2	55.1	56.4
107.5°	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6	60.7	58.8	58.1
110°	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7	84.4	67.1	58.8



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5	154.4	91.2	59.9
115°	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3	240.2	160.0	113.7
117.5°	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6	474.3	454.9	424.7
120°	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2	577.2	579.4	568.7
122.5°	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3	611.6	612.8	611.1
125°	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7	661.9	663.2	664.0
127.5°	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4	709.1	710.9	711.8
130°	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9	738.8	740.7	741.6
132.5°	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6	767.3	768.9	769.6
135°	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7	808.4	810.1	810.8
137.5°	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7	846.4	848.2	848.7
140°	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4	871.0	872.5	872.9
142.5°	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2	893.6	895.0	895.3
145°	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1	925.3	926.4	926.7
147.5°	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8	952.7	953.6	953.7
150°	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9	969.9	970.9	971.0
152.5°	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5	985.5	986.5	986.5
155°	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5	1006.5	1007.5	1007.4
157.5°	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2	1024.4	1025.6	1025.5
160°	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6	1034.5	1035.6	1035.5
162.5°	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2	1044.3	1045.5	1045.4
165°	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4
167.5°	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7	1065.9	1067.1	1067.0
170°	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8	1070.9	1072.1	1072.0
172.5°	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4	1074.6	1075.9	1075.7
175°	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5	1078.7	1079.9	1079.7
177.5°	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0	1078.9	1079.9	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1150.1	1150.8	1149.8	1150.5	1149.8	1150.8	1150.1	1153.8	1154.5	1155.1	1154.5
5°	1071.6	1066.7	1065.8	1064.5	1065.8	1066.7	1071.6	1073.7	1075.4	1078.7	1084.5
7.5°	978.0	977.1	975.1	972.2	975.1	977.1	978.0	985.0	990.8	997.2	1009.1
10°	917.6	915.6	915.2	912.2	915.2	915.6	917.6	926.8	933.4	942.6	958.9
12.5°	847.1	833.6	832.3	825.0	832.3	833.6	847.1	858.9	876.9	885.7	902.9
15°	721.2	718.8	710.4	705.0	710.4	718.8	721.2	731.2	737.8	762.0	789.9
17.5°	649.3	641.2	638.5	637.4	638.5	641.2	649.3	654.1	663.7	676.4	693.2
20°	603.0	595.6	594.3	593.5	594.3	595.6	603.0	608.9	616.4	630.1	647.6
22.5°	571.0	563.2	560.0	557.5	560.0	563.2	571.0	575.6	582.4	593.1	605.0
25°	516.5	513.6	511.9	511.0	511.9	513.6	516.5	520.7	527.3	541.8	554.3
27.5°	473.8	467.3	466.1	464.0	466.1	467.3	473.8	481.2	488.1	494.6	505.8
30°	449.5	447.4	444.5	442.0	444.5	447.4	449.5	453.2	457.8	469.0	479.9
32.5°	420.9	419.1	416.5	415.3	416.5	419.1	420.9	425.9	435.5	442.4	450.2
35°	389.1	383.3	380.8	377.1	380.8	383.3	389.1	393.3	397.1	402.8	417.0
37.5°	355.6	352.5	349.0	350.3	349.0	352.5	355.6	357.3	365.3	373.3	379.4
40°	329.6	327.5	326.7	326.3	326.7	327.5	329.6	335.0	344.6	348.3	357.5
42.5°	309.0	303.2	301.1	301.0	301.1	303.2	309.0	315.0	321.0	327.0	336.6
45°	277.6	272.1	268.4	268.9	268.4	272.1	277.6	279.6	284.6	296.8	302.1
47.5°	245.5	245.3	243.0	243.7	243.0	245.3	245.5	249.1	255.4	262.9	271.5
50°	230.2	227.6	226.0	226.4	226.0	227.6	230.2	233.1	236.8	240.5	253.9
52.5°	215.5	213.4	212.0	213.8	212.0	213.4	215.5	217.1	219.8	223.6	232.5
55°	191.4	188.9	188.5	188.1	188.5	188.9	191.4	193.6	196.8	199.7	203.9
57.5°	164.5	162.9	160.4	159.3	160.4	162.9	164.5	167.6	171.6	175.5	179.8
60°	145.2	141.9	137.8	137.3	137.8	141.9	145.2	150.7	152.3	158.2	163.1
62.5°	127.6	126.9	126.1	126.0	126.1	126.9	127.6	129.3	131.7	140.1	146.2
65°	111.9	111.5	111.9	112.3	111.9	111.5	111.9	112.8	113.2	114.1	116.5
67.5°	97.6	96.8	96.0	96.4	96.0	96.8	97.6	97.8	98.9	99.4	101.1
70°	86.6	86.2	85.8	85.8	85.8	86.2	86.6	87.4	88.2	89.0	91.2
72.5°	75.9	75.8	75.4	75.1	75.4	75.8	75.9	77.4	77.9	78.8	80.1
75°	60.7	59.9	59.9	59.9	59.9	59.9	60.7	61.1	61.6	62.9	63.7
77.5°	46.3	45.9	45.4	45.1	45.4	45.9	46.3	46.4	47.0	47.3	48.2
80°	36.6	36.2	35.8	35.8	35.8	36.2	36.6	37.0	37.0	38.3	37.9
82.5°	28.0	27.6	27.5	27.1	27.5	27.6	28.0	28.0	28.0	28.9	28.9
85°	15.0	15.4	15.0	15.8	15.0	15.4	15.0	14.6	15.0	15.8	15.8
87.5°	8.3	8.1	8.5	8.2	8.5	8.1	8.3	8.2	8.5	8.3	8.2
90°	20.0	20.3	20.7	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3
92.5°	20.4	20.6	20.8	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0
95°	34.0	33.8	33.7	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1
97.5°	44.1	44.3	44.5	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1
100°	51.1	51.5	51.9	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2
102.5°	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2
105°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4
107.5°	58.9	59.5	60.3	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6
110°	59.4	60.2	60.8	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	60.5	61.1	61.6	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5
115°	101.3	88.8	76.3	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3
117.5°	383.7	342.8	301.8	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6
120°	545.4	522.0	498.6	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2
122.5°	606.6	602.1	597.5	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3
125°	664.6	665.0	665.5	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7
127.5°	711.9	712.0	712.1	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4
130°	741.4	741.2	741.0	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9
132.5°	769.4	769.2	769.1	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6
135°	810.5	810.1	809.8	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7
137.5°	848.2	847.5	846.9	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7
140°	872.0	871.1	870.3	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4
142.5°	894.5	893.6	892.8	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2
145°	925.8	924.9	924.1	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1
147.5°	952.9	952.2	951.5	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8
150°	970.2	969.3	968.4	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9
152.5°	985.4	984.2	983.1	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5
155°	1006.0	1004.6	1003.2	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5
157.5°	1024.1	1022.8	1021.4	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2
160°	1034.3	1033.1	1031.9	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6
162.5°	1043.8	1042.4	1040.9	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2
165°	1056.1	1054.9	1053.7	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9
167.5°	1065.4	1063.9	1062.3	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7
170°	1070.4	1068.9	1067.3	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8
172.5°	1074.2	1072.6	1071.1	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4
175°	1077.9	1076.2	1074.5	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5
177.5°	1078.5	1077.3	1076.0	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1151.8	1156.4	1163.4	1167.4	1174.1	1178.4	1180.8	1185.1	1187.4	1195.7	1204.4
5°	1087.4	1094.1	1105.8	1116.6	1128.2	1140.3	1149.1	1159.0	1168.2	1184.0	1200.7
7.5°	1013.7	1023.0	1041.0	1058.3	1078.6	1095.6	1110.7	1127.7	1143.0	1165.6	1189.3
10°	958.5	974.7	998.4	1014.6	1041.3	1058.3	1082.1	1100.7	1122.0	1151.9	1178.6
12.5°	910.9	930.4	949.4	972.0	996.0	1024.3	1050.4	1074.5	1099.7	1130.7	1162.0
15°	824.4	852.7	882.3	905.1	937.7	967.6	998.0	1030.5	1061.3	1098.3	1139.1
17.5°	713.2	746.0	795.7	834.9	873.0	903.1	940.7	980.0	1016.3	1060.9	1106.4
20°	663.0	687.1	720.8	773.6	831.1	863.2	901.4	944.7	986.3	1035.0	1083.7
22.5°	622.6	644.2	671.2	712.4	776.5	820.2	860.1	904.1	952.4	1002.1	1056.1
25°	565.2	580.2	608.5	641.7	685.8	757.8	801.5	845.6	898.1	951.4	1012.9
27.5°	522.0	535.4	553.8	585.6	618.4	670.1	739.6	787.7	840.0	899.9	963.8
30°	489.0	504.8	525.2	547.7	583.5	623.9	693.3	749.1	800.7	862.3	930.6
32.5°	465.0	477.5	494.9	517.7	547.6	586.2	641.7	709.5	759.8	824.7	895.9
35°	425.7	440.3	454.4	476.1	500.3	535.7	577.6	650.0	700.0	764.1	835.7
37.5°	393.4	402.3	417.9	435.0	460.6	486.9	523.3	588.3	642.3	705.2	778.5
40°	368.8	379.9	391.6	410.7	431.5	457.0	492.8	541.0	603.0	664.6	736.2
42.5°	344.8	359.0	371.3	384.1	406.9	432.4	461.5	502.4	565.7	624.0	693.6
45°	315.8	325.1	337.9	352.0	370.8	392.5	418.2	454.0	514.8	565.2	630.5
47.5°	282.3	295.6	304.0	317.9	335.7	356.3	380.3	411.2	460.5	507.7	568.3
50°	259.3	273.0	285.1	297.6	313.4	333.4	353.4	383.3	422.8	472.4	529.0
52.5°	239.6	251.7	263.4	275.9	291.4	309.7	328.7	355.0	388.9	434.4	489.3
55°	212.6	220.1	232.2	244.7	258.4	275.9	294.2	316.3	345.4	383.7	428.3
57.5°	185.0	193.7	203.3	215.8	229.8	243.1	259.6	279.6	302.6	337.2	375.3
60°	169.4	176.0	183.9	196.8	209.8	221.8	237.7	254.3	275.9	305.9	338.3
62.5°	152.1	158.4	165.7	176.8	189.5	200.5	214.3	232.0	250.3	277.6	306.1
65°	123.2	132.3	139.4	149.4	159.8	171.5	182.3	196.4	212.6	234.3	259.7
67.5°	102.2	106.8	113.3	122.5	133.1	143.1	153.4	164.4	178.5	195.2	215.3
70°	92.8	94.5	95.7	104.4	114.5	124.4	134.0	144.4	156.5	170.2	187.7
72.5°	81.9	83.5	85.0	88.8	96.8	106.8	116.7	124.4	135.8	147.2	161.4
75°	64.9	67.4	68.6	70.8	73.7	80.3	89.4	96.9	103.6	112.3	123.6
77.5°	49.4	50.9	52.2	54.4	56.2	59.3	64.4	71.2	77.4	82.5	90.3
80°	39.1	39.5	41.2	42.1	44.5	46.6	49.1	54.5	60.7	62.9	68.2
82.5°	29.4	29.9	31.2	32.0	33.2	35.0	38.2	39.5	44.4	47.2	50.6
85°	16.2	15.8	17.0	17.0	17.9	18.8	19.6	21.6	22.9	26.3	27.1
87.5°	8.3	8.1	8.2	7.9	7.6	8.0	8.0	8.0	8.2	8.9	9.8
90°	16.5	15.6	14.2	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8
92.5°	18.5	18.1	17.4	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7
95°	31.2	30.4	29.2	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6
97.5°	41.3	40.7	37.8	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5
100°	45.8	44.4	41.5	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9
102.5°	47.5	45.7	70.3	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0
105°	49.4	47.5	94.8	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8
107.5°	64.6	66.5	123.2	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7
110°	119.0	136.3	186.4	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.7	343.9	356.2	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0
115°	400.5	480.7	476.4	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9
117.5°	513.0	532.4	529.5	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2
120°	573.2	571.0	567.9	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4
122.5°	609.0	607.8	604.4	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2
125°	659.5	658.3	655.0	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3
127.5°	705.6	703.8	701.3	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5
130°	735.0	733.1	731.2	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1
132.5°	764.0	762.4	760.4	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2
135°	804.9	803.2	801.6	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7
137.5°	843.1	841.4	839.6	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7
140°	867.9	866.3	864.4	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5
142.5°	890.8	889.3	887.2	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9
145°	922.8	921.6	918.7	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1
147.5°	950.9	950.0	947.1	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9
150°	967.8	966.8	964.0	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8
152.5°	983.4	982.4	979.7	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6
155°	1004.4	1003.4	1001.4	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1
157.5°	1022.1	1020.8	1019.4	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3
160°	1032.5	1031.4	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4
162.5°	1042.0	1040.8	1039.9	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5
165°	1053.7	1052.5	1052.0	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8
167.5°	1063.5	1062.3	1061.8	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8
170°	1068.5	1067.3	1067.0	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4
172.5°	1072.3	1071.1	1070.7	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2
175°	1076.3	1075.1	1074.7	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0
177.5°	1077.0	1076.0	1075.9	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1204.8	1205.7	1212.4	1215.4	1221.4	1223.7	1226.4	1225.7	1225.7	1227.0	1236.4
5°	1207.3	1215.6	1228.1	1240.2	1251.8	1261.8	1268.5	1275.1	1277.7	1289.7	1300.6
7.5°	1203.0	1218.3	1238.9	1257.4	1279.4	1296.7	1310.9	1323.9	1332.7	1350.2	1368.2
10°	1197.3	1219.0	1242.3	1266.0	1296.4	1319.2	1342.6	1360.5	1366.3	1392.5	1407.5
12.5°	1186.0	1215.0	1244.6	1275.3	1305.0	1336.6	1362.2	1380.1	1400.6	1424.2	1451.8
15°	1169.1	1202.3	1241.0	1280.6	1323.0	1361.3	1388.8	1420.0	1442.4	1468.3	1492.4
17.5°	1144.6	1187.5	1236.7	1282.5	1331.5	1372.7	1410.5	1440.5	1456.3	1471.0	1474.6
20°	1125.4	1171.5	1229.4	1283.4	1332.6	1380.1	1417.5	1442.4	1446.6	1447.0	1425.0
22.5°	1104.3	1156.5	1217.1	1272.5	1331.2	1384.1	1413.2	1423.8	1407.3	1379.1	1336.4
25°	1065.8	1126.2	1196.5	1259.7	1323.9	1373.8	1383.8	1365.1	1307.2	1246.4	1169.5
27.5°	1024.0	1091.8	1167.3	1237.6	1305.9	1336.8	1315.2	1247.7	1143.5	1053.0	943.2
30°	993.4	1069.6	1143.6	1222.3	1285.6	1298.9	1249.4	1149.9	1028.3	891.9	782.4
32.5°	958.5	1038.3	1119.7	1201.0	1253.9	1241.0	1159.1	1036.7	894.2	760.0	656.6
35°	908.5	990.9	1078.7	1160.3	1194.0	1137.8	1015.5	856.1	710.4	585.1	514.0
37.5°	850.8	940.5	1031.8	1106.8	1104.3	1010.7	844.1	679.6	557.1	483.0	432.4
40°	809.8	900.6	999.2	1062.5	1035.4	913.5	732.9	577.6	488.2	429.1	392.0
42.5°	770.6	861.6	959.6	1009.9	962.9	812.9	633.0	511.4	437.6	391.4	361.4
45°	703.8	799.9	890.6	918.5	834.5	669.2	511.9	423.6	374.5	340.5	319.6
47.5°	638.4	733.0	815.8	816.3	702.5	542.7	431.8	366.6	324.7	298.3	283.2
50°	598.4	688.4	757.8	747.1	618.0	482.7	386.2	330.0	295.1	274.7	258.9
52.5°	553.5	640.7	700.9	670.1	546.4	424.9	345.3	298.1	269.1	251.4	237.3
55°	488.2	565.6	608.1	561.4	445.7	353.4	291.7	254.7	233.1	218.1	206.0
57.5°	424.0	487.9	514.5	460.3	367.1	293.0	246.8	219.0	197.5	186.8	180.5
60°	383.7	438.2	457.0	397.1	319.2	256.3	218.5	192.7	176.8	169.8	163.5
62.5°	344.1	388.7	396.4	341.4	278.3	224.4	191.8	170.1	159.6	152.8	146.9
65°	285.5	317.6	313.8	269.7	220.1	178.1	154.4	141.0	133.1	123.6	113.2
67.5°	235.1	254.6	242.8	209.8	168.0	138.4	122.9	112.8	103.1	94.0	91.6
70°	203.1	214.3	201.9	171.5	137.8	116.1	103.6	91.6	85.8	83.6	79.9
72.5°	172.4	176.3	162.9	136.8	112.1	96.1	84.0	77.2	74.1	72.3	70.0
75°	129.5	126.5	114.9	94.5	77.9	67.0	63.3	60.7	58.7	57.0	55.8
77.5°	90.9	86.7	76.2	62.9	54.2	49.0	46.8	45.4	44.4	43.6	42.4
80°	68.2	65.3	55.0	44.9	41.2	38.7	37.4	35.8	35.8	35.0	33.7
82.5°	50.0	46.7	37.6	32.9	30.9	29.4	28.5	27.5	27.1	27.3	26.4
85°	26.3	21.2	18.8	17.9	16.6	15.8	16.2	15.4	15.4	15.4	15.0
87.5°	8.6	7.3	7.3	7.3	8.0	8.3	8.2	8.5	9.1	9.0	9.5
90°	2.7	4.6	6.5	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3
92.5°	15.6	15.4	15.2	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0
95°	44.9	39.2	33.5	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1
97.5°	84.4	68.3	52.2	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1
100°	114.1	90.4	66.8	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2
102.5°	174.0	169.0	164.0	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2
105°	242.1	247.2	252.4	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4
107.5°	307.0	311.1	315.3	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6
110°	348.8	352.4	356.0	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	388.2	391.4	394.7	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5
115°	450.9	453.9	456.8	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3
117.5°	507.5	510.8	514.0	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6
120°	548.0	550.5	553.1	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2
122.5°	582.9	585.7	588.4	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3
125°	635.6	637.9	640.1	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7
127.5°	684.0	686.5	689.0	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4
130°	714.9	717.6	720.3	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9
132.5°	745.6	748.0	750.2	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6
135°	786.5	789.3	792.1	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7
137.5°	826.6	828.6	830.5	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7
140°	852.9	854.3	855.7	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4
142.5°	875.1	876.4	877.7	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2
145°	909.0	908.8	908.7	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1
147.5°	939.1	938.5	937.8	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8
150°	958.5	957.3	956.2	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9
152.5°	975.3	973.9	972.6	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5
155°	999.5	997.9	996.4	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5
157.5°	1019.0	1017.6	1016.3	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2
160°	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6
162.5°	1040.4	1039.3	1038.3	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2
165°	1053.8	1052.7	1051.7	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9
167.5°	1063.7	1062.7	1061.7	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7
170°	1069.3	1068.4	1067.3	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8
172.5°	1073.1	1072.0	1071.1	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4
175°	1077.7	1076.5	1075.4	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5
177.5°	1078.8	1077.8	1076.8	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1239.7	1244.0	1246.0	1246.0	1248.4	1247.3	1246.3
5°	1310.9	1318.8	1320.5	1328.0	1333.4	1331.7	1332.6
7.5°	1381.8	1394.5	1407.0	1412.8	1413.7	1417.1	1418.3
10°	1425.4	1435.8	1455.4	1452.5	1467.0	1475.4	1461.6
12.5°	1467.4	1481.4	1494.9	1498.7	1507.0	1509.6	1504.2
15°	1505.3	1512.8	1513.6	1511.6	1514.0	1512.0	1504.1
17.5°	1469.8	1457.7	1433.1	1421.4	1412.2	1398.5	1393.0
20°	1411.2	1375.4	1333.8	1317.2	1297.6	1259.3	1268.5
22.5°	1284.7	1243.9	1202.3	1153.7	1130.5	1094.2	1092.0
25°	1087.9	1017.6	940.1	886.1	854.4	818.2	802.4
27.5°	845.8	757.2	693.8	661.7	632.5	603.8	602.6
30°	686.6	620.1	571.0	543.6	525.6	513.6	516.1
32.5°	578.8	533.2	500.1	477.3	464.1	454.9	454.8
35°	473.2	442.0	420.8	411.2	401.6	394.9	395.3
37.5°	405.0	386.2	374.4	363.8	357.8	354.6	352.8
40°	370.0	354.6	345.4	339.2	334.2	329.6	328.8
42.5°	342.3	329.6	320.4	315.5	310.9	307.6	306.8
45°	303.8	293.4	285.1	279.6	277.6	274.7	274.7
47.5°	270.3	260.0	253.6	250.1	246.5	244.6	244.5
50°	247.6	239.7	233.9	231.8	228.9	227.6	227.2
52.5°	227.3	221.4	217.3	215.8	214.6	213.0	213.3
55°	199.7	196.4	194.8	193.6	191.4	188.9	190.6
57.5°	176.5	173.7	169.3	165.3	163.4	161.7	162.3
60°	160.2	154.4	148.5	144.0	142.8	139.0	139.0
62.5°	139.6	131.4	124.3	121.7	120.4	118.7	118.4
65°	107.4	104.0	102.4	100.7	99.9	99.9	99.1
67.5°	88.9	87.6	85.9	85.4	84.5	84.3	84.1
70°	78.7	77.0	76.1	75.7	74.9	75.3	74.1
72.5°	68.6	67.3	67.2	66.1	65.6	65.6	64.7
75°	54.1	54.1	53.6	53.2	52.4	52.0	52.4
77.5°	41.6	41.7	40.9	40.8	40.8	40.8	40.4
80°	33.3	33.7	33.3	32.9	32.4	32.9	32.4
82.5°	26.3	25.7	25.6	25.5	25.4	25.2	25.1
85°	15.0	15.4	15.0	14.6	14.6	14.6	15.0
87.5°	9.3	9.5	9.6	9.6	9.7	9.8	9.5
90°	18.2	19.1	19.6	20.0	20.3	20.7	21.0
92.5°	19.4	19.9	20.2	20.4	20.6	20.8	21.0
95°	33.0	33.8	34.2	34.0	33.8	33.7	33.5
97.5°	42.7	43.5	43.9	44.1	44.3	44.5	44.7
100°	48.6	50.0	50.8	51.1	51.5	51.9	52.2
102.5°	51.0	52.8	54.0	54.5	55.0	55.4	55.9
105°	53.2	55.1	56.4	57.2	57.8	58.5	59.2
107.5°	60.7	58.8	58.1	58.9	59.5	60.3	60.9
110°	84.4	67.1	58.8	59.4	60.2	60.8	61.6



TEST NUMBER: P331813-930

CATALOG NUMBER: S122RDIW-S675D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	154.4	91.2	59.9	60.5	61.1	61.6	62.2
115°	240.2	160.0	113.7	101.3	88.8	76.3	63.9
117.5°	474.3	454.9	424.7	383.7	342.8	301.8	260.8
120°	577.2	579.4	568.7	545.4	522.0	498.6	475.2
122.5°	611.6	612.8	611.1	606.6	602.1	597.5	593.0
125°	661.9	663.2	664.0	664.6	665.0	665.5	666.1
127.5°	709.1	710.9	711.8	711.9	712.0	712.1	712.2
130°	738.8	740.7	741.6	741.4	741.2	741.0	740.9
132.5°	767.3	768.9	769.6	769.4	769.2	769.1	768.9
135°	808.4	810.1	810.8	810.5	810.1	809.8	809.4
137.5°	846.4	848.2	848.7	848.2	847.5	846.9	846.4
140°	871.0	872.5	872.9	872.0	871.1	870.3	869.4
142.5°	893.6	895.0	895.3	894.5	893.6	892.8	891.9
145°	925.3	926.4	926.7	925.8	924.9	924.1	923.2
147.5°	952.7	953.6	953.7	952.9	952.2	951.5	950.7
150°	969.9	970.9	971.0	970.2	969.3	968.4	967.6
152.5°	985.5	986.5	986.5	985.4	984.2	983.1	981.9
155°	1006.5	1007.5	1007.4	1006.0	1004.6	1003.2	1001.8
157.5°	1024.4	1025.6	1025.5	1024.1	1022.8	1021.4	1020.1
160°	1034.5	1035.6	1035.5	1034.3	1033.1	1031.9	1030.7
162.5°	1044.3	1045.5	1045.4	1043.8	1042.4	1040.9	1039.4
165°	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5
167.5°	1065.9	1067.1	1067.0	1065.4	1063.9	1062.3	1060.8
170°	1070.9	1072.1	1072.0	1070.4	1068.9	1067.3	1065.8
172.5°	1074.6	1075.9	1075.7	1074.2	1072.6	1071.1	1069.5
175°	1078.7	1079.9	1079.7	1077.9	1076.2	1074.5	1072.8
177.5°	1078.9	1079.9	1079.8	1078.5	1077.3	1076.0	1074.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6

(END OF REPORT)