

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331541-927

Luminaire Tested: **S122DIW-S675D970U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331541-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D970U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5208.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35				
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29				
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18				
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13				
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.5
10°-20°	222.5	4.3
20°-30°	327.1	6.3
30°-40°	379.9	7.3
40°-50°	379.5	7.3
50°-60°	331.0	6.4
60°-70°	244.7	4.7
70°-80°	138.6	2.7
80°-90°	39.8	0.8
90°-100°	34.9	0.7
100°-110°	128.0	2.5
110°-120°	342.1	6.6
120°-130°	564.7	10.8
130°-140°	600.5	11.5
140°-150°	558.1	10.7
150°-160°	448.7	8.6
160°-170°	289.2	5.6
170°-180°	99.5	1.9
0°-30°	628.7	12.1
0°-40°	1008.6	19.4
0°-60°	1719.1	33.0
0°-90°	2142.3	41.1
90°-120°	504.9	9.7
90°-150°	2228.2	42.8
90°-180°	3066.0	58.9
0°-180°	5208.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	1	9	15	19	20	4
95°	49	26	30	33	33	60
105°	230	240	46	54	58	246
115°	435	448	467	133	62	428
125°	615	626	640	645	647	549
135°	762	773	780	787	786	588
145°	883	883	896	900	897	552
155°	973	967	975	979	973	448
165°	1025	1021	1023	1027	1023	289
175°	1048	1043	1045	1049	1042	100
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.1	12.1	12.1	12.1	11.8
90°	0.8	2.6	4.4	6.3	8.2	9.7	11.1	12.4	13.8	15.1	16.0
92.5°	15.3	15.1	15.0	14.8	14.7	14.9	15.5	16.2	16.9	17.6	18.0
95°	49.2	43.6	38.1	32.6	27.0	24.8	26.0	27.2	28.4	29.5	30.3
97.5°	97.7	82.0	66.4	50.7	35.1	28.6	31.4	34.1	36.8	39.5	40.2
100°	134.0	110.9	87.9	64.9	41.8	31.7	34.5	37.4	40.3	43.2	44.5
102.5°	174.0	169.1	164.2	159.3	154.4	140.1	116.1	92.2	68.3	44.4	46.1
105°	230.1	235.2	240.2	245.3	250.3	229.9	183.9	138.0	92.1	46.2	48.0
107.5°	294.1	298.3	302.3	306.3	310.5	284.9	229.9	174.8	119.7	64.6	62.7
110°	335.3	338.9	342.4	345.9	349.4	326.9	278.3	229.7	181.1	132.5	115.7



TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.1	377.2	380.3	383.5	386.6	382.1	370.2	358.1	346.1	334.1	272.7
115°	435.2	438.1	441.0	443.9	446.7	450.2	454.4	458.6	462.9	467.1	389.1
117.5°	489.9	493.1	496.3	499.5	502.7	505.7	508.7	511.5	514.4	517.3	498.4
120°	529.9	532.4	534.9	537.4	540.0	542.7	545.7	548.8	551.8	554.8	556.9
122.5°	563.8	566.4	569.1	571.7	574.4	577.4	580.7	584.0	587.2	590.6	591.8
125°	615.4	617.6	619.8	621.9	624.2	626.9	630.0	633.3	636.4	639.6	640.8
127.5°	662.2	664.6	667.0	669.5	671.8	674.3	676.7	679.1	681.4	683.8	685.6
130°	691.9	694.6	697.3	699.9	702.6	704.9	706.7	708.6	710.4	712.3	714.2
132.5°	722.2	724.5	726.7	729.0	731.3	733.3	735.2	737.0	738.9	740.8	742.4
135°	761.5	764.2	766.9	769.6	772.3	774.4	775.9	777.4	778.9	780.5	782.1
137.5°	801.3	803.2	805.1	807.0	808.8	810.6	812.4	814.0	815.8	817.5	819.2
140°	827.4	828.7	830.0	831.4	832.7	834.3	836.1	838.0	839.9	841.8	843.3
142.5°	849.1	850.3	851.6	852.8	854.0	855.6	857.8	859.9	862.1	864.1	865.5
145°	883.4	883.2	883.0	882.9	882.7	884.1	886.9	889.8	892.6	895.5	896.7
147.5°	913.2	912.5	911.9	911.2	910.6	911.7	914.6	917.3	920.2	923.1	923.9
150°	932.6	931.4	930.2	929.1	927.9	928.6	931.3	934.0	936.7	939.4	940.4
152.5°	949.0	947.6	946.3	945.0	943.6	944.3	946.8	949.4	952.0	954.5	955.5
155°	972.7	971.1	969.6	968.1	966.6	966.9	968.9	970.9	973.0	974.9	976.0
157.5°	991.3	990.1	988.7	987.5	986.2	986.3	987.7	989.1	990.5	991.9	993.1
160°	1002.2	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2
162.5°	1011.9	1010.9	1009.9	1008.8	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4
165°	1024.9	1023.9	1022.9	1021.9	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8
167.5°	1034.6	1033.6	1032.6	1031.6	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3
170°	1040.1	1039.0	1038.1	1037.0	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2
172.5°	1043.7	1042.7	1041.6	1040.7	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9
175°	1048.4	1047.2	1046.0	1044.9	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8
177.5°	1049.2	1048.2	1047.3	1046.3	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	11.6	11.3	11.0	10.9	10.8	10.7	10.6	10.5
90°	16.8	17.7	18.5	19.1	19.4	19.7	20.1	20.4
92.5°	18.5	18.9	19.3	19.6	19.8	20.0	20.2	20.4
95°	31.2	32.1	32.9	33.2	33.0	32.9	32.7	32.6
97.5°	40.9	41.5	42.2	42.6	42.9	43.0	43.3	43.4
100°	45.9	47.2	48.6	49.4	49.7	50.1	50.4	50.7
102.5°	47.8	49.6	51.3	52.4	52.9	53.4	53.9	54.3
105°	49.9	51.7	53.6	54.8	55.5	56.2	56.9	57.5
107.5°	60.8	59.0	57.1	56.5	57.2	57.8	58.5	59.2
110°	98.8	82.0	65.2	57.1	57.8	58.5	59.1	59.8



TEST NUMBER: P331541-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	211.4	150.0	88.6	58.2	58.8	59.3	59.9	60.4
115°	311.2	233.4	155.5	110.5	98.4	86.3	74.1	62.1
117.5°	479.6	460.8	442.0	412.6	372.8	333.0	293.3	253.4
120°	558.9	560.9	562.9	552.5	529.9	507.2	484.4	461.8
122.5°	593.0	594.2	595.4	593.8	589.4	585.0	580.6	576.2
125°	642.0	643.2	644.4	645.2	645.7	646.2	646.7	647.2
127.5°	687.3	689.0	690.7	691.6	691.7	691.8	691.9	692.0
130°	716.0	717.9	719.7	720.6	720.3	720.2	720.0	719.9
132.5°	743.9	745.5	747.1	747.8	747.6	747.4	747.3	747.1
135°	783.8	785.4	787.1	787.8	787.5	787.1	786.8	786.5
137.5°	820.8	822.4	824.1	824.7	824.1	823.5	822.9	822.4
140°	844.8	846.3	847.8	848.1	847.3	846.4	845.6	844.8
142.5°	866.9	868.3	869.7	869.9	869.1	868.2	867.4	866.6
145°	897.9	899.0	900.2	900.4	899.5	898.7	897.9	897.0
147.5°	924.8	925.7	926.5	926.6	925.9	925.2	924.5	923.8
150°	941.4	942.4	943.4	943.5	942.7	941.8	941.0	940.2
152.5°	956.6	957.5	958.5	958.5	957.4	956.3	955.2	954.1
155°	977.0	977.9	979.0	978.8	977.5	976.1	974.8	973.4
157.5°	994.2	995.4	996.5	996.4	995.1	993.8	992.4	991.2
160°	1004.2	1005.2	1006.2	1006.2	1005.0	1003.8	1002.7	1001.5
162.5°	1013.6	1014.7	1015.9	1015.7	1014.2	1012.8	1011.4	1010.0
165°	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6
167.5°	1034.5	1035.7	1036.9	1036.7	1035.2	1033.7	1032.2	1030.7
170°	1039.4	1040.5	1041.7	1041.6	1040.1	1038.6	1037.0	1035.5
172.5°	1043.0	1044.2	1045.4	1045.2	1043.7	1042.2	1040.7	1039.2
175°	1046.9	1048.1	1049.3	1049.1	1047.3	1045.7	1044.0	1042.4
177.5°	1047.4	1048.3	1049.2	1049.2	1047.9	1046.7	1045.5	1044.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1

(END OF REPORT)