

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331577-927

Luminaire Tested: **S122DIW-S865D1240U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331577-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6709.3 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17651	17651	17651
5°	17718	17462	17566
10°	17613	17285	17372
15°	17396	17061	17043
20°	17086	16725	16706
25°	16778	16311	16311
30°	16384	15933	15795
35°	16015	15477	15248
40°	15553	15022	14733
45°	15098	14570	14209
50°	14601	14099	13599
55°	14083	13551	13050
60°	13511	12897	12426
65°	12894	12248	11687
70°	12109	11462	10914
75°	11017	10555	10293
80°	9772	9484	8991
85°	7984	7595	6817



TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	1.5
10°-20°	289.3	4.3
20°-30°	425.2	6.3
30°-40°	493.9	7.4
40°-50°	493.3	7.4
50°-60°	430.2	6.4
60°-70°	318.1	4.7
70°-80°	180.2	2.7
80°-90°	51.7	0.8
90°-100°	44.7	0.7
100°-110°	163.8	2.4
110°-120°	437.9	6.5
120°-130°	722.9	10.8
130°-140°	768.8	11.5
140°-150°	714.5	10.6
150°-160°	574.5	8.6
160°-170°	370.2	5.5
170°-180°	127.4	1.9
0°-30°	817.2	12.2
0°-40°	1311.1	19.5
0°-60°	2234.6	33.3
0°-90°	2784.6	41.5
90°-120°	646.4	9.6
90°-150°	2852.5	42.5
90°-180°	3925.0	58.5
0°-180°	6709.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1093	1093	1093	1093	1093	
5°	1093	1089	1077	1085	1084	104
15°	1041	1034	1021	1024	1020	293
25°	942	933	916	917	916	433
35°	812	802	785	779	774	507
45°	661	653	638	627	622	510
55°	500	494	481	469	464	447
65°	338	331	321	311	306	334
75°	177	174	169	163	165	189
85°	43	42	41	38	37	49
90°	1	12	19	24	26	5
95°	63	33	38	42	42	77
105°	295	307	59	69	74	315
115°	557	574	598	170	80	548
125°	788	801	819	825	828	702
135°	975	990	999	1008	1007	753
145°	1131	1131	1146	1152	1148	707
155°	1245	1238	1248	1253	1246	574
165°	1312	1307	1309	1315	1309	371
175°	1342	1336	1337	1343	1334	128
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1098.3	1097.3	1096.4	1095.5	1094.6	1093.1	1091.0	1088.9	1086.9	1084.8	1086.7
5°	1093.2	1092.3	1091.4	1090.4	1089.5	1087.7	1085.2	1082.6	1080.1	1077.4	1079.3
7.5°	1083.5	1082.1	1080.7	1079.2	1077.8	1075.7	1073.1	1070.5	1067.9	1065.2	1067.1
10°	1074.3	1072.7	1071.0	1069.4	1067.8	1065.6	1062.7	1059.9	1057.2	1054.3	1056.2
12.5°	1061.7	1060.3	1058.8	1057.3	1055.9	1053.8	1051.0	1048.1	1045.4	1042.6	1043.9
15°	1040.7	1039.3	1037.8	1036.5	1035.1	1032.8	1029.8	1026.7	1023.7	1020.7	1021.6
17.5°	1013.8	1012.3	1011.0	1009.6	1008.1	1005.9	1002.8	999.7	996.6	993.6	994.7
20°	994.4	993.0	991.7	990.2	988.8	986.5	983.2	979.9	976.7	973.4	974.1
22.5°	975.1	973.1	971.1	969.2	967.3	964.7	961.6	958.5	955.5	952.4	952.5
25°	941.8	940.0	938.1	936.3	934.4	931.4	927.5	923.5	919.6	915.6	916.1
27.5°	904.0	902.4	900.6	899.0	897.3	894.8	891.8	888.6	885.5	882.3	881.7
30°	878.8	876.9	875.0	873.2	871.3	868.6	865.1	861.7	858.1	854.6	853.9
32.5°	851.9	850.4	848.9	847.4	845.9	843.3	839.6	835.9	832.3	828.5	827.3
35°	812.5	810.2	807.9	805.6	803.2	800.2	796.5	792.7	788.9	785.2	783.9
37.5°	768.2	766.1	764.1	762.0	760.0	757.1	753.4	749.6	745.8	742.1	740.4
40°	737.9	736.1	734.2	732.3	730.5	727.6	723.9	720.2	716.4	712.7	710.6
42.5°	708.5	706.6	704.7	702.9	701.0	698.2	694.5	690.8	687.0	683.3	681.0
45°	661.2	659.6	657.9	656.3	654.7	652.0	648.6	645.1	641.6	638.1	635.5
47.5°	614.1	612.6	611.0	609.5	607.9	605.3	601.7	598.0	594.4	590.7	588.0
50°	581.3	580.1	579.0	577.8	576.6	574.4	571.2	567.8	564.6	561.3	558.1
52.5°	549.4	547.8	546.3	544.7	543.2	540.9	537.8	534.7	531.6	528.5	525.9
55°	500.3	499.0	497.6	496.1	494.7	492.7	489.9	487.0	484.3	481.4	478.6
57.5°	451.1	450.0	448.9	447.8	446.7	444.6	441.5	438.4	435.3	432.2	429.5
60°	418.4	417.4	416.5	415.6	414.6	412.6	409.2	406.0	402.7	399.4	396.9
62.5°	386.4	384.9	383.4	381.9	380.4	378.4	375.9	373.4	370.8	368.4	366.0
65°	337.5	336.0	334.6	333.2	331.8	329.9	327.6	325.3	323.0	320.6	318.5
67.5°	287.6	286.5	285.3	284.2	283.1	281.5	279.4	277.3	275.2	273.1	271.5
70°	256.5	255.6	254.6	253.7	252.8	251.2	249.1	247.0	244.9	242.8	241.2
72.5°	224.5	223.6	222.7	221.7	220.8	219.7	218.3	217.0	215.6	214.2	212.6
75°	176.6	176.1	175.6	175.2	174.8	173.9	172.8	171.6	170.4	169.2	167.9
77.5°	133.7	132.9	132.1	131.3	130.6	129.9	129.4	129.0	128.5	128.0	127.3
80°	105.1	104.9	104.6	104.4	104.2	103.9	103.4	102.9	102.4	102.0	101.2
82.5°	78.2	78.2	78.1	78.0	78.0	77.9	77.6	77.3	77.0	76.8	75.8
85°	43.1	42.9	42.6	42.4	42.1	41.9	41.7	41.4	41.2	41.0	40.3
87.5°	15.4	15.4	15.5	15.6	15.8	15.8	15.8	15.7	15.7	15.7	15.3
90°	1.0	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4
92.5°	19.6	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1
95°	63.0	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9
97.5°	125.0	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4
100°	171.5	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0
102.5°	222.7	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0
105°	294.6	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5
107.5°	376.6	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3
110°	429.3	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1



TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.9	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2
115°	557.2	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2
117.5°	627.2	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1
120°	678.3	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9
122.5°	721.8	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6
125°	787.8	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4
127.5°	847.7	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7
130°	885.7	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3
132.5°	924.5	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3
135°	974.9	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2
137.5°	1025.8	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7
140°	1059.1	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5
142.5°	1087.1	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0
145°	1130.8	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9
147.5°	1169.0	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8
150°	1193.9	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9
152.5°	1214.8	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3
155°	1245.2	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4
157.5°	1269.1	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3
160°	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3
162.5°	1295.5	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1
165°	1312.1	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7
167.5°	1324.5	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9
170°	1331.5	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1
172.5°	1336.1	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7
175°	1342.1	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8
177.5°	1343.1	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1088.5	1090.4	1092.3	1093.1	1092.7	1092.3	1091.9	1091.5
5°	1081.2	1083.1	1085.0	1085.6	1085.2	1084.7	1084.3	1083.8
7.5°	1069.0	1070.9	1072.8	1073.4	1072.9	1072.4	1071.9	1071.3
10°	1058.0	1059.9	1061.8	1062.4	1061.7	1061.0	1060.3	1059.6
12.5°	1045.2	1046.5	1047.8	1048.2	1047.7	1047.2	1046.6	1046.2
15°	1022.5	1023.5	1024.5	1024.3	1023.2	1022.0	1020.8	1019.6
17.5°	995.7	996.8	997.9	997.8	996.7	995.6	994.5	993.4
20°	974.8	975.5	976.2	976.0	975.2	974.2	973.3	972.3
22.5°	952.7	952.8	952.9	952.8	952.1	951.6	951.0	950.5
25°	916.6	917.0	917.4	917.4	917.0	916.6	916.1	915.6
27.5°	881.0	880.3	879.6	878.7	877.5	876.4	875.3	874.2
30°	853.2	852.5	851.8	851.0	850.1	849.1	848.2	847.2
32.5°	826.0	824.7	823.5	822.4	821.5	820.5	819.6	818.6
35°	782.4	781.0	779.7	778.3	777.2	776.0	774.8	773.6
37.5°	738.7	737.0	735.2	733.8	732.7	731.6	730.5	729.3
40°	708.5	706.4	704.3	702.7	701.9	700.9	700.0	699.0
42.5°	678.7	676.4	674.1	672.3	671.0	669.7	668.4	667.1
45°	633.0	630.3	627.8	626.1	625.1	624.2	623.2	622.3
47.5°	585.3	582.7	580.0	577.9	576.6	575.2	573.9	572.5
50°	554.8	551.5	548.3	546.1	544.9	543.7	542.6	541.4
52.5°	523.1	520.4	517.7	515.6	514.0	512.5	511.0	509.4
55°	475.9	473.0	470.2	468.3	467.1	465.9	464.8	463.6
57.5°	426.7	424.0	421.2	419.4	418.5	417.6	416.8	415.8
60°	394.3	391.7	389.2	387.5	386.8	386.1	385.4	384.8
62.5°	363.5	361.2	358.8	357.2	356.2	355.4	354.5	353.6
65°	316.4	314.3	312.2	310.5	309.4	308.2	307.0	305.9
67.5°	269.8	268.2	266.6	265.3	264.4	263.4	262.4	261.5
70°	239.6	237.9	236.3	235.0	234.1	233.1	232.2	231.2
72.5°	211.0	209.3	207.7	206.5	205.7	205.0	204.2	203.5
75°	166.4	165.0	163.7	163.2	163.7	164.1	164.5	165.0
77.5°	126.7	126.0	125.2	124.5	123.9	123.3	122.6	121.9
80°	100.5	99.9	99.2	98.5	98.1	97.7	97.2	96.7
82.5°	74.9	74.1	73.2	72.7	72.6	72.5	72.4	72.3
85°	39.6	38.9	38.2	37.7	37.5	37.2	37.0	36.8
87.5°	15.0	14.6	14.3	14.0	13.9	13.9	13.7	13.6
90°	21.5	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	23.6	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	39.9	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	52.3	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	58.7	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	61.2	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	63.8	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	78.0	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	126.5	105.0	83.4	73.1	74.0	74.9	75.7	76.5



TEST NUMBER: P331577-927

CATALOG NUMBER: S122DIW-S865D1240U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	270.6	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	398.5	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	614.0	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	715.5	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	759.1	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	821.9	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	879.8	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	916.6	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	952.4	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1003.4	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1050.8	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1081.5	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1109.8	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1149.4	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1183.9	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1205.1	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1224.6	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1250.7	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1272.8	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1285.6	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1297.6	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1324.4	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1330.6	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1335.2	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1340.3	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1340.8	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)