

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331825-930

Luminaire Tested: **S122RDIW-S865D435U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331825-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D435U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4103.1 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	102	98	95	91	96	93	90	87	82	80	78	73	71	69	64	63	61	57
2	94	87	81	76	88	82	77	73	73	69	66	65	62	60	58	55	53	50
3	87	78	71	65	81	73	67	62	66	61	57	59	55	52	52	49	47	43
4	80	70	62	56	75	66	59	54	59	54	50	53	49	45	47	44	41	38
5	74	63	55	49	69	60	53	47	54	48	44	48	44	40	43	40	37	34
6	69	57	49	43	65	54	47	42	49	43	39	44	40	36	40	36	33	31
7	64	52	44	39	60	50	43	38	45	39	35	41	36	32	37	33	30	28
8	60	48	40	35	56	45	39	34	41	36	32	38	33	29	34	30	27	25
9	56	44	37	32	53	42	35	31	38	33	29	35	30	27	32	28	25	23
10	52	41	34	29	50	39	32	28	36	30	26	33	28	25	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	3.6
10°-20°	411.2	10.0
20°-30°	529.9	12.9
30°-40°	503.6	12.3
40°-50°	431.4	10.5
50°-60°	328.5	8.0
60°-70°	207.7	5.1
70°-80°	103.7	2.5
80°-90°	28.2	0.7
90°-100°	16.1	0.4
100°-110°	58.9	1.4
110°-120°	157.5	3.8
120°-130°	259.9	6.3
130°-140°	276.4	6.7
140°-150°	256.9	6.3
150°-160°	206.6	5.0
160°-170°	133.1	3.2
170°-180°	45.8	1.1
0°-30°	1088.7	26.5
0°-40°	1592.3	38.8
0°-60°	2352.3	57.3
0°-90°	2691.8	65.6
90°-120°	232.4	5.7
90°-150°	1025.8	25.0
90°-180°	1411.0	34.4
0°-180°	4103.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	21
90°	9	0	9	0	9	5
95°	15	23	15	23	15	14
105°	26	106	26	106	26	28
115°	28	200	28	200	28	72
125°	298	283	298	283	298	258
135°	362	351	362	351	362	279
145°	413	407	413	407	413	258
155°	448	448	448	448	448	207
165°	471	472	471	472	471	133
175°	480	483	480	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	8.8	9.2	9.2	9.1	9.1	9.0	9.0	9.4	8.8	9.2	8.6
90°	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7	7.3	6.9	6.4
92.5°	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5	8.3	8.1	7.7
95°	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3	13.9	13.6	13.0
97.5°	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8	18.5	18.2	17.0
100°	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1	20.5	19.9	18.5
102.5°	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0	21.2	20.4	31.5
105°	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0	22.1	21.3	42.4
107.5°	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0	28.9	29.8	55.1
110°	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5	53.2	61.0	83.3



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3	125.6	153.8	159.3
115°	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3	179.1	215.0	213.0
117.5°	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8	229.5	238.1	236.8
120°	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3	256.3	255.4	254.0
122.5°	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0	272.5	271.9	270.4
125°	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5	295.0	294.5	293.0
127.5°	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4	315.6	314.8	313.7
130°	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6	328.7	327.9	327.1
132.5°	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5	341.8	341.0	340.1
135°	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9	360.0	359.3	358.6
137.5°	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9	377.1	376.3	375.5
140°	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9	388.2	387.5	386.6
142.5°	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1	398.4	397.8	396.8
145°	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4	412.8	412.2	410.9
147.5°	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7	425.3	424.9	423.6
150°	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4	432.9	432.4	431.2
152.5°	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3	439.9	439.4	438.2
155°	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8	449.3	448.8	447.9
157.5°	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7	457.1	456.6	456.0
160°	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3	461.9	461.4	460.9
162.5°	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6	466.1	465.5	465.1
165°	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8	470.6
167.5°	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3	475.7	475.2	475.0
170°	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5	477.9	477.4	477.3
172.5°	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1	479.6	479.1	478.9
175°	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0	481.4	480.9	480.7
177.5°	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2	481.8	481.3	481.3
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	8.5	8.8	8.7	8.1	8.4	8.6	10.6	12.6	11.1	9.9	9.2
90°	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3	1.2	2.0	2.9
92.5°	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0	6.9	6.8	6.8
95°	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7	20.1	17.5	15.0
97.5°	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9	37.7	30.6	23.3
100°	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7	51.0	40.4	29.8
102.5°	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1	77.9	75.6	73.4
105°	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9	108.3	110.6	112.9
107.5°	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4	137.3	139.2	141.0
110°	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3	156.0	157.6	159.2



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2	173.7	175.1	176.5
115°	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4	201.7	203.0	204.3
117.5°	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5	227.0	228.4	229.9
120°	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9	245.1	246.2	247.4
122.5°	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5	260.7	262.0	263.2
125°	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3	284.3	285.4	286.3
127.5°	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8	306.0	307.0	308.2
130°	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5	319.8	321.0	322.2
132.5°	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5	333.5	334.5	335.6
135°	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6	351.8	353.0	354.2
137.5°	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9	369.7	370.6	371.5
140°	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9	381.5	382.1	382.7
142.5°	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9	391.5	392.0	392.6
145°	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7	406.6	406.5	406.4
147.5°	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4	420.1	419.8	419.6
150°	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3	428.8	428.2	427.7
152.5°	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8	436.3	435.6	435.0
155°	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8	447.1	446.4	445.7
157.5°	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3	455.8	455.2	454.6
160°	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	460.9	460.5	460.0
162.5°	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9	465.4	464.9	464.5
165°	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8	471.4	470.9	470.4
167.5°	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3	475.8	475.4	474.9
170°	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8	478.3	477.8	477.4
172.5°	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5	480.0	479.6	479.1
175°	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7	482.1	481.5	481.0
177.5°	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0	482.6	482.1	481.7
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	9.0	8.7	7.9	8.1	8.2	7.9	8.0	7.6	7.7	7.7	7.4
90°	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7	8.2	8.5	8.8
92.5°	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5	8.7	8.9	9.0
95°	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3	14.8	15.2	15.3
97.5°	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8	19.2	19.4	19.6
100°	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1	21.7	22.3	22.7
102.5°	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0	22.8	23.6	24.1
105°	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0	23.8	24.7	25.3
107.5°	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0	27.1	26.3	26.0
110°	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5	37.7	30.0	26.3



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3	69.1	40.8	26.8
115°	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3	107.5	71.6	50.9
117.5°	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8	212.1	203.4	190.0
120°	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3	258.2	259.2	254.4
122.5°	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0	273.5	274.1	273.4
125°	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5	296.1	296.6	297.0
127.5°	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4	317.2	318.0	318.4
130°	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6	330.4	331.3	331.7
132.5°	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5	343.2	343.9	344.2
135°	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9	361.6	362.4	362.6
137.5°	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9	378.6	379.4	379.6
140°	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9	389.6	390.3	390.4
142.5°	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1	399.7	400.4	400.5
145°	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4	413.8	414.4	414.5
147.5°	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7	426.2	426.6	426.6
150°	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4	433.8	434.3	434.4
152.5°	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3	440.8	441.3	441.2
155°	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8	450.2	450.7	450.6
157.5°	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7	458.2	458.8	458.7
160°	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3	462.8	463.3	463.2
162.5°	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6	467.2	467.7	467.6
165°	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9	472.4	473.0	473.0
167.5°	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3	476.8	477.4	477.3
170°	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5	479.1	479.6	479.5
172.5°	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1	480.7	481.3	481.2
175°	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0	482.5	483.1	483.0
177.5°	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2	482.6	483.1	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	7.4	7.0	7.5	7.1	7.5	7.0	7.4	7.4	7.7	7.7	7.6
90°	9.0	9.1	9.3	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7
92.5°	9.1	9.2	9.3	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5
95°	15.2	15.2	15.1	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3
97.5°	19.7	19.8	19.9	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8
100°	22.9	23.1	23.2	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1
102.5°	24.4	24.6	24.8	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0
105°	25.5	25.8	26.2	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0
107.5°	26.3	26.7	26.9	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0
110°	26.6	26.9	27.2	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	27.1	27.3	27.6	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3
115°	45.3	39.7	34.2	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3
117.5°	171.6	153.3	135.0	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8
120°	243.9	233.5	223.0	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3
122.5°	271.3	269.3	267.3	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0
125°	297.3	297.5	297.7	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5
127.5°	318.5	318.5	318.5	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4
130°	331.7	331.6	331.5	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6
132.5°	344.1	344.1	344.1	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5
135°	362.6	362.4	362.2	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9
137.5°	379.4	379.1	378.9	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9
140°	390.0	389.6	389.3	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9
142.5°	400.1	399.7	399.3	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1
145°	414.1	413.7	413.4	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4
147.5°	426.2	425.9	425.6	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7
150°	434.0	433.6	433.2	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4
152.5°	440.8	440.3	439.7	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3
155°	450.0	449.4	448.7	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8
157.5°	458.1	457.5	456.9	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7
160°	462.7	462.1	461.5	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3
162.5°	466.9	466.3	465.6	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6
165°	472.4	471.9	471.3	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9
167.5°	476.5	475.9	475.2	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3
170°	478.8	478.1	477.4	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5
172.5°	480.5	479.8	479.1	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1
175°	482.2	481.4	480.6	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0
177.5°	482.4	481.8	481.3	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	8.0	7.9	8.2	8.1	7.9	8.7	9.0	9.2	9.9	11.1	12.6
90°	7.3	6.9	6.4	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3
92.5°	8.3	8.1	7.7	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0
95°	13.9	13.6	13.0	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7
97.5°	18.5	18.2	17.0	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9
100°	20.5	19.9	18.5	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7
102.5°	21.2	20.4	31.5	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1
105°	22.1	21.3	42.4	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9
107.5°	28.9	29.8	55.1	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4
110°	53.2	61.0	83.3	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	125.6	153.8	159.3	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2
115°	179.1	215.0	213.0	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4
117.5°	229.5	238.1	236.8	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5
120°	256.3	255.4	254.0	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9
122.5°	272.5	271.9	270.4	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5
125°	295.0	294.5	293.0	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3
127.5°	315.6	314.8	313.7	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8
130°	328.7	327.9	327.1	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5
132.5°	341.8	341.0	340.1	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5
135°	360.0	359.3	358.6	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6
137.5°	377.1	376.3	375.5	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9
140°	388.2	387.5	386.6	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9
142.5°	398.4	397.8	396.8	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9
145°	412.8	412.2	410.9	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7
147.5°	425.3	424.9	423.6	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4
150°	432.9	432.4	431.2	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3
152.5°	439.9	439.4	438.2	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8
155°	449.3	448.8	447.9	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8
157.5°	457.1	456.6	456.0	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3
160°	461.9	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4
162.5°	466.1	465.5	465.1	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9
165°	471.3	470.8	470.6	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8
167.5°	475.7	475.2	475.0	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3
170°	477.9	477.4	477.3	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8
172.5°	479.6	479.1	478.9	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5
175°	481.4	480.9	480.7	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7
177.5°	481.8	481.3	481.3	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	10.6	8.6	8.4	8.1	8.7	8.8	8.5	8.6	9.2	8.8	9.4
90°	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7
92.5°	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5
95°	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3
97.5°	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8
100°	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1
102.5°	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0
105°	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0
107.5°	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0
110°	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3
115°	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3
117.5°	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8
120°	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3
122.5°	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0
125°	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5
127.5°	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4
130°	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6
132.5°	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5
135°	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9
137.5°	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9
140°	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9
142.5°	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1
145°	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4
147.5°	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7
150°	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4
152.5°	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3
155°	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8
157.5°	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7
160°	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3
162.5°	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6
165°	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9
167.5°	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3
170°	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5
172.5°	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1
175°	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0
177.5°	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	9.0	9.0	9.1	9.1	9.2	9.2	8.8
90°	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331825-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)