

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331828-930

Luminaire Tested: **S122RDIW-S865D435U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331828-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D435U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3684.4 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35	33
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19302	19302	19302
5°	19376	19060	19164
10°	19226	18748	18589
15°	19005	18191	17668
20°	18699	17399	16526
25°	18387	16498	15419
30°	17952	15571	13998
35°	17527	14564	12751
40°	17102	13523	11310
45°	16600	12353	10003
50°	16088	11170	8721
55°	15564	9897	7491
60°	14951	8561	6219
65°	14258	7194	5662
70°	13430	5925	5207
75°	12420	5402	4860
80°	10962	4826	4426
85°	8633	3798	3798



TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.9	3.0
10°-20°	307.2	8.3
20°-30°	431.5	11.7
30°-40°	470.5	12.8
40°-50°	432.6	11.7
50°-60°	339.7	9.2
60°-70°	221.5	6.0
70°-80°	114.2	3.1
80°-90°	31.4	0.9
90°-100°	27.7	0.8
100°-110°	86.1	2.3
110°-120°	147.2	4.0
120°-130°	193.6	5.3
130°-140°	217.3	5.9
140°-150°	213.1	5.8
150°-160°	178.7	4.9
160°-170°	118.6	3.2
170°-180°	41.4	1.1
0°-30°	850.6	23.1
0°-40°	1321.1	35.9
0°-60°	2093.4	56.8
0°-90°	2460.5	66.8
90°-120°	261.1	7.1
90°-150°	885.2	24.0
90°-180°	1224.0	33.2
0°-180°	3684.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1196	1190	1176	1185	1182	113
15°	1137	1124	1088	1068	1057	320
25°	1032	995	926	883	866	474
35°	889	832	739	673	647	556
45°	727	652	541	467	438	561
55°	553	467	352	289	266	494
65°	373	285	188	153	148	370
75°	199	126	87	79	78	211
85°	47	25	20	20	20	55
90°	0	5	13	12	13	3
95°	19	23	24	24	23	22
105°	79	80	81	82	82	84
115°	148	150	149	149	148	146
125°	215	218	217	216	216	192
135°	278	282	283	282	281	215
145°	338	340	342	343	341	211
155°	386	387	388	390	389	178
165°	420	420	420	422	420	118
175°	437	436	435	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1199.8	1198.8	1197.8	1196.9	1196.0	1194.4	1192.3	1190.2	1188.1	1185.9	1187.9
5°	1195.5	1194.3	1193.0	1191.8	1190.7	1188.5	1185.4	1182.3	1179.1	1176.0	1178.1
7.5°	1183.1	1181.6	1180.1	1178.7	1177.1	1174.6	1170.9	1167.3	1163.6	1159.9	1160.6
10°	1172.7	1171.0	1169.4	1167.7	1166.0	1162.8	1158.0	1153.2	1148.3	1143.5	1142.8
12.5°	1159.8	1157.6	1155.6	1153.6	1151.4	1147.4	1141.2	1135.1	1128.9	1122.7	1121.4
15°	1137.0	1134.4	1131.7	1129.1	1126.4	1121.0	1112.9	1104.7	1096.5	1088.3	1083.8
17.5°	1109.1	1105.1	1101.1	1097.0	1093.0	1085.7	1075.2	1064.7	1054.3	1043.7	1038.4
20°	1088.3	1083.5	1078.7	1073.9	1069.1	1060.7	1048.6	1036.7	1024.7	1012.6	1006.6
22.5°	1065.8	1060.5	1055.1	1049.7	1044.3	1034.9	1021.2	1007.7	994.2	980.6	972.8
25°	1032.1	1024.4	1016.7	1009.0	1001.4	989.5	973.6	957.8	941.9	926.1	916.2
27.5°	991.4	983.0	974.7	966.3	958.0	944.9	926.9	909.1	891.1	873.3	861.8
30°	962.9	953.7	944.6	935.5	926.3	912.2	892.9	873.7	854.4	835.2	823.0
32.5°	935.1	924.5	913.8	903.1	892.4	877.3	857.7	838.0	818.5	798.8	784.9
35°	889.2	877.0	864.8	852.5	840.2	823.5	802.3	781.2	760.1	738.9	723.7
37.5°	843.4	830.0	816.5	803.0	789.5	771.5	749.0	726.4	703.9	681.3	664.6
40°	811.4	797.0	782.5	768.1	753.7	734.8	711.5	688.2	664.9	641.6	624.4
42.5°	778.5	763.3	748.1	733.0	717.7	698.1	674.0	649.9	625.8	601.7	584.1
45°	727.0	710.9	694.8	678.7	662.6	641.9	616.7	591.4	566.1	541.0	523.8
47.5°	676.8	659.7	642.7	625.6	608.5	586.9	560.9	534.8	508.7	482.7	465.8
50°	640.5	623.4	606.3	589.2	572.2	550.4	524.0	497.5	471.1	444.7	428.0
52.5°	605.0	587.1	569.3	551.5	533.6	511.8	485.9	460.0	434.1	408.3	392.2
55°	552.9	534.1	515.4	496.6	477.8	455.4	429.5	403.5	377.6	351.6	337.2
57.5°	499.4	480.1	460.9	441.6	422.5	400.4	375.4	350.4	325.5	300.5	287.3
60°	463.0	443.8	424.6	405.4	386.1	364.1	339.3	314.5	289.8	265.1	252.8
62.5°	427.5	408.3	389.1	369.8	350.6	329.2	305.6	282.0	258.4	234.7	223.1
65°	373.2	353.8	334.3	314.8	295.4	274.8	253.2	231.5	209.9	188.3	180.1
67.5°	320.9	301.6	282.3	262.9	243.5	224.1	204.7	185.2	165.8	146.3	142.5
70°	284.5	265.8	247.0	228.3	209.5	191.8	175.3	158.7	142.1	125.5	123.1
72.5°	249.9	232.0	213.9	196.0	178.0	162.3	149.0	135.7	122.4	109.1	107.0
75°	199.1	182.2	165.4	148.5	131.8	119.3	111.0	102.9	94.7	86.6	84.9
77.5°	149.1	134.3	119.5	104.8	90.0	80.7	76.7	72.8	68.9	64.9	63.9
80°	117.9	105.7	93.4	81.1	68.9	61.6	59.1	56.7	54.3	51.9	51.0
82.5°	89.4	79.8	70.2	60.7	51.1	45.5	43.9	42.2	40.6	39.0	38.4
85°	46.6	41.5	36.4	31.4	26.3	23.5	22.7	22.0	21.3	20.5	20.5
87.5°	13.9	12.6	11.3	9.9	8.6	8.1	8.4	8.8	9.1	9.5	9.3
90°	0.4	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8
92.5°	6.6	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7
95°	19.2	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6
97.5°	35.1	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7
100°	46.9	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0
102.5°	59.4	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2
105°	79.4	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4
107.5°	99.6	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3
110°	112.7	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.9	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6
115°	147.7	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1
117.5°	168.6	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3
120°	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5
122.5°	195.2	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5
125°	215.0	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0
127.5°	234.2	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8
130°	246.4	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3
132.5°	260.0	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7
135°	278.2	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8
137.5°	297.3	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5
140°	308.8	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0
142.5°	320.7	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3
145°	337.6	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5
147.5°	352.8	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5
150°	363.1	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0
152.5°	372.3	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6
155°	386.0	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7
157.5°	397.8	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7
160°	404.9	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4
162.5°	411.3	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4
165°	420.0	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2
167.5°	427.2	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6
170°	431.0	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2
172.5°	433.7	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8
175°	437.0	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7
177.5°	438.3	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1189.8	1191.7	1193.6	1194.4	1194.0	1193.6	1193.3	1192.9
5°	1180.3	1182.4	1184.6	1185.4	1184.6	1183.9	1183.2	1182.4
7.5°	1161.2	1161.8	1162.5	1162.1	1160.9	1159.7	1158.4	1157.2
10°	1142.1	1141.3	1140.6	1139.5	1138.1	1136.7	1135.2	1133.8
12.5°	1120.1	1118.8	1117.5	1115.7	1113.3	1110.9	1108.5	1106.1
15°	1079.2	1074.6	1070.1	1066.6	1064.2	1061.8	1059.4	1057.0
17.5°	1032.9	1027.4	1022.1	1017.2	1013.1	1009.0	1004.9	1000.7
20°	1000.6	994.6	988.6	982.9	977.6	972.3	967.0	961.8
22.5°	965.2	957.4	949.7	943.8	939.9	935.9	932.0	928.1
25°	906.4	896.5	886.6	879.9	876.3	872.7	869.1	865.5
27.5°	850.3	838.8	827.3	818.7	813.0	807.2	801.5	795.8
30°	810.7	798.4	786.1	776.7	770.3	763.8	757.3	750.8
32.5°	770.9	756.8	742.9	732.8	726.8	720.6	714.5	708.4
35°	708.6	693.5	678.3	668.1	662.8	657.5	652.2	646.9
37.5°	648.0	631.3	614.7	603.2	597.2	591.1	585.1	579.0
40°	607.4	590.4	573.2	561.6	555.4	549.1	542.8	536.6
42.5°	566.5	548.8	531.2	519.3	513.2	507.2	501.1	495.0
45°	506.8	489.8	472.6	461.2	455.4	449.7	443.9	438.1
47.5°	448.7	431.8	414.8	403.7	398.5	393.2	388.0	382.8
50°	411.5	394.8	378.3	367.5	362.4	357.3	352.3	347.2
52.5°	376.3	360.3	344.2	333.9	329.2	324.6	319.9	315.3
55°	322.8	308.3	293.9	284.4	279.8	275.2	270.7	266.1
57.5°	274.1	260.9	247.7	239.1	235.3	231.4	227.6	223.7
60°	240.5	228.3	216.0	208.0	204.1	200.2	196.4	192.6
62.5°	211.4	199.7	188.0	181.0	178.7	176.4	174.1	171.8
65°	171.9	163.7	155.6	151.1	150.3	149.7	149.0	148.2
67.5°	138.8	135.0	131.3	129.0	128.2	127.4	126.7	126.0
70°	120.7	118.3	115.9	114.2	113.2	112.3	111.3	110.3
72.5°	105.0	103.0	100.9	99.7	99.1	98.5	97.9	97.3
75°	83.2	81.5	79.8	78.8	78.6	78.4	78.1	77.9
77.5°	63.0	62.0	61.1	60.4	60.0	59.6	59.3	58.9
80°	50.0	49.1	48.1	47.6	47.6	47.6	47.6	47.6
82.5°	37.8	37.2	36.6	36.4	36.4	36.4	36.4	36.4
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	9.0	8.8	8.6	8.5	8.6	8.6	8.6	8.6
90°	12.6	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.2	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.6	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.4	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331828-930

CATALOG NUMBER: S122RDIW-S865D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	128.4	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	169.1	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.2	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.7	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.5	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.1	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	263.3	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.4	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.3	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.6	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.7	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.1	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.2	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	406.9	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	412.9	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	420.8	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.2	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	430.7	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	433.4	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.3	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)