

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331560-927

Luminaire Tested: **S122DIW-S865D435U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331560-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D435U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3972.2 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53	49
3	85	75	68	61	80	71	65	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17651	17651	17651
5°	17718	17462	17566
10°	17613	17285	17372
15°	17396	17061	17043
20°	17086	16725	16706
25°	16778	16311	16311
30°	16384	15933	15795
35°	16015	15477	15248
40°	15553	15022	14733
45°	15098	14570	14209
50°	14601	14099	13599
55°	14083	13551	13050
60°	13511	12897	12426
65°	12894	12248	11687
70°	12109	11462	10914
75°	11017	10555	10293
80°	9772	9484	8991
85°	7984	7595	6817



TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	2.6
10°-20°	289.3	7.3
20°-30°	425.2	10.7
30°-40°	493.9	12.4
40°-50°	493.3	12.4
50°-60°	430.2	10.8
60°-70°	318.1	8.0
70°-80°	180.2	4.5
80°-90°	50.1	1.3
90°-100°	27.0	0.7
100°-110°	83.7	2.1
110°-120°	143.1	3.6
120°-130°	188.1	4.7
130°-140°	211.2	5.3
140°-150°	207.1	5.2
150°-160°	173.7	4.4
160°-170°	115.2	2.9
170°-180°	40.3	1.0
0°-30°	817.2	20.6
0°-40°	1311.1	33.0
0°-60°	2234.6	56.3
0°-90°	2783.0	70.1
90°-120°	253.7	6.4
90°-150°	860.1	21.7
90°-180°	1189.0	29.9
0°-180°	3972.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1093	1093	1093	1093	1093	
5°	1093	1089	1077	1085	1084	104
15°	1041	1034	1021	1024	1020	293
25°	942	933	916	917	916	433
35°	812	802	785	779	774	507
45°	661	653	638	627	622	510
55°	500	494	481	469	464	447
65°	338	331	321	311	306	334
75°	177	174	169	163	165	189
85°	43	42	41	38	37	49
90°	0	5	13	12	12	3
95°	19	22	23	23	22	21
105°	77	78	79	80	80	82
115°	144	146	145	145	144	142
125°	209	212	211	210	210	187
135°	270	274	275	274	274	209
145°	328	331	333	333	332	205
155°	375	376	377	379	378	173
165°	408	408	408	410	408	115
175°	425	424	423	425	423	40
180°	425	425	425	425	425	



TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1098.3	1097.3	1096.4	1095.5	1094.6	1093.1	1091.0	1088.9	1086.9	1084.8	1086.7
5°	1093.2	1092.3	1091.4	1090.4	1089.5	1087.7	1085.2	1082.6	1080.1	1077.4	1079.3
7.5°	1083.5	1082.1	1080.7	1079.2	1077.8	1075.7	1073.1	1070.5	1067.9	1065.2	1067.1
10°	1074.3	1072.7	1071.0	1069.4	1067.8	1065.6	1062.7	1059.9	1057.2	1054.3	1056.2
12.5°	1061.7	1060.3	1058.8	1057.3	1055.9	1053.8	1051.0	1048.1	1045.4	1042.6	1043.9
15°	1040.7	1039.3	1037.8	1036.5	1035.1	1032.8	1029.8	1026.7	1023.7	1020.7	1021.6
17.5°	1013.8	1012.3	1011.0	1009.6	1008.1	1005.9	1002.8	999.7	996.6	993.6	994.7
20°	994.4	993.0	991.7	990.2	988.8	986.5	983.2	979.9	976.7	973.4	974.1
22.5°	975.1	973.1	971.1	969.2	967.3	964.7	961.6	958.5	955.5	952.4	952.5
25°	941.8	940.0	938.1	936.3	934.4	931.4	927.5	923.5	919.6	915.6	916.1
27.5°	904.0	902.4	900.6	899.0	897.3	894.8	891.8	888.6	885.5	882.3	881.7
30°	878.8	876.9	875.0	873.2	871.3	868.6	865.1	861.7	858.1	854.6	853.9
32.5°	851.9	850.4	848.9	847.4	845.9	843.3	839.6	835.9	832.3	828.5	827.3
35°	812.5	810.2	807.9	805.6	803.2	800.2	796.5	792.7	788.9	785.2	783.9
37.5°	768.2	766.1	764.1	762.0	760.0	757.1	753.4	749.6	745.8	742.1	740.4
40°	737.9	736.1	734.2	732.3	730.5	727.6	723.9	720.2	716.4	712.7	710.6
42.5°	708.5	706.6	704.7	702.9	701.0	698.2	694.5	690.8	687.0	683.3	681.0
45°	661.2	659.6	657.9	656.3	654.7	652.0	648.6	645.1	641.6	638.1	635.5
47.5°	614.1	612.6	611.0	609.5	607.9	605.3	601.7	598.0	594.4	590.7	588.0
50°	581.3	580.1	579.0	577.8	576.6	574.4	571.2	567.8	564.6	561.3	558.1
52.5°	549.4	547.8	546.3	544.7	543.2	540.9	537.8	534.7	531.6	528.5	525.9
55°	500.3	499.0	497.6	496.1	494.7	492.7	489.9	487.0	484.3	481.4	478.6
57.5°	451.1	450.0	448.9	447.8	446.7	444.6	441.5	438.4	435.3	432.2	429.5
60°	418.4	417.4	416.5	415.6	414.6	412.6	409.2	406.0	402.7	399.4	396.9
62.5°	386.4	384.9	383.4	381.9	380.4	378.4	375.9	373.4	370.8	368.4	366.0
65°	337.5	336.0	334.6	333.2	331.8	329.9	327.6	325.3	323.0	320.6	318.5
67.5°	287.6	286.5	285.3	284.2	283.1	281.5	279.4	277.3	275.2	273.1	271.5
70°	256.5	255.6	254.6	253.7	252.8	251.2	249.1	247.0	244.9	242.8	241.2
72.5°	224.5	223.6	222.7	221.7	220.8	219.7	218.3	217.0	215.6	214.2	212.6
75°	176.6	176.1	175.6	175.2	174.8	173.9	172.8	171.6	170.4	169.2	167.9
77.5°	133.7	132.9	132.1	131.3	130.6	129.9	129.4	129.0	128.5	128.0	127.3
80°	105.1	104.9	104.6	104.4	104.2	103.9	103.4	102.9	102.4	102.0	101.2
82.5°	78.2	78.2	78.1	78.0	78.0	77.9	77.6	77.3	77.0	76.8	75.8
85°	43.1	42.9	42.6	42.4	42.1	41.9	41.7	41.4	41.2	41.0	40.3
87.5°	15.2	15.1	14.8	14.7	14.5	14.3	14.3	14.3	14.3	14.3	13.7
90°	0.4	1.3	2.3	3.2	4.2	5.5	7.3	9.0	10.8	12.6	12.4
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.6	11.0	11.4	11.4
95°	18.7	19.5	20.3	21.1	21.9	22.3	22.5	22.7	22.8	23.0	23.0
97.5°	34.1	34.8	35.5	36.2	36.9	37.4	37.7	38.0	38.3	38.6	38.6
100°	45.6	46.2	46.8	47.5	48.2	48.6	48.8	49.0	49.3	49.5	49.5
102.5°	57.7	58.1	58.6	59.2	59.7	60.1	60.4	60.7	61.0	61.3	61.4
105°	77.2	77.4	77.6	77.9	78.1	78.3	78.5	78.7	78.8	79.0	79.1
107.5°	96.8	97.2	97.5	97.9	98.2	98.4	98.4	98.4	98.4	98.4	98.5
110°	109.5	110.0	110.4	110.9	111.4	111.6	111.6	111.6	111.6	111.6	111.6



TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.3	123.7	124.2	124.7	125.2	125.4	125.3	125.2	125.2	125.1	124.9
115°	143.5	144.0	144.5	145.0	145.4	145.6	145.4	145.3	145.1	145.0	144.9
117.5°	163.8	164.5	165.1	165.7	166.4	166.4	166.0	165.6	165.1	164.7	164.5
120°	177.3	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.3
122.5°	189.6	190.4	191.2	191.9	192.7	192.9	192.4	191.9	191.5	191.1	190.9
125°	208.9	209.6	210.3	211.0	211.8	212.0	211.8	211.5	211.3	211.0	210.8
127.5°	227.6	228.5	229.4	230.4	231.2	231.6	231.3	231.0	230.7	230.4	230.1
130°	239.4	240.4	241.5	242.5	243.5	244.0	243.8	243.7	243.5	243.4	243.2
132.5°	252.6	253.4	254.3	255.2	256.0	256.4	256.4	256.5	256.5	256.5	256.2
135°	270.3	271.2	272.0	272.9	273.8	274.3	274.4	274.6	274.7	274.9	274.8
137.5°	288.8	289.5	290.3	291.0	291.7	292.2	292.4	292.6	292.8	293.0	292.9
140°	300.1	300.8	301.5	302.2	302.9	303.5	303.9	304.3	304.7	305.1	305.1
142.5°	311.6	312.3	313.0	313.7	314.4	314.9	315.1	315.4	315.7	316.0	316.1
145°	328.0	328.6	329.2	329.7	330.3	330.8	331.3	331.8	332.2	332.7	332.8
147.5°	342.8	343.4	344.1	344.8	345.5	345.9	346.3	346.6	346.9	347.2	347.4
150°	352.8	353.3	353.8	354.3	354.7	355.1	355.5	355.8	356.1	356.4	356.6
152.5°	361.7	362.2	362.7	363.1	363.6	364.1	364.4	364.8	365.2	365.6	365.9
155°	375.0	375.3	375.5	375.8	376.0	376.3	376.5	376.8	377.0	377.2	377.6
157.5°	386.5	386.7	386.8	387.0	387.1	387.2	387.4	387.5	387.7	387.9	388.4
160°	393.4	393.6	393.7	393.9	394.0	394.1	394.2	394.3	394.3	394.4	394.9
162.5°	399.7	399.7	399.7	399.7	399.8	399.9	400.0	400.1	400.1	400.2	400.7
165°	408.1	408.0	407.9	407.8	407.7	407.7	407.7	407.7	407.7	407.7	408.3
167.5°	415.1	414.9	414.6	414.4	414.2	414.0	414.0	414.0	414.0	414.0	414.5
170°	418.8	418.6	418.4	418.1	417.9	417.7	417.6	417.6	417.5	417.4	418.0
172.5°	421.4	421.2	421.0	420.7	420.5	420.3	420.3	420.2	420.1	420.0	420.6
175°	424.6	424.4	424.1	423.9	423.7	423.4	423.3	423.1	422.9	422.8	423.3
177.5°	425.9	425.7	425.5	425.3	425.1	424.9	424.8	424.7	424.5	424.5	424.8
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1088.5	1090.4	1092.3	1093.1	1092.7	1092.3	1091.9	1091.5
5°	1081.2	1083.1	1085.0	1085.6	1085.2	1084.7	1084.3	1083.8
7.5°	1069.0	1070.9	1072.8	1073.4	1072.9	1072.4	1071.9	1071.3
10°	1058.0	1059.9	1061.8	1062.4	1061.7	1061.0	1060.3	1059.6
12.5°	1045.2	1046.5	1047.8	1048.2	1047.7	1047.2	1046.6	1046.2
15°	1022.5	1023.5	1024.5	1024.3	1023.2	1022.0	1020.8	1019.6
17.5°	995.7	996.8	997.9	997.8	996.7	995.6	994.5	993.4
20°	974.8	975.5	976.2	976.0	975.2	974.2	973.3	972.3
22.5°	952.7	952.8	952.9	952.8	952.1	951.6	951.0	950.5
25°	916.6	917.0	917.4	917.4	917.0	916.6	916.1	915.6
27.5°	881.0	880.3	879.6	878.7	877.5	876.4	875.3	874.2
30°	853.2	852.5	851.8	851.0	850.1	849.1	848.2	847.2
32.5°	826.0	824.7	823.5	822.4	821.5	820.5	819.6	818.6
35°	782.4	781.0	779.7	778.3	777.2	776.0	774.8	773.6
37.5°	738.7	737.0	735.2	733.8	732.7	731.6	730.5	729.3
40°	708.5	706.4	704.3	702.7	701.9	700.9	700.0	699.0
42.5°	678.7	676.4	674.1	672.3	671.0	669.7	668.4	667.1
45°	633.0	630.3	627.8	626.1	625.1	624.2	623.2	622.3
47.5°	585.3	582.7	580.0	577.9	576.6	575.2	573.9	572.5
50°	554.8	551.5	548.3	546.1	544.9	543.7	542.6	541.4
52.5°	523.1	520.4	517.7	515.6	514.0	512.5	511.0	509.4
55°	475.9	473.0	470.2	468.3	467.1	465.9	464.8	463.6
57.5°	426.7	424.0	421.2	419.4	418.5	417.6	416.8	415.8
60°	394.3	391.7	389.2	387.5	386.8	386.1	385.4	384.8
62.5°	363.5	361.2	358.8	357.2	356.2	355.4	354.5	353.6
65°	316.4	314.3	312.2	310.5	309.4	308.2	307.0	305.9
67.5°	269.8	268.2	266.6	265.3	264.4	263.4	262.4	261.5
70°	239.6	237.9	236.3	235.0	234.1	233.1	232.2	231.2
72.5°	211.0	209.3	207.7	206.5	205.7	205.0	204.2	203.5
75°	166.4	165.0	163.7	163.2	163.7	164.1	164.5	165.0
77.5°	126.7	126.0	125.2	124.5	123.9	123.3	122.6	121.9
80°	100.5	99.9	99.2	98.5	98.1	97.7	97.2	96.7
82.5°	74.9	74.1	73.2	72.7	72.6	72.5	72.4	72.3
85°	39.6	38.9	38.2	37.7	37.5	37.2	37.0	36.8
87.5°	13.1	12.5	11.9	11.6	11.3	11.2	11.0	10.9
90°	12.3	12.1	12.0	11.9	12.0	12.0	12.1	12.2
92.5°	11.5	11.5	11.6	11.6	11.6	11.6	11.6	11.6
95°	23.0	23.0	23.0	22.9	22.7	22.6	22.4	22.3
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.5	49.5	49.5	49.5	49.4	49.4	49.3	49.2
102.5°	61.4	61.5	61.6	61.6	61.5	61.4	61.3	61.2
105°	79.3	79.5	79.6	79.7	79.7	79.7	79.7	79.7
107.5°	98.5	98.6	98.7	98.5	98.2	97.8	97.4	97.0
110°	111.6	111.6	111.6	111.5	111.2	111.0	110.7	110.5



TEST NUMBER: P331560-927

CATALOG NUMBER: S122DIW-S865D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.8	124.5	124.4	124.1	124.0	123.8	123.7	123.5
115°	144.8	144.7	144.7	144.5	144.3	144.0	143.8	143.5
117.5°	164.3	164.1	163.9	163.7	163.4	163.2	163.0	162.7
120°	177.3	177.3	177.3	177.2	177.0	176.7	176.5	176.3
122.5°	190.7	190.5	190.3	190.1	190.0	189.8	189.6	189.4
125°	210.6	210.3	210.1	209.9	209.8	209.8	209.7	209.6
127.5°	229.8	229.6	229.3	229.0	228.7	228.5	228.2	228.0
130°	243.0	242.9	242.7	242.5	242.2	241.9	241.5	241.2
132.5°	255.9	255.5	255.2	254.8	254.6	254.3	254.1	253.8
135°	274.7	274.6	274.6	274.4	274.2	273.9	273.7	273.5
137.5°	292.9	292.8	292.8	292.6	292.2	291.9	291.6	291.3
140°	305.1	305.1	305.1	304.9	304.6	304.3	304.0	303.6
142.5°	316.1	316.2	316.2	316.1	315.8	315.4	315.1	314.8
145°	332.9	333.0	333.0	332.9	332.6	332.2	331.9	331.6
147.5°	347.5	347.8	347.9	347.8	347.5	347.2	346.9	346.7
150°	356.9	357.1	357.4	357.4	357.1	356.9	356.6	356.4
152.5°	366.1	366.5	366.8	366.8	366.5	366.1	365.9	365.6
155°	378.0	378.4	378.8	378.9	378.7	378.4	378.2	378.0
157.5°	388.9	389.4	390.0	390.1	389.7	389.3	389.0	388.6
160°	395.4	395.9	396.3	396.4	396.1	395.8	395.5	395.1
162.5°	401.2	401.8	402.3	402.4	402.0	401.6	401.2	400.9
165°	408.8	409.4	410.0	410.0	409.6	409.2	408.8	408.4
167.5°	415.1	415.7	416.2	416.3	415.8	415.4	415.0	414.6
170°	418.5	419.1	419.6	419.7	419.2	418.7	418.3	417.8
172.5°	421.1	421.7	422.2	422.2	421.8	421.3	420.8	420.3
175°	423.9	424.5	425.0	425.1	424.6	424.1	423.7	423.2
177.5°	425.2	425.6	426.0	426.0	425.6	425.2	424.8	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3

(END OF REPORT)