

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331831-930

Luminaire Tested: **S122RDIW-S865D710U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331831-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D710U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4772.2 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32	29
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	19	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19302	19302	19302
5°	19376	19060	19164
10°	19226	18748	18589
15°	19005	18191	17668
20°	18699	17399	16526
25°	18387	16498	15419
30°	17952	15571	13998
35°	17527	14564	12751
40°	17102	13523	11310
45°	16600	12353	10003
50°	16088	11170	8721
55°	15564	9897	7491
60°	14951	8561	6219
65°	14258	7194	5662
70°	13430	5925	5207
75°	12420	5402	4860
80°	10962	4826	4426
85°	8633	3798	3798



TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.9	2.3
10°-20°	307.2	6.4
20°-30°	431.5	9.0
30°-40°	470.5	9.9
40°-50°	432.6	9.1
50°-60°	339.7	7.1
60°-70°	221.5	4.6
70°-80°	114.2	2.4
80°-90°	31.6	0.7
90°-100°	26.3	0.6
100°-110°	96.5	2.0
110°-120°	257.9	5.4
120°-130°	425.7	8.9
130°-140°	452.8	9.5
140°-150°	420.8	8.8
150°-160°	338.4	7.1
160°-170°	218.0	4.6
170°-180°	75.1	1.6
0°-30°	850.6	17.8
0°-40°	1321.1	27.7
0°-60°	2093.4	43.9
0°-90°	2460.7	51.6
90°-120°	380.7	8.0
90°-150°	1680.1	35.2
90°-180°	2312.0	48.4
0°-180°	4772.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1196	1190	1176	1185	1182	113
15°	1137	1124	1088	1068	1057	320
25°	1032	995	926	883	866	474
35°	889	832	739	673	647	556
45°	727	652	541	467	438	561
55°	553	467	352	289	266	494
65°	373	285	188	153	148	370
75°	199	126	87	79	78	211
85°	47	25	20	20	20	55
90°	1	7	11	14	15	4
95°	37	20	22	25	24	45
105°	174	181	35	41	43	185
115°	328	338	352	100	47	323
125°	464	472	482	486	488	414
135°	574	583	588	594	593	443
145°	666	666	675	679	676	416
155°	733	729	735	738	734	338
165°	773	770	771	775	771	218
175°	790	787	788	791	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1199.8	1198.8	1197.8	1196.9	1196.0	1194.4	1192.3	1190.2	1188.1	1185.9	1187.9
5°	1195.5	1194.3	1193.0	1191.8	1190.7	1188.5	1185.4	1182.3	1179.1	1176.0	1178.1
7.5°	1183.1	1181.6	1180.1	1178.7	1177.1	1174.6	1170.9	1167.3	1163.6	1159.9	1160.6
10°	1172.7	1171.0	1169.4	1167.7	1166.0	1162.8	1158.0	1153.2	1148.3	1143.5	1142.8
12.5°	1159.8	1157.6	1155.6	1153.6	1151.4	1147.4	1141.2	1135.1	1128.9	1122.7	1121.4
15°	1137.0	1134.4	1131.7	1129.1	1126.4	1121.0	1112.9	1104.7	1096.5	1088.3	1083.8
17.5°	1109.1	1105.1	1101.1	1097.0	1093.0	1085.7	1075.2	1064.7	1054.3	1043.7	1038.4
20°	1088.3	1083.5	1078.7	1073.9	1069.1	1060.7	1048.6	1036.7	1024.7	1012.6	1006.6
22.5°	1065.8	1060.5	1055.1	1049.7	1044.3	1034.9	1021.2	1007.7	994.2	980.6	972.8
25°	1032.1	1024.4	1016.7	1009.0	1001.4	989.5	973.6	957.8	941.9	926.1	916.2
27.5°	991.4	983.0	974.7	966.3	958.0	944.9	926.9	909.1	891.1	873.3	861.8
30°	962.9	953.7	944.6	935.5	926.3	912.2	892.9	873.7	854.4	835.2	823.0
32.5°	935.1	924.5	913.8	903.1	892.4	877.3	857.7	838.0	818.5	798.8	784.9
35°	889.2	877.0	864.8	852.5	840.2	823.5	802.3	781.2	760.1	738.9	723.7
37.5°	843.4	830.0	816.5	803.0	789.5	771.5	749.0	726.4	703.9	681.3	664.6
40°	811.4	797.0	782.5	768.1	753.7	734.8	711.5	688.2	664.9	641.6	624.4
42.5°	778.5	763.3	748.1	733.0	717.7	698.1	674.0	649.9	625.8	601.7	584.1
45°	727.0	710.9	694.8	678.7	662.6	641.9	616.7	591.4	566.1	541.0	523.8
47.5°	676.8	659.7	642.7	625.6	608.5	586.9	560.9	534.8	508.7	482.7	465.8
50°	640.5	623.4	606.3	589.2	572.2	550.4	524.0	497.5	471.1	444.7	428.0
52.5°	605.0	587.1	569.3	551.5	533.6	511.8	485.9	460.0	434.1	408.3	392.2
55°	552.9	534.1	515.4	496.6	477.8	455.4	429.5	403.5	377.6	351.6	337.2
57.5°	499.4	480.1	460.9	441.6	422.5	400.4	375.4	350.4	325.5	300.5	287.3
60°	463.0	443.8	424.6	405.4	386.1	364.1	339.3	314.5	289.8	265.1	252.8
62.5°	427.5	408.3	389.1	369.8	350.6	329.2	305.6	282.0	258.4	234.7	223.1
65°	373.2	353.8	334.3	314.8	295.4	274.8	253.2	231.5	209.9	188.3	180.1
67.5°	320.9	301.6	282.3	262.9	243.5	224.1	204.7	185.2	165.8	146.3	142.5
70°	284.5	265.8	247.0	228.3	209.5	191.8	175.3	158.7	142.1	125.5	123.1
72.5°	249.9	232.0	213.9	196.0	178.0	162.3	149.0	135.7	122.4	109.1	107.0
75°	199.1	182.2	165.4	148.5	131.8	119.3	111.0	102.9	94.7	86.6	84.9
77.5°	149.1	134.3	119.5	104.8	90.0	80.7	76.7	72.8	68.9	64.9	63.9
80°	117.9	105.7	93.4	81.1	68.9	61.6	59.1	56.7	54.3	51.9	51.0
82.5°	89.4	79.8	70.2	60.7	51.1	45.5	43.9	42.2	40.6	39.0	38.4
85°	46.6	41.5	36.4	31.4	26.3	23.5	22.7	22.0	21.3	20.5	20.5
87.5°	13.9	12.7	11.4	10.2	8.9	8.4	8.6	8.8	9.0	9.2	9.1
90°	0.6	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1
92.5°	11.5	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5
95°	37.1	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9
97.5°	73.6	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3
100°	101.0	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5
102.5°	131.2	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7
105°	173.5	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2
107.5°	221.8	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3
110°	252.8	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2



TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.1	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7
115°	328.2	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4
117.5°	369.4	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9
120°	399.5	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9
122.5°	425.1	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2
125°	464.0	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1
127.5°	499.3	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9
130°	521.6	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5
132.5°	544.5	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7
135°	574.2	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7
137.5°	604.2	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7
140°	623.9	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9
142.5°	640.3	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6
145°	666.1	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1
147.5°	688.5	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7
150°	703.2	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1
152.5°	715.5	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5
155°	733.4	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9
157.5°	747.5	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8
160°	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4
162.5°	763.0	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4
165°	772.8	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0
167.5°	780.1	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2
170°	784.2	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9
172.5°	786.9	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5
175°	790.5	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6
177.5°	791.1	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1189.8	1191.7	1193.6	1194.4	1194.0	1193.6	1193.3	1192.9
5°	1180.3	1182.4	1184.6	1185.4	1184.6	1183.9	1183.2	1182.4
7.5°	1161.2	1161.8	1162.5	1162.1	1160.9	1159.7	1158.4	1157.2
10°	1142.1	1141.3	1140.6	1139.5	1138.1	1136.7	1135.2	1133.8
12.5°	1120.1	1118.8	1117.5	1115.7	1113.3	1110.9	1108.5	1106.1
15°	1079.2	1074.6	1070.1	1066.6	1064.2	1061.8	1059.4	1057.0
17.5°	1032.9	1027.4	1022.1	1017.2	1013.1	1009.0	1004.9	1000.7
20°	1000.6	994.6	988.6	982.9	977.6	972.3	967.0	961.8
22.5°	965.2	957.4	949.7	943.8	939.9	935.9	932.0	928.1
25°	906.4	896.5	886.6	879.9	876.3	872.7	869.1	865.5
27.5°	850.3	838.8	827.3	818.7	813.0	807.2	801.5	795.8
30°	810.7	798.4	786.1	776.7	770.3	763.8	757.3	750.8
32.5°	770.9	756.8	742.9	732.8	726.8	720.6	714.5	708.4
35°	708.6	693.5	678.3	668.1	662.8	657.5	652.2	646.9
37.5°	648.0	631.3	614.7	603.2	597.2	591.1	585.1	579.0
40°	607.4	590.4	573.2	561.6	555.4	549.1	542.8	536.6
42.5°	566.5	548.8	531.2	519.3	513.2	507.2	501.1	495.0
45°	506.8	489.8	472.6	461.2	455.4	449.7	443.9	438.1
47.5°	448.7	431.8	414.8	403.7	398.5	393.2	388.0	382.8
50°	411.5	394.8	378.3	367.5	362.4	357.3	352.3	347.2
52.5°	376.3	360.3	344.2	333.9	329.2	324.6	319.9	315.3
55°	322.8	308.3	293.9	284.4	279.8	275.2	270.7	266.1
57.5°	274.1	260.9	247.7	239.1	235.3	231.4	227.6	223.7
60°	240.5	228.3	216.0	208.0	204.1	200.2	196.4	192.6
62.5°	211.4	199.7	188.0	181.0	178.7	176.4	174.1	171.8
65°	171.9	163.7	155.6	151.1	150.3	149.7	149.0	148.2
67.5°	138.8	135.0	131.3	129.0	128.2	127.4	126.7	126.0
70°	120.7	118.3	115.9	114.2	113.2	112.3	111.3	110.3
72.5°	105.0	103.0	100.9	99.7	99.1	98.5	97.9	97.3
75°	83.2	81.5	79.8	78.8	78.6	78.4	78.1	77.9
77.5°	63.0	62.0	61.1	60.4	60.0	59.6	59.3	58.9
80°	50.0	49.1	48.1	47.6	47.6	47.6	47.6	47.6
82.5°	37.8	37.2	36.6	36.4	36.4	36.4	36.4	36.4
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.1
90°	12.7	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	13.9	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	23.6	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	30.8	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	34.6	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	36.1	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	37.6	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	45.9	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	74.5	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331831-930

CATALOG NUMBER: S122RDIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.4	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	234.7	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	361.7	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	421.4	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	447.1	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.0	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	518.2	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	539.9	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	560.9	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	591.0	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	618.9	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	637.0	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	653.6	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	676.9	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	697.3	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	709.8	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	721.2	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	736.6	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	749.7	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	757.2	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	764.3	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	780.1	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	783.7	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	786.4	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	789.5	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	789.8	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)