

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331860-927

Luminaire Tested: **S122RDIW-S1005D1240U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331860-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6167.6 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	28
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	29	25
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19
7	58	47	39	33	54	43	36	32	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.0
10°-20°	344.8	5.6
20°-30°	484.2	7.9
30°-40°	528.0	8.6
40°-50°	485.4	7.9
50°-60°	381.3	6.2
60°-70°	248.6	4.0
70°-80°	128.2	2.1
80°-90°	38.1	0.6
90°-100°	77.1	1.3
100°-110°	239.6	3.9
110°-120°	409.5	6.6
120°-130°	538.5	8.7
130°-140°	604.4	9.8
140°-150°	592.6	9.6
150°-160°	497.0	8.1
160°-170°	329.7	5.3
170°-180°	115.2	1.9
0°-30°	954.5	15.5
0°-40°	1482.5	24.0
0°-60°	2349.2	38.1
0°-90°	2764.0	44.8
90°-120°	726.2	11.8
90°-150°	2461.6	39.9
90°-180°	3404.0	55.2
0°-180°	6167.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	1	14	36	34	35	5
95°	53	63	66	66	64	61
105°	221	224	226	228	228	233
115°	411	417	415	414	411	406
125°	598	606	604	601	600	534
135°	774	784	787	786	783	597
145°	939	946	952	953	949	586
155°	1073	1076	1080	1084	1082	494
165°	1168	1167	1167	1173	1169	329
175°	1215	1212	1210	1216	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.8	14.6	13.4	12.2	11.0	10.9	12.0	12.9	13.9	15.0	14.7
90°	1.0	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5
92.5°	18.3	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7
95°	53.4	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8
97.5°	97.6	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5
100°	130.5	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7
102.5°	164.9	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6
105°	220.9	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4
107.5°	277.1	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9
110°	313.3	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.8	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5
115°	410.9	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8
117.5°	468.8	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7
120°	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4
122.5°	542.7	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3
125°	597.8	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3
127.5°	651.4	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6
130°	685.2	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9
132.5°	722.9	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2
135°	773.5	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6
137.5°	826.6	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4
140°	858.7	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1
142.5°	891.6	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5
145°	938.8	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4
147.5°	981.0	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2
150°	1009.7	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6
152.5°	1035.2	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2
155°	1073.4	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7
157.5°	1106.0	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5
160°	1125.8	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2
162.5°	1143.8	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8
165°	1167.9	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5
167.5°	1188.0	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4
170°	1198.7	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2
172.5°	1206.1	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6
175°	1215.1	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6
177.5°	1218.9	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	14.3	14.0	13.7	13.6	13.6	13.7	13.7	13.8
90°	35.0	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	32.9	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	175.8	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	226.9	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.0	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331860-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	357.0	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.5	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	470.2	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.8	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	602.6	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.8	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.5	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	732.2	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.4	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.2	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.7	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.7	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	994.7	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1081.9	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1113.1	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1131.6	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1148.4	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1170.1	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1188.0	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1197.8	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1205.2	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1213.2	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)