

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331607

Luminaire Tested: **S122DIW-S1005D1240U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331607
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9013.3 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45				
1	97	92	88	85	88	85	81	79	71	68	66	58	56	54	46	44	44	38				
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32				
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27				
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	52	44	39	43	38	34	36	32	29	29	26	23	20				
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	1.7
10°-20°	421.7	4.7
20°-30°	619.8	6.9
30°-40°	720.0	8.0
40°-50°	719.2	8.0
50°-60°	627.2	7.0
60°-70°	463.8	5.1
70°-80°	262.7	2.9
80°-90°	74.8	0.8
90°-100°	56.4	0.6
100°-110°	206.8	2.3
110°-120°	552.8	6.1
120°-130°	912.5	10.1
130°-140°	970.4	10.8
140°-150°	902.0	10.0
150°-160°	725.2	8.0
160°-170°	467.3	5.2
170°-180°	160.9	1.8
0°-30°	1191.4	13.2
0°-40°	1911.4	21.2
0°-60°	3257.9	36.1
0°-90°	4059.1	45.0
90°-120°	816.0	9.1
90°-150°	3600.9	40.0
90°-180°	4954.0	55.0
0°-180°	9013.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	14	24	30	33	7
95°	80	42	48	53	53	97
105°	372	388	75	88	93	397
115°	703	725	755	215	100	692
125°	994	1011	1034	1042	1046	886
135°	1231	1250	1261	1273	1271	950
145°	1428	1428	1447	1455	1450	893
155°	1572	1562	1576	1582	1573	724
165°	1656	1650	1653	1660	1653	468
175°	1694	1686	1688	1696	1684	161
180°	1690	1690	1690	1690	1690	



TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.3	22.4	22.4	22.5	22.5	22.5	22.4	22.3	22.2	22.1	21.5
90°	1.2	4.2	7.2	10.2	13.2	15.8	17.9	20.1	22.3	24.5	25.8
92.5°	24.7	24.4	24.2	23.9	23.6	24.0	25.1	26.2	27.3	28.4	29.1
95°	79.5	70.5	61.6	52.6	43.6	40.1	42.0	43.9	45.8	47.7	49.1
97.5°	157.8	132.5	107.2	82.0	56.7	46.2	50.6	55.0	59.5	63.9	64.9
100°	216.5	179.3	142.0	104.8	67.6	51.2	55.9	60.5	65.1	69.7	71.9
102.5°	281.1	273.2	265.3	257.5	249.6	226.3	187.6	149.0	110.3	71.7	74.5
105°	371.9	380.0	388.2	396.3	404.5	371.5	297.3	223.0	148.8	74.6	77.6
107.5°	475.4	481.9	488.5	495.1	501.7	460.5	371.5	282.5	193.5	104.5	101.4
110°	541.9	547.6	553.3	559.0	564.7	528.3	449.8	371.2	292.6	214.1	186.9



TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	604.5	609.6	614.6	619.7	624.8	617.6	598.2	578.8	559.4	539.9	440.8
115°	703.4	708.0	712.6	717.2	721.9	727.6	734.4	741.2	748.0	754.8	628.9
117.5°	791.7	796.9	802.0	807.2	812.4	817.3	821.9	826.6	831.3	836.0	805.5
120°	856.3	860.4	864.4	868.5	872.6	877.1	882.0	886.9	891.8	896.6	899.9
122.5°	911.1	915.4	919.7	924.0	928.3	933.1	938.4	943.7	949.1	954.4	956.3
125°	994.5	998.0	1001.6	1005.1	1008.6	1013.0	1018.2	1023.3	1028.5	1033.7	1035.6
127.5°	1070.1	1074.0	1077.9	1081.9	1085.8	1089.7	1093.5	1097.4	1101.2	1105.1	1107.9
130°	1118.1	1122.4	1126.8	1131.1	1135.5	1139.1	1142.1	1145.1	1148.1	1151.1	1154.1
132.5°	1167.0	1170.7	1174.4	1178.1	1181.8	1185.1	1188.1	1191.1	1194.1	1197.1	1199.6
135°	1230.6	1234.9	1239.3	1243.6	1248.0	1251.4	1253.8	1256.3	1258.7	1261.2	1263.9
137.5°	1294.9	1298.0	1301.0	1304.1	1307.1	1310.0	1312.8	1315.6	1318.3	1321.1	1323.8
140°	1337.0	1339.2	1341.4	1343.5	1345.7	1348.3	1351.3	1354.3	1357.3	1360.3	1362.7
142.5°	1372.3	1374.2	1376.2	1378.1	1380.1	1382.8	1386.2	1389.6	1393.0	1396.5	1398.7
145°	1427.5	1427.3	1427.0	1426.7	1426.5	1428.6	1433.3	1437.9	1442.5	1447.1	1449.0
147.5°	1475.7	1474.7	1473.7	1472.6	1471.6	1473.4	1477.9	1482.5	1487.1	1491.6	1493.1
150°	1507.1	1505.2	1503.3	1501.3	1499.4	1500.7	1505.0	1509.4	1513.7	1518.1	1519.7
152.5°	1533.5	1531.4	1529.2	1527.1	1525.0	1526.0	1530.1	1534.3	1538.4	1542.5	1544.2
155°	1571.9	1569.4	1567.0	1564.5	1562.1	1562.5	1565.8	1569.0	1572.3	1575.6	1577.2
157.5°	1602.0	1599.9	1597.8	1595.8	1593.7	1593.8	1596.1	1598.4	1600.7	1603.0	1604.8
160°	1619.6	1618.0	1616.3	1614.7	1613.1	1613.1	1614.7	1616.3	1618.0	1619.6	1621.2
162.5°	1635.3	1633.6	1632.0	1630.4	1628.7	1628.6	1630.0	1631.4	1632.9	1634.3	1636.1
165°	1656.3	1654.7	1653.0	1651.4	1649.8	1649.4	1650.2	1651.0	1651.8	1652.6	1654.5
167.5°	1672.0	1670.3	1668.7	1667.1	1665.4	1665.0	1665.8	1666.5	1667.3	1668.0	1669.9
170°	1680.8	1679.1	1677.5	1675.9	1674.2	1673.7	1674.2	1674.8	1675.3	1675.9	1677.8
172.5°	1686.6	1685.0	1683.4	1681.7	1680.1	1679.6	1680.1	1680.6	1681.2	1681.7	1683.6
175°	1694.2	1692.3	1690.4	1688.5	1686.6	1685.9	1686.5	1687.0	1687.6	1688.1	1690.0
177.5°	1695.4	1693.9	1692.4	1690.9	1689.3	1688.7	1688.9	1689.1	1689.3	1689.6	1691.1
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5



TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	21.0	20.4	19.9	19.5	19.4	19.2	19.0	18.9
90°	27.2	28.5	29.9	30.9	31.4	31.9	32.5	33.0
92.5°	29.8	30.5	31.2	31.7	32.0	32.4	32.7	33.0
95°	50.4	51.8	53.1	53.7	53.4	53.1	52.9	52.6
97.5°	66.0	67.1	68.2	68.9	69.2	69.6	69.9	70.2
100°	74.1	76.2	78.4	79.8	80.3	80.9	81.4	82.0
102.5°	77.3	80.2	83.0	84.8	85.5	86.3	87.1	87.8
105°	80.6	83.6	86.6	88.6	89.7	90.8	91.9	93.0
107.5°	98.4	95.3	92.3	91.3	92.4	93.5	94.6	95.7
110°	159.7	132.5	105.3	92.3	93.4	94.5	95.6	96.6



TEST NUMBER: P331607

CATALOG NUMBER: S122DIW-S1005D1240U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	341.6	242.5	143.3	94.1	95.0	95.9	96.7	97.6
115°	503.0	377.2	251.3	178.6	159.0	139.5	119.9	100.3
117.5°	775.1	744.6	714.2	666.8	602.5	538.2	473.9	409.5
120°	903.2	906.4	909.7	893.0	856.3	819.6	782.9	746.2
122.5°	958.3	960.3	962.2	959.6	952.5	945.4	938.3	931.1
125°	1037.5	1039.4	1041.3	1042.6	1043.4	1044.3	1045.1	1045.9
127.5°	1110.6	1113.4	1116.2	1117.7	1117.8	1118.0	1118.1	1118.3
130°	1157.1	1160.1	1163.0	1164.4	1164.1	1163.9	1163.6	1163.3
132.5°	1202.2	1204.7	1207.3	1208.4	1208.2	1207.9	1207.6	1207.4
135°	1266.6	1269.3	1272.1	1273.1	1272.6	1272.1	1271.5	1271.0
137.5°	1326.4	1329.1	1331.8	1332.6	1331.7	1330.8	1329.9	1328.9
140°	1365.2	1367.6	1370.1	1370.6	1369.2	1367.9	1366.5	1365.2
142.5°	1400.9	1403.2	1405.4	1405.8	1404.5	1403.1	1401.7	1400.4
145°	1450.9	1452.8	1454.7	1455.0	1453.6	1452.3	1450.9	1449.6
147.5°	1494.5	1495.9	1497.3	1497.4	1496.3	1495.1	1494.0	1492.9
150°	1521.3	1523.0	1524.6	1524.7	1523.4	1522.0	1520.6	1519.3
152.5°	1545.8	1547.4	1549.1	1549.0	1547.2	1545.4	1543.6	1541.8
155°	1578.8	1580.5	1582.1	1581.8	1579.6	1577.5	1575.3	1573.1
157.5°	1606.7	1608.5	1610.4	1610.2	1608.1	1606.0	1603.9	1601.7
160°	1622.9	1624.5	1626.1	1626.0	1624.1	1622.2	1620.3	1618.4
162.5°	1638.0	1639.8	1641.7	1641.4	1639.1	1636.7	1634.4	1632.1
165°	1656.4	1658.3	1660.2	1660.2	1658.3	1656.4	1654.5	1652.6
167.5°	1671.8	1673.7	1675.6	1675.4	1672.9	1670.5	1668.0	1665.6
170°	1679.7	1681.6	1683.5	1683.2	1680.8	1678.3	1675.9	1673.4
172.5°	1685.5	1687.4	1689.3	1689.1	1686.6	1684.2	1681.7	1679.3
175°	1691.9	1693.8	1695.7	1695.3	1692.6	1689.9	1687.1	1684.4
177.5°	1692.6	1694.1	1695.7	1695.4	1693.5	1691.5	1689.6	1687.6
180°	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5	1690.5

(END OF REPORT)