

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331861-927

Luminaire Tested: **S122RDIW-S1005D1440U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331861-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1440U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7586.2 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	20	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.6	2.2
10°-20°	461.5	6.1
20°-30°	594.7	7.8
30°-40°	565.1	7.4
40°-50°	484.1	6.4
50°-60°	368.7	4.9
60°-70°	233.1	3.1
70°-80°	116.4	1.5
80°-90°	34.1	0.4
90°-100°	51.9	0.7
100°-110°	190.5	2.5
110°-120°	509.1	6.7
120°-130°	840.4	11.1
130°-140°	893.8	11.8
140°-150°	830.7	11.0
150°-160°	667.9	8.8
160°-170°	430.4	5.7
170°-180°	148.2	2.0
0°-30°	1221.8	16.1
0°-40°	1786.9	23.6
0°-60°	2639.7	34.8
0°-90°	3023.2	39.9
90°-120°	751.5	9.9
90°-150°	3316.5	43.7
90°-180°	4563.0	60.1
0°-180°	7586.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	24
90°	30	1	30	1	30	14
95°	48	73	48	73	48	45
105°	86	342	86	342	86	89
115°	92	648	92	648	92	231
125°	963	916	963	916	963	834
135°	1171	1134	1171	1134	1171	902
145°	1335	1315	1335	1315	1335	835
155°	1449	1448	1449	1448	1449	669
165°	1522	1526	1522	1526	1522	430
175°	1551	1560	1551	1560	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	13.9	14.3	14.1	14.0	13.9	13.8	13.5	13.8	13.0	13.2	12.4
90°	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0	23.8	22.5	20.5
92.5°	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4	26.8	26.1	25.1
95°	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4	45.2	44.0	42.2
97.5°	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8	59.8	58.8	54.7
100°	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2	66.2	64.2	60.0
102.5°	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2	68.6	66.0	101.6
105°	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2	71.5	68.8	137.0
107.5°	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6	93.4	96.3	178.2
110°	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1	172.1	197.2	269.5



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7	406.0	497.3	515.2
115°	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3	579.2	695.1	688.9
117.5°	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9	742.0	770.0	765.6
120°	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9	828.9	825.9	821.3
122.5°	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6	880.8	879.0	874.1
125°	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5	953.8	952.0	947.3
127.5°	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9	1020.4	1017.9	1014.3
130°	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7	1063.0	1060.2	1057.4
132.5°	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2	1104.9	1102.6	1099.8
135°	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6	1164.1	1161.6	1159.4
137.5°	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7	1219.2	1216.8	1214.3
140°	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4	1255.1	1252.8	1250.1
142.5°	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3	1288.2	1286.2	1283.0
145°	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3	1334.6	1332.8	1328.6
147.5°	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5	1375.1	1373.9	1369.7
150°	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2	1399.7	1398.2	1394.2
152.5°	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7	1422.2	1420.7	1416.9
155°	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1	1452.6	1451.1	1448.2
157.5°	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8	1478.1	1476.4	1474.3
160°	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7	1493.2	1491.7	1490.2
162.5°	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6	1507.0	1505.2	1504.0
165°	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1	1521.4
167.5°	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8	1538.1	1536.4	1535.6
170°	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1	1545.3	1543.6	1543.0
172.5°	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4	1550.7	1549.0	1548.5
175°	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3	1556.6	1554.8	1554.3
177.5°	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9	1557.6	1556.2	1555.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	12.0	12.0	11.6	10.7	10.6	10.5	12.4	14.3	12.9	12.0	11.6
90°	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1	3.9	6.7	9.4
92.5°	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7	22.5	22.3	22.0
95°	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2	65.0	56.7	48.5
97.5°	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4	122.1	98.8	75.5
100°	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4	165.1	130.8	96.5
102.5°	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9	251.7	244.4	237.1
105°	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5	350.0	357.5	365.0
107.5°	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8	443.9	450.0	456.0
110°	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2	504.4	509.6	514.9





TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8	561.4	566.1	570.8
115°	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8	652.1	656.3	660.6
117.5°	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2	734.0	738.7	743.5
120°	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7	792.4	796.1	799.9
122.5°	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2	843.1	847.1	851.0
125°	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0	919.2	922.5	925.7
127.5°	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6	989.2	992.8	996.4
130°	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8	1033.8	1037.8	1041.8
132.5°	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8	1078.2	1081.6	1085.1
135°	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5	1137.4	1141.5	1145.4
137.5°	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7	1195.5	1198.3	1201.1
140°	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4	1233.4	1235.5	1237.5
142.5°	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9	1265.7	1267.5	1269.3
145°	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9	1314.5	1314.3	1314.1
147.5°	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2	1358.3	1357.3	1356.4
150°	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1	1386.3	1384.6	1382.8
152.5°	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4	1410.5	1408.5	1406.5
155°	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8	1445.5	1443.3	1441.0
157.5°	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5	1473.6	1471.7	1469.8
160°	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1490.2	1488.7	1487.2
162.5°	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1	1504.7	1503.2	1501.7
165°	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5	1524.0	1522.5	1521.0
167.5°	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9	1538.4	1536.9	1535.4
170°	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1	1546.6	1545.1	1543.6
172.5°	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5	1552.0	1550.5	1549.0
175°	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4	1558.7	1557.0	1555.2
177.5°	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5	1560.2	1558.8	1557.4
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	11.6	11.6	11.1	11.5	11.9	11.8	12.0	11.8	12.0	12.3	12.0
90°	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0	26.3	27.6	28.4
92.5°	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4	28.1	28.8	29.2
95°	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4	47.7	49.0	49.4
97.5°	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8	61.8	62.8	63.5
100°	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2	70.3	72.2	73.5
102.5°	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2	73.8	76.4	78.1
105°	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2	77.0	79.8	81.6
107.5°	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6	87.8	85.0	84.1
110°	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1	122.1	97.0	85.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7	223.3	132.0	86.7
115°	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3	347.4	231.5	164.5
117.5°	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9	685.9	657.8	614.2
120°	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9	834.9	837.9	822.4
122.5°	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6	884.5	886.2	883.8
125°	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5	957.3	959.0	960.3
127.5°	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9	1025.5	1028.0	1029.4
130°	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7	1068.5	1071.2	1072.5
132.5°	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2	1109.6	1112.0	1113.0
135°	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6	1169.1	1171.6	1172.6
137.5°	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7	1224.2	1226.6	1227.4
140°	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4	1259.6	1261.9	1262.3
142.5°	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3	1292.4	1294.4	1294.8
145°	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3	1338.1	1339.9	1340.1
147.5°	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5	1377.8	1379.1	1379.2
150°	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2	1402.7	1404.2	1404.3
152.5°	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7	1425.2	1426.7	1426.6
155°	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1	1455.6	1457.1	1456.9
157.5°	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8	1481.5	1483.2	1483.0
160°	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7	1496.2	1497.7	1497.6
162.5°	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6	1510.4	1512.0	1511.8
165°	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1
167.5°	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8	1541.6	1543.3	1543.1
170°	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1	1548.8	1550.5	1550.3
172.5°	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4	1554.2	1555.9	1555.7
175°	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3	1560.0	1561.8	1561.5
177.5°	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9	1560.4	1561.8	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	12.1	11.7	12.3	11.9	12.3	11.7	12.1	12.0	12.3	12.0	11.8
90°	28.9	29.4	29.9	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0
92.5°	29.5	29.8	30.1	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4
95°	49.2	49.0	48.7	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4
97.5°	63.8	64.1	64.4	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8
100°	74.0	74.5	75.0	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2
102.5°	78.8	79.5	80.2	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2
105°	82.6	83.7	84.6	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2
107.5°	85.1	86.1	87.1	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6
110°	86.0	87.0	88.0	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	87.5	88.3	89.1	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7
115°	146.5	128.4	110.4	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3
117.5°	554.9	495.7	436.4	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9
120°	788.7	754.9	721.0	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9
122.5°	877.3	870.8	864.2	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6
125°	961.1	961.8	962.6	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5
127.5°	1029.5	1029.7	1029.8	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9
130°	1072.2	1072.0	1071.7	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7
132.5°	1112.8	1112.5	1112.3	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2
135°	1172.1	1171.6	1171.1	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6
137.5°	1226.5	1225.7	1224.9	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7
140°	1261.2	1259.9	1258.6	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4
142.5°	1293.6	1292.3	1291.1	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3
145°	1338.9	1337.6	1336.3	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3
147.5°	1378.2	1377.1	1376.0	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5
150°	1403.1	1401.8	1400.6	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2
152.5°	1425.0	1423.4	1421.7	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7
155°	1454.9	1452.9	1450.9	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1
157.5°	1481.1	1479.2	1477.2	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8
160°	1495.9	1494.1	1492.3	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7
162.5°	1509.7	1507.5	1505.4	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6
165°	1527.4	1525.7	1523.9	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7
167.5°	1540.9	1538.6	1536.4	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8
170°	1548.1	1545.8	1543.6	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1
172.5°	1553.5	1551.2	1549.0	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4
175°	1558.9	1556.4	1553.9	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3
177.5°	1559.7	1558.0	1556.2	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	12.0	11.8	11.9	11.5	11.1	11.6	11.6	11.6	12.0	12.9	14.3
90°	23.8	22.5	20.5	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1
92.5°	26.8	26.1	25.1	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7
95°	45.2	44.0	42.2	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2
97.5°	59.8	58.8	54.7	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4
100°	66.2	64.2	60.0	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4
102.5°	68.6	66.0	101.6	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9
105°	71.5	68.8	137.0	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5
107.5°	93.4	96.3	178.2	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8
110°	172.1	197.2	269.5	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	406.0	497.3	515.2	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8
115°	579.2	695.1	688.9	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8
117.5°	742.0	770.0	765.6	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2
120°	828.9	825.9	821.3	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7
122.5°	880.8	879.0	874.1	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2
125°	953.8	952.0	947.3	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0
127.5°	1020.4	1017.9	1014.3	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6
130°	1063.0	1060.2	1057.4	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8
132.5°	1104.9	1102.6	1099.8	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8
135°	1164.1	1161.6	1159.4	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5
137.5°	1219.2	1216.8	1214.3	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7
140°	1255.1	1252.8	1250.1	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4
142.5°	1288.2	1286.2	1283.0	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9
145°	1334.6	1332.8	1328.6	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9
147.5°	1375.1	1373.9	1369.7	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2
150°	1399.7	1398.2	1394.2	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1
152.5°	1422.2	1420.7	1416.9	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4
155°	1452.6	1451.1	1448.2	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8
157.5°	1478.1	1476.4	1474.3	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5
160°	1493.2	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7
162.5°	1507.0	1505.2	1504.0	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1
165°	1523.9	1522.1	1521.4	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5
167.5°	1538.1	1536.4	1535.6	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9
170°	1545.3	1543.6	1543.0	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1
172.5°	1550.7	1549.0	1548.5	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5
175°	1556.6	1554.8	1554.3	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4
177.5°	1557.6	1556.2	1555.9	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.4	10.5	10.6	10.7	11.6	12.0	12.0	12.4	13.2	13.0	13.8
90°	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0
92.5°	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4
95°	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4
97.5°	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8
100°	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2
102.5°	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2
105°	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2
107.5°	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6
110°	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1





TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7
115°	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3
117.5°	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9
120°	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9
122.5°	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6
125°	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5
127.5°	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9
130°	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7
132.5°	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2
135°	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6
137.5°	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7
140°	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4
142.5°	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3
145°	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3
147.5°	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5
150°	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2
152.5°	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7
155°	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1
157.5°	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8
160°	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7
162.5°	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6
165°	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7
167.5°	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8
170°	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1
172.5°	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4
175°	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3
177.5°	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	13.5	13.8	13.9	14.0	14.1	14.3	13.9
90°	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331861-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)