

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331610

Luminaire Tested: **S122DIW-S1005D1440U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331610
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9401.6 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47																				
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40																				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35																				
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30																				
4	75	64	57	51	69	60	53	48	51	46	42	42	38	36	34	32	30	26																				
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23																				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20																				
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18																				
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16																				
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15																				
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32195	32195	32195	32195
5°	36094	32405	28716	32405
10°	41361	32139	24851	32139
15°	45757	31550	21956	31550
20°	45060	30917	20015	30917
25°	40631	30077	18786	30077
30°	33575	28732	17889	28732
35°	24471	27325	17251	27325
40°	19545	25665	16895	25665
45°	17080	23745	16413	23745
50°	16053	21886	16093	21886
55°	14798	19997	15662	19997
60°	13563	17990	14996	17990
65°	12355	16191	14346	16191
70°	11216	14436	13388	14436
75°	9944	12477	11859	12477
80°	8554	10330	9549	10330
85°	7669	7669	5687	7669



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.9	2.0
10°-20°	552.1	5.9
20°-30°	801.2	8.5
30°-40°	845.5	9.0
40°-50°	748.6	8.0
50°-60°	597.4	6.4
60°-70°	406.1	4.3
70°-80°	208.2	2.2
80°-90°	57.3	0.6
90°-100°	113.2	1.2
100°-110°	351.6	3.7
110°-120°	601.0	6.4
120°-130°	790.3	8.4
130°-140°	887.0	9.4
140°-150°	869.7	9.3
150°-160°	729.5	7.8
160°-170°	483.8	5.1
170°-180°	169.1	1.8
0°-30°	1543.2	16.4
0°-40°	2388.7	25.4
0°-60°	3734.8	39.7
0°-90°	4406.4	46.9
90°-120°	1065.7	11.3
90°-150°	3612.8	38.4
90°-180°	4995.0	53.1
0°-180°	9401.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1994	1994	1994	1994	1994	
5°	2227	1999	1772	1999	2227	222
15°	2737	1888	1314	1888	2737	755
25°	2281	1688	1054	1688	2281	1031
35°	1242	1386	875	1386	1242	807
45°	748	1040	719	1040	748	588
55°	526	710	556	710	526	471
65°	323	424	376	424	323	322
75°	159	200	190	200	159	170
85°	41	41	31	41	41	47
90°	51	2	51	2	51	24
95°	94	78	94	78	94	104
105°	335	324	335	324	335	352
115°	603	603	603	603	603	596
125°	880	877	880	877	880	785
135°	1149	1135	1149	1135	1149	884
145°	1393	1378	1393	1378	1393	870
155°	1588	1575	1588	1575	1588	731
165°	1716	1714	1716	1714	1716	484
175°	1777	1783	1777	1783	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2086.0	2086.6	2087.8	2078.0	2076.8	2076.8	2068.2	2060.9	2052.3	2040.6	2041.9
5°	2227.0	2235.4	2238.5	2229.3	2215.5	2214.0	2201.0	2179.5	2159.6	2143.5	2132.0
7.5°	2395.3	2398.7	2391.2	2379.1	2368.8	2350.4	2326.2	2302.4	2269.2	2238.7	2216.0
10°	2522.8	2527.4	2514.4	2496.8	2482.2	2460.8	2425.5	2389.5	2345.8	2303.7	2269.9
12.5°	2619.7	2631.0	2614.3	2612.0	2587.1	2557.6	2515.6	2497.4	2435.9	2377.2	2341.1
15°	2737.4	2736.6	2738.2	2723.6	2705.2	2700.6	2656.2	2607.9	2521.3	2486.8	2427.0
17.5°	2703.4	2715.0	2720.4	2720.2	2719.8	2716.9	2702.6	2672.1	2628.7	2572.8	2503.8
20°	2622.5	2637.8	2640.1	2657.7	2667.7	2680.7	2686.1	2677.6	2650.8	2604.1	2544.3
22.5°	2497.4	2501.7	2508.9	2536.3	2557.9	2590.6	2607.6	2635.9	2625.7	2602.8	2552.9
25°	2280.7	2273.0	2299.8	2313.6	2363.4	2415.5	2453.1	2494.5	2531.3	2553.5	2538.9
27.5°	2020.4	2008.9	2049.1	2085.7	2126.2	2182.6	2241.1	2310.2	2367.7	2439.6	2464.3
30°	1800.9	1807.8	1846.1	1885.2	1946.5	2026.2	2092.1	2168.0	2250.0	2330.5	2386.4
32.5°	1564.3	1590.8	1615.0	1674.9	1728.9	1817.8	1914.3	2009.2	2111.5	2203.0	2289.6
35°	1241.5	1272.1	1305.9	1349.5	1425.4	1513.5	1607.8	1735.8	1875.3	2000.2	2102.9
37.5°	1045.0	1040.1	1059.4	1091.0	1152.4	1223.6	1332.1	1458.5	1622.7	1769.5	1914.3
40°	927.3	924.2	938.0	967.1	1013.9	1066.0	1161.0	1272.1	1424.6	1604.0	1776.4
42.5°	846.4	848.2	855.9	876.4	908.4	951.3	1022.5	1117.0	1256.7	1425.6	1610.9
45°	748.0	753.3	761.8	771.7	790.1	825.4	865.2	932.7	1043.0	1184.0	1366.4
47.5°	677.1	677.3	685.9	694.6	705.5	725.4	757.9	800.2	878.1	992.9	1149.7
50°	639.1	633.8	639.9	646.8	658.3	672.1	693.5	733.4	785.5	878.2	1009.3
52.5°	592.5	592.7	598.2	600.8	611.1	624.9	644.5	672.1	719.3	791.8	899.5
55°	525.7	529.5	532.6	537.2	546.4	556.4	571.7	590.1	626.9	681.3	761.0
57.5°	462.9	464.1	467.2	475.9	481.7	490.9	505.5	522.2	546.1	586.4	646.3
60°	420.0	420.0	426.1	429.9	437.6	446.8	458.3	474.4	495.8	528.8	577.1
62.5°	380.7	380.1	382.6	388.8	394.7	403.3	414.7	428.4	448.6	477.9	517.6
65°	323.4	321.9	326.5	328.0	334.1	342.6	351.8	366.3	382.4	403.9	439.1
67.5°	268.2	270.1	272.5	275.4	278.8	287.7	293.8	304.1	317.7	335.5	359.4
70°	237.6	237.6	237.6	239.9	244.5	249.1	255.2	263.6	276.7	292.0	313.4
72.5°	203.2	205.7	208.1	206.8	212.6	215.3	222.7	227.5	239.9	249.7	268.7
75°	159.4	159.4	159.4	163.2	165.5	167.8	172.4	177.0	183.2	195.4	205.4
77.5°	118.9	118.6	119.4	120.3	122.8	125.5	126.9	131.0	136.7	142.4	150.8
80°	92.0	93.5	94.3	95.8	95.8	97.3	98.1	103.5	107.3	111.1	116.5
82.5°	71.1	71.4	71.6	71.9	72.5	73.4	75.4	77.1	78.5	81.7	85.8
85°	41.4	40.6	40.6	42.1	41.4	41.4	42.9	44.4	44.4	45.2	47.5
87.5°	26.2	26.1	26.7	26.0	25.9	26.6	26.7	26.2	27.0	27.7	26.9
90°	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4	52.1	52.8	45.4
92.5°	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2	48.1	47.9	46.2
95°	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5	96.5	96.5	95.8
97.5°	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2	162.2	162.2	160.9
100°	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0	208.0	208.0	207.0
102.5°	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0	257.8	257.5	256.2
105°	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0	332.3	331.7	331.0
107.5°	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9	413.6	413.4	413.4
110°	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9	524.7	525.5	525.8
115°	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4	608.7	609.1	609.7
117.5°	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1	690.9	691.7	693.5
120°	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7	744.7	744.7	747.4
122.5°	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0	801.8	802.6	804.5
125°	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4	885.4	886.4	887.5
127.5°	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4	966.6	967.9	969.1
130°	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8	1021.5	1022.1	1022.8
132.5°	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7	1076.1	1077.6	1077.5
135°	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1	1154.5	1154.8	1154.1
137.5°	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2	1230.5	1230.8	1229.9
140°	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4	1281.4	1281.4	1279.8
142.5°	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8	1327.5	1327.3	1326.1
145°	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2	1397.8	1397.5	1395.5
147.5°	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9	1459.2	1458.4	1457.1
150°	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0	1495.7
152.5°	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6	1534.0
155°	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8	1586.1	1584.4	1583.4
157.5°	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6	1631.3	1629.1	1628.5
160°	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8	1658.8	1656.8	1656.5
162.5°	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5	1683.2	1680.9	1680.6
165°	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3	1714.9	1712.6	1712.6
167.5°	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5	1741.2	1738.8	1738.9
170°	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0	1755.6	1753.3	1753.6
172.5°	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8	1766.5	1764.1	1764.5
175°	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6	1778.3	1775.9	1776.6
177.5°	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8	1783.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2046.2	2041.3	2038.2	2027.2	2017.3	2007.5	2004.5	2005.7	1992.2	1979.3	1973.8
5°	2125.9	2110.5	2096.0	2075.3	2050.8	2023.9	2010.1	1999.4	1972.6	1943.5	1926.6
7.5°	2197.3	2175.4	2147.3	2108.4	2072.7	2030.5	2003.7	1979.9	1940.7	1899.6	1874.5
10°	2240.8	2210.9	2174.9	2127.4	2083.7	2032.4	1996.3	1960.3	1914.3	1865.3	1834.6
12.5°	2278.2	2237.9	2202.5	2141.5	2089.8	2025.6	1982.9	1932.1	1883.7	1825.4	1795.4
15°	2367.3	2292.9	2225.5	2156.5	2092.9	2003.2	1955.7	1887.5	1823.9	1751.9	1717.4
17.5°	2436.1	2352.5	2246.3	2158.7	2084.5	1985.2	1915.4	1833.7	1758.5	1676.2	1629.3
20°	2475.3	2379.5	2265.3	2161.1	2072.2	1958.8	1882.9	1799.4	1711.3	1618.5	1568.0
22.5°	2498.6	2397.9	2285.0	2151.9	2047.7	1937.3	1841.8	1750.3	1661.0	1560.9	1507.9
25°	2506.0	2414.0	2294.5	2144.3	2017.0	1892.1	1777.2	1688.3	1580.2	1486.7	1409.3
27.5°	2469.5	2403.6	2288.6	2129.8	1981.6	1835.6	1707.4	1606.7	1492.7	1391.2	1313.4
30°	2424.7	2386.4	2274.5	2115.1	1953.4	1796.3	1655.3	1541.1	1427.7	1325.0	1245.3
32.5°	2355.5	2347.2	2248.8	2094.3	1923.4	1746.7	1600.8	1485.3	1359.7	1258.8	1182.8
35°	2219.4	2256.1	2194.1	2047.7	1866.8	1676.0	1518.1	1386.3	1256.1	1159.5	1088.2
37.5°	2037.0	2128.3	2112.1	1979.5	1790.5	1599.1	1424.8	1287.0	1162.9	1065.4	995.5
40°	1911.3	2027.8	2044.6	1927.4	1736.6	1539.6	1354.9	1217.7	1096.6	1007.8	937.2
42.5°	1776.4	1912.5	1958.8	1864.8	1677.7	1477.1	1292.4	1150.3	1030.4	944.0	881.5
45°	1550.3	1730.4	1814.0	1760.3	1579.5	1374.1	1184.0	1039.9	931.1	849.9	801.6
47.5°	1339.0	1535.8	1648.1	1629.1	1470.2	1266.8	1078.9	940.6	834.7	769.9	726.7
50°	1189.4	1391.7	1527.3	1533.5	1391.7	1190.1	1001.6	871.3	774.0	713.5	678.2
52.5°	1059.4	1252.5	1400.4	1432.9	1304.0	1110.4	932.3	802.7	717.0	661.4	629.8
55°	889.7	1053.0	1217.0	1276.7	1173.3	989.4	824.6	710.4	629.9	591.6	564.0
57.5°	739.7	875.8	1027.2	1093.3	1029.5	872.1	717.6	618.4	553.2	519.6	498.4
60°	660.6	767.9	902.8	981.7	926.5	786.3	651.4	557.1	503.5	473.6	453.7
62.5°	587.0	682.1	796.1	868.3	838.2	706.0	585.2	502.0	455.7	427.6	413.2
65°	484.3	559.4	647.6	714.2	694.3	593.9	495.1	423.8	387.0	364.8	353.3
67.5°	398.8	453.1	514.2	572.6	556.5	485.4	406.0	350.5	323.1	303.9	297.0
70°	344.9	386.2	440.7	487.4	474.4	416.1	353.3	305.8	282.0	265.9	259.0
72.5°	293.4	327.4	368.9	407.1	398.3	349.9	297.5	261.6	243.4	228.5	222.9
75°	221.5	247.5	272.8	298.1	295.8	258.3	227.6	200.0	185.5	174.0	171.7
77.5°	163.5	178.1	195.3	210.3	206.1	184.7	160.6	144.8	134.1	126.4	125.2
80°	124.9	133.3	145.6	156.3	151.0	141.8	122.6	111.1	103.5	95.8	92.7
82.5°	90.6	99.0	106.4	112.2	108.1	99.5	87.7	79.9	75.3	70.0	68.8
85°	47.5	52.1	55.2	56.7	55.2	49.8	44.4	41.4	37.6	35.3	34.5
87.5°	26.0	24.5	23.0	23.1	20.5	19.7	16.4	13.8	14.0	14.2	13.7
90°	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5	5.5	9.5	13.6
92.5°	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8	29.8	32.7	35.7
95°	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4	81.7	85.1	88.4
97.5°	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2	146.2	149.1	152.1
100°	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5	194.1	196.8	199.5
102.5°	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1	244.3	246.4	248.5
105°	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1	325.1	326.1	327.1
107.5°	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7	408.2	409.7	411.2
110°	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8	461.8	463.8	465.8



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7	519.7	521.7	523.7
115°	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0	605.0	607.0	609.1
117.5°	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1	690.7	693.4	696.1
120°	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	747.4	750.1	752.8
122.5°	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6	799.8	803.0	806.2
125°	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4	880.4	883.4	886.4
127.5°	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1	959.9	963.7	967.6
130°	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5	1009.9	1014.3	1018.6
132.5°	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0	1064.6	1068.1	1071.7
135°	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2	1138.9	1142.6	1146.2
137.5°	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3	1216.3	1219.3	1222.3
140°	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3	1263.3	1266.4	1269.4
142.5°	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6	1311.6	1314.6	1317.6
145°	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9	1380.3	1382.6	1384.9
147.5°	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7	1442.5	1445.3	1448.2
150°	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9	1483.9	1486.0	1488.0
152.5°	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3	1521.3	1523.3	1525.3
155°	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4	1576.4	1577.4	1578.4
157.5°	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3	1624.0	1624.7	1625.4
160°	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3	1653.0	1653.6	1654.3
162.5°	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8	1679.0	1679.1	1679.2
165°	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8	1713.4	1713.1
167.5°	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6	1742.6	1741.6	1740.6
170°	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3	1758.3	1757.3	1756.3
172.5°	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2	1769.2	1768.2	1767.2
175°	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4	1782.4	1781.4	1780.4
177.5°	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9	1788.1	1787.3	1786.5
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1967.7	1964.0	1951.1	1944.4	1933.4	1922.9	1916.2	1919.3	1921.7	1920.5	1918.6
5°	1911.3	1896.7	1874.5	1855.3	1841.5	1816.3	1805.5	1800.2	1795.6	1790.2	1784.8
7.5°	1844.1	1821.2	1789.3	1762.0	1736.2	1704.8	1686.9	1676.2	1665.1	1653.0	1642.3
10°	1796.3	1764.1	1730.4	1692.1	1661.5	1633.1	1607.8	1590.9	1575.6	1561.1	1550.3
12.5°	1746.1	1709.0	1667.3	1614.9	1581.1	1540.5	1536.7	1507.0	1483.0	1474.0	1461.4
15°	1666.0	1613.9	1561.1	1499.0	1472.2	1435.4	1412.4	1389.4	1368.7	1354.1	1350.3
17.5°	1575.2	1507.7	1455.1	1410.5	1366.6	1328.9	1307.7	1289.3	1272.3	1252.8	1250.2
20°	1505.9	1447.6	1390.2	1351.1	1305.9	1267.5	1241.5	1223.1	1208.5	1197.0	1187.1
22.5°	1440.3	1376.5	1323.9	1281.2	1236.6	1205.6	1185.1	1167.3	1155.2	1142.5	1133.1
25°	1335.0	1285.2	1227.7	1179.4	1142.6	1122.7	1105.8	1090.5	1082.9	1074.4	1063.7
27.5°	1242.9	1187.5	1133.7	1096.3	1064.0	1046.4	1034.4	1024.0	1016.8	1011.9	1005.8
30°	1177.9	1121.9	1079.8	1043.0	1016.2	998.6	990.9	984.8	976.3	973.3	970.2
32.5°	1115.3	1064.9	1028.9	997.0	971.4	959.9	952.9	947.4	940.8	937.7	931.6
35°	1026.9	984.8	949.5	931.9	911.2	901.2	895.9	888.2	882.1	879.0	878.2
37.5°	943.7	907.1	883.9	861.2	852.5	846.4	839.0	833.8	832.0	831.5	830.7
40°	889.7	859.8	839.2	820.8	816.9	807.7	801.6	797.0	797.0	797.8	797.0
42.5°	840.7	813.9	795.6	779.7	775.2	769.7	763.6	763.3	764.5	767.1	764.5
45°	766.4	747.2	734.2	726.5	718.1	712.7	711.9	714.2	715.0	715.8	718.1
47.5°	698.0	685.3	673.5	665.0	661.4	660.4	659.5	663.5	667.2	668.6	672.1
50°	657.5	643.0	633.0	627.6	624.6	623.0	624.6	629.2	632.2	636.1	638.4
52.5°	612.2	601.9	595.0	590.9	589.6	590.6	590.9	596.1	601.0	602.4	603.4
55°	549.5	541.8	540.3	533.4	536.4	535.7	539.5	542.6	547.2	551.8	552.5
57.5°	486.9	480.8	476.7	477.3	478.2	481.6	484.8	490.2	495.1	500.0	500.4
60°	445.3	442.2	439.9	439.9	441.4	446.0	449.8	455.2	458.3	461.3	463.6
62.5°	407.2	404.2	401.9	403.1	407.1	409.8	414.3	417.2	420.3	423.3	424.4
65°	347.2	345.6	347.9	349.5	350.2	354.1	359.4	361.7	364.8	366.3	371.7
67.5°	291.8	292.1	291.8	294.0	298.4	299.3	304.4	309.8	310.4	313.3	316.8
70°	254.4	256.0	257.5	259.0	262.9	264.4	268.2	270.5	273.6	275.9	278.2
72.5°	220.1	220.4	221.9	221.6	224.8	228.2	231.4	233.7	236.8	239.7	242.0
75°	169.4	169.4	170.9	171.7	175.5	179.3	178.6	180.1	183.2	186.2	187.8
77.5°	123.7	122.0	123.7	124.5	125.7	128.9	129.5	131.7	135.2	134.1	135.8
80°	94.3	92.0	94.3	95.0	95.0	98.9	98.9	100.4	102.7	100.4	102.7
82.5°	67.3	66.2	67.9	68.1	69.3	69.4	70.7	71.0	73.3	72.2	73.3
85°	33.7	33.0	33.7	33.0	33.7	34.5	34.5	33.7	33.7	35.3	33.0
87.5°	13.9	14.5	15.3	16.8	17.7	18.5	17.8	17.6	17.5	16.1	16.1
90°	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4	50.8	50.1	49.9
92.5°	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2	48.3	48.5	48.6
95°	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5	96.5	96.5	96.1
97.5°	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2	162.2	162.2	162.2
100°	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0	208.0	208.0	207.9
102.5°	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0	258.3	258.6	258.5
105°	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0	333.7	334.3	334.7
107.5°	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9	414.2	414.4	413.8
110°	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.3



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9	523.1	522.3	521.5
115°	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4	608.0	607.7	607.0
117.5°	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1	689.3	688.5	687.5
120°	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7	744.7	744.7	744.2
122.5°	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0	800.2	799.4	798.6
125°	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4	883.4	882.4	881.8
127.5°	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4	964.2	963.0	961.9
130°	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8	1020.1	1019.4	1018.4
132.5°	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7	1073.2	1071.7	1070.4
135°	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1	1153.8	1153.5	1152.8
137.5°	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2	1230.0	1229.7	1228.9
140°	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4	1281.4	1281.4	1280.8
142.5°	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8	1328.1	1328.3	1327.8
145°	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2	1398.5	1398.8	1398.3
147.5°	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9	1460.6	1461.4	1461.1
150°	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0
152.5°	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7
155°	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8	1589.5	1591.1	1591.5
157.5°	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6	1635.9	1638.2	1638.5
160°	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8	1662.8	1664.8	1665.2
162.5°	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5	1687.8	1690.0	1690.4
165°	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3	1719.6	1722.0	1722.3
167.5°	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5	1745.9	1748.2	1748.5
170°	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0	1760.3	1762.7	1762.8
172.5°	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8	1771.2	1773.5	1773.7
175°	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6	1782.9	1785.3	1785.5
177.5°	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1912.5	1911.3	1911.3	1905.8	1911.3	1911.3	1912.5	1918.6	1920.5	1921.7	1919.3
5°	1774.1	1771.8	1768.0	1771.8	1768.0	1771.8	1774.1	1784.8	1790.2	1795.6	1800.2
7.5°	1637.2	1628.0	1626.7	1617.6	1626.7	1628.0	1637.2	1642.3	1653.0	1665.1	1676.2
10°	1537.3	1531.2	1530.4	1515.8	1530.4	1531.2	1537.3	1550.3	1561.1	1575.6	1590.9
12.5°	1461.3	1446.6	1449.5	1441.0	1449.5	1446.6	1461.3	1461.4	1474.0	1483.0	1507.0
15°	1329.6	1329.6	1326.6	1313.5	1326.6	1329.6	1329.6	1350.3	1354.1	1368.7	1389.4
17.5°	1235.1	1233.5	1226.2	1229.8	1226.2	1233.5	1235.1	1250.2	1252.8	1272.3	1289.3
20°	1178.6	1174.1	1164.9	1164.9	1164.9	1174.1	1178.6	1187.1	1197.0	1208.5	1223.1
22.5°	1125.3	1125.0	1115.2	1118.3	1115.2	1125.0	1125.3	1133.1	1142.5	1155.2	1167.3
25°	1062.9	1056.8	1052.2	1054.5	1052.2	1056.8	1062.9	1063.7	1074.4	1082.9	1090.5
27.5°	1003.8	1000.4	1000.1	993.8	1000.1	1000.4	1003.8	1005.8	1011.9	1016.8	1024.0
30°	969.4	961.8	963.3	959.5	963.3	961.8	969.4	970.2	973.3	976.3	984.8
32.5°	930.2	927.4	925.9	922.7	925.9	927.4	930.2	931.6	937.7	940.8	947.4
35°	876.7	877.5	873.6	875.2	873.6	877.5	876.7	878.2	879.0	882.1	888.2
37.5°	830.0	832.4	830.6	831.0	830.6	832.4	830.0	830.7	831.5	832.0	833.8
40°	799.3	799.3	799.3	801.6	799.3	799.3	799.3	797.0	797.8	797.0	797.0
42.5°	769.9	768.7	767.4	767.3	767.4	768.7	769.9	764.5	767.1	764.5	763.3
45°	719.6	721.9	722.7	718.8	722.7	721.9	719.6	718.1	715.8	715.0	714.2
47.5°	674.1	674.4	674.1	677.5	674.1	674.4	674.1	672.1	668.6	667.2	663.5
50°	642.2	640.7	642.2	640.7	642.2	640.7	642.2	638.4	636.1	632.2	629.2
52.5°	608.5	608.8	607.9	607.6	607.9	608.8	608.5	603.4	602.4	601.0	596.1
55°	555.6	557.1	556.4	556.4	556.4	557.1	555.6	552.5	551.8	547.2	542.6
57.5°	500.9	502.3	503.3	500.0	503.3	502.3	500.9	500.4	500.0	495.1	490.2
60°	462.9	466.7	465.9	464.4	465.9	466.7	462.9	463.6	461.3	458.3	455.2
62.5°	427.9	429.3	429.2	428.9	429.2	429.3	427.9	424.4	423.3	420.3	417.2
65°	374.0	375.5	373.2	375.5	373.2	375.5	374.0	371.7	366.3	364.8	361.7
67.5°	315.9	316.4	318.0	319.1	318.0	316.4	315.9	316.8	313.3	310.4	309.8
70°	279.7	279.0	281.3	283.6	281.3	279.0	279.7	278.2	275.9	273.6	270.5
72.5°	241.7	243.4	242.6	244.3	242.6	243.4	241.7	242.0	239.7	236.8	233.7
75°	186.2	188.5	187.8	190.1	187.8	188.5	186.2	187.8	186.2	183.2	180.1
77.5°	134.6	134.9	134.6	135.8	134.6	134.9	134.6	135.8	134.1	135.2	131.7
80°	102.7	101.2	99.6	102.7	99.6	101.2	102.7	102.7	100.4	102.7	100.4
82.5°	71.4	72.3	70.8	70.8	70.8	72.3	71.4	73.3	72.2	73.3	71.0
85°	33.0	32.2	30.7	30.7	30.7	32.2	33.0	33.0	35.3	33.7	33.7
87.5°	16.2	15.6	15.7	15.2	15.7	15.6	16.2	16.1	16.1	17.5	17.6
90°	50.3	50.6	50.9	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4
92.5°	48.6	48.7	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2
95°	95.5	94.8	94.1	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5
97.5°	162.1	162.0	162.0	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2
100°	207.5	207.2	206.9	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0
102.5°	258.2	257.9	257.5	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0
105°	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0
107.5°	412.3	410.7	409.2	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9
110°	467.3	466.3	465.3	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.8	520.1	519.3	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9
115°	606.0	605.0	604.0	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4
117.5°	686.5	685.5	684.5	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1
120°	743.2	742.2	741.2	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7
122.5°	797.9	797.2	796.4	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0
125°	881.4	881.1	880.8	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4
127.5°	960.8	959.7	958.7	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4
130°	1017.1	1015.8	1014.4	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8
132.5°	1069.4	1068.3	1067.2	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7
135°	1151.8	1150.8	1149.8	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1
137.5°	1227.6	1226.2	1224.9	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2
140°	1279.4	1278.1	1276.7	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4
142.5°	1326.5	1325.1	1323.8	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8
145°	1397.0	1395.7	1394.3	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2
147.5°	1459.8	1458.5	1457.3	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9
150°	1500.0	1499.0	1498.0	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0
152.5°	1539.4	1538.1	1536.9	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1
155°	1590.5	1589.5	1588.5	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8
157.5°	1636.9	1635.3	1633.7	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6
160°	1663.8	1662.5	1661.2	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8
162.5°	1688.8	1687.2	1685.6	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5
165°	1720.6	1719.0	1717.3	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3
167.5°	1746.8	1745.0	1743.3	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5
170°	1760.8	1758.8	1756.8	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0
172.5°	1771.7	1769.7	1767.7	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8
175°	1783.4	1781.4	1779.4	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6
177.5°	1787.7	1786.1	1784.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1916.2	1922.9	1933.4	1944.4	1951.1	1964.0	1967.7	1973.8	1979.3	1992.2	2005.7
5°	1805.5	1816.3	1841.5	1855.3	1874.5	1896.7	1911.3	1926.6	1943.5	1972.6	1999.4
7.5°	1686.9	1704.8	1736.2	1762.0	1789.3	1821.2	1844.1	1874.5	1899.6	1940.7	1979.9
10°	1607.8	1633.1	1661.5	1692.1	1730.4	1764.1	1796.3	1834.6	1865.3	1914.3	1960.3
12.5°	1536.7	1540.5	1581.1	1614.9	1667.3	1709.0	1746.1	1795.4	1825.4	1883.7	1932.1
15°	1412.4	1435.4	1472.2	1499.0	1561.1	1613.9	1666.0	1717.4	1751.9	1823.9	1887.5
17.5°	1307.7	1328.9	1366.6	1410.5	1455.1	1507.7	1575.2	1629.3	1676.2	1758.5	1833.7
20°	1241.5	1267.5	1305.9	1351.1	1390.2	1447.6	1505.9	1568.0	1618.5	1711.3	1799.4
22.5°	1185.1	1205.6	1236.6	1281.2	1323.9	1376.5	1440.3	1507.9	1560.9	1661.0	1750.3
25°	1105.8	1122.7	1142.6	1179.4	1227.7	1285.2	1335.0	1409.3	1486.7	1580.2	1688.3
27.5°	1034.4	1046.4	1064.0	1096.3	1133.7	1187.5	1242.9	1313.4	1391.2	1492.7	1606.7
30°	990.9	998.6	1016.2	1043.0	1079.8	1121.9	1177.9	1245.3	1325.0	1427.7	1541.1
32.5°	952.9	959.9	971.4	997.0	1028.9	1064.9	1115.3	1182.8	1258.8	1359.7	1485.3
35°	895.9	901.2	911.2	931.9	949.5	984.8	1026.9	1088.2	1159.5	1256.1	1386.3
37.5°	839.0	846.4	852.5	861.2	883.9	907.1	943.7	995.5	1065.4	1162.9	1287.0
40°	801.6	807.7	816.9	820.8	839.2	859.8	889.7	937.2	1007.8	1096.6	1217.7
42.5°	763.6	769.7	775.2	779.7	795.6	813.9	840.7	881.5	944.0	1030.4	1150.3
45°	711.9	712.7	718.1	726.5	734.2	747.2	766.4	801.6	849.9	931.1	1039.9
47.5°	659.5	660.4	661.4	665.0	673.5	685.3	698.0	726.7	769.9	834.7	940.6
50°	624.6	623.0	624.6	627.6	633.0	643.0	657.5	678.2	713.5	774.0	871.3
52.5°	590.9	590.6	589.6	590.9	595.0	601.9	612.2	629.8	661.4	717.0	802.7
55°	539.5	535.7	536.4	533.4	540.3	541.8	549.5	564.0	591.6	629.9	710.4
57.5°	484.8	481.6	478.2	477.3	476.7	480.8	486.9	498.4	519.6	553.2	618.4
60°	449.8	446.0	441.4	439.9	439.9	442.2	445.3	453.7	473.6	503.5	557.1
62.5°	414.3	409.8	407.1	403.1	401.9	404.2	407.2	413.2	427.6	455.7	502.0
65°	359.4	354.1	350.2	349.5	347.9	345.6	347.2	353.3	364.8	387.0	423.8
67.5°	304.4	299.3	298.4	294.0	291.8	292.1	291.8	297.0	303.9	323.1	350.5
70°	268.2	264.4	262.9	259.0	257.5	256.0	254.4	259.0	265.9	282.0	305.8
72.5°	231.4	228.2	224.8	221.6	221.9	220.4	220.1	222.9	228.5	243.4	261.6
75°	178.6	179.3	175.5	171.7	170.9	169.4	169.4	171.7	174.0	185.5	200.0
77.5°	129.5	128.9	125.7	124.5	123.7	122.0	123.7	125.2	126.4	134.1	144.8
80°	98.9	98.9	95.0	95.0	94.3	92.0	94.3	92.7	95.8	103.5	111.1
82.5°	70.7	69.4	69.3	68.1	67.9	66.2	67.3	68.8	70.0	75.3	79.9
85°	34.5	34.5	33.7	33.0	33.7	33.0	33.7	34.5	35.3	37.6	41.4
87.5°	17.8	18.5	17.7	16.8	15.3	14.5	13.9	13.7	14.2	14.0	13.8
90°	52.1	52.8	45.4	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5
92.5°	48.1	47.9	46.2	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8
95°	96.5	96.5	95.8	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4
97.5°	162.2	162.2	160.9	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2
100°	208.0	208.0	207.0	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5
102.5°	257.8	257.5	256.2	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1
105°	332.3	331.7	331.0	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1
107.5°	413.6	413.4	413.4	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7
110°	468.9	468.9	468.9	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	524.7	525.5	525.8	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7
115°	608.7	609.1	609.7	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0
117.5°	690.9	691.7	693.5	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1
120°	744.7	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7
122.5°	801.8	802.6	804.5	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6
125°	885.4	886.4	887.5	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4
127.5°	966.6	967.9	969.1	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1
130°	1021.5	1022.1	1022.8	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5
132.5°	1076.1	1077.6	1077.5	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0
135°	1154.5	1154.8	1154.1	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2
137.5°	1230.5	1230.8	1229.9	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3
140°	1281.4	1281.4	1279.8	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3
142.5°	1327.5	1327.3	1326.1	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6
145°	1397.8	1397.5	1395.5	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9
147.5°	1459.2	1458.4	1457.1	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7
150°	1498.0	1497.0	1495.7	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9
152.5°	1536.9	1535.6	1534.0	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3
155°	1586.1	1584.4	1583.4	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4
157.5°	1631.3	1629.1	1628.5	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3
160°	1658.8	1656.8	1656.5	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3
162.5°	1683.2	1680.9	1680.6	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8
165°	1714.9	1712.6	1712.6	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1
167.5°	1741.2	1738.8	1738.9	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6
170°	1755.6	1753.3	1753.6	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3
172.5°	1766.5	1764.1	1764.5	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2
175°	1778.3	1775.9	1776.6	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4
177.5°	1784.4	1782.8	1783.4	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2004.5	2007.5	2017.3	2027.2	2038.2	2041.3	2046.2	2041.9	2040.6	2052.3	2060.9
5°	2010.1	2023.9	2050.8	2075.3	2096.0	2110.5	2125.9	2132.0	2143.5	2159.6	2179.5
7.5°	2003.7	2030.5	2072.7	2108.4	2147.3	2175.4	2197.3	2216.0	2238.7	2269.2	2302.4
10°	1996.3	2032.4	2083.7	2127.4	2174.9	2210.9	2240.8	2269.9	2303.7	2345.8	2389.5
12.5°	1982.9	2025.6	2089.8	2141.5	2202.5	2237.9	2278.2	2341.1	2377.2	2435.9	2497.4
15°	1955.7	2003.2	2092.9	2156.5	2225.5	2292.9	2367.3	2427.0	2486.8	2521.3	2607.9
17.5°	1915.4	1985.2	2084.5	2158.7	2246.3	2352.5	2436.1	2503.8	2572.8	2628.7	2672.1
20°	1882.9	1958.8	2072.2	2161.1	2265.3	2379.5	2475.3	2544.3	2604.1	2650.8	2677.6
22.5°	1841.8	1937.3	2047.7	2151.9	2285.0	2397.9	2498.6	2552.9	2602.8	2625.7	2635.9
25°	1777.2	1892.1	2017.0	2144.3	2294.5	2414.0	2506.0	2538.9	2553.5	2531.3	2494.5
27.5°	1707.4	1835.6	1981.6	2129.8	2288.6	2403.6	2469.5	2464.3	2439.6	2367.7	2310.2
30°	1655.3	1796.3	1953.4	2115.1	2274.5	2386.4	2424.7	2386.4	2330.5	2250.0	2168.0
32.5°	1600.8	1746.7	1923.4	2094.3	2248.8	2347.2	2355.5	2289.6	2203.0	2111.5	2009.2
35°	1518.1	1676.0	1866.8	2047.7	2194.1	2256.1	2219.4	2102.9	2000.2	1875.3	1735.8
37.5°	1424.8	1599.1	1790.5	1979.5	2112.1	2128.3	2037.0	1914.3	1769.5	1622.7	1458.5
40°	1354.9	1539.6	1736.6	1927.4	2044.6	2027.8	1911.3	1776.4	1604.0	1424.6	1272.1
42.5°	1292.4	1477.1	1677.7	1864.8	1958.8	1912.5	1776.4	1610.9	1425.6	1256.7	1117.0
45°	1184.0	1374.1	1579.5	1760.3	1814.0	1730.4	1550.3	1366.4	1184.0	1043.0	932.7
47.5°	1078.9	1266.8	1470.2	1629.1	1648.1	1535.8	1339.0	1149.7	992.9	878.1	800.2
50°	1001.6	1190.1	1391.7	1533.5	1527.3	1391.7	1189.4	1009.3	878.2	785.5	733.4
52.5°	932.3	1110.4	1304.0	1432.9	1400.4	1252.5	1059.4	899.5	791.8	719.3	672.1
55°	824.6	989.4	1173.3	1276.7	1217.0	1053.0	889.7	761.0	681.3	626.9	590.1
57.5°	717.6	872.1	1029.5	1093.3	1027.2	875.8	739.7	646.3	586.4	546.1	522.2
60°	651.4	786.3	926.5	981.7	902.8	767.9	660.6	577.1	528.8	495.8	474.4
62.5°	585.2	706.0	838.2	868.3	796.1	682.1	587.0	517.6	477.9	448.6	428.4
65°	495.1	593.9	694.3	714.2	647.6	559.4	484.3	439.1	403.9	382.4	366.3
67.5°	406.0	485.4	556.5	572.6	514.2	453.1	398.8	359.4	335.5	317.7	304.1
70°	353.3	416.1	474.4	487.4	440.7	386.2	344.9	313.4	292.0	276.7	263.6
72.5°	297.5	349.9	398.3	407.1	368.9	327.4	293.4	268.7	249.7	239.9	227.5
75°	227.6	258.3	295.8	298.1	272.8	247.5	221.5	205.4	195.4	183.2	177.0
77.5°	160.6	184.7	206.1	210.3	195.3	178.1	163.5	150.8	142.4	136.7	131.0
80°	122.6	141.8	151.0	156.3	145.6	133.3	124.9	116.5	111.1	107.3	103.5
82.5°	87.7	99.5	108.1	112.2	106.4	99.0	90.6	85.8	81.7	78.5	77.1
85°	44.4	49.8	55.2	56.7	55.2	52.1	47.5	47.5	45.2	44.4	44.4
87.5°	16.4	19.7	20.5	23.1	23.0	24.5	26.0	26.9	27.7	27.0	26.2
90°	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4
92.5°	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2
95°	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5
97.5°	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2
100°	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0
102.5°	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0
105°	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0
107.5°	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9
110°	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9
115°	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4
117.5°	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1
120°	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7
122.5°	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0
125°	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4
127.5°	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4
130°	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8
132.5°	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7
135°	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1
137.5°	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2
140°	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4
142.5°	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8
145°	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2
147.5°	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9
150°	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0
152.5°	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1
155°	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8
157.5°	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6
160°	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8
162.5°	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5
165°	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3
167.5°	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5
170°	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0
172.5°	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8
175°	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6
177.5°	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2068.2	2076.8	2076.8	2078.0	2087.8	2086.6	2086.0
5°	2201.0	2214.0	2215.5	2229.3	2238.5	2235.4	2227.0
7.5°	2326.2	2350.4	2368.8	2379.1	2391.2	2398.7	2395.3
10°	2425.5	2460.8	2482.2	2496.8	2514.4	2527.4	2522.8
12.5°	2515.6	2557.6	2587.1	2612.0	2614.3	2631.0	2619.7
15°	2656.2	2700.6	2705.2	2723.6	2738.2	2736.6	2737.4
17.5°	2702.6	2716.9	2719.8	2720.2	2720.4	2715.0	2703.4
20°	2686.1	2680.7	2667.7	2657.7	2640.1	2637.8	2622.5
22.5°	2607.6	2590.6	2557.9	2536.3	2508.9	2501.7	2497.4
25°	2453.1	2415.5	2363.4	2313.6	2299.8	2273.0	2280.7
27.5°	2241.1	2182.6	2126.2	2085.7	2049.1	2008.9	2020.4
30°	2092.1	2026.2	1946.5	1885.2	1846.1	1807.8	1800.9
32.5°	1914.3	1817.8	1728.9	1674.9	1615.0	1590.8	1564.3
35°	1607.8	1513.5	1425.4	1349.5	1305.9	1272.1	1241.5
37.5°	1332.1	1223.6	1152.4	1091.0	1059.4	1040.1	1045.0
40°	1161.0	1066.0	1013.9	967.1	938.0	924.2	927.3
42.5°	1022.5	951.3	908.4	876.4	855.9	848.2	846.4
45°	865.2	825.4	790.1	771.7	761.8	753.3	748.0
47.5°	757.9	725.4	705.5	694.6	685.9	677.3	677.1
50°	693.5	672.1	658.3	646.8	639.9	633.8	639.1
52.5°	644.5	624.9	611.1	600.8	598.2	592.7	592.5
55°	571.7	556.4	546.4	537.2	532.6	529.5	525.7
57.5°	505.5	490.9	481.7	475.9	467.2	464.1	462.9
60°	458.3	446.8	437.6	429.9	426.1	420.0	420.0
62.5°	414.7	403.3	394.7	388.8	382.6	380.1	380.7
65°	351.8	342.6	334.1	328.0	326.5	321.9	323.4
67.5°	293.8	287.7	278.8	275.4	272.5	270.1	268.2
70°	255.2	249.1	244.5	239.9	237.6	237.6	237.6
72.5°	222.7	215.3	212.6	206.8	208.1	205.7	203.2
75°	172.4	167.8	165.5	163.2	159.4	159.4	159.4
77.5°	126.9	125.5	122.8	120.3	119.4	118.6	118.9
80°	98.1	97.3	95.8	95.8	94.3	93.5	92.0
82.5°	75.4	73.4	72.5	71.9	71.6	71.4	71.1
85°	42.9	41.4	41.4	42.1	40.6	40.6	41.4
87.5°	26.7	26.6	25.9	26.0	26.7	26.1	26.2
90°	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331610

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)