

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331613

Luminaire Tested: **S122DIW-S1005D1440U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331613
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9819.8 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	43	42	41	35				
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	37	36	34	29				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18				
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13				
9	49	37	30	25	45	34	27	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	1.5
10°-20°	421.7	4.3
20°-30°	619.8	6.3
30°-40°	720.0	7.3
40°-50°	719.2	7.3
50°-60°	627.2	6.4
60°-70°	463.8	4.7
70°-80°	262.7	2.7
80°-90°	75.5	0.8
90°-100°	65.6	0.7
100°-110°	240.4	2.4
110°-120°	642.7	6.5
120°-130°	1060.9	10.8
130°-140°	1128.3	11.5
140°-150°	1048.7	10.7
150°-160°	843.1	8.6
160°-170°	543.3	5.5
170°-180°	187.0	1.9
0°-30°	1191.4	12.1
0°-40°	1911.4	19.5
0°-60°	3257.9	33.2
0°-90°	4059.8	41.3
90°-120°	948.7	9.7
90°-150°	4186.6	42.6
90°-180°	5760.0	58.7
0°-180°	9819.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	17	28	35	38	7
95°	92	49	56	62	61	113
105°	432	451	87	102	108	462
115°	818	843	878	250	117	805
125°	1156	1175	1202	1211	1216	1031
135°	1431	1453	1466	1480	1478	1105
145°	1660	1660	1682	1692	1685	1038
155°	1828	1816	1832	1839	1829	842
165°	1926	1918	1921	1930	1921	544
175°	1970	1961	1963	1971	1958	187
180°	1966	1966	1966	1966	1966	



TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.4	22.5	22.7	22.8	23.0	23.0	23.0	22.9	22.9	22.9	22.4
90°	1.4	4.9	8.4	11.9	15.3	18.3	20.9	23.4	25.9	28.4	30.0
92.5°	28.7	28.4	28.1	27.8	27.5	27.9	29.2	30.5	31.7	33.0	33.8
95°	92.4	82.0	71.6	61.2	50.7	46.6	48.8	51.0	53.3	55.5	57.0
97.5°	183.5	154.1	124.7	95.3	65.9	53.8	58.9	64.0	69.1	74.2	75.5
100°	251.7	208.4	165.1	121.8	78.5	59.6	64.9	70.3	75.7	81.1	83.6
102.5°	326.8	317.7	308.5	299.3	290.2	263.1	218.2	173.2	128.3	83.3	86.6
105°	432.4	441.8	451.3	460.8	470.3	431.9	345.6	259.3	173.0	86.8	90.2
107.5°	552.7	560.3	568.0	575.6	583.3	535.4	431.9	328.4	224.9	121.5	117.9
110°	630.1	636.7	643.3	650.0	656.6	614.2	522.9	431.6	340.2	248.9	217.3



TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	702.9	708.7	714.6	720.5	726.4	718.0	695.5	672.9	650.3	627.8	512.5
115°	817.8	823.2	828.5	833.9	839.3	845.9	853.8	861.7	869.6	877.5	731.2
117.5°	920.5	926.5	932.5	938.5	944.5	950.2	955.6	961.1	966.5	972.0	936.6
120°	995.6	1000.3	1005.0	1009.8	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3
122.5°	1059.3	1064.3	1069.3	1074.3	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9
125°	1156.3	1160.4	1164.5	1168.6	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0
127.5°	1244.2	1248.7	1253.3	1257.8	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1
130°	1299.9	1305.0	1310.0	1315.1	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8
132.5°	1356.8	1361.1	1365.4	1369.7	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8
135°	1430.8	1435.8	1440.9	1445.9	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5
137.5°	1505.6	1509.1	1512.7	1516.2	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1
140°	1554.5	1557.0	1559.6	1562.1	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4
142.5°	1595.5	1597.7	1600.0	1602.3	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2
145°	1659.8	1659.4	1659.1	1658.8	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7
147.5°	1715.8	1714.6	1713.4	1712.2	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9
150°	1752.2	1750.0	1747.8	1745.6	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9
152.5°	1782.9	1780.5	1778.0	1775.5	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3
155°	1827.6	1824.7	1821.9	1819.0	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7
157.5°	1862.6	1860.2	1857.8	1855.4	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9
160°	1883.0	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9
162.5°	1901.2	1899.4	1897.5	1895.6	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3
165°	1925.7	1923.8	1921.9	1920.0	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7
167.5°	1943.9	1942.0	1940.1	1938.2	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6
170°	1954.2	1952.3	1950.4	1948.5	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7
172.5°	1961.0	1959.1	1957.2	1955.3	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5
175°	1969.8	1967.6	1965.4	1963.2	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9
177.5°	1971.2	1969.5	1967.7	1965.9	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	21.9	21.3	20.8	20.5	20.4	20.2	20.1	19.9
90°	31.6	33.2	34.8	35.9	36.5	37.1	37.8	38.4
92.5°	34.6	35.5	36.3	36.9	37.3	37.6	38.0	38.4
95°	58.6	60.2	61.8	62.4	62.1	61.8	61.5	61.2
97.5°	76.8	78.0	79.3	80.1	80.5	80.9	81.3	81.6
100°	86.1	88.7	91.2	92.8	93.4	94.0	94.7	95.3
102.5°	89.9	93.2	96.5	98.6	99.5	100.3	101.2	102.1
105°	93.7	97.2	100.7	103.0	104.3	105.6	106.8	108.1
107.5°	114.4	110.8	107.3	106.2	107.4	108.7	110.0	111.2
110°	185.7	154.1	122.5	107.3	108.6	109.8	111.1	112.4



TEST NUMBER: P331613

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	397.2	281.9	166.6	109.4	110.5	111.5	112.5	113.5
115°	584.9	438.5	292.2	207.6	184.9	162.1	139.4	116.6
117.5°	901.2	865.8	830.4	775.3	700.5	625.7	550.9	476.2
120°	1050.1	1053.9	1057.7	1038.2	995.6	952.9	910.2	867.6
122.5°	1114.2	1116.5	1118.7	1115.7	1107.4	1099.2	1090.9	1082.6
125°	1206.2	1208.4	1210.6	1212.2	1213.2	1214.1	1215.1	1216.0
127.5°	1291.3	1294.5	1297.7	1299.5	1299.6	1299.8	1300.0	1300.2
130°	1345.3	1348.8	1352.2	1353.8	1353.5	1353.2	1352.9	1352.5
132.5°	1397.7	1400.7	1403.7	1405.0	1404.7	1404.4	1404.1	1403.7
135°	1472.6	1475.8	1479.0	1480.2	1479.6	1479.0	1478.3	1477.7
137.5°	1542.2	1545.3	1548.4	1549.4	1548.3	1547.3	1546.2	1545.1
140°	1587.2	1590.1	1592.9	1593.5	1592.0	1590.4	1588.8	1587.2
142.5°	1628.8	1631.4	1634.0	1634.5	1632.9	1631.3	1629.8	1628.2
145°	1686.9	1689.1	1691.4	1691.7	1690.1	1688.5	1686.9	1685.4
147.5°	1737.6	1739.2	1740.9	1741.0	1739.7	1738.4	1737.0	1735.7
150°	1768.8	1770.7	1772.6	1772.7	1771.2	1769.6	1768.0	1766.4
152.5°	1797.2	1799.1	1801.0	1800.9	1798.8	1796.8	1794.7	1792.6
155°	1835.6	1837.5	1839.4	1839.1	1836.6	1834.1	1831.5	1829.0
157.5°	1868.0	1870.1	1872.3	1872.1	1869.7	1867.2	1864.7	1862.3
160°	1886.8	1888.7	1890.6	1890.5	1888.3	1886.0	1883.8	1881.6
162.5°	1904.4	1906.6	1908.7	1908.4	1905.7	1903.0	1900.3	1897.6
165°	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4
167.5°	1943.8	1946.0	1948.2	1947.9	1945.1	1942.2	1939.4	1936.5
170°	1952.9	1955.1	1957.3	1957.0	1954.2	1951.3	1948.5	1945.6
172.5°	1959.7	1961.9	1964.1	1963.8	1961.0	1958.1	1955.3	1952.4
175°	1967.1	1969.3	1971.5	1971.1	1967.9	1964.7	1961.6	1958.4
177.5°	1967.9	1969.7	1971.5	1971.2	1968.9	1966.7	1964.4	1962.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5

(END OF REPORT)