

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331767-927

Luminaire Tested: **S122RDIW-S290D435U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331767-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D435U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2190.3 lumens  
Efficiency: N/A  
Efficacy: 95.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	18	16	14	12				
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.2	1.7
10°-20°	102.2	4.7
20°-30°	143.5	6.6
30°-40°	156.5	7.1
40°-50°	143.9	6.6
50°-60°	113.0	5.2
60°-70°	73.7	3.4
70°-80°	38.0	1.7
80°-90°	11.0	0.5
90°-100°	15.6	0.7
100°-110°	57.2	2.6
110°-120°	153.0	7.0
120°-130°	252.6	11.5
130°-140°	268.6	12.3
140°-150°	249.7	11.4
150°-160°	200.7	9.2
160°-170°	129.3	5.9
170°-180°	44.5	2.0
0°-30°	282.9	12.9
0°-40°	439.4	20.1
0°-60°	696.4	31.8
0°-90°	819.0	37.4
90°-120°	225.9	10.3
90°-150°	996.7	45.5
90°-180°	1371.0	62.6
0°-180°	2190.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	0	4	7	8	9	2
95°	22	12	13	15	15	27
105°	103	107	21	24	26	110
115°	195	201	209	60	28	192
125°	275	280	286	288	290	245
135°	341	346	349	352	352	263
145°	395	395	400	403	401	247
155°	435	432	436	438	436	200
165°	458	457	457	460	457	129
175°	469	467	467	469	466	45
180°	468	468	468	468	468	



TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.7	4.4	4.0	3.6	3.3	3.2	3.3	3.4	3.6	3.6	3.6
90°	0.3	1.2	2.0	2.9	3.6	4.4	5.0	5.5	6.2	6.7	7.1
92.5°	6.8	6.7	6.7	6.6	6.6	6.7	7.0	7.3	7.5	7.8	8.1
95°	22.0	19.5	17.0	14.6	12.0	11.1	11.6	12.1	12.7	13.2	13.5
97.5°	43.6	36.7	29.7	22.7	15.7	12.8	14.0	15.2	16.5	17.7	18.0
100°	60.0	49.6	39.3	29.0	18.7	14.2	15.4	16.7	18.0	19.3	19.9
102.5°	77.8	75.7	73.4	71.3	69.1	62.7	52.0	41.3	30.6	19.8	20.6
105°	102.9	105.2	107.4	109.7	111.9	102.8	82.3	61.7	41.2	20.7	21.5
107.5°	131.6	133.4	135.2	137.0	138.9	127.5	102.8	78.2	53.6	28.9	28.0
110°	150.0	151.5	153.1	154.7	156.3	146.2	124.5	102.7	81.0	59.3	51.7



TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.3	168.7	170.2	171.5	172.9	171.0	165.6	160.2	154.8	149.5	122.0
115°	194.7	196.0	197.3	198.5	199.8	201.4	203.3	205.2	207.0	208.9	174.0
117.5°	219.1	220.5	222.0	223.4	224.8	226.2	227.5	228.8	230.1	231.4	223.0
120°	237.0	238.1	239.2	240.4	241.5	242.8	244.2	245.5	246.8	248.2	249.1
122.5°	252.2	253.3	254.5	255.7	256.9	258.3	259.8	261.2	262.7	264.2	264.7
125°	275.3	276.2	277.3	278.2	279.2	280.4	281.9	283.3	284.7	286.1	286.6
127.5°	296.2	297.3	298.3	299.4	300.6	301.6	302.7	303.7	304.8	305.9	306.7
130°	309.5	310.7	311.9	313.1	314.3	315.3	316.2	317.0	317.8	318.6	319.4
132.5°	323.1	324.0	325.0	326.1	327.1	328.0	328.8	329.7	330.5	331.4	332.1
135°	340.6	341.8	343.0	344.2	345.5	346.3	347.1	347.8	348.4	349.1	349.8
137.5°	358.5	359.3	360.1	361.0	361.8	362.6	363.4	364.2	364.9	365.7	366.4
140°	370.1	370.7	371.3	371.9	372.5	373.2	374.1	374.9	375.7	376.5	377.2
142.5°	379.9	380.4	380.9	381.4	382.0	382.8	383.7	384.6	385.6	386.5	387.1
145°	395.1	395.1	395.0	394.9	394.8	395.5	396.7	398.0	399.3	400.5	401.1
147.5°	408.4	408.2	407.9	407.7	407.3	407.8	409.1	410.4	411.6	412.9	413.3
150°	417.2	416.6	416.1	415.6	415.0	415.3	416.6	417.8	419.0	420.2	420.6
152.5°	424.5	423.9	423.3	422.7	422.1	422.4	423.5	424.7	425.8	427.0	427.4
155°	435.1	434.4	433.7	433.1	432.4	432.5	433.4	434.3	435.2	436.1	436.6
157.5°	443.4	442.8	442.3	441.7	441.2	441.2	441.8	442.4	443.1	443.7	444.2
160°	448.3	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	448.8
162.5°	452.7	452.2	451.7	451.3	450.8	450.8	451.1	451.5	451.9	452.3	452.9
165°	458.4	458.0	457.6	457.1	456.6	456.5	456.8	457.0	457.2	457.4	458.0
167.5°	462.8	462.3	461.9	461.4	461.0	460.9	461.1	461.3	461.5	461.7	462.2
170°	465.2	464.8	464.3	463.9	463.4	463.3	463.4	463.6	463.7	463.9	464.4
172.5°	466.8	466.4	466.0	465.5	465.0	464.9	465.0	465.2	465.3	465.5	466.0
175°	469.0	468.4	467.9	467.4	466.8	466.7	466.8	467.0	467.1	467.2	467.8
177.5°	469.3	468.9	468.4	468.0	467.6	467.4	467.5	467.5	467.6	467.6	468.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	3.6	3.7	3.7	3.7	3.7	3.8	3.8	3.9
90°	7.5	7.9	8.2	8.6	8.7	8.9	9.0	9.1
92.5°	8.2	8.5	8.6	8.8	8.9	9.0	9.0	9.1
95°	13.9	14.3	14.7	14.9	14.8	14.7	14.7	14.6
97.5°	18.3	18.6	18.9	19.1	19.2	19.3	19.3	19.4
100°	20.5	21.1	21.7	22.1	22.3	22.4	22.5	22.7
102.5°	21.4	22.2	23.0	23.4	23.7	23.9	24.1	24.3
105°	22.3	23.1	24.0	24.6	24.8	25.1	25.4	25.7
107.5°	27.3	26.4	25.5	25.3	25.6	25.9	26.1	26.5
110°	44.2	36.7	29.2	25.5	25.8	26.1	26.5	26.8





TEST NUMBER: P331767-927

CATALOG NUMBER: S122RDIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	94.6	67.1	39.7	26.1	26.3	26.5	26.8	27.0
115°	139.3	104.4	69.6	49.4	44.0	38.6	33.2	27.7
117.5°	214.5	206.1	197.6	184.6	166.8	148.9	131.2	113.4
120°	250.0	250.9	251.8	247.2	237.0	226.9	216.7	206.5
122.5°	265.2	265.8	266.3	265.6	263.6	261.7	259.7	257.7
125°	287.2	287.7	288.2	288.6	288.8	289.1	289.3	289.5
127.5°	307.4	308.2	309.0	309.3	309.4	309.4	309.5	309.5
130°	320.3	321.1	321.9	322.3	322.3	322.2	322.1	322.0
132.5°	332.8	333.4	334.1	334.5	334.4	334.3	334.3	334.2
135°	350.6	351.3	352.1	352.4	352.3	352.1	352.0	351.8
137.5°	367.2	367.9	368.6	368.8	368.6	368.4	368.1	367.8
140°	377.9	378.6	379.2	379.4	379.0	378.6	378.3	377.9
142.5°	387.8	388.4	389.0	389.1	388.7	388.4	388.0	387.6
145°	401.6	402.1	402.7	402.7	402.3	402.0	401.6	401.2
147.5°	413.7	414.1	414.5	414.5	414.2	413.8	413.5	413.2
150°	421.1	421.5	422.0	422.1	421.7	421.3	420.9	420.6
152.5°	427.9	428.3	428.8	428.7	428.3	427.8	427.2	426.7
155°	437.0	437.4	437.9	437.8	437.2	436.7	436.0	435.5
157.5°	444.7	445.2	445.8	445.7	445.1	444.5	443.9	443.4
160°	449.2	449.6	450.1	450.0	449.6	449.0	448.5	448.0
162.5°	453.4	453.9	454.4	454.3	453.7	453.0	452.4	451.8
165°	458.5	459.0	459.5	459.5	459.0	458.5	458.0	457.4
167.5°	462.8	463.3	463.8	463.7	463.0	462.4	461.7	461.1
170°	464.9	465.5	466.0	465.9	465.2	464.5	463.9	463.2
172.5°	466.5	467.1	467.6	467.5	466.8	466.2	465.5	464.9
175°	468.3	468.8	469.4	469.3	468.5	467.8	467.0	466.3
177.5°	468.5	468.9	469.4	469.3	468.7	468.2	467.6	467.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9

(END OF REPORT)