

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331614

Luminaire Tested: **S122DIW-S1005D1440U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331614  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1440U835-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9057.3 lumens  
Efficiency: N/A  
Efficacy: 109.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45					45			
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38					38			
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32					32			
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27					27			
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23					23			
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20					20			
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18					18			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16					16			
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14					14			
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13					13			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11					11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	1.7
10°-20°	421.7	4.7
20°-30°	619.8	6.8
30°-40°	720.0	7.9
40°-50°	719.2	7.9
50°-60°	627.2	6.9
60°-70°	463.8	5.1
70°-80°	262.7	2.9
80°-90°	77.8	0.9
90°-100°	113.2	1.2
100°-110°	351.6	3.9
110°-120°	601.0	6.6
120°-130°	790.3	8.7
130°-140°	887.0	9.8
140°-150°	869.7	9.6
150°-160°	729.5	8.1
160°-170°	483.8	5.3
170°-180°	169.1	1.9
0°-30°	1191.4	13.2
0°-40°	1911.4	21.1
0°-60°	3257.9	36.0
0°-90°	4062.1	44.8
90°-120°	1065.7	11.8
90°-150°	3612.8	39.9
90°-180°	4995.0	55.1
0°-180°	9057.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	2	20	53	50	51	7
95°	78	93	96	96	94	90
105°	324	329	332	334	335	342
115°	603	611	609	607	603	596
125°	877	890	886	882	880	784
135°	1135	1151	1155	1153	1149	877
145°	1378	1388	1398	1399	1393	860
155°	1575	1580	1584	1591	1588	725
165°	1714	1713	1713	1722	1716	483
175°	1783	1779	1776	1785	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.4	22.6	22.9	23.1	23.4	24.0	24.9	25.9	26.8	27.7	26.8
90°	1.5	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1
92.5°	26.8	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1
95°	78.4	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5
97.5°	143.2	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2
100°	191.5	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0
102.5°	242.1	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8
105°	324.1	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3
107.5°	406.7	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6
110°	459.8	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	517.7	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7
115°	603.0	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7
117.5°	688.1	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9
120°	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7
122.5°	796.6	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8
125°	877.4	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4
127.5°	956.1	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6
130°	1005.5	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5
132.5°	1061.0	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1
135°	1135.2	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5
137.5°	1213.3	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5
140°	1260.3	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4
142.5°	1308.6	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5
145°	1377.9	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8
147.5°	1439.7	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2
150°	1481.9	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0
152.5°	1519.3	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9
155°	1575.4	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1
157.5°	1623.3	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3
160°	1652.3	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8
162.5°	1678.8	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2
165°	1714.1	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9
167.5°	1743.6	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2
170°	1759.3	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6
172.5°	1770.2	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5
175°	1783.4	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3
177.5°	1788.9	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	25.8	24.9	23.9	23.3	23.1	22.9	22.7	22.5
90°	51.4	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.2	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.0	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.0	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	413.9	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.9	468.3	467.3	466.3	465.3	464.3





TEST NUMBER: P331614

CATALOG NUMBER: S122DIW-S1005D1440U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	523.9	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.4	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	690.1	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	801.0	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	884.4	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	965.4	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.8	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1074.7	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1154.1	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.2	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1327.8	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.2	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1459.9	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1587.8	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1633.6	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1660.8	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1685.5	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1717.3	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1743.5	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1758.0	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1768.8	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1780.6	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)