

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331585

Luminaire Tested: **S122DIW-S1005D435U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331585  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D435U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6131.8 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72																												
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62																												
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53																												
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	46																												
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43	40																												
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35																												
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31																												
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	28																												
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25																												
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23																												
10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23	21																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	32195	32195	32195	32195
5°	36094	32405	28716	32405
10°	41361	32139	24851	32139
15°	45757	31550	21956	31550
20°	45060	30917	20015	30917
25°	40631	30077	18786	30077
30°	33575	28732	17889	28732
35°	24471	27325	17251	27325
40°	19545	25665	16895	25665
45°	17080	23745	16413	23745
50°	16053	21886	16093	21886
55°	14798	19997	15662	19997
60°	13563	17990	14996	17990
65°	12355	16191	14346	16191
70°	11216	14436	13388	14436
75°	9944	12477	11859	12477
80°	8554	10330	9549	10330
85°	7669	7669	5687	7669



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.9	3.1
10°-20°	552.1	9.0
20°-30°	801.2	13.1
30°-40°	845.5	13.8
40°-50°	748.6	12.2
50°-60°	597.4	9.7
60°-70°	406.1	6.6
70°-80°	208.2	3.4
80°-90°	51.7	0.8
90°-100°	19.7	0.3
100°-110°	72.3	1.2
110°-120°	193.1	3.1
120°-130°	318.8	5.2
130°-140°	339.1	5.5
140°-150°	315.2	5.1
150°-160°	253.4	4.1
160°-170°	163.3	2.7
170°-180°	56.2	0.9
0°-30°	1543.2	25.2
0°-40°	2388.7	39.0
0°-60°	3734.8	60.9
0°-90°	4400.7	71.8
90°-120°	285.1	4.6
90°-150°	1258.2	20.5
90°-180°	1731.0	28.2
0°-180°	6131.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1994	1994	1994	1994	1994	
5°	2227	1999	1772	1999	2227	222
15°	2737	1888	1314	1888	2737	755
25°	2281	1688	1054	1688	2281	1031
35°	1242	1386	875	1386	1242	807
45°	748	1040	719	1040	748	588
55°	526	710	556	710	526	471
65°	323	424	376	424	323	322
75°	159	200	190	200	159	170
85°	41	41	31	41	41	46
90°	12	0	12	0	12	7
95°	18	28	18	28	18	17
105°	32	130	32	130	32	34
115°	35	246	35	246	35	88
125°	365	348	365	348	365	316
135°	444	430	444	430	444	342
145°	506	499	506	499	506	317
155°	550	549	550	549	550	254
165°	577	579	577	579	577	163
175°	589	592	589	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2086.0	2086.6	2087.8	2078.0	2076.8	2076.8	2068.2	2060.9	2052.3	2040.6	2041.9
5°	2227.0	2235.4	2238.5	2229.3	2215.5	2214.0	2201.0	2179.5	2159.6	2143.5	2132.0
7.5°	2395.3	2398.7	2391.2	2379.1	2368.8	2350.4	2326.2	2302.4	2269.2	2238.7	2216.0
10°	2522.8	2527.4	2514.4	2496.8	2482.2	2460.8	2425.5	2389.5	2345.8	2303.7	2269.9
12.5°	2619.7	2631.0	2614.3	2612.0	2587.1	2557.6	2515.6	2497.4	2435.9	2377.2	2341.1
15°	2737.4	2736.6	2738.2	2723.6	2705.2	2700.6	2656.2	2607.9	2521.3	2486.8	2427.0
17.5°	2703.4	2715.0	2720.4	2720.2	2719.8	2716.9	2702.6	2672.1	2628.7	2572.8	2503.8
20°	2622.5	2637.8	2640.1	2657.7	2667.7	2680.7	2686.1	2677.6	2650.8	2604.1	2544.3
22.5°	2497.4	2501.7	2508.9	2536.3	2557.9	2590.6	2607.6	2635.9	2625.7	2602.8	2552.9
25°	2280.7	2273.0	2299.8	2313.6	2363.4	2415.5	2453.1	2494.5	2531.3	2553.5	2538.9
27.5°	2020.4	2008.9	2049.1	2085.7	2126.2	2182.6	2241.1	2310.2	2367.7	2439.6	2464.3
30°	1800.9	1807.8	1846.1	1885.2	1946.5	2026.2	2092.1	2168.0	2250.0	2330.5	2386.4
32.5°	1564.3	1590.8	1615.0	1674.9	1728.9	1817.8	1914.3	2009.2	2111.5	2203.0	2289.6
35°	1241.5	1272.1	1305.9	1349.5	1425.4	1513.5	1607.8	1735.8	1875.3	2000.2	2102.9
37.5°	1045.0	1040.1	1059.4	1091.0	1152.4	1223.6	1332.1	1458.5	1622.7	1769.5	1914.3
40°	927.3	924.2	938.0	967.1	1013.9	1066.0	1161.0	1272.1	1424.6	1604.0	1776.4
42.5°	846.4	848.2	855.9	876.4	908.4	951.3	1022.5	1117.0	1256.7	1425.6	1610.9
45°	748.0	753.3	761.8	771.7	790.1	825.4	865.2	932.7	1043.0	1184.0	1366.4
47.5°	677.1	677.3	685.9	694.6	705.5	725.4	757.9	800.2	878.1	992.9	1149.7
50°	639.1	633.8	639.9	646.8	658.3	672.1	693.5	733.4	785.5	878.2	1009.3
52.5°	592.5	592.7	598.2	600.8	611.1	624.9	644.5	672.1	719.3	791.8	899.5
55°	525.7	529.5	532.6	537.2	546.4	556.4	571.7	590.1	626.9	681.3	761.0
57.5°	462.9	464.1	467.2	475.9	481.7	490.9	505.5	522.2	546.1	586.4	646.3
60°	420.0	420.0	426.1	429.9	437.6	446.8	458.3	474.4	495.8	528.8	577.1
62.5°	380.7	380.1	382.6	388.8	394.7	403.3	414.7	428.4	448.6	477.9	517.6
65°	323.4	321.9	326.5	328.0	334.1	342.6	351.8	366.3	382.4	403.9	439.1
67.5°	268.2	270.1	272.5	275.4	278.8	287.7	293.8	304.1	317.7	335.5	359.4
70°	237.6	237.6	237.6	239.9	244.5	249.1	255.2	263.6	276.7	292.0	313.4
72.5°	203.2	205.7	208.1	206.8	212.6	215.3	222.7	227.5	239.9	249.7	268.7
75°	159.4	159.4	159.4	163.2	165.5	167.8	172.4	177.0	183.2	195.4	205.4
77.5°	118.9	118.6	119.4	120.3	122.8	125.5	126.9	131.0	136.7	142.4	150.8
80°	92.0	93.5	94.3	95.8	95.8	97.3	98.1	103.5	107.3	111.1	116.5
82.5°	71.1	71.4	71.6	71.9	72.5	73.4	75.4	77.1	78.5	81.7	85.8
85°	41.4	40.6	40.6	42.1	41.4	41.4	42.9	44.4	44.4	45.2	47.5
87.5°	18.2	18.2	18.8	18.1	18.1	18.6	18.5	17.8	18.4	18.9	19.3
90°	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5	9.0	8.5	7.8
92.5°	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4	10.2	9.9	9.5
95°	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6	17.1	16.7	16.0
97.5°	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1	22.7	22.3	20.8
100°	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9	25.1	24.4	22.7
102.5°	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0	26.0	25.0	38.6
105°	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2	27.1	26.1	52.0
107.5°	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4	35.4	36.5	67.6
110°	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8	65.3	74.8	102.2



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4	154.0	188.7	195.4
115°	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8	219.7	263.7	261.3
117.5°	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8	281.5	292.1	290.5
120°	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6	314.4	313.3	311.6
122.5°	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8	334.2	333.5	331.6
125°	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5	361.8	361.2	359.4
127.5°	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1	387.1	386.1	384.8
130°	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3	403.2	402.2	401.2
132.5°	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1	419.2	418.3	417.2
135°	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6	441.6	440.7	439.8
137.5°	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5	462.5	461.6	460.6
140°	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0	476.1	475.3	474.2
142.5°	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5	488.7	487.9	486.7
145°	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0	506.3	505.6	504.0
147.5°	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2	521.7	521.2	519.6
150°	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6	531.0	530.4	528.9
152.5°	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1	539.5	539.0	537.5
155°	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7	551.1	550.5	549.4
157.5°	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4	560.7	560.1	559.3
160°	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0	566.5	565.9	565.3
162.5°	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3	571.7	571.0	570.5
165°	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4	577.2
167.5°	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2	583.5	582.8	582.6
170°	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9	586.2	585.6	585.4
172.5°	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9	588.3	587.6	587.4
175°	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2	590.5	589.8	589.6
177.5°	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4	590.9	590.3	590.3
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2046.2	2041.3	2038.2	2027.2	2017.3	2007.5	2004.5	2005.7	1992.2	1979.3	1973.8
5°	2125.9	2110.5	2096.0	2075.3	2050.8	2023.9	2010.1	1999.4	1972.6	1943.5	1926.6
7.5°	2197.3	2175.4	2147.3	2108.4	2072.7	2030.5	2003.7	1979.9	1940.7	1899.6	1874.5
10°	2240.8	2210.9	2174.9	2127.4	2083.7	2032.4	1996.3	1960.3	1914.3	1865.3	1834.6
12.5°	2278.2	2237.9	2202.5	2141.5	2089.8	2025.6	1982.9	1932.1	1883.7	1825.4	1795.4
15°	2367.3	2292.9	2225.5	2156.5	2092.9	2003.2	1955.7	1887.5	1823.9	1751.9	1717.4
17.5°	2436.1	2352.5	2246.3	2158.7	2084.5	1985.2	1915.4	1833.7	1758.5	1676.2	1629.3
20°	2475.3	2379.5	2265.3	2161.1	2072.2	1958.8	1882.9	1799.4	1711.3	1618.5	1568.0
22.5°	2498.6	2397.9	2285.0	2151.9	2047.7	1937.3	1841.8	1750.3	1661.0	1560.9	1507.9
25°	2506.0	2414.0	2294.5	2144.3	2017.0	1892.1	1777.2	1688.3	1580.2	1486.7	1409.3
27.5°	2469.5	2403.6	2288.6	2129.8	1981.6	1835.6	1707.4	1606.7	1492.7	1391.2	1313.4
30°	2424.7	2386.4	2274.5	2115.1	1953.4	1796.3	1655.3	1541.1	1427.7	1325.0	1245.3
32.5°	2355.5	2347.2	2248.8	2094.3	1923.4	1746.7	1600.8	1485.3	1359.7	1258.8	1182.8
35°	2219.4	2256.1	2194.1	2047.7	1866.8	1676.0	1518.1	1386.3	1256.1	1159.5	1088.2
37.5°	2037.0	2128.3	2112.1	1979.5	1790.5	1599.1	1424.8	1287.0	1162.9	1065.4	995.5
40°	1911.3	2027.8	2044.6	1927.4	1736.6	1539.6	1354.9	1217.7	1096.6	1007.8	937.2
42.5°	1776.4	1912.5	1958.8	1864.8	1677.7	1477.1	1292.4	1150.3	1030.4	944.0	881.5
45°	1550.3	1730.4	1814.0	1760.3	1579.5	1374.1	1184.0	1039.9	931.1	849.9	801.6
47.5°	1339.0	1535.8	1648.1	1629.1	1470.2	1266.8	1078.9	940.6	834.7	769.9	726.7
50°	1189.4	1391.7	1527.3	1533.5	1391.7	1190.1	1001.6	871.3	774.0	713.5	678.2
52.5°	1059.4	1252.5	1400.4	1432.9	1304.0	1110.4	932.3	802.7	717.0	661.4	629.8
55°	889.7	1053.0	1217.0	1276.7	1173.3	989.4	824.6	710.4	629.9	591.6	564.0
57.5°	739.7	875.8	1027.2	1093.3	1029.5	872.1	717.6	618.4	553.2	519.6	498.4
60°	660.6	767.9	902.8	981.7	926.5	786.3	651.4	557.1	503.5	473.6	453.7
62.5°	587.0	682.1	796.1	868.3	838.2	706.0	585.2	502.0	455.7	427.6	413.2
65°	484.3	559.4	647.6	714.2	694.3	593.9	495.1	423.8	387.0	364.8	353.3
67.5°	398.8	453.1	514.2	572.6	556.5	485.4	406.0	350.5	323.1	303.9	297.0
70°	344.9	386.2	440.7	487.4	474.4	416.1	353.3	305.8	282.0	265.9	259.0
72.5°	293.4	327.4	368.9	407.1	398.3	349.9	297.5	261.6	243.4	228.5	222.9
75°	221.5	247.5	272.8	298.1	295.8	258.3	227.6	200.0	185.5	174.0	171.7
77.5°	163.5	178.1	195.3	210.3	206.1	184.7	160.6	144.8	134.1	126.4	125.2
80°	124.9	133.3	145.6	156.3	151.0	141.8	122.6	111.1	103.5	95.8	92.7
82.5°	90.6	99.0	106.4	112.2	108.1	99.5	87.7	79.9	75.3	70.0	68.8
85°	47.5	52.1	55.2	56.7	55.2	49.8	44.4	41.4	37.6	35.3	34.5
87.5°	19.8	19.6	19.5	20.5	18.5	18.3	15.6	13.6	13.2	12.8	11.7
90°	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8	24.6	21.5	18.4
97.5°	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1	46.3	37.5	28.6
100°	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7	62.6	49.6	36.6
102.5°	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2	95.5	92.7	90.0
105°	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9	132.8	135.6	138.5
107.5°	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1	168.4	170.7	173.0
110°	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3	191.3	193.3	195.3





TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2	213.0	214.8	216.5
115°	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8	247.4	249.0	250.6
117.5°	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6	278.4	280.2	282.0
120°	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2	300.6	302.0	303.5
122.5°	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3	319.8	321.3	322.8
125°	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5	348.7	350.0	351.2
127.5°	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9	375.3	376.6	378.0
130°	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7	392.2	393.7	395.2
132.5°	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8	409.0	410.3	411.6
135°	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0	431.5	433.0	434.5
137.5°	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5	453.5	454.6	455.7
140°	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2	467.9	468.7	469.4
142.5°	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5	480.2	480.8	481.5
145°	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8	498.7	498.6	498.5
147.5°	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6	515.3	514.9	514.6
150°	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6	525.9	525.2	524.6
152.5°	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8	535.1	534.3	533.6
155°	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2	548.4	547.5	546.7
157.5°	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7	559.0	558.3	557.6
160°	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	565.3	564.8	564.2
162.5°	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4	570.8	570.2	569.7
165°	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7	578.2	577.6	577.0
167.5°	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2	583.6	583.1	582.5
170°	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3	586.7	586.1	585.6
172.5°	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3	588.8	588.2	587.6
175°	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0	591.3	590.6	590.0
177.5°	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4	591.9	591.3	590.8
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1967.7	1964.0	1951.1	1944.4	1933.4	1922.9	1916.2	1919.3	1921.7	1920.5	1918.6
5°	1911.3	1896.7	1874.5	1855.3	1841.5	1816.3	1805.5	1800.2	1795.6	1790.2	1784.8
7.5°	1844.1	1821.2	1789.3	1762.0	1736.2	1704.8	1686.9	1676.2	1665.1	1653.0	1642.3
10°	1796.3	1764.1	1730.4	1692.1	1661.5	1633.1	1607.8	1590.9	1575.6	1561.1	1550.3
12.5°	1746.1	1709.0	1667.3	1614.9	1581.1	1540.5	1536.7	1507.0	1483.0	1474.0	1461.4
15°	1666.0	1613.9	1561.1	1499.0	1472.2	1435.4	1412.4	1389.4	1368.7	1354.1	1350.3
17.5°	1575.2	1507.7	1455.1	1410.5	1366.6	1328.9	1307.7	1289.3	1272.3	1252.8	1250.2
20°	1505.9	1447.6	1390.2	1351.1	1305.9	1267.5	1241.5	1223.1	1208.5	1197.0	1187.1
22.5°	1440.3	1376.5	1323.9	1281.2	1236.6	1205.6	1185.1	1167.3	1155.2	1142.5	1133.1
25°	1335.0	1285.2	1227.7	1179.4	1142.6	1122.7	1105.8	1090.5	1082.9	1074.4	1063.7
27.5°	1242.9	1187.5	1133.7	1096.3	1064.0	1046.4	1034.4	1024.0	1016.8	1011.9	1005.8
30°	1177.9	1121.9	1079.8	1043.0	1016.2	998.6	990.9	984.8	976.3	973.3	970.2
32.5°	1115.3	1064.9	1028.9	997.0	971.4	959.9	952.9	947.4	940.8	937.7	931.6
35°	1026.9	984.8	949.5	931.9	911.2	901.2	895.9	888.2	882.1	879.0	878.2
37.5°	943.7	907.1	883.9	861.2	852.5	846.4	839.0	833.8	832.0	831.5	830.7
40°	889.7	859.8	839.2	820.8	816.9	807.7	801.6	797.0	797.0	797.8	797.0
42.5°	840.7	813.9	795.6	779.7	775.2	769.7	763.6	763.3	764.5	767.1	764.5
45°	766.4	747.2	734.2	726.5	718.1	712.7	711.9	714.2	715.0	715.8	718.1
47.5°	698.0	685.3	673.5	665.0	661.4	660.4	659.5	663.5	667.2	668.6	672.1
50°	657.5	643.0	633.0	627.6	624.6	623.0	624.6	629.2	632.2	636.1	638.4
52.5°	612.2	601.9	595.0	590.9	589.6	590.6	590.9	596.1	601.0	602.4	603.4
55°	549.5	541.8	540.3	533.4	536.4	535.7	539.5	542.6	547.2	551.8	552.5
57.5°	486.9	480.8	476.7	477.3	478.2	481.6	484.8	490.2	495.1	500.0	500.4
60°	445.3	442.2	439.9	439.9	441.4	446.0	449.8	455.2	458.3	461.3	463.6
62.5°	407.2	404.2	401.9	403.1	407.1	409.8	414.3	417.2	420.3	423.3	424.4
65°	347.2	345.6	347.9	349.5	350.2	354.1	359.4	361.7	364.8	366.3	371.7
67.5°	291.8	292.1	291.8	294.0	298.4	299.3	304.4	309.8	310.4	313.3	316.8
70°	254.4	256.0	257.5	259.0	262.9	264.4	268.2	270.5	273.6	275.9	278.2
72.5°	220.1	220.4	221.9	221.6	224.8	228.2	231.4	233.7	236.8	239.7	242.0
75°	169.4	169.4	170.9	171.7	175.5	179.3	178.6	180.1	183.2	186.2	187.8
77.5°	123.7	122.0	123.7	124.5	125.7	128.9	129.5	131.7	135.2	134.1	135.8
80°	94.3	92.0	94.3	95.0	95.0	98.9	98.9	100.4	102.7	100.4	102.7
82.5°	67.3	66.2	67.9	68.1	69.3	69.4	70.7	71.0	73.3	72.2	73.3
85°	33.7	33.0	33.7	33.0	33.7	34.5	34.5	33.7	33.7	35.3	33.0
87.5°	11.3	10.9	10.4	10.6	10.1	9.7	9.2	9.3	9.4	8.2	8.3
90°	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5	10.0	10.4	10.8
92.5°	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4	10.7	10.9	11.1
95°	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6	18.1	18.6	18.8
97.5°	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1	23.5	23.8	24.1
100°	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9	26.6	27.4	27.9
102.5°	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0	28.0	29.0	29.6
105°	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2	29.2	30.3	31.0
107.5°	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4	33.3	32.2	31.9
110°	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8	46.3	36.8	32.2



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4	84.7	50.1	32.9
115°	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8	131.8	87.8	62.4
117.5°	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8	260.2	249.5	233.0
120°	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6	316.7	317.9	312.0
122.5°	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8	335.5	336.2	335.3
125°	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5	363.2	363.8	364.3
127.5°	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1	389.0	390.0	390.5
130°	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3	405.3	406.4	406.9
132.5°	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1	420.9	421.8	422.2
135°	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6	443.5	444.5	444.8
137.5°	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5	464.4	465.3	465.6
140°	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0	477.9	478.7	478.9
142.5°	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5	490.3	491.1	491.2
145°	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0	507.6	508.3	508.4
147.5°	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2	522.7	523.2	523.2
150°	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6	532.1	532.7	532.8
152.5°	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1	540.7	541.3	541.2
155°	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7	552.2	552.8	552.7
157.5°	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4	562.0	562.7	562.6
160°	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0	567.6	568.2	568.1
162.5°	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3	573.0	573.6	573.5
165°	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8	579.4	580.1	580.1
167.5°	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2	584.8	585.5	585.4
170°	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9	587.6	588.2	588.1
172.5°	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9	589.6	590.3	590.2
175°	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2	591.8	592.5	592.4
177.5°	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4	591.9	592.5	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1912.5	1911.3	1911.3	1905.8	1911.3	1911.3	1912.5	1918.6	1920.5	1921.7	1919.3
5°	1774.1	1771.8	1768.0	1771.8	1768.0	1771.8	1774.1	1784.8	1790.2	1795.6	1800.2
7.5°	1637.2	1628.0	1626.7	1617.6	1626.7	1628.0	1637.2	1642.3	1653.0	1665.1	1676.2
10°	1537.3	1531.2	1530.4	1515.8	1530.4	1531.2	1537.3	1550.3	1561.1	1575.6	1590.9
12.5°	1461.3	1446.6	1449.5	1441.0	1449.5	1446.6	1461.3	1461.4	1474.0	1483.0	1507.0
15°	1329.6	1329.6	1326.6	1313.5	1326.6	1329.6	1329.6	1350.3	1354.1	1368.7	1389.4
17.5°	1235.1	1233.5	1226.2	1229.8	1226.2	1233.5	1235.1	1250.2	1252.8	1272.3	1289.3
20°	1178.6	1174.1	1164.9	1164.9	1164.9	1174.1	1178.6	1187.1	1197.0	1208.5	1223.1
22.5°	1125.3	1125.0	1115.2	1118.3	1115.2	1125.0	1125.3	1133.1	1142.5	1155.2	1167.3
25°	1062.9	1056.8	1052.2	1054.5	1052.2	1056.8	1062.9	1063.7	1074.4	1082.9	1090.5
27.5°	1003.8	1000.4	1000.1	993.8	1000.1	1000.4	1003.8	1005.8	1011.9	1016.8	1024.0
30°	969.4	961.8	963.3	959.5	963.3	961.8	969.4	970.2	973.3	976.3	984.8
32.5°	930.2	927.4	925.9	922.7	925.9	927.4	930.2	931.6	937.7	940.8	947.4
35°	876.7	877.5	873.6	875.2	873.6	877.5	876.7	878.2	879.0	882.1	888.2
37.5°	830.0	832.4	830.6	831.0	830.6	832.4	830.0	830.7	831.5	832.0	833.8
40°	799.3	799.3	799.3	801.6	799.3	799.3	799.3	797.0	797.8	797.0	797.0
42.5°	769.9	768.7	767.4	767.3	767.4	768.7	769.9	764.5	767.1	764.5	763.3
45°	719.6	721.9	722.7	718.8	722.7	721.9	719.6	718.1	715.8	715.0	714.2
47.5°	674.1	674.4	674.1	677.5	674.1	674.4	674.1	672.1	668.6	667.2	663.5
50°	642.2	640.7	642.2	640.7	642.2	640.7	642.2	638.4	636.1	632.2	629.2
52.5°	608.5	608.8	607.9	607.6	607.9	608.8	608.5	603.4	602.4	601.0	596.1
55°	555.6	557.1	556.4	556.4	556.4	557.1	555.6	552.5	551.8	547.2	542.6
57.5°	500.9	502.3	503.3	500.0	503.3	502.3	500.9	500.4	500.0	495.1	490.2
60°	462.9	466.7	465.9	464.4	465.9	466.7	462.9	463.6	461.3	458.3	455.2
62.5°	427.9	429.3	429.2	428.9	429.2	429.3	427.9	424.4	423.3	420.3	417.2
65°	374.0	375.5	373.2	375.5	373.2	375.5	374.0	371.7	366.3	364.8	361.7
67.5°	315.9	316.4	318.0	319.1	318.0	316.4	315.9	316.8	313.3	310.4	309.8
70°	279.7	279.0	281.3	283.6	281.3	279.0	279.7	278.2	275.9	273.6	270.5
72.5°	241.7	243.4	242.6	244.3	242.6	243.4	241.7	242.0	239.7	236.8	233.7
75°	186.2	188.5	187.8	190.1	187.8	188.5	186.2	187.8	186.2	183.2	180.1
77.5°	134.6	134.9	134.6	135.8	134.6	134.9	134.6	135.8	134.1	135.2	131.7
80°	102.7	101.2	99.6	102.7	99.6	101.2	102.7	102.7	100.4	102.7	100.4
82.5°	71.4	72.3	70.8	70.8	70.8	72.3	71.4	73.3	72.2	73.3	71.0
85°	33.0	32.2	30.7	30.7	30.7	32.2	33.0	33.0	35.3	33.7	33.7
87.5°	8.3	7.7	7.8	7.2	7.8	7.7	8.3	8.3	8.2	9.4	9.3
90°	11.0	11.2	11.4	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4
95°	18.7	18.6	18.5	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6
97.5°	24.2	24.3	24.4	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1
100°	28.1	28.3	28.4	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9
102.5°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0
105°	31.3	31.7	32.1	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2
107.5°	32.3	32.7	33.0	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4
110°	32.6	33.0	33.4	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.2	33.5	33.8	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4
115°	55.6	48.7	41.9	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8
117.5°	210.5	188.0	165.6	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8
120°	299.2	286.4	273.5	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6
122.5°	332.8	330.3	327.8	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8
125°	364.6	364.9	365.2	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5
127.5°	390.6	390.6	390.7	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1
130°	406.8	406.7	406.6	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3
132.5°	422.1	422.0	422.0	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1
135°	444.7	444.5	444.3	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6
137.5°	465.3	465.0	464.7	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5
140°	478.4	477.9	477.5	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0
142.5°	490.7	490.3	489.8	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5
145°	507.9	507.4	507.0	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0
147.5°	522.8	522.4	522.0	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2
150°	532.3	531.8	531.3	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6
152.5°	540.6	540.0	539.3	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1
155°	551.9	551.2	550.4	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7
157.5°	561.9	561.1	560.4	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4
160°	567.5	566.8	566.1	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0
162.5°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3
165°	579.4	578.8	578.1	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8
167.5°	584.5	583.7	582.8	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2
170°	587.3	586.4	585.6	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9
172.5°	589.3	588.5	587.6	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9
175°	591.4	590.5	589.5	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2
177.5°	591.7	591.0	590.3	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1916.2	1922.9	1933.4	1944.4	1951.1	1964.0	1967.7	1973.8	1979.3	1992.2	2005.7
5°	1805.5	1816.3	1841.5	1855.3	1874.5	1896.7	1911.3	1926.6	1943.5	1972.6	1999.4
7.5°	1686.9	1704.8	1736.2	1762.0	1789.3	1821.2	1844.1	1874.5	1899.6	1940.7	1979.9
10°	1607.8	1633.1	1661.5	1692.1	1730.4	1764.1	1796.3	1834.6	1865.3	1914.3	1960.3
12.5°	1536.7	1540.5	1581.1	1614.9	1667.3	1709.0	1746.1	1795.4	1825.4	1883.7	1932.1
15°	1412.4	1435.4	1472.2	1499.0	1561.1	1613.9	1666.0	1717.4	1751.9	1823.9	1887.5
17.5°	1307.7	1328.9	1366.6	1410.5	1455.1	1507.7	1575.2	1629.3	1676.2	1758.5	1833.7
20°	1241.5	1267.5	1305.9	1351.1	1390.2	1447.6	1505.9	1568.0	1618.5	1711.3	1799.4
22.5°	1185.1	1205.6	1236.6	1281.2	1323.9	1376.5	1440.3	1507.9	1560.9	1661.0	1750.3
25°	1105.8	1122.7	1142.6	1179.4	1227.7	1285.2	1335.0	1409.3	1486.7	1580.2	1688.3
27.5°	1034.4	1046.4	1064.0	1096.3	1133.7	1187.5	1242.9	1313.4	1391.2	1492.7	1606.7
30°	990.9	998.6	1016.2	1043.0	1079.8	1121.9	1177.9	1245.3	1325.0	1427.7	1541.1
32.5°	952.9	959.9	971.4	997.0	1028.9	1064.9	1115.3	1182.8	1258.8	1359.7	1485.3
35°	895.9	901.2	911.2	931.9	949.5	984.8	1026.9	1088.2	1159.5	1256.1	1386.3
37.5°	839.0	846.4	852.5	861.2	883.9	907.1	943.7	995.5	1065.4	1162.9	1287.0
40°	801.6	807.7	816.9	820.8	839.2	859.8	889.7	937.2	1007.8	1096.6	1217.7
42.5°	763.6	769.7	775.2	779.7	795.6	813.9	840.7	881.5	944.0	1030.4	1150.3
45°	711.9	712.7	718.1	726.5	734.2	747.2	766.4	801.6	849.9	931.1	1039.9
47.5°	659.5	660.4	661.4	665.0	673.5	685.3	698.0	726.7	769.9	834.7	940.6
50°	624.6	623.0	624.6	627.6	633.0	643.0	657.5	678.2	713.5	774.0	871.3
52.5°	590.9	590.6	589.6	590.9	595.0	601.9	612.2	629.8	661.4	717.0	802.7
55°	539.5	535.7	536.4	533.4	540.3	541.8	549.5	564.0	591.6	629.9	710.4
57.5°	484.8	481.6	478.2	477.3	476.7	480.8	486.9	498.4	519.6	553.2	618.4
60°	449.8	446.0	441.4	439.9	439.9	442.2	445.3	453.7	473.6	503.5	557.1
62.5°	414.3	409.8	407.1	403.1	401.9	404.2	407.2	413.2	427.6	455.7	502.0
65°	359.4	354.1	350.2	349.5	347.9	345.6	347.2	353.3	364.8	387.0	423.8
67.5°	304.4	299.3	298.4	294.0	291.8	292.1	291.8	297.0	303.9	323.1	350.5
70°	268.2	264.4	262.9	259.0	257.5	256.0	254.4	259.0	265.9	282.0	305.8
72.5°	231.4	228.2	224.8	221.6	221.9	220.4	220.1	222.9	228.5	243.4	261.6
75°	178.6	179.3	175.5	171.7	170.9	169.4	169.4	171.7	174.0	185.5	200.0
77.5°	129.5	128.9	125.7	124.5	123.7	122.0	123.7	125.2	126.4	134.1	144.8
80°	98.9	98.9	95.0	95.0	94.3	92.0	94.3	92.7	95.8	103.5	111.1
82.5°	70.7	69.4	69.3	68.1	67.9	66.2	67.3	68.8	70.0	75.3	79.9
85°	34.5	34.5	33.7	33.0	33.7	33.0	33.7	34.5	35.3	37.6	41.4
87.5°	9.2	9.7	10.1	10.6	10.4	10.9	11.3	11.7	12.8	13.2	13.6
90°	9.0	8.5	7.8	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4
92.5°	10.2	9.9	9.5	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6
95°	17.1	16.7	16.0	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8
97.5°	22.7	22.3	20.8	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1
100°	25.1	24.4	22.7	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7
102.5°	26.0	25.0	38.6	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2
105°	27.1	26.1	52.0	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9
107.5°	35.4	36.5	67.6	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1
110°	65.3	74.8	102.2	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	154.0	188.7	195.4	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2
115°	219.7	263.7	261.3	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8
117.5°	281.5	292.1	290.5	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6
120°	314.4	313.3	311.6	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2
122.5°	334.2	333.5	331.6	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3
125°	361.8	361.2	359.4	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5
127.5°	387.1	386.1	384.8	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9
130°	403.2	402.2	401.2	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7
132.5°	419.2	418.3	417.2	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8
135°	441.6	440.7	439.8	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0
137.5°	462.5	461.6	460.6	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5
140°	476.1	475.3	474.2	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2
142.5°	488.7	487.9	486.7	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5
145°	506.3	505.6	504.0	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8
147.5°	521.7	521.2	519.6	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6
150°	531.0	530.4	528.9	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6
152.5°	539.5	539.0	537.5	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8
155°	551.1	550.5	549.4	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2
157.5°	560.7	560.1	559.3	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7
160°	566.5	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9
162.5°	571.7	571.0	570.5	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4
165°	578.1	577.4	577.2	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7
167.5°	583.5	582.8	582.6	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2
170°	586.2	585.6	585.4	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3
172.5°	588.3	587.6	587.4	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3
175°	590.5	589.8	589.6	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0
177.5°	590.9	590.3	590.3	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2004.5	2007.5	2017.3	2027.2	2038.2	2041.3	2046.2	2041.9	2040.6	2052.3	2060.9
5°	2010.1	2023.9	2050.8	2075.3	2096.0	2110.5	2125.9	2132.0	2143.5	2159.6	2179.5
7.5°	2003.7	2030.5	2072.7	2108.4	2147.3	2175.4	2197.3	2216.0	2238.7	2269.2	2302.4
10°	1996.3	2032.4	2083.7	2127.4	2174.9	2210.9	2240.8	2269.9	2303.7	2345.8	2389.5
12.5°	1982.9	2025.6	2089.8	2141.5	2202.5	2237.9	2278.2	2341.1	2377.2	2435.9	2497.4
15°	1955.7	2003.2	2092.9	2156.5	2225.5	2292.9	2367.3	2427.0	2486.8	2521.3	2607.9
17.5°	1915.4	1985.2	2084.5	2158.7	2246.3	2352.5	2436.1	2503.8	2572.8	2628.7	2672.1
20°	1882.9	1958.8	2072.2	2161.1	2265.3	2379.5	2475.3	2544.3	2604.1	2650.8	2677.6
22.5°	1841.8	1937.3	2047.7	2151.9	2285.0	2397.9	2498.6	2552.9	2602.8	2625.7	2635.9
25°	1777.2	1892.1	2017.0	2144.3	2294.5	2414.0	2506.0	2538.9	2553.5	2531.3	2494.5
27.5°	1707.4	1835.6	1981.6	2129.8	2288.6	2403.6	2469.5	2464.3	2439.6	2367.7	2310.2
30°	1655.3	1796.3	1953.4	2115.1	2274.5	2386.4	2424.7	2386.4	2330.5	2250.0	2168.0
32.5°	1600.8	1746.7	1923.4	2094.3	2248.8	2347.2	2355.5	2289.6	2203.0	2111.5	2009.2
35°	1518.1	1676.0	1866.8	2047.7	2194.1	2256.1	2219.4	2102.9	2000.2	1875.3	1735.8
37.5°	1424.8	1599.1	1790.5	1979.5	2112.1	2128.3	2037.0	1914.3	1769.5	1622.7	1458.5
40°	1354.9	1539.6	1736.6	1927.4	2044.6	2027.8	1911.3	1776.4	1604.0	1424.6	1272.1
42.5°	1292.4	1477.1	1677.7	1864.8	1958.8	1912.5	1776.4	1610.9	1425.6	1256.7	1117.0
45°	1184.0	1374.1	1579.5	1760.3	1814.0	1730.4	1550.3	1366.4	1184.0	1043.0	932.7
47.5°	1078.9	1266.8	1470.2	1629.1	1648.1	1535.8	1339.0	1149.7	992.9	878.1	800.2
50°	1001.6	1190.1	1391.7	1533.5	1527.3	1391.7	1189.4	1009.3	878.2	785.5	733.4
52.5°	932.3	1110.4	1304.0	1432.9	1400.4	1252.5	1059.4	899.5	791.8	719.3	672.1
55°	824.6	989.4	1173.3	1276.7	1217.0	1053.0	889.7	761.0	681.3	626.9	590.1
57.5°	717.6	872.1	1029.5	1093.3	1027.2	875.8	739.7	646.3	586.4	546.1	522.2
60°	651.4	786.3	926.5	981.7	902.8	767.9	660.6	577.1	528.8	495.8	474.4
62.5°	585.2	706.0	838.2	868.3	796.1	682.1	587.0	517.6	477.9	448.6	428.4
65°	495.1	593.9	694.3	714.2	647.6	559.4	484.3	439.1	403.9	382.4	366.3
67.5°	406.0	485.4	556.5	572.6	514.2	453.1	398.8	359.4	335.5	317.7	304.1
70°	353.3	416.1	474.4	487.4	440.7	386.2	344.9	313.4	292.0	276.7	263.6
72.5°	297.5	349.9	398.3	407.1	368.9	327.4	293.4	268.7	249.7	239.9	227.5
75°	227.6	258.3	295.8	298.1	272.8	247.5	221.5	205.4	195.4	183.2	177.0
77.5°	160.6	184.7	206.1	210.3	195.3	178.1	163.5	150.8	142.4	136.7	131.0
80°	122.6	141.8	151.0	156.3	145.6	133.3	124.9	116.5	111.1	107.3	103.5
82.5°	87.7	99.5	108.1	112.2	106.4	99.0	90.6	85.8	81.7	78.5	77.1
85°	44.4	49.8	55.2	56.7	55.2	52.1	47.5	47.5	45.2	44.4	44.4
87.5°	15.6	18.3	18.5	20.5	19.5	19.6	19.8	19.3	18.9	18.4	17.8
90°	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4
95°	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6
97.5°	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1
100°	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9
102.5°	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0
105°	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2
107.5°	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4
110°	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8





TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4
115°	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8
117.5°	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8
120°	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6
122.5°	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8
125°	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5
127.5°	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1
130°	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3
132.5°	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1
135°	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6
137.5°	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5
140°	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0
142.5°	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5
145°	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0
147.5°	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2
150°	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6
152.5°	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1
155°	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7
157.5°	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4
160°	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0
162.5°	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3
165°	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8
167.5°	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2
170°	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9
172.5°	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9
175°	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2
177.5°	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2068.2	2076.8	2076.8	2078.0	2087.8	2086.6	2086.0
5°	2201.0	2214.0	2215.5	2229.3	2238.5	2235.4	2227.0
7.5°	2326.2	2350.4	2368.8	2379.1	2391.2	2398.7	2395.3
10°	2425.5	2460.8	2482.2	2496.8	2514.4	2527.4	2522.8
12.5°	2515.6	2557.6	2587.1	2612.0	2614.3	2631.0	2619.7
15°	2656.2	2700.6	2705.2	2723.6	2738.2	2736.6	2737.4
17.5°	2702.6	2716.9	2719.8	2720.2	2720.4	2715.0	2703.4
20°	2686.1	2680.7	2667.7	2657.7	2640.1	2637.8	2622.5
22.5°	2607.6	2590.6	2557.9	2536.3	2508.9	2501.7	2497.4
25°	2453.1	2415.5	2363.4	2313.6	2299.8	2273.0	2280.7
27.5°	2241.1	2182.6	2126.2	2085.7	2049.1	2008.9	2020.4
30°	2092.1	2026.2	1946.5	1885.2	1846.1	1807.8	1800.9
32.5°	1914.3	1817.8	1728.9	1674.9	1615.0	1590.8	1564.3
35°	1607.8	1513.5	1425.4	1349.5	1305.9	1272.1	1241.5
37.5°	1332.1	1223.6	1152.4	1091.0	1059.4	1040.1	1045.0
40°	1161.0	1066.0	1013.9	967.1	938.0	924.2	927.3
42.5°	1022.5	951.3	908.4	876.4	855.9	848.2	846.4
45°	865.2	825.4	790.1	771.7	761.8	753.3	748.0
47.5°	757.9	725.4	705.5	694.6	685.9	677.3	677.1
50°	693.5	672.1	658.3	646.8	639.9	633.8	639.1
52.5°	644.5	624.9	611.1	600.8	598.2	592.7	592.5
55°	571.7	556.4	546.4	537.2	532.6	529.5	525.7
57.5°	505.5	490.9	481.7	475.9	467.2	464.1	462.9
60°	458.3	446.8	437.6	429.9	426.1	420.0	420.0
62.5°	414.7	403.3	394.7	388.8	382.6	380.1	380.7
65°	351.8	342.6	334.1	328.0	326.5	321.9	323.4
67.5°	293.8	287.7	278.8	275.4	272.5	270.1	268.2
70°	255.2	249.1	244.5	239.9	237.6	237.6	237.6
72.5°	222.7	215.3	212.6	206.8	208.1	205.7	203.2
75°	172.4	167.8	165.5	163.2	159.4	159.4	159.4
77.5°	126.9	125.5	122.8	120.3	119.4	118.6	118.9
80°	98.1	97.3	95.8	95.8	94.3	93.5	92.0
82.5°	75.4	73.4	72.5	71.9	71.6	71.4	71.1
85°	42.9	41.4	41.4	42.1	40.6	40.6	41.4
87.5°	18.5	18.6	18.1	18.1	18.8	18.2	18.2
90°	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331585

CATALOG NUMBER: S122DIW-S1005D435U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)