

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331801-927

Luminaire Tested: **S122RDIW-S485D1440U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331801-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6038.3 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	85	82	82	79	76	73	61	59	57	44	43	42	29	29	28	21				21
2	84	78	72	67	75	69	65	61	54	51	48	40	38	36	26	25	24	18				18
3	77	68	62	56	69	61	56	51	48	44	41	35	33	31	24	22	21	16				16
4	71	61	53	48	63	55	48	44	43	38	35	32	29	27	21	20	19	14				14
5	65	54	47	41	58	49	42	37	38	34	30	29	26	23	19	18	16	13				13
6	60	49	41	36	53	44	37	33	35	30	27	26	23	21	18	16	15	11				11
7	55	44	37	31	49	40	33	29	31	27	23	24	21	18	16	15	13	10				10
8	51	40	33	28	46	36	30	25	29	24	21	22	19	16	15	13	12	9				9
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	12	11	9				9
10	45	33	27	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13747	13747	13747	13747
5°	15352	13833	12266	13833
10°	17033	13736	10632	13736
15°	17870	13534	8376	13534
20°	15493	13235	7247	13235
25°	10162	12827	6472	12827
30°	6840	12333	5858	12333
35°	5541	11710	5282	11710
40°	4926	11030	4890	11030
45°	4459	10234	4364	10234
50°	4057	9445	4042	9445
55°	3814	8569	3764	8569
60°	3190	7766	3152	7766
65°	2690	7053	3053	7053
70°	2488	6297	2875	6297
75°	2327	5483	2658	5483
80°	2148	4510	2362	4510
85°	1964	3575	2075	3575



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.3
10°-20°	224.9	3.7
20°-30°	289.8	4.8
30°-40°	275.4	4.6
40°-50°	235.9	3.9
50°-60°	179.7	3.0
60°-70°	113.6	1.9
70°-80°	56.7	0.9
80°-90°	18.6	0.3
90°-100°	51.9	0.9
100°-110°	190.5	3.2
110°-120°	509.1	8.4
120°-130°	840.4	13.9
130°-140°	893.8	14.8
140°-150°	830.7	13.8
150°-160°	667.9	11.1
160°-170°	430.4	7.1
170°-180°	148.2	2.5
0°-30°	595.4	9.9
0°-40°	870.8	14.4
0°-60°	1286.4	21.3
0°-90°	1475.2	24.4
90°-120°	751.5	12.4
90°-150°	3316.5	54.9
90°-180°	4563.0	75.6
0°-180°	6038.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	851	851	851	851	851	
5°	947	854	757	854	947	93
15°	1069	810	501	810	1069	288
25°	570	720	363	720	570	271
35°	281	594	268	594	281	180
45°	195	448	191	448	195	151
55°	136	304	134	304	136	119
65°	70	185	80	185	70	72
75°	37	88	43	88	37	40
85°	11	19	11	19	11	12
90°	30	1	30	1	30	14
95°	48	73	48	73	48	45
105°	86	342	86	342	86	89
115°	92	648	92	648	92	231
125°	963	916	963	916	963	834
135°	1171	1134	1171	1134	1171	902
145°	1335	1315	1335	1315	1335	835
155°	1449	1448	1449	1448	1449	669
165°	1522	1526	1522	1526	1522	430
175°	1551	1560	1551	1560	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	886.0	886.7	887.4	885.7	885.7	884.3	881.2	878.8	872.2	871.2	871.2
5°	947.2	946.7	947.8	944.0	938.7	937.5	931.8	924.5	916.8	908.2	906.4
7.5°	1008.2	1007.3	1005.0	1004.2	1000.2	991.3	982.2	972.6	959.8	947.3	941.0
10°	1038.9	1048.7	1042.8	1032.5	1034.5	1020.6	1013.2	1000.5	989.8	971.2	967.1
12.5°	1069.2	1073.1	1071.2	1065.3	1062.7	1053.0	1043.1	1032.0	1012.3	995.6	981.0
15°	1069.1	1074.8	1076.3	1074.4	1075.9	1075.3	1070.0	1060.8	1043.7	1025.3	1009.4
17.5°	990.2	994.1	1003.8	1010.3	1018.7	1036.2	1044.8	1048.2	1045.6	1035.1	1023.9
20°	901.7	895.2	922.4	936.3	948.2	977.7	1003.1	1012.9	1028.6	1028.3	1025.3
22.5°	776.3	777.8	803.6	820.1	854.7	884.2	913.2	950.0	980.3	1000.4	1012.1
25°	570.4	581.6	607.4	629.8	668.3	723.3	773.3	831.3	886.0	929.2	970.3
27.5°	428.3	429.2	449.6	470.4	493.2	538.3	601.3	670.5	748.5	812.9	886.9
30°	366.9	365.0	373.7	386.3	405.9	440.8	488.1	556.2	634.0	731.0	817.4
32.5°	323.3	323.4	329.9	339.3	355.5	379.0	411.5	466.7	540.3	635.6	736.9
35°	281.1	280.7	285.5	292.3	299.0	314.2	336.4	365.4	416.0	505.0	608.6
37.5°	250.7	252.1	254.4	258.6	266.1	274.5	287.9	307.3	343.3	396.0	483.0
40°	233.7	234.3	237.6	241.1	245.6	252.1	263.0	278.7	305.0	347.0	410.6
42.5°	218.1	218.6	221.0	224.3	227.8	234.3	243.4	256.9	278.3	311.0	363.5
45°	195.3	195.3	197.3	198.8	202.6	208.6	215.9	227.2	242.0	266.3	301.2
47.5°	173.8	173.9	175.2	177.8	180.2	184.8	192.1	201.3	212.1	230.8	260.6
50°	161.5	161.8	162.7	164.8	166.3	170.4	176.0	184.0	195.3	209.8	234.6
52.5°	151.5	151.4	152.5	153.4	154.4	157.4	161.6	168.7	178.7	191.3	211.9
55°	135.5	134.3	136.1	137.5	138.5	139.7	142.0	146.5	155.0	165.6	181.0
57.5°	115.3	114.9	116.1	117.5	120.3	123.5	125.5	128.3	132.8	140.4	155.7
60°	98.8	98.8	101.5	102.3	105.6	109.7	113.9	116.3	120.7	125.7	137.0
62.5°	84.1	84.4	85.6	86.5	88.3	93.4	99.3	104.4	108.6	113.4	120.9
65°	70.4	71.0	71.0	71.6	72.8	74.0	76.3	80.5	87.9	94.7	100.3
67.5°	59.7	60.0	60.1	60.7	61.0	62.3	63.2	65.1	66.8	73.3	80.2
70°	52.7	53.6	53.2	53.9	54.1	54.7	55.9	56.8	59.5	60.9	65.1
72.5°	46.0	46.7	46.7	47.0	47.8	47.8	48.8	49.7	51.4	52.7	54.9
75°	37.3	37.0	37.3	37.9	38.2	38.4	38.4	39.6	40.6	41.7	43.2
77.5°	28.8	29.1	29.0	29.1	29.1	29.6	29.5	30.1	31.0	31.6	32.3
80°	23.1	23.4	23.1	23.4	23.7	23.9	23.7	23.9	24.9	25.4	25.4
82.5°	17.9	17.9	18.1	18.1	18.2	18.3	18.7	18.8	19.4	19.3	19.5
85°	10.6	10.4	10.4	10.4	10.6	10.9	10.6	10.6	10.9	10.9	10.9
87.5°	9.9	10.0	9.9	9.8	9.7	9.5	9.3	9.3	8.8	8.8	8.2
90°	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0	23.8	22.5	20.5
92.5°	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4	26.8	26.1	25.1
95°	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4	45.2	44.0	42.2
97.5°	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8	59.8	58.8	54.7
100°	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2	66.2	64.2	60.0
102.5°	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2	68.6	66.0	101.6
105°	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2	71.5	68.8	137.0
107.5°	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6	93.4	96.3	178.2
110°	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1	172.1	197.2	269.5



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7	406.0	497.3	515.2
115°	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3	579.2	695.1	688.9
117.5°	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9	742.0	770.0	765.6
120°	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9	828.9	825.9	821.3
122.5°	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6	880.8	879.0	874.1
125°	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5	953.8	952.0	947.3
127.5°	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9	1020.4	1017.9	1014.3
130°	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7	1063.0	1060.2	1057.4
132.5°	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2	1104.9	1102.6	1099.8
135°	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6	1164.1	1161.6	1159.4
137.5°	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7	1219.2	1216.8	1214.3
140°	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4	1255.1	1252.8	1250.1
142.5°	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3	1288.2	1286.2	1283.0
145°	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3	1334.6	1332.8	1328.6
147.5°	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5	1375.1	1373.9	1369.7
150°	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2	1399.7	1398.2	1394.2
152.5°	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7	1422.2	1420.7	1416.9
155°	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1	1452.6	1451.1	1448.2
157.5°	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8	1478.1	1476.4	1474.3
160°	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7	1493.2	1491.7	1490.2
162.5°	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6	1507.0	1505.2	1504.0
165°	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1	1521.4
167.5°	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8	1538.1	1536.4	1535.6
170°	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1	1545.3	1543.6	1543.0
172.5°	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4	1550.7	1549.0	1548.5
175°	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3	1556.6	1554.8	1554.3
177.5°	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9	1557.6	1556.2	1555.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	871.7	869.9	868.2	864.0	861.8	857.1	856.3	856.1	850.0	844.1	842.4
5°	901.7	897.0	889.9	881.5	873.0	864.1	858.2	853.5	841.6	830.4	823.9
7.5°	931.8	921.7	909.4	893.7	880.7	866.0	855.2	845.3	828.5	812.5	801.6
10°	954.3	937.8	921.5	899.9	883.0	866.5	851.1	837.8	818.9	797.6	782.4
12.5°	968.3	950.1	927.6	906.6	884.7	863.6	843.0	825.9	803.7	781.7	763.7
15°	987.2	967.7	940.5	910.3	882.2	854.7	831.0	809.7	780.7	754.4	732.5
17.5°	1002.7	975.7	946.5	911.6	879.1	844.1	813.7	786.4	754.2	722.4	696.6
20°	1007.6	981.0	947.2	912.4	873.9	832.7	799.9	770.3	735.7	701.1	671.5
22.5°	1004.5	983.8	946.3	904.5	865.1	822.1	785.1	750.7	712.3	677.0	642.7
25°	983.7	976.5	941.0	895.5	850.5	800.5	757.6	720.0	676.3	638.4	601.1
27.5°	934.9	950.3	928.3	879.7	829.7	776.1	727.9	685.2	639.7	597.1	559.9
30°	888.1	923.3	913.8	868.9	812.9	760.3	706.2	661.5	613.0	569.2	532.5
32.5°	823.9	882.1	891.4	853.7	795.9	738.0	681.3	636.8	586.2	540.0	504.3
35°	721.8	808.8	848.7	824.7	766.8	704.4	645.8	594.1	543.1	497.6	462.1
37.5°	600.0	718.4	785.1	786.7	733.5	668.6	604.8	553.4	501.3	456.6	418.2
40°	520.9	649.4	736.0	755.3	710.3	640.2	575.7	523.3	472.5	428.6	384.6
42.5°	450.0	577.9	684.4	717.9	682.1	612.5	547.8	493.1	443.5	402.1	357.1
45°	363.8	475.7	593.1	652.9	633.1	568.5	500.3	448.2	401.7	365.9	322.7
47.5°	307.0	385.8	499.4	580.3	579.9	521.0	453.8	403.9	360.8	327.3	292.3
50°	274.5	343.2	439.3	531.0	538.7	489.3	425.4	376.0	335.8	300.6	272.4
52.5°	245.4	302.0	388.4	476.3	498.2	455.4	393.5	347.8	308.8	276.4	252.3
55°	207.4	251.1	316.9	399.1	432.2	402.0	347.0	304.4	272.7	245.6	224.8
57.5°	175.4	208.3	260.9	327.2	365.8	346.7	301.4	266.8	239.7	215.1	198.8
60°	155.3	182.2	226.9	282.3	324.8	311.5	272.7	240.5	217.5	196.1	180.8
62.5°	136.4	159.5	197.8	242.7	281.8	276.2	244.6	217.5	197.3	177.9	164.9
65°	109.7	126.6	156.5	191.7	223.1	225.7	203.0	184.6	166.5	151.1	139.7
67.5°	87.4	98.4	119.5	149.1	172.6	181.0	167.1	153.0	138.7	126.8	116.8
70°	73.7	82.5	97.9	121.9	143.5	152.3	144.3	133.4	121.0	111.2	102.7
72.5°	59.7	68.4	79.7	97.3	115.8	125.4	122.6	114.7	104.6	96.6	88.5
75°	45.0	47.6	55.3	67.2	81.7	89.9	92.0	87.9	79.9	73.7	68.9
77.5°	33.3	34.9	38.5	44.8	54.2	61.6	64.6	64.2	58.6	55.1	50.6
80°	26.6	27.5	29.3	31.9	39.1	46.4	48.5	48.5	44.7	43.2	38.7
82.5°	20.2	20.9	21.9	23.4	26.8	33.2	35.5	36.0	33.5	31.6	28.1
85°	11.6	11.2	11.8	12.8	13.3	15.1	18.6	19.3	18.6	16.2	15.4
87.5°	7.8	7.5	7.1	6.4	6.1	5.9	6.4	7.1	6.7	6.5	6.6
90°	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1	3.9	6.7	9.4
92.5°	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7	22.5	22.3	22.0
95°	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2	65.0	56.7	48.5
97.5°	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4	122.1	98.8	75.5
100°	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4	165.1	130.8	96.5
102.5°	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9	251.7	244.4	237.1
105°	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5	350.0	357.5	365.0
107.5°	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8	443.9	450.0	456.0
110°	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2	504.4	509.6	514.9



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8	561.4	566.1	570.8
115°	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8	652.1	656.3	660.6
117.5°	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2	734.0	738.7	743.5
120°	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7	792.4	796.1	799.9
122.5°	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2	843.1	847.1	851.0
125°	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0	919.2	922.5	925.7
127.5°	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6	989.2	992.8	996.4
130°	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8	1033.8	1037.8	1041.8
132.5°	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8	1078.2	1081.6	1085.1
135°	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5	1137.4	1141.5	1145.4
137.5°	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7	1195.5	1198.3	1201.1
140°	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4	1233.4	1235.5	1237.5
142.5°	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9	1265.7	1267.5	1269.3
145°	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9	1314.5	1314.3	1314.1
147.5°	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2	1358.3	1357.3	1356.4
150°	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1	1386.3	1384.6	1382.8
152.5°	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4	1410.5	1408.5	1406.5
155°	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8	1445.5	1443.3	1441.0
157.5°	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5	1473.6	1471.7	1469.8
160°	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1490.2	1488.7	1487.2
162.5°	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1	1504.7	1503.2	1501.7
165°	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5	1524.0	1522.5	1521.0
167.5°	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9	1538.4	1536.9	1535.4
170°	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1	1546.6	1545.1	1543.6
172.5°	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5	1552.0	1550.5	1549.0
175°	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4	1558.7	1557.0	1555.2
177.5°	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5	1560.2	1558.8	1557.4
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	839.3	837.7	834.6	829.9	827.0	822.0	818.7	820.6	821.1	820.6	820.1
5°	816.8	810.6	802.0	793.7	786.0	777.8	773.0	771.0	766.8	764.5	763.3
7.5°	789.5	778.8	766.7	752.3	740.0	727.1	720.6	717.3	708.8	704.3	700.2
10°	769.1	752.3	740.1	721.2	709.7	692.8	681.3	681.6	670.0	663.5	658.8
12.5°	746.7	728.2	708.0	690.9	674.9	661.4	647.5	641.8	629.5	623.3	610.5
15°	709.4	687.8	666.5	643.4	627.2	606.2	586.1	561.5	541.7	524.5	519.8
17.5°	668.7	642.0	620.6	593.5	565.6	530.3	507.0	492.7	480.8	471.7	465.0
20°	640.8	613.5	590.8	549.9	512.4	488.4	471.3	460.3	447.9	438.2	432.8
22.5°	611.4	583.0	552.0	506.4	477.1	457.9	442.6	430.0	421.6	414.0	409.2
25°	569.7	538.7	487.5	456.1	432.5	412.4	401.7	394.0	385.2	374.8	370.1
27.5°	525.8	476.3	439.6	416.3	393.7	380.6	371.1	359.6	351.6	347.0	342.1
30°	492.8	443.5	414.8	389.3	373.4	358.9	347.6	341.1	333.4	325.4	322.2
32.5°	456.1	416.7	389.2	368.0	351.8	339.5	330.6	320.0	314.5	309.6	302.8
35°	410.6	380.7	355.6	338.4	323.1	313.0	302.6	296.4	286.4	282.3	279.6
37.5°	372.0	346.1	327.3	309.3	297.1	286.0	279.6	269.7	265.4	259.6	254.0
40°	350.2	324.8	306.8	292.0	278.4	270.1	262.1	254.1	247.6	244.9	238.1
42.5°	328.0	307.3	289.2	273.1	264.0	255.2	245.1	239.2	232.4	228.1	223.9
45°	297.3	279.0	263.6	250.3	240.2	231.1	224.5	214.8	211.0	202.3	198.8
47.5°	270.3	253.3	238.6	225.9	216.1	210.2	200.7	193.0	186.9	181.6	177.1
50°	251.1	236.9	222.8	211.5	202.6	194.1	184.3	180.5	171.0	168.3	165.6
52.5°	233.6	220.1	207.2	196.1	187.3	179.0	170.3	165.3	158.9	156.2	154.3
55°	209.1	196.1	183.7	174.0	165.1	156.5	151.1	145.0	142.0	139.9	137.5
57.5°	184.5	172.9	163.3	153.4	144.5	137.7	131.5	127.8	124.7	122.0	119.1
60°	168.9	157.6	149.1	139.9	130.8	125.2	120.4	116.0	112.4	108.3	107.1
62.5°	152.3	142.5	134.7	125.7	117.7	112.6	108.1	103.9	99.7	93.6	92.0
65°	129.6	121.9	113.6	106.2	99.1	94.1	87.5	82.9	81.0	80.5	80.2
67.5°	109.0	101.7	94.6	87.1	80.6	75.9	72.6	71.9	70.7	70.3	69.5
70°	95.2	88.5	81.4	74.2	68.0	67.2	66.0	64.8	63.3	62.7	62.1
72.5°	82.9	75.9	68.8	63.1	60.4	59.3	58.1	57.0	56.0	55.4	55.1
75°	63.6	57.1	52.4	50.3	48.8	47.9	46.2	45.2	44.7	43.8	43.5
77.5°	45.8	42.1	39.9	38.7	37.1	36.1	35.2	34.2	33.6	33.4	33.0
80°	34.9	33.1	31.7	29.9	29.3	28.1	27.8	26.9	27.3	26.3	26.3
82.5°	27.1	24.9	23.6	22.8	22.2	21.2	20.9	20.5	20.6	20.0	20.0
85°	13.9	13.3	12.8	12.1	12.1	11.2	11.6	11.2	11.2	10.6	10.4
87.5°	6.9	7.1	7.1	7.5	7.9	8.1	8.3	8.3	8.6	8.8	8.8
90°	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0	26.3	27.6	28.4
92.5°	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4	28.1	28.8	29.2
95°	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4	47.7	49.0	49.4
97.5°	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8	61.8	62.8	63.5
100°	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2	70.3	72.2	73.5
102.5°	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2	73.8	76.4	78.1
105°	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2	77.0	79.8	81.6
107.5°	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6	87.8	85.0	84.1
110°	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1	122.1	97.0	85.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7	223.3	132.0	86.7
115°	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3	347.4	231.5	164.5
117.5°	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9	685.9	657.8	614.2
120°	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9	834.9	837.9	822.4
122.5°	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6	884.5	886.2	883.8
125°	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5	957.3	959.0	960.3
127.5°	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9	1025.5	1028.0	1029.4
130°	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7	1068.5	1071.2	1072.5
132.5°	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2	1109.6	1112.0	1113.0
135°	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6	1169.1	1171.6	1172.6
137.5°	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7	1224.2	1226.6	1227.4
140°	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4	1259.6	1261.9	1262.3
142.5°	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3	1292.4	1294.4	1294.8
145°	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3	1338.1	1339.9	1340.1
147.5°	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5	1377.8	1379.1	1379.2
150°	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2	1402.7	1404.2	1404.3
152.5°	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7	1425.2	1426.7	1426.6
155°	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1	1455.6	1457.1	1456.9
157.5°	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8	1481.5	1483.2	1483.0
160°	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7	1496.2	1497.7	1497.6
162.5°	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6	1510.4	1512.0	1511.8
165°	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1
167.5°	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8	1541.6	1543.3	1543.1
170°	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1	1548.8	1550.5	1550.3
172.5°	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4	1554.2	1555.9	1555.7
175°	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3	1560.0	1561.8	1561.5
177.5°	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9	1560.4	1561.8	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	817.5	818.0	817.3	817.8	817.3	818.0	817.5	820.1	820.6	821.1	820.6
5°	761.8	758.2	757.6	756.8	757.6	758.2	761.8	763.3	764.5	766.8	771.0
7.5°	695.1	694.6	693.2	691.0	693.2	694.6	695.1	700.2	704.3	708.8	717.3
10°	652.3	650.9	650.5	648.5	650.5	650.9	652.3	658.8	663.5	670.0	681.6
12.5°	602.1	592.6	591.6	586.5	591.6	592.6	602.1	610.5	623.3	629.5	641.8
15°	512.7	510.9	505.0	501.1	505.0	510.9	512.7	519.8	524.5	541.7	561.5
17.5°	461.5	455.7	453.9	453.1	453.9	455.7	461.5	465.0	471.7	480.8	492.7
20°	428.6	423.3	422.5	421.8	422.5	423.3	428.6	432.8	438.2	447.9	460.3
22.5°	405.9	400.4	398.1	396.3	398.1	400.4	405.9	409.2	414.0	421.6	430.0
25°	367.1	365.0	363.8	363.3	363.8	365.0	367.1	370.1	374.8	385.2	394.0
27.5°	336.8	332.2	331.3	329.8	331.3	332.2	336.8	342.1	347.0	351.6	359.6
30°	319.5	318.0	315.9	314.2	315.9	318.0	319.5	322.2	325.4	333.4	341.1
32.5°	299.1	297.9	296.0	295.2	296.0	297.9	299.1	302.8	309.6	314.5	320.0
35°	276.6	272.4	270.7	268.0	270.7	272.4	276.6	279.6	282.3	286.4	296.4
37.5°	252.8	250.6	248.1	249.0	248.1	250.6	252.8	254.0	259.6	265.4	269.7
40°	234.3	232.8	232.2	232.0	232.2	232.8	234.3	238.1	244.9	247.6	254.1
42.5°	219.6	215.6	214.0	214.0	214.0	215.6	219.6	223.9	228.1	232.4	239.2
45°	197.3	193.5	190.8	191.1	190.8	193.5	197.3	198.8	202.3	211.0	214.8
47.5°	174.5	174.4	172.7	173.3	172.7	174.4	174.5	177.1	181.6	186.9	193.0
50°	163.6	161.8	160.7	160.9	160.7	161.8	163.6	165.6	168.3	171.0	180.5
52.5°	153.2	151.6	150.7	151.9	150.7	151.6	153.2	154.3	156.2	158.9	165.3
55°	136.1	134.3	134.0	133.7	134.0	134.3	136.1	137.5	139.9	142.0	145.0
57.5°	117.0	115.8	114.0	113.3	114.0	115.8	117.0	119.1	122.0	124.7	127.8
60°	103.2	100.8	97.9	97.6	97.9	100.8	103.2	107.1	108.3	112.4	116.0
62.5°	90.7	90.2	89.7	89.6	89.7	90.2	90.7	92.0	93.6	99.7	103.9
65°	79.6	79.3	79.6	79.9	79.6	79.3	79.6	80.2	80.5	81.0	82.9
67.5°	69.3	68.8	68.3	68.5	68.3	68.8	69.3	69.5	70.3	70.7	71.9
70°	61.6	61.2	60.9	60.9	60.9	61.2	61.6	62.1	62.7	63.3	64.8
72.5°	53.9	53.9	53.6	53.4	53.6	53.9	53.9	55.1	55.4	56.0	57.0
75°	43.2	42.6	42.6	42.6	42.6	42.6	43.2	43.5	43.8	44.7	45.2
77.5°	32.9	32.6	32.3	32.1	32.3	32.6	32.9	33.0	33.4	33.6	34.2
80°	26.1	25.7	25.4	25.4	25.4	25.7	26.1	26.3	26.3	27.3	26.9
82.5°	19.9	19.6	19.5	19.3	19.5	19.6	19.9	20.0	20.0	20.6	20.5
85°	10.6	10.9	10.6	11.2	10.6	10.9	10.6	10.4	10.6	11.2	11.2
87.5°	8.9	8.7	9.0	9.0	9.0	8.7	8.9	8.8	8.8	8.6	8.3
90°	28.9	29.4	29.9	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0
92.5°	29.5	29.8	30.1	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4
95°	49.2	49.0	48.7	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4
97.5°	63.8	64.1	64.4	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8
100°	74.0	74.5	75.0	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2
102.5°	78.8	79.5	80.2	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2
105°	82.6	83.7	84.6	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2
107.5°	85.1	86.1	87.1	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6
110°	86.0	87.0	88.0	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	87.5	88.3	89.1	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7
115°	146.5	128.4	110.4	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3
117.5°	554.9	495.7	436.4	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9
120°	788.7	754.9	721.0	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9
122.5°	877.3	870.8	864.2	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6
125°	961.1	961.8	962.6	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5
127.5°	1029.5	1029.7	1029.8	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9
130°	1072.2	1072.0	1071.7	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7
132.5°	1112.8	1112.5	1112.3	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2
135°	1172.1	1171.6	1171.1	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6
137.5°	1226.5	1225.7	1224.9	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7
140°	1261.2	1259.9	1258.6	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4
142.5°	1293.6	1292.3	1291.1	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3
145°	1338.9	1337.6	1336.3	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3
147.5°	1378.2	1377.1	1376.0	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5
150°	1403.1	1401.8	1400.6	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2
152.5°	1425.0	1423.4	1421.7	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7
155°	1454.9	1452.9	1450.9	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1
157.5°	1481.1	1479.2	1477.2	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8
160°	1495.9	1494.1	1492.3	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7
162.5°	1509.7	1507.5	1505.4	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6
165°	1527.4	1525.7	1523.9	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7
167.5°	1540.9	1538.6	1536.4	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8
170°	1548.1	1545.8	1543.6	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1
172.5°	1553.5	1551.2	1549.0	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4
175°	1558.9	1556.4	1553.9	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3
177.5°	1559.7	1558.0	1556.2	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	818.7	822.0	827.0	829.9	834.6	837.7	839.3	842.4	844.1	850.0	856.1
5°	773.0	777.8	786.0	793.7	802.0	810.6	816.8	823.9	830.4	841.6	853.5
7.5°	720.6	727.1	740.0	752.3	766.7	778.8	789.5	801.6	812.5	828.5	845.3
10°	681.3	692.8	709.7	721.2	740.1	752.3	769.1	782.4	797.6	818.9	837.8
12.5°	647.5	661.4	674.9	690.9	708.0	728.2	746.7	763.7	781.7	803.7	825.9
15°	586.1	606.2	627.2	643.4	666.5	687.8	709.4	732.5	754.4	780.7	809.7
17.5°	507.0	530.3	565.6	593.5	620.6	642.0	668.7	696.6	722.4	754.2	786.4
20°	471.3	488.4	512.4	549.9	590.8	613.5	640.8	671.5	701.1	735.7	770.3
22.5°	442.6	457.9	477.1	506.4	552.0	583.0	611.4	642.7	677.0	712.3	750.7
25°	401.7	412.4	432.5	456.1	487.5	538.7	569.7	601.1	638.4	676.3	720.0
27.5°	371.1	380.6	393.7	416.3	439.6	476.3	525.8	559.9	597.1	639.7	685.2
30°	347.6	358.9	373.4	389.3	414.8	443.5	492.8	532.5	569.2	613.0	661.5
32.5°	330.6	339.5	351.8	368.0	389.2	416.7	456.1	504.3	540.0	586.2	636.8
35°	302.6	313.0	323.1	338.4	355.6	380.7	410.6	462.1	497.6	543.1	594.1
37.5°	279.6	286.0	297.1	309.3	327.3	346.1	372.0	418.2	456.6	501.3	553.4
40°	262.1	270.1	278.4	292.0	306.8	324.8	350.2	384.6	428.6	472.5	523.3
42.5°	245.1	255.2	264.0	273.1	289.2	307.3	328.0	357.1	402.1	443.5	493.1
45°	224.5	231.1	240.2	250.3	263.6	279.0	297.3	322.7	365.9	401.7	448.2
47.5°	200.7	210.2	216.1	225.9	238.6	253.3	270.3	292.3	327.3	360.8	403.9
50°	184.3	194.1	202.6	211.5	222.8	236.9	251.1	272.4	300.6	335.8	376.0
52.5°	170.3	179.0	187.3	196.1	207.2	220.1	233.6	252.3	276.4	308.8	347.8
55°	151.1	156.5	165.1	174.0	183.7	196.1	209.1	224.8	245.6	272.7	304.4
57.5°	131.5	137.7	144.5	153.4	163.3	172.9	184.5	198.8	215.1	239.7	266.8
60°	120.4	125.2	130.8	139.9	149.1	157.6	168.9	180.8	196.1	217.5	240.5
62.5°	108.1	112.6	117.7	125.7	134.7	142.5	152.3	164.9	177.9	197.3	217.5
65°	87.5	94.1	99.1	106.2	113.6	121.9	129.6	139.7	151.1	166.5	184.6
67.5°	72.6	75.9	80.6	87.1	94.6	101.7	109.0	116.8	126.8	138.7	153.0
70°	66.0	67.2	68.0	74.2	81.4	88.5	95.2	102.7	111.2	121.0	133.4
72.5°	58.1	59.3	60.4	63.1	68.8	75.9	82.9	88.5	96.6	104.6	114.7
75°	46.2	47.9	48.8	50.3	52.4	57.1	63.6	68.9	73.7	79.9	87.9
77.5°	35.2	36.1	37.1	38.7	39.9	42.1	45.8	50.6	55.1	58.6	64.2
80°	27.8	28.1	29.3	29.9	31.7	33.1	34.9	38.7	43.2	44.7	48.5
82.5°	20.9	21.2	22.2	22.8	23.6	24.9	27.1	28.1	31.6	33.5	36.0
85°	11.6	11.2	12.1	12.1	12.8	13.3	13.9	15.4	16.2	18.6	19.3
87.5°	8.3	8.1	7.9	7.5	7.1	7.1	6.9	6.6	6.5	6.7	7.1
90°	23.8	22.5	20.5	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1
92.5°	26.8	26.1	25.1	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7
95°	45.2	44.0	42.2	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2
97.5°	59.8	58.8	54.7	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4
100°	66.2	64.2	60.0	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4
102.5°	68.6	66.0	101.6	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9
105°	71.5	68.8	137.0	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5
107.5°	93.4	96.3	178.2	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8
110°	172.1	197.2	269.5	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	406.0	497.3	515.2	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8
115°	579.2	695.1	688.9	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8
117.5°	742.0	770.0	765.6	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2
120°	828.9	825.9	821.3	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7
122.5°	880.8	879.0	874.1	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2
125°	953.8	952.0	947.3	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0
127.5°	1020.4	1017.9	1014.3	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6
130°	1063.0	1060.2	1057.4	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8
132.5°	1104.9	1102.6	1099.8	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8
135°	1164.1	1161.6	1159.4	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5
137.5°	1219.2	1216.8	1214.3	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7
140°	1255.1	1252.8	1250.1	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4
142.5°	1288.2	1286.2	1283.0	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9
145°	1334.6	1332.8	1328.6	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9
147.5°	1375.1	1373.9	1369.7	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2
150°	1399.7	1398.2	1394.2	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1
152.5°	1422.2	1420.7	1416.9	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4
155°	1452.6	1451.1	1448.2	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8
157.5°	1478.1	1476.4	1474.3	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5
160°	1493.2	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7
162.5°	1507.0	1505.2	1504.0	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1
165°	1523.9	1522.1	1521.4	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5
167.5°	1538.1	1536.4	1535.6	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9
170°	1545.3	1543.6	1543.0	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1
172.5°	1550.7	1549.0	1548.5	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5
175°	1556.6	1554.8	1554.3	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4
177.5°	1557.6	1556.2	1555.9	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	856.3	857.1	861.8	864.0	868.2	869.9	871.7	871.2	871.2	872.2	878.8
5°	858.2	864.1	873.0	881.5	889.9	897.0	901.7	906.4	908.2	916.8	924.5
7.5°	855.2	866.0	880.7	893.7	909.4	921.7	931.8	941.0	947.3	959.8	972.6
10°	851.1	866.5	883.0	899.9	921.5	937.8	954.3	967.1	971.2	989.8	1000.5
12.5°	843.0	863.6	884.7	906.6	927.6	950.1	968.3	981.0	995.6	1012.3	1032.0
15°	831.0	854.7	882.2	910.3	940.5	967.7	987.2	1009.4	1025.3	1043.7	1060.8
17.5°	813.7	844.1	879.1	911.6	946.5	975.7	1002.7	1023.9	1035.1	1045.6	1048.2
20°	799.9	832.7	873.9	912.4	947.2	981.0	1007.6	1025.3	1028.3	1028.6	1012.9
22.5°	785.1	822.1	865.1	904.5	946.3	983.8	1004.5	1012.1	1000.4	980.3	950.0
25°	757.6	800.5	850.5	895.5	941.0	976.5	983.7	970.3	929.2	886.0	831.3
27.5°	727.9	776.1	829.7	879.7	928.3	950.3	934.9	886.9	812.9	748.5	670.5
30°	706.2	760.3	812.9	868.9	913.8	923.3	888.1	817.4	731.0	634.0	556.2
32.5°	681.3	738.0	795.9	853.7	891.4	882.1	823.9	736.9	635.6	540.3	466.7
35°	645.8	704.4	766.8	824.7	848.7	808.8	721.8	608.6	505.0	416.0	365.4
37.5°	604.8	668.6	733.5	786.7	785.1	718.4	600.0	483.0	396.0	343.3	307.3
40°	575.7	640.2	710.3	755.3	736.0	649.4	520.9	410.6	347.0	305.0	278.7
42.5°	547.8	612.5	682.1	717.9	684.4	577.9	450.0	363.5	311.0	278.3	256.9
45°	500.3	568.5	633.1	652.9	593.1	475.7	363.8	301.2	266.3	242.0	227.2
47.5°	453.8	521.0	579.9	580.3	499.4	385.8	307.0	260.6	230.8	212.1	201.3
50°	425.4	489.3	538.7	531.0	439.3	343.2	274.5	234.6	209.8	195.3	184.0
52.5°	393.5	455.4	498.2	476.3	388.4	302.0	245.4	211.9	191.3	178.7	168.7
55°	347.0	402.0	432.2	399.1	316.9	251.1	207.4	181.0	165.6	155.0	146.5
57.5°	301.4	346.7	365.8	327.2	260.9	208.3	175.4	155.7	140.4	132.8	128.3
60°	272.7	311.5	324.8	282.3	226.9	182.2	155.3	137.0	125.7	120.7	116.3
62.5°	244.6	276.2	281.8	242.7	197.8	159.5	136.4	120.9	113.4	108.6	104.4
65°	203.0	225.7	223.1	191.7	156.5	126.6	109.7	100.3	94.7	87.9	80.5
67.5°	167.1	181.0	172.6	149.1	119.5	98.4	87.4	80.2	73.3	66.8	65.1
70°	144.3	152.3	143.5	121.9	97.9	82.5	73.7	65.1	60.9	59.5	56.8
72.5°	122.6	125.4	115.8	97.3	79.7	68.4	59.7	54.9	52.7	51.4	49.7
75°	92.0	89.9	81.7	67.2	55.3	47.6	45.0	43.2	41.7	40.6	39.6
77.5°	64.6	61.6	54.2	44.8	38.5	34.9	33.3	32.3	31.6	31.0	30.1
80°	48.5	46.4	39.1	31.9	29.3	27.5	26.6	25.4	25.4	24.9	23.9
82.5°	35.5	33.2	26.8	23.4	21.9	20.9	20.2	19.5	19.3	19.4	18.8
85°	18.6	15.1	13.3	12.8	11.8	11.2	11.6	10.9	10.9	10.9	10.6
87.5°	6.4	5.9	6.1	6.4	7.1	7.5	7.8	8.2	8.8	8.8	9.3
90°	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0
92.5°	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4
95°	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4
97.5°	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8
100°	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2
102.5°	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2
105°	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2
107.5°	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6
110°	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7
115°	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3
117.5°	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9
120°	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9
122.5°	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6
125°	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5
127.5°	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9
130°	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7
132.5°	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2
135°	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6
137.5°	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7
140°	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4
142.5°	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3
145°	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3
147.5°	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5
150°	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2
152.5°	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7
155°	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1
157.5°	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8
160°	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7
162.5°	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6
165°	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7
167.5°	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8
170°	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1
172.5°	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4
175°	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3
177.5°	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	881.2	884.3	885.7	885.7	887.4	886.7	886.0
5°	931.8	937.5	938.7	944.0	947.8	946.7	947.2
7.5°	982.2	991.3	1000.2	1004.2	1005.0	1007.3	1008.2
10°	1013.2	1020.6	1034.5	1032.5	1042.8	1048.7	1038.9
12.5°	1043.1	1053.0	1062.7	1065.3	1071.2	1073.1	1069.2
15°	1070.0	1075.3	1075.9	1074.4	1076.3	1074.8	1069.1
17.5°	1044.8	1036.2	1018.7	1010.3	1003.8	994.1	990.2
20°	1003.1	977.7	948.2	936.3	922.4	895.2	901.7
22.5°	913.2	884.2	854.7	820.1	803.6	777.8	776.3
25°	773.3	723.3	668.3	629.8	607.4	581.6	570.4
27.5°	601.3	538.3	493.2	470.4	449.6	429.2	428.3
30°	488.1	440.8	405.9	386.3	373.7	365.0	366.9
32.5°	411.5	379.0	355.5	339.3	329.9	323.4	323.3
35°	336.4	314.2	299.0	292.3	285.5	280.7	281.1
37.5°	287.9	274.5	266.1	258.6	254.4	252.1	250.7
40°	263.0	252.1	245.6	241.1	237.6	234.3	233.7
42.5°	243.4	234.3	227.8	224.3	221.0	218.6	218.1
45°	215.9	208.6	202.6	198.8	197.3	195.3	195.3
47.5°	192.1	184.8	180.2	177.8	175.2	173.9	173.8
50°	176.0	170.4	166.3	164.8	162.7	161.8	161.5
52.5°	161.6	157.4	154.4	153.4	152.5	151.4	151.5
55°	142.0	139.7	138.5	137.5	136.1	134.3	135.5
57.5°	125.5	123.5	120.3	117.5	116.1	114.9	115.3
60°	113.9	109.7	105.6	102.3	101.5	98.8	98.8
62.5°	99.3	93.4	88.3	86.5	85.6	84.4	84.1
65°	76.3	74.0	72.8	71.6	71.0	71.0	70.4
67.5°	63.2	62.3	61.0	60.7	60.1	60.0	59.7
70°	55.9	54.7	54.1	53.9	53.2	53.6	52.7
72.5°	48.8	47.8	47.8	47.0	46.7	46.7	46.0
75°	38.4	38.4	38.2	37.9	37.3	37.0	37.3
77.5°	29.5	29.6	29.1	29.1	29.0	29.1	28.8
80°	23.7	23.9	23.7	23.4	23.1	23.4	23.1
82.5°	18.7	18.3	18.2	18.1	18.1	17.9	17.9
85°	10.6	10.9	10.6	10.4	10.4	10.4	10.6
87.5°	9.3	9.5	9.7	9.8	9.9	10.0	9.9
90°	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331801-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)