

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331804-927

Luminaire Tested: **S122RDIW-S485D1440U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331804-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D1440U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5307.4 lumens  
Efficiency: N/A  
Efficacy: 87.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.2	1.2
10°-20°	168.0	3.2
20°-30°	235.9	4.4
30°-40°	257.3	4.8
40°-50°	236.6	4.5
50°-60°	185.8	3.5
60°-70°	121.1	2.3
70°-80°	62.5	1.2
80°-90°	21.8	0.4
90°-100°	89.7	1.7
100°-110°	278.5	5.2
110°-120°	476.1	9.0
120°-130°	626.1	11.8
130°-140°	702.7	13.2
140°-150°	689.0	13.0
150°-160°	577.9	10.9
160°-170°	383.3	7.2
170°-180°	134.0	2.5
0°-30°	465.2	8.8
0°-40°	722.4	13.6
0°-60°	1144.8	21.6
0°-90°	1350.2	25.4
90°-120°	844.3	15.9
90°-150°	2862.0	53.9
90°-180°	3957.0	74.6
0°-180°	5307.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	16	42	40	41	4
95°	62	74	76	76	74	71
105°	257	260	263	265	265	271
115°	478	484	482	481	478	472
125°	695	705	702	699	697	621
135°	899	912	915	914	910	694
145°	1092	1100	1107	1108	1104	682
155°	1248	1252	1255	1261	1258	574
165°	1358	1357	1357	1364	1359	383
175°	1413	1409	1407	1414	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.8	7.6	7.4	7.2	7.0	7.4	8.6	9.8	11.0	12.1	12.0
90°	1.2	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3
92.5°	21.2	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1
95°	62.1	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4
97.5°	113.4	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5
100°	151.7	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8
102.5°	191.8	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2
105°	256.7	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2
107.5°	322.2	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6
110°	364.2	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.1	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7
115°	477.7	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2
117.5°	545.1	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3
120°	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9
122.5°	631.1	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2
125°	695.1	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4
127.5°	757.4	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7
130°	796.5	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2
132.5°	840.5	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5
135°	899.3	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6
137.5°	961.2	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8
140°	998.4	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1
142.5°	1036.6	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6
145°	1091.5	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3
147.5°	1140.5	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0
150°	1173.9	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7
152.5°	1203.6	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5
155°	1248.0	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5
157.5°	1285.9	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3
160°	1308.9	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1
162.5°	1329.9	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4
165°	1357.9	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5
167.5°	1381.2	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3
170°	1393.7	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8
172.5°	1402.3	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4
175°	1412.8	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7
177.5°	1417.1	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	11.7	11.5	11.3	11.2	11.2	11.3	11.4	11.4
90°	40.7	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.2	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.4	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	263.8	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	327.9	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.5	371.0	370.2	369.4	368.6	367.8





TEST NUMBER: P331804-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.0	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	482.0	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.7	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	634.5	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	700.6	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	764.8	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.7	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	851.4	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.3	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.5	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1051.9	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.6	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1156.5	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1257.8	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1294.1	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1315.7	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1335.2	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1360.4	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1381.2	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1392.7	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1401.2	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1410.6	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)