

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331788-927

Luminaire Tested: **S122RDIW-S485D435U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331788-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2535.5 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	44	39
3	83	74	67	61	77	69	62	57	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	2.4
10°-20°	168.0	6.6
20°-30°	235.9	9.3
30°-40°	257.3	10.1
40°-50°	236.6	9.3
50°-60°	185.8	7.3
60°-70°	121.1	4.8
70°-80°	62.5	2.5
80°-90°	17.9	0.7
90°-100°	27.0	1.1
100°-110°	83.7	3.3
110°-120°	143.1	5.6
120°-130°	188.1	7.4
130°-140°	211.2	8.3
140°-150°	207.1	8.2
150°-160°	173.7	6.8
160°-170°	115.2	4.5
170°-180°	40.3	1.6
0°-30°	465.2	18.3
0°-40°	722.4	28.5
0°-60°	1144.8	45.2
0°-90°	1346.3	53.1
90°-120°	253.7	10.0
90°-150°	860.1	33.9
90°-180°	1189.0	46.9
0°-180°	2535.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	0	5	13	12	12	2
95°	19	22	23	23	22	21
105°	77	78	79	80	80	82
115°	144	146	145	145	144	142
125°	209	212	211	210	210	187
135°	270	274	275	274	274	209
145°	328	331	333	333	332	205
155°	375	376	377	379	378	173
165°	408	408	408	410	408	115
175°	425	424	423	425	423	40
180°	425	425	425	425	425	



TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.7	7.0	6.3	5.7	5.1	4.9	5.2	5.6	5.9	6.3	6.2
90°	0.4	1.3	2.3	3.2	4.2	5.5	7.3	9.0	10.8	12.6	12.4
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.6	11.0	11.4	11.4
95°	18.7	19.5	20.3	21.1	21.9	22.3	22.5	22.7	22.8	23.0	23.0
97.5°	34.1	34.8	35.5	36.2	36.9	37.4	37.7	38.0	38.3	38.6	38.6
100°	45.6	46.2	46.8	47.5	48.2	48.6	48.8	49.0	49.3	49.5	49.5
102.5°	57.7	58.1	58.6	59.2	59.7	60.1	60.4	60.7	61.0	61.3	61.4
105°	77.2	77.4	77.6	77.9	78.1	78.3	78.5	78.7	78.8	79.0	79.1
107.5°	96.8	97.2	97.5	97.9	98.2	98.4	98.4	98.4	98.4	98.4	98.5
110°	109.5	110.0	110.4	110.9	111.4	111.6	111.6	111.6	111.6	111.6	111.6



TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.3	123.7	124.2	124.7	125.2	125.4	125.3	125.2	125.2	125.1	124.9
115°	143.5	144.0	144.5	145.0	145.4	145.6	145.4	145.3	145.1	145.0	144.9
117.5°	163.8	164.5	165.1	165.7	166.4	166.4	166.0	165.6	165.1	164.7	164.5
120°	177.3	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.3
122.5°	189.6	190.4	191.2	191.9	192.7	192.9	192.4	191.9	191.5	191.1	190.9
125°	208.9	209.6	210.3	211.0	211.8	212.0	211.8	211.5	211.3	211.0	210.8
127.5°	227.6	228.5	229.4	230.4	231.2	231.6	231.3	231.0	230.7	230.4	230.1
130°	239.4	240.4	241.5	242.5	243.5	244.0	243.8	243.7	243.5	243.4	243.2
132.5°	252.6	253.4	254.3	255.2	256.0	256.4	256.4	256.5	256.5	256.5	256.2
135°	270.3	271.2	272.0	272.9	273.8	274.3	274.4	274.6	274.7	274.9	274.8
137.5°	288.8	289.5	290.3	291.0	291.7	292.2	292.4	292.6	292.8	293.0	292.9
140°	300.1	300.8	301.5	302.2	302.9	303.5	303.9	304.3	304.7	305.1	305.1
142.5°	311.6	312.3	313.0	313.7	314.4	314.9	315.1	315.4	315.7	316.0	316.1
145°	328.0	328.6	329.2	329.7	330.3	330.8	331.3	331.8	332.2	332.7	332.8
147.5°	342.8	343.4	344.1	344.8	345.5	345.9	346.3	346.6	346.9	347.2	347.4
150°	352.8	353.3	353.8	354.3	354.7	355.1	355.5	355.8	356.1	356.4	356.6
152.5°	361.7	362.2	362.7	363.1	363.6	364.1	364.4	364.8	365.2	365.6	365.9
155°	375.0	375.3	375.5	375.8	376.0	376.3	376.5	376.8	377.0	377.2	377.6
157.5°	386.5	386.7	386.8	387.0	387.1	387.2	387.4	387.5	387.7	387.9	388.4
160°	393.4	393.6	393.7	393.9	394.0	394.1	394.2	394.3	394.3	394.4	394.9
162.5°	399.7	399.7	399.7	399.7	399.8	399.9	400.0	400.1	400.1	400.2	400.7
165°	408.1	408.0	407.9	407.8	407.7	407.7	407.7	407.7	407.7	407.7	408.3
167.5°	415.1	414.9	414.6	414.4	414.2	414.0	414.0	414.0	414.0	414.0	414.5
170°	418.8	418.6	418.4	418.1	417.9	417.7	417.6	417.6	417.5	417.4	418.0
172.5°	421.4	421.2	421.0	420.7	420.5	420.3	420.3	420.2	420.1	420.0	420.6
175°	424.6	424.4	424.1	423.9	423.7	423.4	423.3	423.1	422.9	422.8	423.3
177.5°	425.9	425.7	425.5	425.3	425.1	424.9	424.8	424.7	424.5	424.5	424.8
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	6.0	5.9	5.8	5.7	5.7	5.7	5.7	5.8
90°	12.3	12.1	12.0	11.9	12.0	12.0	12.1	12.2
92.5°	11.5	11.5	11.6	11.6	11.6	11.6	11.6	11.6
95°	23.0	23.0	23.0	22.9	22.7	22.6	22.4	22.3
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.5	49.5	49.5	49.5	49.4	49.4	49.3	49.2
102.5°	61.4	61.5	61.6	61.6	61.5	61.4	61.3	61.2
105°	79.3	79.5	79.6	79.7	79.7	79.7	79.7	79.7
107.5°	98.5	98.6	98.7	98.5	98.2	97.8	97.4	97.0
110°	111.6	111.6	111.6	111.5	111.2	111.0	110.7	110.5



TEST NUMBER: P331788-927

CATALOG NUMBER: S122RDIW-S485D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.8	124.5	124.4	124.1	124.0	123.8	123.7	123.5
115°	144.8	144.7	144.7	144.5	144.3	144.0	143.8	143.5
117.5°	164.3	164.1	163.9	163.7	163.4	163.2	163.0	162.7
120°	177.3	177.3	177.3	177.2	177.0	176.7	176.5	176.3
122.5°	190.7	190.5	190.3	190.1	190.0	189.8	189.6	189.4
125°	210.6	210.3	210.1	209.9	209.8	209.8	209.7	209.6
127.5°	229.8	229.6	229.3	229.0	228.7	228.5	228.2	228.0
130°	243.0	242.9	242.7	242.5	242.2	241.9	241.5	241.2
132.5°	255.9	255.5	255.2	254.8	254.6	254.3	254.1	253.8
135°	274.7	274.6	274.6	274.4	274.2	273.9	273.7	273.5
137.5°	292.9	292.8	292.8	292.6	292.2	291.9	291.6	291.3
140°	305.1	305.1	305.1	304.9	304.6	304.3	304.0	303.6
142.5°	316.1	316.2	316.2	316.1	315.8	315.4	315.1	314.8
145°	332.9	333.0	333.0	332.9	332.6	332.2	331.9	331.6
147.5°	347.5	347.8	347.9	347.8	347.5	347.2	346.9	346.7
150°	356.9	357.1	357.4	357.4	357.1	356.9	356.6	356.4
152.5°	366.1	366.5	366.8	366.8	366.5	366.1	365.9	365.6
155°	378.0	378.4	378.8	378.9	378.7	378.4	378.2	378.0
157.5°	388.9	389.4	390.0	390.1	389.7	389.3	389.0	388.6
160°	395.4	395.9	396.3	396.4	396.1	395.8	395.5	395.1
162.5°	401.2	401.8	402.3	402.4	402.0	401.6	401.2	400.9
165°	408.8	409.4	410.0	410.0	409.6	409.2	408.8	408.4
167.5°	415.1	415.7	416.2	416.3	415.8	415.4	415.0	414.6
170°	418.5	419.1	419.6	419.7	419.2	418.7	418.3	417.8
172.5°	421.1	421.7	422.2	422.2	421.8	421.3	420.8	420.3
175°	423.9	424.5	425.0	425.1	424.6	424.1	423.7	423.2
177.5°	425.2	425.6	426.0	426.0	425.6	425.2	424.8	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3

(END OF REPORT)