

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331469

Luminaire Tested: **S122DIW-S290D435U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331469
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D435U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2934.4 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	42	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7627	7627	7627
5°	7656	7546	7592
10°	7612	7470	7507
15°	7517	7373	7366
20°	7383	7228	7220
25°	7251	7049	7049
30°	7081	6885	6825
35°	6922	6688	6589
40°	6721	6492	6367
45°	6524	6295	6140
50°	6310	6094	5878
55°	6086	5858	5638
60°	5838	5574	5370
65°	5570	5295	5051
70°	5231	4952	4716
75°	4760	4560	4448
80°	4221	4100	3887
85°	3446	3279	2946



TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	1.5
10°-20°	125.0	4.3
20°-30°	183.7	6.3
30°-40°	213.4	7.3
40°-50°	213.2	7.3
50°-60°	185.9	6.3
60°-70°	137.5	4.7
70°-80°	77.9	2.7
80°-90°	22.4	0.8
90°-100°	19.7	0.7
100°-110°	72.3	2.5
110°-120°	193.1	6.6
120°-130°	318.8	10.9
130°-140°	339.1	11.6
140°-150°	315.2	10.7
150°-160°	253.4	8.6
160°-170°	163.3	5.6
170°-180°	56.2	1.9
0°-30°	353.2	12.0
0°-40°	566.6	19.3
0°-60°	965.7	32.9
0°-90°	1203.4	41.0
90°-120°	285.1	9.7
90°-150°	1258.2	42.9
90°-180°	1731.0	59.0
0°-180°	2934.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	472	472	472	472	472	
5°	472	470	466	469	468	45
15°	450	447	441	443	441	127
25°	407	403	396	396	396	187
35°	351	346	339	337	334	219
45°	286	282	276	271	269	220
55°	216	213	208	203	200	193
65°	146	143	139	135	132	144
75°	76	75	73	71	71	82
85°	19	18	18	16	16	21
90°	0	5	8	11	12	2
95°	28	15	17	19	18	34
105°	130	136	26	31	32	139
115°	246	253	264	75	35	242
125°	348	353	361	364	365	310
135°	430	437	441	445	444	332
145°	499	499	506	508	506	312
155°	549	546	550	553	550	253
165°	579	576	577	580	577	163
175°	592	589	590	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	474.6	474.2	473.8	473.4	473.0	472.4	471.5	470.6	469.7	468.8	469.6
5°	472.4	472.0	471.6	471.2	470.8	470.1	469.0	467.9	466.7	465.6	466.4
7.5°	468.3	467.6	467.0	466.4	465.8	464.9	463.8	462.6	461.5	460.4	461.2
10°	464.3	463.6	462.9	462.2	461.4	460.5	459.3	458.1	456.9	455.6	456.4
12.5°	458.8	458.2	457.6	456.9	456.3	455.4	454.2	453.0	451.8	450.6	451.1
15°	449.7	449.1	448.5	447.9	447.3	446.4	445.0	443.7	442.4	441.1	441.5
17.5°	438.1	437.5	436.9	436.3	435.7	434.7	433.4	432.0	430.7	429.4	429.8
20°	429.7	429.1	428.5	427.9	427.3	426.3	424.9	423.5	422.1	420.7	421.0
22.5°	421.4	420.5	419.7	418.8	418.0	416.9	415.6	414.2	412.9	411.6	411.6
25°	407.0	406.2	405.4	404.6	403.8	402.5	400.8	399.1	397.4	395.7	395.9
27.5°	390.7	390.0	389.2	388.5	387.8	386.7	385.4	384.0	382.7	381.3	381.0
30°	379.8	379.0	378.2	377.4	376.5	375.4	373.9	372.4	370.8	369.3	369.0
32.5°	368.1	367.5	366.9	366.2	365.6	364.4	362.8	361.3	359.7	358.1	357.5
35°	351.2	350.1	349.1	348.1	347.1	345.8	344.2	342.6	341.0	339.3	338.7
37.5°	332.0	331.1	330.2	329.3	328.4	327.2	325.6	324.0	322.3	320.7	320.0
40°	318.9	318.1	317.3	316.5	315.7	314.5	312.8	311.2	309.6	308.0	307.1
42.5°	306.2	305.4	304.6	303.8	303.0	301.7	300.1	298.5	296.9	295.3	294.3
45°	285.7	285.0	284.3	283.6	282.9	281.8	280.3	278.8	277.3	275.7	274.6
47.5°	265.4	264.7	264.1	263.4	262.7	261.6	260.0	258.5	256.9	255.3	254.1
50°	251.2	250.7	250.2	249.7	249.2	248.2	246.8	245.4	244.0	242.6	241.2
52.5°	237.4	236.7	236.1	235.4	234.7	233.7	232.4	231.1	229.7	228.4	227.2
55°	216.2	215.6	215.0	214.4	213.8	212.9	211.7	210.5	209.3	208.1	206.8
57.5°	195.0	194.5	194.0	193.5	193.0	192.1	190.8	189.5	188.1	186.8	185.6
60°	180.8	180.4	180.0	179.6	179.2	178.3	176.9	175.5	174.0	172.6	171.5
62.5°	167.0	166.3	165.7	165.1	164.4	163.5	162.4	161.4	160.3	159.2	158.1
65°	145.8	145.2	144.6	144.0	143.4	142.6	141.6	140.6	139.6	138.6	137.6
67.5°	124.3	123.8	123.3	122.8	122.4	121.7	120.7	119.8	118.9	118.0	117.3
70°	110.8	110.4	110.0	109.6	109.2	108.6	107.7	106.8	105.8	104.9	104.2
72.5°	97.0	96.6	96.2	95.8	95.4	94.9	94.3	93.8	93.2	92.6	91.9
75°	76.3	76.1	75.9	75.7	75.5	75.2	74.7	74.1	73.6	73.1	72.5
77.5°	57.8	57.4	57.1	56.8	56.4	56.1	55.9	55.7	55.5	55.3	55.0
80°	45.4	45.3	45.2	45.1	45.0	44.9	44.7	44.5	44.3	44.1	43.8
82.5°	33.8	33.8	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2	32.8
85°	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.8	17.7	17.4
87.5°	6.6	6.7	6.7	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.7
90°	0.4	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2
95°	27.8	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1
97.5°	55.1	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7
100°	75.7	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1
102.5°	98.2	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0
105°	129.9	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1
107.5°	166.1	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4
110°	189.3	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3



TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.2	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0
115°	245.8	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7
117.5°	276.6	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5
120°	299.2	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4
122.5°	318.3	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2
125°	347.5	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8
127.5°	373.9	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1
130°	390.7	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2
132.5°	407.8	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2
135°	430.0	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6
137.5°	452.5	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5
140°	467.2	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1
142.5°	479.5	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7
145°	498.8	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3
147.5°	515.6	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7
150°	526.6	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0
152.5°	535.8	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5
155°	549.2	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1
157.5°	559.7	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7
160°	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5
162.5°	571.4	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7
165°	578.7	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1
167.5°	584.2	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5
170°	587.3	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2
172.5°	589.3	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3
175°	592.0	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5
177.5°	592.4	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	470.4	471.2	472.0	472.4	472.2	472.0	471.9	471.7
5°	467.3	468.1	468.9	469.2	469.0	468.8	468.6	468.4
7.5°	462.0	462.8	463.6	463.9	463.7	463.4	463.2	463.0
10°	457.3	458.1	458.9	459.1	458.8	458.5	458.2	457.9
12.5°	451.7	452.2	452.8	453.0	452.8	452.5	452.3	452.1
15°	441.9	442.3	442.7	442.7	442.2	441.7	441.2	440.7
17.5°	430.3	430.8	431.2	431.2	430.7	430.3	429.8	429.3
20°	421.3	421.6	421.9	421.8	421.4	421.0	420.6	420.2
22.5°	411.7	411.8	411.8	411.7	411.5	411.2	411.0	410.8
25°	396.1	396.3	396.5	396.5	396.3	396.1	395.9	395.7
27.5°	380.7	380.4	380.1	379.7	379.2	378.7	378.3	377.8
30°	368.7	368.4	368.1	367.8	367.4	367.0	366.6	366.1
32.5°	357.0	356.4	355.9	355.4	355.0	354.6	354.2	353.8
35°	338.1	337.5	336.9	336.4	335.9	335.4	334.9	334.3
37.5°	319.2	318.5	317.7	317.1	316.6	316.1	315.7	315.2
40°	306.2	305.3	304.4	303.7	303.3	302.9	302.5	302.1
42.5°	293.3	292.3	291.3	290.5	290.0	289.4	288.9	288.3
45°	273.5	272.4	271.3	270.5	270.1	269.7	269.3	268.9
47.5°	253.0	251.8	250.6	249.7	249.2	248.6	248.0	247.4
50°	239.8	238.3	236.9	236.0	235.5	235.0	234.5	234.0
52.5°	226.1	224.9	223.7	222.8	222.1	221.5	220.8	220.1
55°	205.6	204.4	203.2	202.4	201.9	201.3	200.8	200.3
57.5°	184.4	183.2	182.0	181.2	180.9	180.5	180.1	179.7
60°	170.4	169.3	168.2	167.5	167.2	166.9	166.6	166.3
62.5°	157.1	156.1	155.1	154.4	154.0	153.6	153.2	152.8
65°	136.7	135.8	134.9	134.2	133.7	133.2	132.7	132.2
67.5°	116.6	115.9	115.2	114.6	114.2	113.8	113.4	113.0
70°	103.5	102.8	102.1	101.6	101.2	100.7	100.3	99.9
72.5°	91.2	90.5	89.8	89.2	88.9	88.6	88.3	87.9
75°	71.9	71.3	70.7	70.5	70.7	70.9	71.1	71.3
77.5°	54.7	54.4	54.1	53.8	53.5	53.3	53.0	52.7
80°	43.5	43.2	42.9	42.6	42.4	42.2	42.0	41.8
82.5°	32.4	32.0	31.6	31.4	31.4	31.3	31.3	31.3
85°	17.1	16.8	16.5	16.3	16.2	16.1	16.0	15.9
87.5°	6.5	6.4	6.2	6.1	6.1	6.0	6.0	5.9
90°	9.5	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	17.6	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.1	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	25.9	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	27.0	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	28.2	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	34.4	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	55.8	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331469

CATALOG NUMBER: S122DIW-S290D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	119.4	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	175.8	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	270.8	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	315.6	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	334.8	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	362.5	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	388.1	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	404.3	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.1	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	442.6	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	463.5	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.0	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	489.5	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.0	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.2	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	531.6	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.1	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	551.7	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	561.4	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.0	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	572.3	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.2	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	586.9	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	588.9	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.2	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.4	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)