

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331817-927

Luminaire Tested: **S122RDIW-S675D1240U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331817-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5939.2 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34																				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	30																				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26																				
3	79	71	64	58	72	64	58	54	52	48	44	41	38	36	30	29	27	22																				
4	73	63	55	50	66	57	51	46	46	42	38	37	34	31	27	25	24	20																				
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18																				
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16																				
7	57	46	38	33	52	42	35	31	34	30	26	28	24	22	21	19	17	14																				
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	13																				
9	50	38	31	26	45	35	29	24	29	24	21	23	20	18	18	16	14	12																				
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	1.9
10°-20°	307.4	5.2
20°-30°	396.1	6.7
30°-40°	376.4	6.3
40°-50°	322.5	5.4
50°-60°	245.6	4.1
60°-70°	155.2	2.6
70°-80°	77.5	1.3
80°-90°	23.5	0.4
90°-100°	44.7	0.8
100°-110°	163.8	2.8
110°-120°	437.9	7.4
120°-130°	722.9	12.2
130°-140°	768.8	12.9
140°-150°	714.5	12.0
150°-160°	574.5	9.7
160°-170°	370.2	6.2
170°-180°	127.4	2.1
0°-30°	813.8	13.7
0°-40°	1190.3	20.0
0°-60°	1758.3	29.6
0°-90°	2014.6	33.9
90°-120°	646.4	10.9
90°-150°	2852.5	48.0
90°-180°	3925.0	66.1
0°-180°	5939.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	26	1	26	1	26	12
95°	42	63	42	63	42	39
105°	74	295	74	295	74	77
115°	80	557	80	557	80	199
125°	828	788	828	788	828	717
135°	1007	975	1007	975	1007	776
145°	1148	1131	1148	1131	1148	718
155°	1246	1245	1246	1245	1246	575
165°	1309	1312	1309	1312	1309	370
175°	1334	1342	1334	1342	1334	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	10.4	10.6	10.5	10.5	10.4	10.2	10.1	10.1	9.6	9.7	9.0
90°	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5	20.4	19.4	17.7
92.5°	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6	23.1	22.5	21.6
95°	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9	38.9	37.8	36.3
97.5°	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3	51.4	50.6	47.1
100°	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7	57.0	55.2	51.6
102.5°	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2	59.0	56.8	87.4
105°	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8	61.5	59.1	117.9
107.5°	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0	80.3	82.8	153.3
110°	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5	148.1	169.6	231.8



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6	349.2	427.7	443.1
115°	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5	498.2	597.9	592.6
117.5°	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0	638.1	662.3	658.5
120°	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5	712.9	710.3	706.5
122.5°	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1	757.6	756.1	751.9
125°	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9	820.4	818.9	814.8
127.5°	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8	877.7	875.4	872.4
130°	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6	914.3	911.9	909.5
132.5°	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4	950.3	948.3	945.9
135°	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4	1001.2	999.1	997.1
137.5°	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8	1048.7	1046.6	1044.3
140°	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5	1079.5	1077.6	1075.2
142.5°	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8	1108.0	1106.3	1103.5
145°	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4	1147.9	1146.4	1142.7
147.5°	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9	1182.8	1181.6	1178.1
150°	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1	1203.9	1202.6	1199.1
152.5°	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6	1223.3	1221.9	1218.7
155°	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7	1249.4	1248.2	1245.5
157.5°	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8	1271.3	1269.9	1268.0
160°	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6	1284.3	1283.0	1281.8
162.5°	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6	1296.1	1294.7	1293.6
165°	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2	1308.5
167.5°	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4	1322.9	1321.4	1320.8
170°	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6	1329.1	1327.6	1327.1
172.5°	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2	1333.7	1332.2	1331.8
175°	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3	1338.8	1337.3	1336.9
177.5°	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8	1339.7	1338.5	1338.2
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	8.7	8.6	8.3	7.6	7.4	7.3	8.4	9.6	8.8	8.2	8.1
90°	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6	19.3	19.2	18.9
95°	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0	55.8	48.8	41.7
97.5°	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0	105.0	84.9	65.0
100°	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5	142.0	112.5	83.0
102.5°	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7	216.4	210.2	204.0
105°	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6	301.0	307.5	313.9
107.5°	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6	381.8	387.0	392.2
110°	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3	433.8	438.3	442.8



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9	482.9	486.9	490.9
115°	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2	560.9	564.5	568.2
117.5°	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2	631.3	635.3	639.4
120°	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3	681.6	684.8	688.0
122.5°	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8	725.2	728.6	732.0
125°	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8	790.6	793.4	796.2
127.5°	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7	850.8	853.9	857.1
130°	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7	889.1	892.6	896.0
132.5°	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5	927.4	930.3	933.3
135°	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9	978.3	981.8	985.2
137.5°	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8	1028.3	1030.6	1033.1
140°	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1	1060.9	1062.6	1064.3
142.5°	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1	1088.6	1090.2	1091.7
145°	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8	1130.7	1130.4	1130.2
147.5°	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0	1168.2	1167.4	1166.6
150°	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9	1192.4	1190.9	1189.3
152.5°	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8	1213.1	1211.4	1209.7
155°	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2	1243.3	1241.3	1239.4
157.5°	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1	1267.4	1265.7	1264.2
160°	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1281.8	1280.4	1279.1
162.5°	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5	1294.1	1292.8	1291.6
165°	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1	1310.8	1309.5	1308.2
167.5°	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5	1323.2	1321.9	1320.6
170°	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5	1330.2	1328.9	1327.6
172.5°	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1	1334.8	1333.6	1332.2
175°	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1	1340.6	1339.1	1337.6
177.5°	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1	1341.9	1340.7	1339.5
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	8.2	8.3	8.0	8.4	8.7	8.7	9.0	8.9	9.0	9.3	9.1
90°	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5	22.6	23.7	24.5
92.5°	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6	24.2	24.7	25.1
95°	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9	41.0	42.1	42.5
97.5°	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3	53.2	54.0	54.6
100°	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7	60.4	62.1	63.2
102.5°	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2	63.5	65.8	67.2
105°	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8	66.2	68.6	70.2
107.5°	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0	75.5	73.1	72.3
110°	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5	105.0	83.4	73.1



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6	192.1	113.5	74.5
115°	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5	298.8	199.1	141.5
117.5°	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0	589.9	565.8	528.2
120°	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5	718.0	720.6	707.4
122.5°	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1	760.7	762.2	760.2
125°	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9	823.4	824.9	825.9
127.5°	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8	882.0	884.2	885.4
130°	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6	919.0	921.3	922.4
132.5°	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4	954.3	956.4	957.3
135°	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4	1005.5	1007.7	1008.5
137.5°	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8	1052.9	1055.0	1055.7
140°	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5	1083.4	1085.4	1085.8
142.5°	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8	1111.6	1113.3	1113.6
145°	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4	1150.9	1152.4	1152.6
147.5°	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9	1185.0	1186.1	1186.2
150°	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1	1206.5	1207.8	1207.8
152.5°	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6	1225.8	1227.2	1227.1
155°	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7	1252.0	1253.3	1253.1
157.5°	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8	1274.2	1275.7	1275.6
160°	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6	1286.9	1288.2	1288.1
162.5°	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6	1299.0	1300.5	1300.3
165°	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2
167.5°	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4	1325.9	1327.4	1327.2
170°	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6	1332.1	1333.6	1333.4
172.5°	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2	1336.7	1338.2	1338.1
175°	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3	1341.8	1343.3	1343.0
177.5°	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8	1342.0	1343.3	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	9.2	9.0	9.3	9.1	9.3	9.0	9.2	9.1	9.3	9.0	8.9
90°	24.9	25.3	25.7	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5
92.5°	25.3	25.7	25.9	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6
95°	42.3	42.1	41.9	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9
97.5°	54.8	55.1	55.4	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3
100°	63.6	64.1	64.5	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7
102.5°	67.7	68.4	69.0	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2
105°	71.1	71.9	72.8	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8
107.5°	73.2	74.1	74.9	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0
110°	74.0	74.9	75.7	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	75.3	76.0	76.6	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6
115°	126.0	110.5	95.0	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5
117.5°	477.3	426.4	375.4	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0
120°	678.3	649.3	620.2	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5
122.5°	754.6	748.9	743.3	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1
125°	826.6	827.3	827.9	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9
127.5°	885.5	885.7	885.7	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8
130°	922.2	922.0	921.8	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6
132.5°	957.1	956.9	956.6	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4
135°	1008.1	1007.7	1007.3	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4
137.5°	1054.9	1054.2	1053.5	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8
140°	1084.7	1083.6	1082.5	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5
142.5°	1112.6	1111.5	1110.4	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8
145°	1151.5	1150.5	1149.4	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4
147.5°	1185.3	1184.4	1183.5	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9
150°	1206.8	1205.7	1204.6	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1
152.5°	1225.7	1224.2	1222.8	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6
155°	1251.3	1249.7	1247.9	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7
157.5°	1273.9	1272.2	1270.6	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8
160°	1286.6	1285.1	1283.6	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6
162.5°	1298.5	1296.6	1294.7	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6
165°	1313.7	1312.2	1310.7	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2
167.5°	1325.2	1323.3	1321.4	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4
170°	1331.5	1329.5	1327.6	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6
172.5°	1336.1	1334.2	1332.2	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2
175°	1340.8	1338.7	1336.5	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3
177.5°	1341.6	1340.0	1338.5	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	9.0	8.7	8.7	8.4	8.0	8.3	8.2	8.1	8.2	8.8	9.6
90°	20.4	19.4	17.7	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0
92.5°	23.1	22.5	21.6	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6
95°	38.9	37.8	36.3	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0
97.5°	51.4	50.6	47.1	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0
100°	57.0	55.2	51.6	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5
102.5°	59.0	56.8	87.4	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7
105°	61.5	59.1	117.9	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6
107.5°	80.3	82.8	153.3	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6
110°	148.1	169.6	231.8	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.2	427.7	443.1	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9
115°	498.2	597.9	592.6	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2
117.5°	638.1	662.3	658.5	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2
120°	712.9	710.3	706.5	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3
122.5°	757.6	756.1	751.9	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8
125°	820.4	818.9	814.8	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8
127.5°	877.7	875.4	872.4	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7
130°	914.3	911.9	909.5	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7
132.5°	950.3	948.3	945.9	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5
135°	1001.2	999.1	997.1	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9
137.5°	1048.7	1046.6	1044.3	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8
140°	1079.5	1077.6	1075.2	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1
142.5°	1108.0	1106.3	1103.5	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1
145°	1147.9	1146.4	1142.7	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8
147.5°	1182.8	1181.6	1178.1	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0
150°	1203.9	1202.6	1199.1	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9
152.5°	1223.3	1221.9	1218.7	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8
155°	1249.4	1248.2	1245.5	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2
157.5°	1271.3	1269.9	1268.0	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1
160°	1284.3	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0
162.5°	1296.1	1294.7	1293.6	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5
165°	1310.7	1309.2	1308.5	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1
167.5°	1322.9	1321.4	1320.8	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5
170°	1329.1	1327.6	1327.1	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5
172.5°	1333.7	1332.2	1331.8	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1
175°	1338.8	1337.3	1336.9	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1
177.5°	1339.7	1338.5	1338.2	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.4	7.3	7.4	7.6	8.3	8.6	8.7	9.0	9.7	9.6	10.1
90°	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5
92.5°	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6
95°	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9
97.5°	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3
100°	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7
102.5°	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2
105°	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8
107.5°	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0
110°	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6
115°	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5
117.5°	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0
120°	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5
122.5°	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1
125°	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9
127.5°	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8
130°	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6
132.5°	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4
135°	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4
137.5°	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8
140°	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5
142.5°	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8
145°	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4
147.5°	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9
150°	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1
152.5°	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6
155°	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7
157.5°	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8
160°	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6
162.5°	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6
165°	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2
167.5°	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4
170°	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6
172.5°	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2
175°	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3
177.5°	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	10.1	10.2	10.4	10.5	10.5	10.6	10.4
90°	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	105.0	83.4	73.1	74.0	74.9	75.7	76.5



TEST NUMBER: P331817-927

CATALOG NUMBER: S122RDIW-S675D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)