

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331481

Luminaire Tested: **S122DIW-S290D970U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331481
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5075.1 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	28	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7627	7627	7627
5°	7656	7546	7592
10°	7612	7470	7507
15°	7517	7373	7366
20°	7383	7228	7220
25°	7251	7049	7049
30°	7081	6885	6825
35°	6922	6688	6589
40°	6721	6492	6367
45°	6524	6295	6140
50°	6310	6094	5878
55°	6086	5858	5638
60°	5838	5574	5370
65°	5570	5295	5051
70°	5231	4952	4716
75°	4760	4560	4448
80°	4221	4100	3887
85°	3446	3279	2946



TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	0.9
10°-20°	125.0	2.5
20°-30°	183.7	3.6
30°-40°	213.4	4.2
40°-50°	213.2	4.2
50°-60°	185.9	3.7
60°-70°	137.5	2.7
70°-80°	77.9	1.5
80°-90°	24.2	0.5
90°-100°	44.1	0.9
100°-110°	161.5	3.2
110°-120°	431.8	8.5
120°-130°	712.8	14.0
130°-140°	758.0	14.9
140°-150°	704.6	13.9
150°-160°	566.5	11.2
160°-170°	365.0	7.2
170°-180°	125.6	2.5
0°-30°	353.2	7.0
0°-40°	566.6	11.2
0°-60°	965.7	19.0
0°-90°	1205.2	23.7
90°-120°	637.4	12.6
90°-150°	2812.8	55.4
90°-180°	3870.0	76.3
0°-180°	5075.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	472	472	472	472	472	
5°	472	470	466	469	468	45
15°	450	447	441	443	441	127
25°	407	403	396	396	396	187
35°	351	346	339	337	334	219
45°	286	282	276	271	269	220
55°	216	213	208	203	200	193
65°	146	143	139	135	132	144
75°	76	75	73	71	71	82
85°	19	18	18	16	16	21
90°	1	11	19	24	26	4
95°	62	33	37	42	41	76
105°	290	303	58	68	73	310
115°	549	566	590	168	78	541
125°	777	790	807	814	817	692
135°	961	976	985	994	993	742
145°	1115	1115	1130	1136	1132	697
155°	1228	1220	1231	1236	1229	566
165°	1294	1289	1291	1297	1291	365
175°	1323	1317	1319	1324	1316	126
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	474.6	474.2	473.8	473.4	473.0	472.4	471.5	470.6	469.7	468.8	469.6
5°	472.4	472.0	471.6	471.2	470.8	470.1	469.0	467.9	466.7	465.6	466.4
7.5°	468.3	467.6	467.0	466.4	465.8	464.9	463.8	462.6	461.5	460.4	461.2
10°	464.3	463.6	462.9	462.2	461.4	460.5	459.3	458.1	456.9	455.6	456.4
12.5°	458.8	458.2	457.6	456.9	456.3	455.4	454.2	453.0	451.8	450.6	451.1
15°	449.7	449.1	448.5	447.9	447.3	446.4	445.0	443.7	442.4	441.1	441.5
17.5°	438.1	437.5	436.9	436.3	435.7	434.7	433.4	432.0	430.7	429.4	429.8
20°	429.7	429.1	428.5	427.9	427.3	426.3	424.9	423.5	422.1	420.7	421.0
22.5°	421.4	420.5	419.7	418.8	418.0	416.9	415.6	414.2	412.9	411.6	411.6
25°	407.0	406.2	405.4	404.6	403.8	402.5	400.8	399.1	397.4	395.7	395.9
27.5°	390.7	390.0	389.2	388.5	387.8	386.7	385.4	384.0	382.7	381.3	381.0
30°	379.8	379.0	378.2	377.4	376.5	375.4	373.9	372.4	370.8	369.3	369.0
32.5°	368.1	367.5	366.9	366.2	365.6	364.4	362.8	361.3	359.7	358.1	357.5
35°	351.2	350.1	349.1	348.1	347.1	345.8	344.2	342.6	341.0	339.3	338.7
37.5°	332.0	331.1	330.2	329.3	328.4	327.2	325.6	324.0	322.3	320.7	320.0
40°	318.9	318.1	317.3	316.5	315.7	314.5	312.8	311.2	309.6	308.0	307.1
42.5°	306.2	305.4	304.6	303.8	303.0	301.7	300.1	298.5	296.9	295.3	294.3
45°	285.7	285.0	284.3	283.6	282.9	281.8	280.3	278.8	277.3	275.7	274.6
47.5°	265.4	264.7	264.1	263.4	262.7	261.6	260.0	258.5	256.9	255.3	254.1
50°	251.2	250.7	250.2	249.7	249.2	248.2	246.8	245.4	244.0	242.6	241.2
52.5°	237.4	236.7	236.1	235.4	234.7	233.7	232.4	231.1	229.7	228.4	227.2
55°	216.2	215.6	215.0	214.4	213.8	212.9	211.7	210.5	209.3	208.1	206.8
57.5°	195.0	194.5	194.0	193.5	193.0	192.1	190.8	189.5	188.1	186.8	185.6
60°	180.8	180.4	180.0	179.6	179.2	178.3	176.9	175.5	174.0	172.6	171.5
62.5°	167.0	166.3	165.7	165.1	164.4	163.5	162.4	161.4	160.3	159.2	158.1
65°	145.8	145.2	144.6	144.0	143.4	142.6	141.6	140.6	139.6	138.6	137.6
67.5°	124.3	123.8	123.3	122.8	122.4	121.7	120.7	119.8	118.9	118.0	117.3
70°	110.8	110.4	110.0	109.6	109.2	108.6	107.7	106.8	105.8	104.9	104.2
72.5°	97.0	96.6	96.2	95.8	95.4	94.9	94.3	93.8	93.2	92.6	91.9
75°	76.3	76.1	75.9	75.7	75.5	75.2	74.7	74.1	73.6	73.1	72.5
77.5°	57.8	57.4	57.1	56.8	56.4	56.1	55.9	55.7	55.5	55.3	55.0
80°	45.4	45.3	45.2	45.1	45.0	44.9	44.7	44.5	44.3	44.1	43.8
82.5°	33.8	33.8	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2	32.8
85°	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.8	17.7	17.4
87.5°	6.7	7.0	7.3	7.6	8.0	8.2	8.4	8.6	8.7	8.9	8.9
90°	1.0	3.3	5.6	8.0	10.3	12.3	14.0	15.7	17.4	19.1	20.2
92.5°	19.3	19.1	18.9	18.7	18.5	18.8	19.6	20.5	21.3	22.2	22.7
95°	62.1	55.1	48.1	41.1	34.1	31.3	32.8	34.3	35.8	37.3	38.3
97.5°	123.3	103.5	83.8	64.0	44.3	36.1	39.6	43.0	46.4	49.9	50.7
100°	169.1	140.0	110.9	81.9	52.8	40.0	43.6	47.2	50.9	54.5	56.2
102.5°	219.6	213.4	207.3	201.1	194.9	176.8	146.6	116.4	86.2	56.0	58.2
105°	290.5	296.9	303.2	309.6	316.0	290.2	232.2	174.2	116.3	58.3	60.6
107.5°	371.3	376.5	381.6	386.7	391.9	359.7	290.2	220.6	151.1	81.6	79.2
110°	423.3	427.8	432.2	436.7	441.1	412.7	351.3	290.0	228.6	167.2	146.0



TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	472.2	476.2	480.1	484.1	488.0	482.4	467.3	452.1	436.9	421.8	344.3
115°	549.4	553.0	556.7	560.3	563.9	568.3	573.6	578.9	584.3	589.6	491.2
117.5°	618.4	622.5	626.5	630.5	634.6	638.4	642.1	645.7	649.4	653.0	629.2
120°	668.9	672.1	675.2	678.4	681.6	685.1	688.9	692.8	696.6	700.4	703.0
122.5°	711.7	715.0	718.4	721.7	725.1	728.9	733.0	737.2	741.3	745.5	747.0
125°	776.8	779.6	782.4	785.1	787.9	791.3	795.3	799.4	803.4	807.4	808.9
127.5°	835.9	839.0	842.0	845.1	848.1	851.2	854.2	857.2	860.2	863.2	865.4
130°	873.4	876.8	880.2	883.5	886.9	889.8	892.1	894.5	896.8	899.2	901.5
132.5°	911.6	914.5	917.4	920.2	923.1	925.7	928.1	930.4	932.7	935.1	937.1
135°	961.3	964.7	968.1	971.5	974.9	977.5	979.4	981.3	983.2	985.2	987.3
137.5°	1011.5	1013.9	1016.3	1018.7	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1
140°	1044.4	1046.1	1047.8	1049.5	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5
142.5°	1071.9	1073.4	1075.0	1076.5	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6
145°	1115.1	1114.9	1114.7	1114.5	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9
147.5°	1152.8	1151.9	1151.1	1150.3	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3
150°	1177.2	1175.7	1174.2	1172.8	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1
152.5°	1197.9	1196.2	1194.5	1192.9	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2
155°	1227.9	1225.9	1224.0	1222.1	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0
157.5°	1251.4	1249.8	1248.1	1246.5	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6
160°	1265.1	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4
162.5°	1277.4	1276.1	1274.8	1273.5	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0
165°	1293.8	1292.5	1291.2	1290.0	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4
167.5°	1306.0	1304.7	1303.5	1302.2	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4
170°	1312.9	1311.6	1310.4	1309.1	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6
172.5°	1317.5	1316.2	1314.9	1313.7	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2
175°	1323.4	1321.9	1320.4	1319.0	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1
177.5°	1324.4	1323.2	1322.0	1320.8	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	470.4	471.2	472.0	472.4	472.2	472.0	471.9	471.7
5°	467.3	468.1	468.9	469.2	469.0	468.8	468.6	468.4
7.5°	462.0	462.8	463.6	463.9	463.7	463.4	463.2	463.0
10°	457.3	458.1	458.9	459.1	458.8	458.5	458.2	457.9
12.5°	451.7	452.2	452.8	453.0	452.8	452.5	452.3	452.1
15°	441.9	442.3	442.7	442.7	442.2	441.7	441.2	440.7
17.5°	430.3	430.8	431.2	431.2	430.7	430.3	429.8	429.3
20°	421.3	421.6	421.9	421.8	421.4	421.0	420.6	420.2
22.5°	411.7	411.8	411.8	411.7	411.5	411.2	411.0	410.8
25°	396.1	396.3	396.5	396.5	396.3	396.1	395.9	395.7
27.5°	380.7	380.4	380.1	379.7	379.2	378.7	378.3	377.8
30°	368.7	368.4	368.1	367.8	367.4	367.0	366.6	366.1
32.5°	357.0	356.4	355.9	355.4	355.0	354.6	354.2	353.8
35°	338.1	337.5	336.9	336.4	335.9	335.4	334.9	334.3
37.5°	319.2	318.5	317.7	317.1	316.6	316.1	315.7	315.2
40°	306.2	305.3	304.4	303.7	303.3	302.9	302.5	302.1
42.5°	293.3	292.3	291.3	290.5	290.0	289.4	288.9	288.3
45°	273.5	272.4	271.3	270.5	270.1	269.7	269.3	268.9
47.5°	253.0	251.8	250.6	249.7	249.2	248.6	248.0	247.4
50°	239.8	238.3	236.9	236.0	235.5	235.0	234.5	234.0
52.5°	226.1	224.9	223.7	222.8	222.1	221.5	220.8	220.1
55°	205.6	204.4	203.2	202.4	201.9	201.3	200.8	200.3
57.5°	184.4	183.2	182.0	181.2	180.9	180.5	180.1	179.7
60°	170.4	169.3	168.2	167.5	167.2	166.9	166.6	166.3
62.5°	157.1	156.1	155.1	154.4	154.0	153.6	153.2	152.8
65°	136.7	135.8	134.9	134.2	133.7	133.2	132.7	132.2
67.5°	116.6	115.9	115.2	114.6	114.2	113.8	113.4	113.0
70°	103.5	102.8	102.1	101.6	101.2	100.7	100.3	99.9
72.5°	91.2	90.5	89.8	89.2	88.9	88.6	88.3	87.9
75°	71.9	71.3	70.7	70.5	70.7	70.9	71.1	71.3
77.5°	54.7	54.4	54.1	53.8	53.5	53.3	53.0	52.7
80°	43.5	43.2	42.9	42.6	42.4	42.2	42.0	41.8
82.5°	32.4	32.0	31.6	31.4	31.4	31.3	31.3	31.3
85°	17.1	16.8	16.5	16.3	16.2	16.1	16.0	15.9
87.5°	8.9	8.8	8.8	8.8	8.8	8.8	8.8	8.8
90°	21.2	22.3	23.4	24.1	24.5	24.9	25.4	25.8
92.5°	23.3	23.8	24.4	24.8	25.0	25.3	25.5	25.8
95°	39.4	40.5	41.5	41.9	41.7	41.5	41.3	41.1
97.5°	51.6	52.4	53.3	53.8	54.1	54.3	54.6	54.8
100°	57.9	59.6	61.3	62.3	62.7	63.2	63.6	64.0
102.5°	60.4	62.6	64.8	66.2	66.8	67.4	68.0	68.6
105°	63.0	65.3	67.6	69.2	70.1	70.9	71.8	72.6
107.5°	76.8	74.5	72.1	71.3	72.2	73.0	73.9	74.7
110°	124.7	103.5	82.3	72.1	72.9	73.8	74.6	75.5



TEST NUMBER: P331481

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	266.8	189.4	111.9	73.5	74.2	74.9	75.6	76.3
115°	392.9	294.6	196.3	139.5	124.2	108.9	93.6	78.4
117.5°	605.4	581.7	557.9	520.9	470.6	420.4	370.2	319.9
120°	705.5	708.0	710.6	697.5	668.9	640.2	611.5	582.9
122.5°	748.6	750.1	751.6	749.6	744.0	738.5	732.9	727.4
125°	810.4	811.9	813.4	814.4	815.1	815.7	816.3	817.0
127.5°	867.6	869.7	871.9	873.0	873.2	873.3	873.4	873.5
130°	903.8	906.2	908.5	909.6	909.3	909.1	908.9	908.7
132.5°	939.1	941.1	943.1	944.0	943.7	943.5	943.3	943.1
135°	989.4	991.5	993.6	994.5	994.1	993.6	993.2	992.8
137.5°	1036.1	1038.2	1040.3	1041.0	1040.3	1039.5	1038.8	1038.1
140°	1066.4	1068.3	1070.2	1070.6	1069.6	1068.5	1067.4	1066.4
142.5°	1094.3	1096.1	1097.8	1098.1	1097.1	1096.0	1095.0	1093.9
145°	1133.4	1134.9	1136.3	1136.6	1135.5	1134.4	1133.4	1132.3
147.5°	1167.4	1168.5	1169.6	1169.7	1168.8	1167.9	1167.0	1166.1
150°	1188.4	1189.6	1190.9	1191.0	1190.0	1188.9	1187.8	1186.8
152.5°	1207.5	1208.7	1210.0	1210.0	1208.6	1207.2	1205.8	1204.4
155°	1233.3	1234.5	1235.8	1235.6	1233.9	1232.2	1230.5	1228.8
157.5°	1255.0	1256.5	1257.9	1257.8	1256.1	1254.5	1252.8	1251.2
160°	1267.7	1268.9	1270.2	1270.1	1268.6	1267.1	1265.7	1264.2
162.5°	1279.5	1280.9	1282.4	1282.2	1280.3	1278.5	1276.7	1274.9
165°	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9
167.5°	1305.9	1307.4	1308.9	1308.7	1306.8	1304.9	1303.0	1301.1
170°	1312.1	1313.5	1315.0	1314.8	1312.9	1311.0	1309.1	1307.2
172.5°	1316.6	1318.1	1319.6	1319.4	1317.5	1315.6	1313.7	1311.8
175°	1321.6	1323.1	1324.6	1324.3	1322.1	1320.0	1317.9	1315.8
177.5°	1322.2	1323.3	1324.5	1324.4	1322.8	1321.3	1319.8	1318.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)