

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331514

Luminaire Tested: **S122DIW-S485D1240U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331514
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6446.4 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33																												
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29																												
2	86	79	73	68	77	72	67	63	58	54	51	45	42	40	32	31	30	25																												
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21																												
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18																												
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16																												
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14																												
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13																												
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12																												
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11																												
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	1.4
10°-20°	269.0	4.2
20°-30°	390.5	6.1
30°-40°	412.0	6.4
40°-50°	364.8	5.7
50°-60°	291.1	4.5
60°-70°	197.9	3.1
70°-80°	101.5	1.6
80°-90°	30.6	0.5
90°-100°	97.4	1.5
100°-110°	302.4	4.7
110°-120°	516.9	8.0
120°-130°	679.7	10.5
130°-140°	762.9	11.8
140°-150°	748.1	11.6
150°-160°	627.4	9.7
160°-170°	416.2	6.5
170°-180°	145.5	2.3
0°-30°	752.0	11.7
0°-40°	1164.1	18.1
0°-60°	1820.1	28.2
0°-90°	2150.0	33.4
90°-120°	916.6	14.2
90°-150°	3107.4	48.2
90°-180°	4296.0	66.6
0°-180°	6446.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	44	1	44	1	44	20
95°	80	67	80	67	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	512
125°	757	755	757	755	757	675
135°	988	976	988	976	988	761
145°	1198	1185	1198	1185	1198	748
155°	1365	1355	1365	1355	1365	628
165°	1476	1474	1476	1474	1476	416
175°	1529	1534	1529	1534	1529	145
180°	1536	1536	1536	1536	1536	



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	16.6	16.5	16.8	16.4	16.4	16.7	16.8	16.6	17.0	17.4	16.5
90°	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2	44.8	45.4	39.0
92.5°	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5	41.3	41.2	39.7
95°	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0	83.0	83.0	82.4
97.5°	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5	139.5	139.5	138.4
100°	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9	178.9	178.9	178.1
102.5°	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9	221.7	221.5	220.4
105°	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4	285.8	285.3	284.7
107.5°	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0	355.8	355.5	355.5
110°	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6	451.3	452.0	452.2
115°	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3	523.6	523.8	524.4
117.5°	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5	594.2	594.9	596.5
120°	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5	640.5	640.5	642.8
122.5°	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0	689.6	690.3	691.9
125°	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7	761.6	762.4	763.3
127.5°	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4	831.4	832.4	833.5
130°	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0	878.5	879.1	879.7
132.5°	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3	925.6	926.8	926.7
135°	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7	992.9	993.2	992.7
137.5°	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1	1058.4	1058.6	1057.8
140°	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1	1102.1	1102.1	1100.7
142.5°	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0	1141.8	1141.6	1140.6
145°	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6	1202.3	1202.0	1200.3
147.5°	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6	1255.0	1254.4	1253.2
150°	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6	1286.4
152.5°	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8	1319.4
155°	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7	1364.2	1362.8	1361.9
157.5°	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1	1403.1	1401.2	1400.6
160°	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5	1426.7	1425.0	1424.7
162.5°	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7	1447.7	1445.8	1445.5
165°	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0	1475.0	1473.0	1473.0
167.5°	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6	1497.6	1495.5	1495.6
170°	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0	1510.0	1508.0	1508.3
172.5°	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4	1519.4	1517.3	1517.6
175°	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5	1529.5	1527.4	1528.0
177.5°	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4	1533.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	15.5	14.2	13.0	12.6	11.0	10.3	8.4	6.8	7.2	7.6	7.7
90°	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3	4.8	8.2	11.7
92.5°	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1	25.6	28.2	30.7
95°	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4	70.3	73.2	76.1
97.5°	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2	125.7	128.3	130.8
100°	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7	167.0	169.3	171.6
102.5°	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2	210.1	211.9	213.8
105°	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8	279.6	280.5	281.4
107.5°	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8	351.1	352.4	353.6
110°	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5	397.2	398.9	400.7



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3	447.0	448.7	450.5
115°	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7	520.4	522.1	523.8
117.5°	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8	594.1	596.4	598.7
120°	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	642.8	645.2	647.5
122.5°	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1	687.9	690.7	693.4
125°	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6	757.2	759.8	762.4
127.5°	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3	825.6	828.9	832.2
130°	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9	868.6	872.4	876.1
132.5°	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6	915.6	918.7	921.7
135°	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4	979.5	982.7	985.9
137.5°	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5	1046.1	1048.7	1051.3
140°	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0	1086.6	1089.2	1091.8
142.5°	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5	1128.1	1130.7	1133.3
145°	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1	1187.2	1189.2	1191.2
147.5°	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3	1240.7	1243.1	1245.6
150°	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6	1276.3	1278.1	1279.8
152.5°	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8	1308.5	1310.2	1311.9
155°	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0	1355.9	1356.7	1357.6
157.5°	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2	1396.8	1397.4	1398.0
160°	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1	1421.7	1422.3	1422.9
162.5°	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9	1444.1	1444.2	1444.3
165°	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3	1474.0	1473.7	1473.4
167.5°	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7	1498.8	1498.0	1497.1
170°	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2	1512.3	1511.5	1510.6
172.5°	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5	1521.7	1520.8	1519.9
175°	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9	1533.1	1532.2	1531.3
177.5°	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6	1537.9	1537.2	1536.5
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	8.1	8.8	9.8	11.0	12.0	13.0	12.5	12.4	12.3	11.6	11.6
90°	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2	43.7	43.1	42.9
92.5°	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5	41.6	41.7	41.8
95°	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0	83.0	83.0	82.7
97.5°	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5	139.5	139.5	139.5
100°	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9	178.9	178.9	178.8
102.5°	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9	222.2	222.4	222.4
105°	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4	287.0	287.6	287.9
107.5°	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0	356.2	356.5	355.9
110°	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	403.3	402.8



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6	449.9	449.2	448.6
115°	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3	523.0	522.7	522.1
117.5°	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5	592.8	592.1	591.4
120°	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5	640.5	640.5	640.1
122.5°	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0	688.3	687.6	686.9
125°	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7	759.8	759.0	758.4
127.5°	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4	829.3	828.3	827.3
130°	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0	877.4	876.8	876.0
132.5°	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3	923.0	921.8	920.7
135°	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7	992.4	992.1	991.5
137.5°	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1	1057.9	1057.7	1057.0
140°	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1	1102.1	1102.1	1101.6
142.5°	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0	1142.3	1142.5	1142.0
145°	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6	1202.9	1203.1	1202.7
147.5°	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6	1256.3	1256.9	1256.7
150°	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0
152.5°	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1
155°	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7	1367.1	1368.5	1368.8
157.5°	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1	1407.0	1409.0	1409.3
160°	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5	1430.2	1431.9	1432.2
162.5°	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7	1451.6	1453.6	1453.9
165°	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0	1479.0	1481.1	1481.3
167.5°	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6	1501.6	1503.6	1503.9
170°	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0	1514.0	1516.1	1516.2
172.5°	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4	1523.4	1525.4	1525.5
175°	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5	1533.5	1535.5	1535.7
177.5°	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	11.6	11.4	11.4	11.2	11.4	11.4	11.6	11.6	11.6	12.3	12.4
90°	43.2	43.5	43.8	44.1	43.8	43.5	43.2	42.9	43.1	43.7	44.2
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.7	41.6	41.5
95°	82.1	81.5	81.0	80.4	81.0	81.5	82.1	82.7	83.0	83.0	83.0
97.5°	139.4	139.4	139.3	139.3	139.3	139.4	139.4	139.5	139.5	139.5	139.5
100°	178.5	178.2	177.9	177.6	177.9	178.2	178.5	178.8	178.9	178.9	178.9
102.5°	222.1	221.8	221.5	221.2	221.5	221.8	222.1	222.4	222.4	222.2	221.9
105°	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.6	287.0	286.4
107.5°	354.6	353.3	351.9	350.6	351.9	353.3	354.6	355.9	356.5	356.2	356.0
110°	402.0	401.1	400.2	399.4	400.2	401.1	402.0	402.8	403.3	403.3	403.3



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	447.9	447.3	446.7	446.0	446.7	447.3	447.9	448.6	449.2	449.9	450.6
115°	521.3	520.4	519.5	518.7	519.5	520.4	521.3	522.1	522.7	523.0	523.3
117.5°	590.5	589.6	588.8	587.9	588.8	589.6	590.5	591.4	592.1	592.8	593.5
120°	639.2	638.4	637.5	636.7	637.5	638.4	639.2	640.1	640.5	640.5	640.5
122.5°	686.3	685.6	685.0	684.4	685.0	685.6	686.3	686.9	687.6	688.3	689.0
125°	758.1	757.8	757.5	757.2	757.5	757.8	758.1	758.4	759.0	759.8	760.7
127.5°	826.4	825.5	824.6	823.6	824.6	825.5	826.4	827.3	828.3	829.3	830.4
130°	874.8	873.7	872.5	871.3	872.5	873.7	874.8	876.0	876.8	877.4	878.0
132.5°	919.8	918.8	917.9	917.0	917.9	918.8	919.8	920.7	921.8	923.0	924.3
135°	990.6	989.8	988.9	988.0	988.9	989.8	990.6	991.5	992.1	992.4	992.7
137.5°	1055.8	1054.7	1053.5	1052.4	1053.5	1054.7	1055.8	1057.0	1057.7	1057.9	1058.1
140°	1100.4	1099.3	1098.1	1097.0	1098.1	1099.3	1100.4	1101.6	1102.1	1102.1	1102.1
142.5°	1140.9	1139.7	1138.6	1137.4	1138.6	1139.7	1140.9	1142.0	1142.5	1142.3	1142.0
145°	1201.6	1200.4	1199.3	1198.1	1199.3	1200.4	1201.6	1202.7	1203.1	1202.9	1202.6
147.5°	1255.6	1254.5	1253.4	1252.3	1253.4	1254.5	1255.6	1256.7	1256.9	1256.3	1255.6
150°	1290.2	1289.3	1288.4	1287.6	1288.4	1289.3	1290.2	1291.0	1291.0	1290.2	1289.3
152.5°	1324.0	1323.0	1321.9	1320.8	1321.9	1323.0	1324.0	1325.1	1325.1	1324.0	1323.0
155°	1368.0	1367.1	1366.2	1365.4	1366.2	1367.1	1368.0	1368.8	1368.5	1367.1	1365.7
157.5°	1407.9	1406.5	1405.1	1403.7	1405.1	1406.5	1407.9	1409.3	1409.0	1407.0	1405.1
160°	1431.1	1429.9	1428.8	1427.6	1428.8	1429.9	1431.1	1432.2	1431.9	1430.2	1428.5
162.5°	1452.5	1451.1	1449.7	1448.4	1449.7	1451.1	1452.5	1453.9	1453.6	1451.6	1449.7
165°	1479.9	1478.5	1477.0	1475.6	1477.0	1478.5	1479.9	1481.3	1481.1	1479.0	1477.0
167.5°	1502.4	1500.9	1499.4	1497.9	1499.4	1500.9	1502.4	1503.9	1503.6	1501.6	1499.6
170°	1514.5	1512.8	1511.0	1509.3	1511.0	1512.8	1514.5	1516.2	1516.1	1514.0	1512.0
172.5°	1523.8	1522.1	1520.4	1518.6	1520.4	1522.1	1523.8	1525.5	1525.4	1523.4	1521.4
175°	1533.9	1532.2	1530.5	1528.7	1530.5	1532.2	1533.9	1535.7	1535.5	1533.5	1531.5
177.5°	1537.6	1536.2	1534.8	1533.4	1534.8	1536.2	1537.6	1538.9	1538.9	1537.6	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	12.5	13.0	12.0	11.0	9.8	8.8	8.1	7.7	7.6	7.2	6.8
90°	44.8	45.4	39.0	32.7	26.4	20.0	15.1	11.7	8.2	4.8	1.3
92.5°	41.3	41.2	39.7	38.2	36.7	35.2	33.2	30.7	28.2	25.6	23.1
95°	83.0	83.0	82.4	81.8	81.3	80.7	79.0	76.1	73.2	70.3	67.4
97.5°	139.5	139.5	138.4	137.3	136.2	135.1	133.3	130.8	128.3	125.7	123.2
100°	178.9	178.9	178.1	177.2	176.3	175.5	173.9	171.6	169.3	167.0	164.7
102.5°	221.7	221.5	220.4	219.3	218.2	217.1	215.6	213.8	211.9	210.1	208.2
105°	285.8	285.3	284.7	284.1	283.5	283.0	282.2	281.4	280.5	279.6	278.8
107.5°	355.8	355.5	355.5	355.5	355.5	355.5	354.9	353.6	352.4	351.1	349.8
110°	403.3	403.3	403.3	403.3	403.3	403.3	402.4	400.7	398.9	397.2	395.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.3	452.0	452.2	452.5	452.7	452.9	452.2	450.5	448.7	447.0	445.3
115°	523.6	523.8	524.4	525.0	525.6	526.1	525.6	523.8	522.1	520.4	518.7
117.5°	594.2	594.9	596.5	598.1	599.7	601.4	601.0	598.7	596.4	594.1	591.8
120°	640.5	640.5	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5
122.5°	689.6	690.3	691.9	693.6	695.2	696.8	696.2	693.4	690.7	687.9	685.1
125°	761.6	762.4	763.3	764.2	765.0	765.9	765.0	762.4	759.8	757.2	754.6
127.5°	831.4	832.4	833.5	834.5	835.6	836.6	835.5	832.2	828.9	825.6	822.3
130°	878.5	879.1	879.7	880.3	880.9	881.4	879.8	876.1	872.4	868.6	864.9
132.5°	925.6	926.8	926.7	926.6	926.5	926.4	924.8	921.7	918.7	915.6	912.6
135°	992.9	993.2	992.7	992.1	991.5	990.9	989.1	985.9	982.7	979.5	976.4
137.5°	1058.4	1058.6	1057.8	1057.1	1056.3	1055.6	1053.9	1051.3	1048.7	1046.1	1043.5
140°	1102.1	1102.1	1100.7	1099.3	1097.8	1096.4	1094.4	1091.8	1089.2	1086.6	1084.0
142.5°	1141.8	1141.6	1140.6	1139.6	1138.6	1137.6	1135.9	1133.3	1130.7	1128.1	1125.5
145°	1202.3	1202.0	1200.3	1198.5	1196.8	1195.1	1193.2	1191.2	1189.2	1187.2	1185.1
147.5°	1255.0	1254.4	1253.2	1252.1	1250.9	1249.8	1248.0	1245.6	1243.1	1240.7	1238.3
150°	1288.4	1287.6	1286.4	1285.3	1284.1	1283.0	1281.5	1279.8	1278.1	1276.3	1274.6
152.5°	1321.9	1320.8	1319.4	1318.0	1316.6	1315.2	1313.7	1311.9	1310.2	1308.5	1306.8
155°	1364.2	1362.8	1361.9	1361.0	1360.2	1359.3	1358.5	1357.6	1356.7	1355.9	1355.0
157.5°	1403.1	1401.2	1400.6	1400.1	1399.6	1399.1	1398.5	1398.0	1397.4	1396.8	1396.2
160°	1426.7	1425.0	1424.7	1424.4	1424.1	1423.9	1423.4	1422.9	1422.3	1421.7	1421.1
162.5°	1447.7	1445.8	1445.5	1445.2	1444.9	1444.6	1444.4	1444.3	1444.2	1444.1	1443.9
165°	1475.0	1473.0	1473.0	1473.0	1473.0	1473.0	1473.1	1473.4	1473.7	1474.0	1474.3
167.5°	1497.6	1495.5	1495.6	1495.7	1495.7	1495.8	1496.2	1497.1	1498.0	1498.8	1499.7
170°	1510.0	1508.0	1508.3	1508.6	1508.9	1509.2	1509.7	1510.6	1511.5	1512.3	1513.2
172.5°	1519.4	1517.3	1517.6	1517.9	1518.2	1518.5	1519.1	1519.9	1520.8	1521.7	1522.5
175°	1529.5	1527.4	1528.0	1528.6	1529.2	1529.8	1530.5	1531.3	1532.2	1533.1	1533.9
177.5°	1534.8	1533.4	1533.9	1534.3	1534.8	1535.3	1535.8	1536.5	1537.2	1537.9	1538.6
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.4	10.3	11.0	12.6	13.0	14.2	15.5	16.5	17.4	17.0	16.6
90°	4.8	8.2	11.7	15.1	20.0	26.4	32.7	39.0	45.4	44.8	44.2
92.5°	25.6	28.2	30.7	33.2	35.2	36.7	38.2	39.7	41.2	41.3	41.5
95°	70.3	73.2	76.1	79.0	80.7	81.3	81.8	82.4	83.0	83.0	83.0
97.5°	125.7	128.3	130.8	133.3	135.1	136.2	137.3	138.4	139.5	139.5	139.5
100°	167.0	169.3	171.6	173.9	175.5	176.3	177.2	178.1	178.9	178.9	178.9
102.5°	210.1	211.9	213.8	215.6	217.1	218.2	219.3	220.4	221.5	221.7	221.9
105°	279.6	280.5	281.4	282.2	283.0	283.5	284.1	284.7	285.3	285.8	286.4
107.5°	351.1	352.4	353.6	354.9	355.5	355.5	355.5	355.5	355.5	355.8	356.0
110°	397.2	398.9	400.7	402.4	403.3	403.3	403.3	403.3	403.3	403.3	403.3



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.0	448.7	450.5	452.2	452.9	452.7	452.5	452.2	452.0	451.3	450.6
115°	520.4	522.1	523.8	525.6	526.1	525.6	525.0	524.4	523.8	523.6	523.3
117.5°	594.1	596.4	598.7	601.0	601.4	599.7	598.1	596.5	594.9	594.2	593.5
120°	642.8	645.2	647.5	649.8	649.8	647.5	645.2	642.8	640.5	640.5	640.5
122.5°	687.9	690.7	693.4	696.2	696.8	695.2	693.6	691.9	690.3	689.6	689.0
125°	757.2	759.8	762.4	765.0	765.9	765.0	764.2	763.3	762.4	761.6	760.7
127.5°	825.6	828.9	832.2	835.5	836.6	835.6	834.5	833.5	832.4	831.4	830.4
130°	868.6	872.4	876.1	879.8	881.4	880.9	880.3	879.7	879.1	878.5	878.0
132.5°	915.6	918.7	921.7	924.8	926.4	926.5	926.6	926.7	926.8	925.6	924.3
135°	979.5	982.7	985.9	989.1	990.9	991.5	992.1	992.7	993.2	992.9	992.7
137.5°	1046.1	1048.7	1051.3	1053.9	1055.6	1056.3	1057.1	1057.8	1058.6	1058.4	1058.1
140°	1086.6	1089.2	1091.8	1094.4	1096.4	1097.8	1099.3	1100.7	1102.1	1102.1	1102.1
142.5°	1128.1	1130.7	1133.3	1135.9	1137.6	1138.6	1139.6	1140.6	1141.6	1141.8	1142.0
145°	1187.2	1189.2	1191.2	1193.2	1195.1	1196.8	1198.5	1200.3	1202.0	1202.3	1202.6
147.5°	1240.7	1243.1	1245.6	1248.0	1249.8	1250.9	1252.1	1253.2	1254.4	1255.0	1255.6
150°	1276.3	1278.1	1279.8	1281.5	1283.0	1284.1	1285.3	1286.4	1287.6	1288.4	1289.3
152.5°	1308.5	1310.2	1311.9	1313.7	1315.2	1316.6	1318.0	1319.4	1320.8	1321.9	1323.0
155°	1355.9	1356.7	1357.6	1358.5	1359.3	1360.2	1361.0	1361.9	1362.8	1364.2	1365.7
157.5°	1396.8	1397.4	1398.0	1398.5	1399.1	1399.6	1400.1	1400.6	1401.2	1403.1	1405.1
160°	1421.7	1422.3	1422.9	1423.4	1423.9	1424.1	1424.4	1424.7	1425.0	1426.7	1428.5
162.5°	1444.1	1444.2	1444.3	1444.4	1444.6	1444.9	1445.2	1445.5	1445.8	1447.7	1449.7
165°	1474.0	1473.7	1473.4	1473.1	1473.0	1473.0	1473.0	1473.0	1473.0	1475.0	1477.0
167.5°	1498.8	1498.0	1497.1	1496.2	1495.8	1495.7	1495.7	1495.6	1495.5	1497.6	1499.6
170°	1512.3	1511.5	1510.6	1509.7	1509.2	1508.9	1508.6	1508.3	1508.0	1510.0	1512.0
172.5°	1521.7	1520.8	1519.9	1519.1	1518.5	1518.2	1517.9	1517.6	1517.3	1519.4	1521.4
175°	1533.1	1532.2	1531.3	1530.5	1529.8	1529.2	1528.6	1528.0	1527.4	1529.5	1531.5
177.5°	1537.9	1537.2	1536.5	1535.8	1535.3	1534.8	1534.3	1533.9	1533.4	1534.8	1536.2
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	16.8	16.7	16.4	16.4	16.8	16.5	16.6
90°	43.7	43.1	42.9	43.2	43.5	43.8	44.1
92.5°	41.6	41.7	41.8	41.8	41.9	42.0	42.0
95°	83.0	83.0	82.7	82.1	81.5	81.0	80.4
97.5°	139.5	139.5	139.5	139.4	139.4	139.3	139.3
100°	178.9	178.9	178.8	178.5	178.2	177.9	177.6
102.5°	222.2	222.4	222.4	222.1	221.8	221.5	221.2
105°	287.0	287.6	287.9	287.9	287.9	287.9	287.9
107.5°	356.2	356.5	355.9	354.6	353.3	351.9	350.6
110°	403.3	403.3	402.8	402.0	401.1	400.2	399.4



TEST NUMBER: P331514

CATALOG NUMBER: S122DIW-S485D1240U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	449.9	449.2	448.6	447.9	447.3	446.7	446.0
115°	523.0	522.7	522.1	521.3	520.4	519.5	518.7
117.5°	592.8	592.1	591.4	590.5	589.6	588.8	587.9
120°	640.5	640.5	640.1	639.2	638.4	637.5	636.7
122.5°	688.3	687.6	686.9	686.3	685.6	685.0	684.4
125°	759.8	759.0	758.4	758.1	757.8	757.5	757.2
127.5°	829.3	828.3	827.3	826.4	825.5	824.6	823.6
130°	877.4	876.8	876.0	874.8	873.7	872.5	871.3
132.5°	923.0	921.8	920.7	919.8	918.8	917.9	917.0
135°	992.4	992.1	991.5	990.6	989.8	988.9	988.0
137.5°	1057.9	1057.7	1057.0	1055.8	1054.7	1053.5	1052.4
140°	1102.1	1102.1	1101.6	1100.4	1099.3	1098.1	1097.0
142.5°	1142.3	1142.5	1142.0	1140.9	1139.7	1138.6	1137.4
145°	1202.9	1203.1	1202.7	1201.6	1200.4	1199.3	1198.1
147.5°	1256.3	1256.9	1256.7	1255.6	1254.5	1253.4	1252.3
150°	1290.2	1291.0	1291.0	1290.2	1289.3	1288.4	1287.6
152.5°	1324.0	1325.1	1325.1	1324.0	1323.0	1321.9	1320.8
155°	1367.1	1368.5	1368.8	1368.0	1367.1	1366.2	1365.4
157.5°	1407.0	1409.0	1409.3	1407.9	1406.5	1405.1	1403.7
160°	1430.2	1431.9	1432.2	1431.1	1429.9	1428.8	1427.6
162.5°	1451.6	1453.6	1453.9	1452.5	1451.1	1449.7	1448.4
165°	1479.0	1481.1	1481.3	1479.9	1478.5	1477.0	1475.6
167.5°	1501.6	1503.6	1503.9	1502.4	1500.9	1499.4	1497.9
170°	1514.0	1516.1	1516.2	1514.5	1512.8	1511.0	1509.3
172.5°	1523.4	1525.4	1525.5	1523.8	1522.1	1520.4	1518.6
175°	1533.5	1535.5	1535.7	1533.9	1532.2	1530.5	1528.7
177.5°	1537.6	1538.9	1538.9	1537.6	1536.2	1534.8	1533.4
180°	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5

(END OF REPORT)