

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331822-927

Luminaire Tested: **S122RDIW-S675D1440U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331822-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5974.1 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	55	50	66	57	51	46	46	42	38	36	33	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18				
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	35	31	34	30	26	27	24	21	21	19	17	14				
8	53	42	34	29	48	38	32	27	31	27	23	25	22	19	19	17	15	13				
9	50	38	31	26	45	35	29	24	29	24	21	23	20	17	18	16	14	12				
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	1.8
10°-20°	307.4	5.1
20°-30°	396.1	6.6
30°-40°	376.4	6.3
40°-50°	322.5	5.4
50°-60°	245.6	4.1
60°-70°	155.2	2.6
70°-80°	77.5	1.3
80°-90°	25.8	0.4
90°-100°	89.7	1.5
100°-110°	278.5	4.7
110°-120°	476.1	8.0
120°-130°	626.1	10.5
130°-140°	702.7	11.8
140°-150°	689.0	11.5
150°-160°	577.9	9.7
160°-170°	383.3	6.4
170°-180°	134.0	2.2
0°-30°	813.8	13.6
0°-40°	1190.3	19.9
0°-60°	1758.3	29.4
0°-90°	2016.9	33.8
90°-120°	844.3	14.1
90°-150°	2862.0	47.9
90°-180°	3957.0	66.2
0°-180°	5974.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	17
90°	41	1	41	1	41	18
95°	74	62	74	62	74	83
105°	265	257	265	257	265	279
115°	478	478	478	478	478	472
125°	697	695	697	695	697	622
135°	910	899	910	899	910	700
145°	1104	1092	1104	1092	1104	689
155°	1258	1248	1258	1248	1258	579
165°	1359	1358	1359	1358	1359	383
175°	1408	1413	1408	1413	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	13.3	13.5	13.5	13.5	13.4	13.5	13.5	13.9	13.8	14.2	12.7
90°	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7	41.3	41.8	36.0
92.5°	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2	38.1	37.9	36.6
95°	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4	76.4	76.4	75.9
97.5°	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5	128.5	128.5	127.5
100°	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8	164.8	164.8	164.0
102.5°	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4	204.2	204.0	203.0
105°	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8	263.2	262.8	262.2
107.5°	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9	327.6	327.5	327.5
110°	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0	415.7	416.3	416.5
115°	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0	482.2	482.5	483.0
117.5°	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7	547.3	548.0	549.4
120°	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9	589.9	589.9	592.1
122.5°	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5	635.2	635.8	637.3
125°	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6	701.4	702.2	703.1
127.5°	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8	765.7	766.8	767.7
130°	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7	809.2	809.7	810.2
132.5°	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4	852.5	853.7	853.6
135°	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3	914.6	914.8	914.3
137.5°	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5	974.8	975.0	974.3
140°	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1	1015.1	1015.1	1013.8
142.5°	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9	1051.6	1051.5	1050.5
145°	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6	1107.3	1107.1	1105.5
147.5°	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5	1156.0	1155.3	1154.3
150°	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9	1184.9
152.5°	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5	1215.2
155°	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8	1256.5	1255.1	1254.3
157.5°	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1	1292.3	1290.5	1290.1
160°	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7	1314.1	1312.5	1312.2
162.5°	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2	1333.4	1331.6	1331.3
165°	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4	1358.5	1356.7	1356.7
167.5°	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2	1379.3	1377.4	1377.5
170°	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7	1390.8	1388.9	1389.2
172.5°	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2	1399.4	1397.5	1397.8
175°	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6	1408.7	1406.8	1407.4
177.5°	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3	1412.8
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	11.5	10.7	9.5	8.3	8.0	7.7	8.6	9.6	9.0	8.6	8.6
90°	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2	4.4	7.5	10.8
92.5°	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2	23.6	25.9	28.3
95°	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1	64.7	67.4	70.0
97.5°	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4	115.8	118.1	120.5
100°	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7	153.8	155.9	158.0
102.5°	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8	193.5	195.2	196.9
105°	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7	257.5	258.3	259.1
107.5°	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2	323.4	324.6	325.7
110°	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2	365.8	367.4	369.0



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1	411.7	413.3	414.9
115°	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7	479.3	480.9	482.5
117.5°	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1	547.2	549.3	551.4
120°	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	592.1	594.2	596.4
122.5°	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1	633.6	636.1	638.7
125°	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1	697.4	699.8	702.2
127.5°	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4	760.4	763.4	766.5
130°	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5	800.0	803.5	806.9
132.5°	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5	843.4	846.1	849.0
135°	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3	902.2	905.1	908.0
137.5°	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2	963.5	965.9	968.3
140°	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4	1000.8	1003.2	1005.6
142.5°	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6	1039.0	1041.4	1043.8
145°	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5	1093.4	1095.3	1097.1
147.5°	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5	1142.7	1144.9	1147.2
150°	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9	1175.5	1177.2	1178.8
152.5°	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6	1205.1	1206.7	1208.3
155°	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0	1248.8	1249.6	1250.4
157.5°	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9	1286.5	1287.1	1287.6
160°	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9	1309.5	1310.0	1310.5
162.5°	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9	1330.1	1330.2	1330.2
165°	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9	1357.6	1357.3	1357.1
167.5°	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2	1380.5	1379.7	1378.9
170°	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7	1392.9	1392.1	1391.3
172.5°	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3	1401.5	1400.7	1399.9
175°	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8	1412.0	1411.2	1410.4
177.5°	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1	1416.5	1415.9	1415.2
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	9.0	9.5	10.1	11.2	12.4	13.2	13.1	12.7	12.6	12.4	12.1
90°	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7	40.2	39.7	39.5
92.5°	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2	38.3	38.4	38.5
95°	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4	76.4	76.4	76.1
97.5°	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5	128.5	128.5	128.5
100°	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8	164.8	164.8	164.7
102.5°	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4	204.6	204.9	204.8
105°	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8	264.4	264.8	265.1
107.5°	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9	328.1	328.3	327.8
110°	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.0



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0	414.4	413.8	413.1
115°	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0	481.6	481.4	480.9
117.5°	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7	546.1	545.4	544.6
120°	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9	589.9	589.9	589.5
122.5°	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5	633.9	633.3	632.6
125°	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6	699.8	699.0	698.5
127.5°	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8	763.8	762.9	762.0
130°	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7	808.1	807.6	806.8
132.5°	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4	850.2	849.0	848.0
135°	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3	914.0	913.8	913.2
137.5°	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5	974.4	974.1	973.5
140°	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1	1015.1	1015.1	1014.6
142.5°	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9	1052.1	1052.3	1051.9
145°	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6	1107.9	1108.1	1107.7
147.5°	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5	1157.1	1157.7	1157.5
150°	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1
152.5°	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5
155°	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8	1259.2	1260.4	1260.8
157.5°	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1	1295.9	1297.8	1298.0
160°	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7	1317.2	1318.8	1319.1
162.5°	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2	1337.0	1338.8	1339.1
165°	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4	1362.2	1364.1	1364.4
167.5°	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2	1383.1	1384.9	1385.1
170°	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7	1394.5	1396.4	1396.5
172.5°	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2	1403.1	1404.9	1405.1
175°	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6	1412.4	1414.3	1414.4
177.5°	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	12.2	11.9	12.3	12.0	12.3	11.9	12.2	12.1	12.4	12.6	12.7
90°	39.8	40.1	40.3	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7
92.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2
95°	75.7	75.1	74.5	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4
97.5°	128.4	128.3	128.3	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5
100°	164.4	164.1	163.9	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8
102.5°	204.5	204.3	204.0	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4
105°	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8
107.5°	326.6	325.3	324.2	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9
110°	370.2	369.4	368.6	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.6	412.0	411.4	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0
115°	480.1	479.3	478.5	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0
117.5°	543.8	543.0	542.2	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7
120°	588.7	588.0	587.2	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9
122.5°	632.1	631.5	630.9	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5
125°	698.2	698.0	697.8	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6
127.5°	761.1	760.3	759.5	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8
130°	805.7	804.7	803.6	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7
132.5°	847.2	846.3	845.4	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4
135°	912.4	911.6	910.9	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3
137.5°	972.5	971.4	970.3	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5
140°	1013.5	1012.5	1011.4	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1
142.5°	1050.8	1049.7	1048.7	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9
145°	1106.7	1105.6	1104.5	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6
147.5°	1156.4	1155.4	1154.4	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5
150°	1188.3	1187.5	1186.7	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5
152.5°	1219.5	1218.5	1217.5	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5
155°	1260.0	1259.2	1258.4	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8
157.5°	1296.7	1295.5	1294.2	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1
160°	1318.0	1317.0	1316.0	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7
162.5°	1337.8	1336.6	1335.3	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2
165°	1363.0	1361.8	1360.4	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4
167.5°	1383.8	1382.4	1381.0	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2
170°	1394.9	1393.3	1391.7	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7
172.5°	1403.5	1401.9	1400.3	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2
175°	1412.8	1411.2	1409.6	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6
177.5°	1416.2	1414.9	1413.6	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	13.1	13.2	12.4	11.2	10.1	9.5	9.0	8.6	8.6	9.0	9.6
90°	41.3	41.8	36.0	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2
92.5°	38.1	37.9	36.6	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2
95°	76.4	76.4	75.9	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1
97.5°	128.5	128.5	127.5	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4
100°	164.8	164.8	164.0	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7
102.5°	204.2	204.0	203.0	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8
105°	263.2	262.8	262.2	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7
107.5°	327.6	327.5	327.5	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2
110°	371.5	371.5	371.5	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.7	416.3	416.5	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1
115°	482.2	482.5	483.0	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7
117.5°	547.3	548.0	549.4	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1
120°	589.9	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9
122.5°	635.2	635.8	637.3	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1
125°	701.4	702.2	703.1	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1
127.5°	765.7	766.8	767.7	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4
130°	809.2	809.7	810.2	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5
132.5°	852.5	853.7	853.6	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5
135°	914.6	914.8	914.3	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3
137.5°	974.8	975.0	974.3	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2
140°	1015.1	1015.1	1013.8	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4
142.5°	1051.6	1051.5	1050.5	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6
145°	1107.3	1107.1	1105.5	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5
147.5°	1156.0	1155.3	1154.3	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5
150°	1186.7	1185.9	1184.9	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9
152.5°	1217.5	1216.5	1215.2	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6
155°	1256.5	1255.1	1254.3	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0
157.5°	1292.3	1290.5	1290.1	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9
160°	1314.1	1312.5	1312.2	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9
162.5°	1333.4	1331.6	1331.3	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9
165°	1358.5	1356.7	1356.7	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9
167.5°	1379.3	1377.4	1377.5	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2
170°	1390.8	1388.9	1389.2	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7
172.5°	1399.4	1397.5	1397.8	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3
175°	1408.7	1406.8	1407.4	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8
177.5°	1413.6	1412.3	1412.8	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.6	7.7	8.0	8.3	9.5	10.7	11.5	12.7	14.2	13.8	13.9
90°	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7
92.5°	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2
95°	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4
97.5°	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5
100°	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8
102.5°	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4
105°	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8
107.5°	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9
110°	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0
115°	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0
117.5°	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7
120°	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9
122.5°	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5
125°	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6
127.5°	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8
130°	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7
132.5°	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4
135°	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3
137.5°	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5
140°	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1
142.5°	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9
145°	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6
147.5°	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5
150°	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5
152.5°	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5
155°	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8
157.5°	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1
160°	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7
162.5°	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2
165°	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4
167.5°	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2
170°	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7
172.5°	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2
175°	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6
177.5°	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	13.5	13.5	13.4	13.5	13.5	13.5	13.3
90°	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.0	370.2	369.4	368.6	367.8



TEST NUMBER: P331822-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)