

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331499

Luminaire Tested: **S122DIW-S485D435U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331499
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3708.5 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	41	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	2.0
10°-20°	205.5	5.5
20°-30°	302.1	8.1
30°-40°	350.9	9.5
40°-50°	350.5	9.5
50°-60°	305.6	8.2
60°-70°	226.0	6.1
70°-80°	128.0	3.5
80°-90°	35.9	1.0
90°-100°	19.7	0.5
100°-110°	72.3	1.9
110°-120°	193.1	5.2
120°-130°	318.8	8.6
130°-140°	339.1	9.1
140°-150°	315.2	8.5
150°-160°	253.4	6.8
160°-170°	163.3	4.4
170°-180°	56.2	1.5
0°-30°	580.6	15.7
0°-40°	931.5	25.1
0°-60°	1587.6	42.8
0°-90°	1977.5	53.3
90°-120°	285.1	7.7
90°-150°	1258.2	33.9
90°-180°	1731.0	46.7
0°-180°	3708.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	0	5	8	11	12	3
95°	28	15	17	19	18	34
105°	130	136	26	31	32	139
115°	246	253	264	75	35	242
125°	348	353	361	364	365	310
135°	430	437	441	445	444	332
145°	499	499	506	508	506	312
155°	549	546	550	553	550	253
165°	579	576	577	580	577	163
175°	592	589	590	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.8	10.8	10.7	10.7	10.6	10.5	10.4	10.3	10.2	10.1	9.8
90°	0.4	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2
95°	27.8	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1
97.5°	55.1	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7
100°	75.7	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1
102.5°	98.2	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0
105°	129.9	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1
107.5°	166.1	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4
110°	189.3	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3



TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.2	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0
115°	245.8	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7
117.5°	276.6	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5
120°	299.2	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4
122.5°	318.3	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2
125°	347.5	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8
127.5°	373.9	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1
130°	390.7	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2
132.5°	407.8	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2
135°	430.0	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6
137.5°	452.5	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5
140°	467.2	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1
142.5°	479.5	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7
145°	498.8	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3
147.5°	515.6	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7
150°	526.6	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0
152.5°	535.8	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5
155°	549.2	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1
157.5°	559.7	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7
160°	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5
162.5°	571.4	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7
165°	578.7	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1
167.5°	584.2	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5
170°	587.3	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2
172.5°	589.3	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3
175°	592.0	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5
177.5°	592.4	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	9.5	9.2	8.9	8.7	8.6	8.5	8.4	8.3
90°	9.5	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	17.6	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.1	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	25.9	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	27.0	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	28.2	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	34.4	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	55.8	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331499

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	119.4	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	175.8	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	270.8	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	315.6	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	334.8	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	362.5	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	388.1	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	404.3	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.1	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	442.6	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	463.5	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.0	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	489.5	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.0	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.2	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	531.6	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.1	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	551.7	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	561.4	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.0	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	572.3	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.2	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	586.9	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	588.9	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.2	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.4	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)