

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331823-927

Luminaire Tested: **S122RDIW-S675D1440U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331823-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6404.8 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27
3	78	69	62	57	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.3
10°-20°	229.7	3.6
20°-30°	322.5	5.0
30°-40°	351.7	5.5
40°-50°	323.4	5.0
50°-60°	254.0	4.0
60°-70°	165.6	2.6
70°-80°	85.4	1.3
80°-90°	26.0	0.4
90°-100°	51.9	0.8
100°-110°	190.5	3.0
110°-120°	509.1	7.9
120°-130°	840.4	13.1
130°-140°	893.8	14.0
140°-150°	830.7	13.0
150°-160°	667.9	10.4
160°-170°	430.4	6.7
170°-180°	148.2	2.3
0°-30°	635.8	9.9
0°-40°	987.5	15.4
0°-60°	1564.8	24.4
0°-90°	1841.8	28.8
90°-120°	751.5	11.7
90°-150°	3316.5	51.8
90°-180°	4563.0	71.2
0°-180°	6404.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	1	13	22	28	30	5
95°	73	39	44	49	48	90
105°	342	357	69	81	86	366
115°	648	668	695	198	92	638
125°	916	931	952	960	963	816
135°	1134	1151	1162	1172	1171	875
145°	1315	1315	1333	1340	1335	822
155°	1448	1439	1451	1457	1449	667
165°	1526	1519	1522	1529	1522	431
175°	1560	1553	1555	1562	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.6	10.0	9.3	8.8	8.2	8.1	8.5	8.9	9.3	9.7	9.8
90°	1.1	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8
92.5°	22.7	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8
95°	73.2	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2
97.5°	145.4	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8
100°	199.4	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2
102.5°	258.9	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6
105°	342.5	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5
107.5°	437.8	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4
110°	499.2	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1



TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.8	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0
115°	647.8	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2
117.5°	729.2	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0
120°	788.7	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9
122.5°	839.2	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8
125°	916.0	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8
127.5°	985.6	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4
130°	1029.8	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0
132.5°	1074.8	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9
135°	1133.5	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1
137.5°	1192.7	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2
140°	1231.4	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1
142.5°	1263.9	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2
145°	1314.9	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6
147.5°	1359.2	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1
150°	1388.1	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7
152.5°	1412.4	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2
155°	1447.8	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6
157.5°	1475.5	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1
160°	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2
162.5°	1506.1	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0
165°	1525.5	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9
167.5°	1539.9	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1
170°	1548.1	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3
172.5°	1553.5	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7
175°	1560.4	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6
177.5°	1561.5	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	9.9	10.0	10.1	10.2	10.3	10.4	10.5	10.6
90°	25.0	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	27.4	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	46.4	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	60.8	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	68.2	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	71.2	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	74.2	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	90.6	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	147.1	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331823-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	314.7	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	463.3	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	713.9	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	831.9	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	882.6	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	955.5	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1022.9	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1065.7	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1107.2	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1166.6	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1221.7	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1257.4	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1290.3	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1376.5	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1401.2	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1423.7	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1454.1	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1479.8	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1494.7	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1508.6	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1539.8	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1547.1	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1552.4	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1558.3	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1558.9	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)