

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331500

Luminaire Tested: **S122DIW-S485D435U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331500
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3479.4 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331500
CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331500

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331500

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	2.1
10°-20°	205.5	5.9
20°-30°	302.1	8.7
30°-40°	350.9	10.1
40°-50°	350.5	10.1
50°-60°	305.6	8.8
60°-70°	226.0	6.5
70°-80°	128.0	3.7
80°-90°	36.6	1.1
90°-100°	34.0	1.0
100°-110°	105.7	3.0
110°-120°	180.6	5.2
120°-130°	237.5	6.8
130°-140°	266.6	7.7
140°-150°	261.4	7.5
150°-160°	219.2	6.3
160°-170°	145.4	4.2
170°-180°	50.8	1.5
0°-30°	580.6	16.7
0°-40°	931.5	26.8
0°-60°	1587.6	45.6
0°-90°	1978.2	56.9
90°-120°	320.3	9.2
90°-150°	1085.7	31.2
90°-180°	1501.0	43.1
0°-180°	3479.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	0	6	16	15	15	3
95°	24	28	29	29	28	27
105°	97	99	100	101	101	103
115°	181	184	183	182	181	179
125°	264	267	266	265	265	236
135°	341	346	347	346	345	263
145°	414	417	420	420	419	259
155°	473	475	476	478	477	218
165°	515	515	515	518	516	145
175°	536	535	534	537	534	51
180°	537	537	537	537	537	



TEST NUMBER: P331500

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.8	10.8	10.8	10.8	10.7	10.8	11.0	11.2	11.4	11.5	11.1
90°	0.5	1.7	2.9	4.1	5.3	7.0	9.2	11.4	13.6	15.9	15.7
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.4	13.9	14.4	14.4
95°	23.6	24.6	25.6	26.6	27.6	28.2	28.4	28.6	28.8	29.0	29.0
97.5°	43.0	43.9	44.8	45.7	46.6	47.2	47.6	48.0	48.4	48.7	48.7
100°	57.5	58.3	59.1	60.0	60.8	61.3	61.6	61.9	62.2	62.5	62.5
102.5°	72.8	73.4	74.0	74.7	75.3	75.9	76.2	76.6	77.0	77.4	77.5
105°	97.4	97.7	98.0	98.3	98.6	98.9	99.1	99.3	99.5	99.7	99.9
107.5°	122.2	122.7	123.1	123.6	124.0	124.2	124.2	124.2	124.2	124.2	124.3
110°	138.2	138.8	139.4	140.0	140.6	140.9	140.9	140.9	140.9	140.9	140.9



TEST NUMBER: P331500

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.6	156.2	156.8	157.4	158.0	158.3	158.2	158.1	158.0	157.9	157.7
115°	181.2	181.8	182.4	183.0	183.6	183.8	183.6	183.4	183.2	183.0	182.9
117.5°	206.8	207.6	208.4	209.2	210.0	210.1	209.6	209.0	208.4	207.9	207.6
120°	223.8	224.6	225.4	226.2	227.0	227.0	226.2	225.4	224.6	223.8	223.8
122.5°	239.4	240.4	241.3	242.3	243.3	243.5	242.9	242.3	241.8	241.2	241.0
125°	263.7	264.6	265.5	266.4	267.3	267.6	267.3	267.0	266.7	266.4	266.1
127.5°	287.3	288.5	289.6	290.8	291.9	292.3	292.0	291.6	291.2	290.9	290.5
130°	302.2	303.5	304.8	306.1	307.4	308.0	307.8	307.6	307.4	307.2	307.0
132.5°	318.9	319.9	321.0	322.1	323.1	323.7	323.7	323.8	323.8	323.8	323.4
135°	341.2	342.3	343.4	344.5	345.6	346.2	346.4	346.6	346.8	347.0	346.9
137.5°	364.6	365.5	366.4	367.3	368.2	368.8	369.1	369.4	369.6	369.9	369.8
140°	378.8	379.7	380.6	381.5	382.4	383.1	383.6	384.1	384.6	385.1	385.1
142.5°	393.3	394.2	395.1	396.0	396.9	397.5	397.8	398.2	398.5	398.9	399.0
145°	414.1	414.8	415.5	416.2	416.9	417.6	418.2	418.8	419.4	420.0	420.1
147.5°	432.7	433.5	434.4	435.2	436.1	436.7	437.1	437.5	437.9	438.3	438.5
150°	445.4	446.0	446.6	447.2	447.8	448.3	448.7	449.1	449.5	449.9	450.2
152.5°	456.6	457.2	457.8	458.4	459.0	459.6	460.0	460.5	461.0	461.5	461.9
155°	473.4	473.7	474.0	474.4	474.7	475.0	475.3	475.6	475.9	476.2	476.7
157.5°	487.9	488.1	488.3	488.5	488.7	488.8	489.0	489.2	489.4	489.6	490.3
160°	496.6	496.8	497.0	497.2	497.4	497.5	497.6	497.7	497.8	497.9	498.5
162.5°	504.5	504.6	504.6	504.6	504.7	504.8	504.9	505.0	505.1	505.2	505.8
165°	515.1	515.0	514.9	514.8	514.7	514.7	514.7	514.7	514.7	514.7	515.4
167.5°	524.0	523.7	523.4	523.1	522.8	522.6	522.6	522.6	522.6	522.6	523.3
170°	528.7	528.4	528.1	527.8	527.5	527.3	527.2	527.1	527.0	526.9	527.6
172.5°	532.0	531.7	531.4	531.1	530.8	530.6	530.5	530.4	530.3	530.2	530.9
175°	536.0	535.7	535.4	535.1	534.8	534.5	534.3	534.1	533.9	533.7	534.4
177.5°	537.6	537.4	537.1	536.9	536.6	536.4	536.3	536.1	535.9	535.8	536.3
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331500

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	10.7	10.2	9.8	9.5	9.4	9.3	9.2	9.1
90°	15.5	15.3	15.1	15.0	15.1	15.2	15.3	15.4
92.5°	14.5	14.5	14.6	14.6	14.6	14.6	14.7	14.7
95°	29.0	29.0	29.0	28.9	28.7	28.5	28.3	28.1
97.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7
100°	62.5	62.5	62.5	62.5	62.4	62.3	62.2	62.1
102.5°	77.5	77.6	77.7	77.7	77.6	77.5	77.4	77.3
105°	100.1	100.3	100.5	100.6	100.6	100.6	100.6	100.6
107.5°	124.4	124.5	124.6	124.4	123.9	123.4	123.0	122.5
110°	140.9	140.9	140.9	140.7	140.4	140.1	139.8	139.5



TEST NUMBER: P331500

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	157.2	157.0	156.7	156.5	156.3	156.1	155.9
115°	182.8	182.7	182.6	182.4	182.1	181.8	181.5	181.2
117.5°	207.4	207.1	206.9	206.6	206.3	206.0	205.7	205.4
120°	223.8	223.8	223.8	223.7	223.4	223.1	222.8	222.5
122.5°	240.7	240.5	240.2	240.0	239.8	239.6	239.3	239.1
125°	265.8	265.5	265.2	265.0	264.9	264.8	264.7	264.6
127.5°	290.1	289.8	289.4	289.1	288.7	288.4	288.1	287.8
130°	306.8	306.6	306.4	306.1	305.7	305.3	304.9	304.5
132.5°	323.0	322.5	322.1	321.7	321.4	321.0	320.7	320.4
135°	346.8	346.7	346.6	346.4	346.1	345.8	345.5	345.2
137.5°	369.7	369.6	369.6	369.3	368.9	368.5	368.1	367.7
140°	385.1	385.1	385.1	384.9	384.5	384.1	383.7	383.3
142.5°	399.0	399.1	399.2	399.0	398.6	398.2	397.8	397.4
145°	420.2	420.3	420.4	420.2	419.8	419.4	419.0	418.6
147.5°	438.7	439.0	439.2	439.1	438.7	438.3	437.9	437.6
150°	450.5	450.8	451.1	451.1	450.8	450.5	450.2	449.9
152.5°	462.2	462.6	463.0	463.0	462.6	462.2	461.9	461.5
155°	477.2	477.7	478.2	478.3	478.0	477.7	477.4	477.1
157.5°	490.9	491.6	492.3	492.4	491.9	491.4	491.0	490.5
160°	499.1	499.7	500.3	500.4	500.0	499.6	499.2	498.8
162.5°	506.5	507.2	507.9	508.0	507.5	507.0	506.5	506.1
165°	516.1	516.8	517.5	517.6	517.1	516.6	516.1	515.6
167.5°	524.0	524.7	525.4	525.5	524.9	524.4	523.9	523.4
170°	528.3	529.0	529.7	529.8	529.2	528.6	528.0	527.4
172.5°	531.6	532.3	533.0	533.0	532.4	531.8	531.2	530.6
175°	535.1	535.8	536.5	536.6	536.0	535.4	534.8	534.2
177.5°	536.8	537.2	537.7	537.7	537.2	536.8	536.3	535.8
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9

(END OF REPORT)