

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331506

Luminaire Tested: **S122DIW-S485D710U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331506
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4438.3 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38				38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31				31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27	23				23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20				20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12				12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.6
10°-20°	205.5	4.6
20°-30°	302.1	6.8
30°-40°	350.9	7.9
40°-50°	350.5	7.9
50°-60°	305.6	6.9
60°-70°	226.0	5.1
70°-80°	128.0	2.9
80°-90°	37.9	0.9
90°-100°	55.7	1.3
100°-110°	173.1	3.9
110°-120°	295.8	6.7
120°-130°	389.0	8.8
130°-140°	436.6	9.8
140°-150°	428.1	9.6
150°-160°	359.1	8.1
160°-170°	238.2	5.4
170°-180°	83.2	1.9
0°-30°	580.6	13.1
0°-40°	931.5	21.0
0°-60°	1587.6	35.8
0°-90°	1979.6	44.6
90°-120°	524.6	11.8
90°-150°	1778.3	40.1
90°-180°	2459.0	55.4
0°-180°	4438.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	1	10	26	25	25	3
95°	39	46	48	47	46	44
105°	160	162	163	165	165	168
115°	297	301	300	299	297	294
125°	432	438	436	434	433	386
135°	559	567	568	568	565	431
145°	678	683	688	688	686	424
155°	775	778	780	783	781	357
165°	844	843	843	848	844	238
175°	878	876	874	879	875	83
180°	879	879	879	879	879	



TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.9	11.0	11.2	11.3	11.4	11.7	12.2	12.6	13.1	13.6	13.1
90°	0.7	2.7	4.7	6.7	8.7	11.5	15.1	18.7	22.3	26.0	25.6
92.5°	13.2	14.7	16.1	17.6	19.0	20.2	21.0	21.9	22.7	23.6	23.7
95°	38.6	40.2	41.9	43.5	45.2	46.2	46.5	46.8	47.2	47.5	47.5
97.5°	70.5	71.9	73.4	74.8	76.3	77.3	78.0	78.6	79.2	79.8	79.8
100°	94.2	95.6	96.9	98.2	99.5	100.4	100.9	101.4	101.9	102.4	102.4
102.5°	119.2	120.2	121.3	122.3	123.4	124.2	124.9	125.5	126.1	126.7	126.9
105°	159.5	160.0	160.5	161.0	161.5	161.9	162.3	162.6	162.9	163.3	163.6
107.5°	200.2	200.9	201.7	202.4	203.1	203.5	203.5	203.5	203.5	203.5	203.6
110°	226.3	227.3	228.3	229.3	230.3	230.8	230.8	230.8	230.8	230.8	230.8



TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.8	255.8	256.8	257.8	258.8	259.2	259.1	258.9	258.8	258.7	258.3
115°	296.8	297.8	298.8	299.8	300.8	301.1	300.8	300.4	300.1	299.8	299.6
117.5°	338.7	340.0	341.3	342.6	343.9	344.1	343.2	342.3	341.4	340.5	340.1
120°	366.6	367.9	369.2	370.5	371.8	371.8	370.5	369.2	367.9	366.6	366.6
122.5°	392.1	393.7	395.3	396.8	398.4	398.8	397.8	396.9	396.0	395.1	394.7
125°	431.9	433.4	434.8	436.3	437.8	438.3	437.8	437.3	436.8	436.3	435.8
127.5°	470.6	472.5	474.4	476.2	478.1	478.8	478.2	477.6	477.0	476.4	475.8
130°	494.9	497.1	499.2	501.4	503.5	504.4	504.1	503.8	503.4	503.1	502.8
132.5°	522.3	524.0	525.8	527.5	529.2	530.2	530.2	530.3	530.4	530.4	529.7
135°	558.8	560.6	562.4	564.2	566.0	567.1	567.4	567.8	568.1	568.4	568.2
137.5°	597.2	598.7	600.2	601.7	603.1	604.1	604.5	605.0	605.4	605.8	605.7
140°	620.4	621.8	623.3	624.8	626.3	627.4	628.3	629.1	629.9	630.7	630.7
142.5°	644.1	645.6	647.1	648.6	650.0	651.1	651.6	652.2	652.7	653.3	653.4
145°	678.2	679.4	680.5	681.7	682.9	683.9	684.9	685.9	686.9	687.9	688.0
147.5°	708.7	710.0	711.4	712.8	714.2	715.2	715.9	716.5	717.2	717.9	718.2
150°	729.4	730.4	731.4	732.4	733.4	734.2	734.9	735.5	736.2	736.9	737.4
152.5°	747.8	748.8	749.8	750.8	751.8	752.7	753.5	754.3	755.1	755.9	756.5
155°	775.4	775.9	776.4	776.9	777.4	777.9	778.4	778.9	779.4	779.9	780.7
157.5°	799.0	799.4	799.7	800.0	800.4	800.7	801.0	801.3	801.6	801.9	803.0
160°	813.3	813.6	813.9	814.3	814.6	814.9	815.0	815.2	815.3	815.5	816.5
162.5°	826.3	826.4	826.5	826.5	826.6	826.7	826.9	827.1	827.2	827.4	828.5
165°	843.7	843.5	843.4	843.2	843.1	843.0	843.0	843.0	843.0	843.0	844.1
167.5°	858.3	857.8	857.3	856.8	856.3	856.0	856.0	855.9	855.9	855.9	857.0
170°	866.0	865.5	865.0	864.5	864.0	863.7	863.5	863.3	863.2	863.0	864.2
172.5°	871.3	870.8	870.3	869.8	869.3	869.0	868.8	868.7	868.5	868.3	869.5
175°	877.8	877.4	876.9	876.4	875.9	875.5	875.1	874.8	874.5	874.1	875.3
177.5°	880.5	880.1	879.7	879.3	878.9	878.6	878.3	878.1	877.8	877.5	878.3
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3



TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	12.6	12.2	11.7	11.4	11.3	11.2	11.1	11.0
90°	25.3	25.0	24.7	24.6	24.7	24.9	25.1	25.2
92.5°	23.7	23.8	23.9	23.9	23.9	24.0	24.0	24.0
95°	47.5	47.5	47.5	47.3	47.0	46.7	46.3	46.0
97.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.7	79.7
100°	102.4	102.4	102.4	102.3	102.2	102.0	101.8	101.7
102.5°	127.0	127.1	127.3	127.3	127.1	126.9	126.8	126.6
105°	163.9	164.2	164.6	164.7	164.7	164.7	164.7	164.7
107.5°	203.7	203.9	204.0	203.7	202.9	202.2	201.4	200.7
110°	230.8	230.8	230.8	230.5	230.0	229.5	229.0	228.6



TEST NUMBER: P331506

CATALOG NUMBER: S122DIW-S485D710U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.5	257.1	256.7	256.4	256.0	255.6	255.3
115°	299.5	299.3	299.1	298.8	298.3	297.8	297.3	296.8
117.5°	339.7	339.3	338.9	338.4	337.9	337.4	336.9	336.4
120°	366.6	366.6	366.6	366.3	365.8	365.3	364.8	364.3
122.5°	394.3	393.9	393.5	393.1	392.7	392.4	392.0	391.7
125°	435.3	434.8	434.3	434.0	433.9	433.7	433.5	433.4
127.5°	475.2	474.6	474.0	473.5	472.9	472.4	471.9	471.4
130°	502.5	502.1	501.8	501.3	500.6	500.0	499.3	498.7
132.5°	529.0	528.2	527.5	526.9	526.4	525.8	525.3	524.8
135°	568.1	567.9	567.8	567.4	566.9	566.4	565.9	565.4
137.5°	605.5	605.4	605.3	604.9	604.2	603.6	602.9	602.2
140°	630.7	630.7	630.7	630.4	629.8	629.1	628.4	627.8
142.5°	653.6	653.7	653.8	653.6	652.9	652.2	651.6	650.9
145°	688.2	688.4	688.5	688.3	687.6	687.0	686.3	685.7
147.5°	718.6	718.9	719.3	719.2	718.6	717.9	717.3	716.7
150°	737.8	738.3	738.8	738.8	738.3	737.8	737.4	736.9
152.5°	757.1	757.7	758.4	758.4	757.7	757.1	756.5	755.9
155°	781.5	782.4	783.2	783.4	782.9	782.4	781.9	781.4
157.5°	804.1	805.2	806.3	806.5	805.7	804.9	804.1	803.3
160°	817.5	818.5	819.5	819.6	819.0	818.3	817.7	817.0
162.5°	829.6	830.8	831.9	832.0	831.2	830.5	829.7	828.9
165°	845.3	846.4	847.6	847.8	846.9	846.1	845.3	844.5
167.5°	858.2	859.3	860.5	860.6	859.8	858.9	858.1	857.2
170°	865.3	866.5	867.6	867.7	866.7	865.7	864.7	863.7
172.5°	870.7	871.8	873.0	873.0	872.1	871.1	870.1	869.1
175°	876.4	877.6	878.8	878.8	877.8	876.9	875.9	874.9
177.5°	879.1	879.9	880.7	880.7	879.9	879.1	878.3	877.5
180°	879.3	879.3	879.3	879.3	879.3	879.3	879.3	879.3

(END OF REPORT)