

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331813-927

Luminaire Tested: **S122RDIW-S675D970U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331813-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5079.5 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35																				
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30																				
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26																				
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23																				
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21																				
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19																				
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17																				
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15																				
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14																				
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	2.2
10°-20°	307.4	6.1
20°-30°	396.1	7.8
30°-40°	376.4	7.4
40°-50°	322.5	6.3
50°-60°	245.6	4.8
60°-70°	155.2	3.1
70°-80°	77.5	1.5
80°-90°	22.8	0.4
90°-100°	34.9	0.7
100°-110°	128.0	2.5
110°-120°	342.1	6.7
120°-130°	564.7	11.1
130°-140°	600.5	11.8
140°-150°	558.1	11.0
150°-160°	448.7	8.8
160°-170°	289.2	5.7
170°-180°	99.5	2.0
0°-30°	813.8	16.0
0°-40°	1190.3	23.4
0°-60°	1758.3	34.6
0°-90°	2013.9	39.6
90°-120°	504.9	9.9
90°-150°	2228.2	43.9
90°-180°	3066.0	60.4
0°-180°	5079.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	20	1	20	1	20	10
95°	33	49	33	49	33	30
105°	58	230	58	230	58	60
115°	62	435	62	435	62	155
125°	647	615	647	615	647	560
135°	786	762	786	762	786	606
145°	897	883	897	883	897	561
155°	973	973	973	973	973	449
165°	1023	1025	1023	1025	1023	289
175°	1042	1048	1042	1048	1042	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	9.3	9.5	9.4	9.3	9.3	9.2	9.0	9.2	8.7	8.9	8.2
90°	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8	16.0	15.1	13.8
92.5°	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5	18.0	17.6	16.9
95°	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2	30.3	29.5	28.4
97.5°	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9	40.2	39.5	36.8
100°	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9	44.5	43.2	40.3
102.5°	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8	46.1	44.4	68.3
105°	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9	48.0	46.2	92.1
107.5°	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8	62.7	64.6	119.7
110°	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8	115.7	132.5	181.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4	272.7	334.1	346.1
115°	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2	389.1	467.1	462.9
117.5°	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6	498.4	517.3	514.4
120°	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9	556.9	554.8	551.8
122.5°	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0	591.8	590.6	587.2
125°	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0	640.8	639.6	636.4
127.5°	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3	685.6	683.8	681.4
130°	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0	714.2	712.3	710.4
132.5°	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9	742.4	740.8	738.9
135°	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8	782.1	780.5	778.9
137.5°	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8	819.2	817.5	815.8
140°	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8	843.3	841.8	839.9
142.5°	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9	865.5	864.1	862.1
145°	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9	896.7	895.5	892.6
147.5°	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8	923.9	923.1	920.2
150°	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4	940.4	939.4	936.7
152.5°	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6	955.5	954.5	952.0
155°	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0	976.0	974.9	973.0
157.5°	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2	993.1	991.9	990.5
160°	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2	1003.2	1002.2	1001.2
162.5°	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6	1012.4	1011.3	1010.4
165°	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6	1022.2
167.5°	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5	1033.3	1032.2	1031.7
170°	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4	1038.2	1037.0	1036.7
172.5°	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0	1041.9	1040.7	1040.3
175°	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9	1045.8	1044.6	1044.3
177.5°	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4	1046.5	1045.5	1045.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	8.0	8.1	7.8	7.1	7.1	7.1	8.3	9.5	8.6	8.0	7.8
90°	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3	15.1	15.0	14.8
95°	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2	43.6	38.1	32.6
97.5°	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7	82.0	66.4	50.7
100°	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0	110.9	87.9	64.9
102.5°	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0	169.1	164.2	159.3
105°	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1	235.2	240.2	245.3
107.5°	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1	298.3	302.3	306.3
110°	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3	338.9	342.4	345.9



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1	377.2	380.3	383.5
115°	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2	438.1	441.0	443.9
117.5°	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9	493.1	496.3	499.5
120°	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9	532.4	534.9	537.4
122.5°	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8	566.4	569.1	571.7
125°	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4	617.6	619.8	621.9
127.5°	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2	664.6	667.0	669.5
130°	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9	694.6	697.3	699.9
132.5°	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2	724.5	726.7	729.0
135°	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5	764.2	766.9	769.6
137.5°	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3	803.2	805.1	807.0
140°	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4	828.7	830.0	831.4
142.5°	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1	850.3	851.6	852.8
145°	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4	883.2	883.0	882.9
147.5°	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2	912.5	911.9	911.2
150°	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6	931.4	930.2	929.1
152.5°	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0	947.6	946.3	945.0
155°	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7	971.1	969.6	968.1
157.5°	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3	990.1	988.7	987.5
160°	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1001.2	1000.2	999.2
162.5°	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9	1010.9	1009.9	1008.8
165°	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9	1023.9	1022.9	1021.9
167.5°	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6	1033.6	1032.6	1031.6
170°	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1	1039.0	1038.1	1037.0
172.5°	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7	1042.7	1041.6	1040.7
175°	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4	1047.2	1046.0	1044.9
177.5°	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2	1048.2	1047.3	1046.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	7.8	7.8	7.4	7.7	7.9	7.8	8.1	7.9	8.1	8.2	8.0
90°	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8	17.7	18.5	19.1
92.5°	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5	18.9	19.3	19.6
95°	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2	32.1	32.9	33.2
97.5°	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9	41.5	42.2	42.6
100°	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9	47.2	48.6	49.4
102.5°	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8	49.6	51.3	52.4
105°	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9	51.7	53.6	54.8
107.5°	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8	59.0	57.1	56.5
110°	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8	82.0	65.2	57.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4	150.0	88.6	58.2
115°	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2	233.4	155.5	110.5
117.5°	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6	460.8	442.0	412.6
120°	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9	560.9	562.9	552.5
122.5°	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0	594.2	595.4	593.8
125°	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0	643.2	644.4	645.2
127.5°	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3	689.0	690.7	691.6
130°	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0	717.9	719.7	720.6
132.5°	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9	745.5	747.1	747.8
135°	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8	785.4	787.1	787.8
137.5°	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8	822.4	824.1	824.7
140°	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8	846.3	847.8	848.1
142.5°	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9	868.3	869.7	869.9
145°	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9	899.0	900.2	900.4
147.5°	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8	925.7	926.5	926.6
150°	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4	942.4	943.4	943.5
152.5°	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6	957.5	958.5	958.5
155°	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0	977.9	979.0	978.8
157.5°	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2	995.4	996.5	996.4
160°	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2	1005.2	1006.2	1006.2
162.5°	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6	1014.7	1015.9	1015.7
165°	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4
167.5°	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5	1035.7	1036.9	1036.7
170°	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4	1040.5	1041.7	1041.6
172.5°	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0	1044.2	1045.4	1045.2
175°	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9	1048.1	1049.3	1049.1
177.5°	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4	1048.3	1049.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	8.1	7.8	8.2	8.0	8.2	7.8	8.1	8.0	8.2	8.1	7.9
90°	19.4	19.7	20.1	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8
92.5°	19.8	20.0	20.2	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5
95°	33.0	32.9	32.7	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2
97.5°	42.9	43.0	43.3	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9
100°	49.7	50.1	50.4	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9
102.5°	52.9	53.4	53.9	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8
105°	55.5	56.2	56.9	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9
107.5°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8
110°	57.8	58.5	59.1	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	58.8	59.3	59.9	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4
115°	98.4	86.3	74.1	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2
117.5°	372.8	333.0	293.3	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6
120°	529.9	507.2	484.4	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9
122.5°	589.4	585.0	580.6	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0
125°	645.7	646.2	646.7	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0
127.5°	691.7	691.8	691.9	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3
130°	720.3	720.2	720.0	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0
132.5°	747.6	747.4	747.3	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9
135°	787.5	787.1	786.8	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8
137.5°	824.1	823.5	822.9	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8
140°	847.3	846.4	845.6	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8
142.5°	869.1	868.2	867.4	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9
145°	899.5	898.7	897.9	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9
147.5°	925.9	925.2	924.5	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8
150°	942.7	941.8	941.0	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4
152.5°	957.4	956.3	955.2	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6
155°	977.5	976.1	974.8	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0
157.5°	995.1	993.8	992.4	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2
160°	1005.0	1003.8	1002.7	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2
162.5°	1014.2	1012.8	1011.4	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6
165°	1026.2	1025.0	1023.8	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0
167.5°	1035.2	1033.7	1032.2	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5
170°	1040.1	1038.6	1037.0	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4
172.5°	1043.7	1042.2	1040.7	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0
175°	1047.3	1045.7	1044.0	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9
177.5°	1047.9	1046.7	1045.5	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	8.1	7.8	7.9	7.7	7.4	7.8	7.8	7.8	8.0	8.6	9.5
90°	16.0	15.1	13.8	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8
92.5°	18.0	17.6	16.9	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3
95°	30.3	29.5	28.4	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2
97.5°	40.2	39.5	36.8	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7
100°	44.5	43.2	40.3	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0
102.5°	46.1	44.4	68.3	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0
105°	48.0	46.2	92.1	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1
107.5°	62.7	64.6	119.7	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1
110°	115.7	132.5	181.1	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.7	334.1	346.1	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1
115°	389.1	467.1	462.9	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2
117.5°	498.4	517.3	514.4	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9
120°	556.9	554.8	551.8	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9
122.5°	591.8	590.6	587.2	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8
125°	640.8	639.6	636.4	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4
127.5°	685.6	683.8	681.4	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2
130°	714.2	712.3	710.4	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9
132.5°	742.4	740.8	738.9	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2
135°	782.1	780.5	778.9	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5
137.5°	819.2	817.5	815.8	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3
140°	843.3	841.8	839.9	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4
142.5°	865.5	864.1	862.1	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1
145°	896.7	895.5	892.6	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4
147.5°	923.9	923.1	920.2	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2
150°	940.4	939.4	936.7	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6
152.5°	955.5	954.5	952.0	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0
155°	976.0	974.9	973.0	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7
157.5°	993.1	991.9	990.5	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3
160°	1003.2	1002.2	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2
162.5°	1012.4	1011.3	1010.4	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9
165°	1023.8	1022.6	1022.2	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9
167.5°	1033.3	1032.2	1031.7	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6
170°	1038.2	1037.0	1036.7	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1
172.5°	1041.9	1040.7	1040.3	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7
175°	1045.8	1044.6	1044.3	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4
177.5°	1046.5	1045.5	1045.4	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.3	7.1	7.1	7.1	7.8	8.1	8.0	8.2	8.9	8.7	9.2
90°	2.6	4.4	6.3	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8
92.5°	15.1	15.0	14.8	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5
95°	43.6	38.1	32.6	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2
97.5°	82.0	66.4	50.7	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9
100°	110.9	87.9	64.9	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9
102.5°	169.1	164.2	159.3	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8
105°	235.2	240.2	245.3	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9
107.5°	298.3	302.3	306.3	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8
110°	338.9	342.4	345.9	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	377.2	380.3	383.5	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4
115°	438.1	441.0	443.9	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2
117.5°	493.1	496.3	499.5	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6
120°	532.4	534.9	537.4	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9
122.5°	566.4	569.1	571.7	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0
125°	617.6	619.8	621.9	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0
127.5°	664.6	667.0	669.5	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3
130°	694.6	697.3	699.9	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0
132.5°	724.5	726.7	729.0	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9
135°	764.2	766.9	769.6	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8
137.5°	803.2	805.1	807.0	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8
140°	828.7	830.0	831.4	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8
142.5°	850.3	851.6	852.8	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9
145°	883.2	883.0	882.9	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9
147.5°	912.5	911.9	911.2	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8
150°	931.4	930.2	929.1	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4
152.5°	947.6	946.3	945.0	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6
155°	971.1	969.6	968.1	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0
157.5°	990.1	988.7	987.5	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2
160°	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2
162.5°	1010.9	1009.9	1008.8	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6
165°	1023.9	1022.9	1021.9	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0
167.5°	1033.6	1032.6	1031.6	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5
170°	1039.0	1038.1	1037.0	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4
172.5°	1042.7	1041.6	1040.7	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0
175°	1047.2	1046.0	1044.9	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9
177.5°	1048.2	1047.3	1046.3	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	9.0	9.2	9.3	9.3	9.4	9.5	9.3
90°	17.7	18.5	19.1	19.4	19.7	20.1	20.4
92.5°	18.9	19.3	19.6	19.8	20.0	20.2	20.4
95°	32.1	32.9	33.2	33.0	32.9	32.7	32.6
97.5°	41.5	42.2	42.6	42.9	43.0	43.3	43.4
100°	47.2	48.6	49.4	49.7	50.1	50.4	50.7
102.5°	49.6	51.3	52.4	52.9	53.4	53.9	54.3
105°	51.7	53.6	54.8	55.5	56.2	56.9	57.5
107.5°	59.0	57.1	56.5	57.2	57.8	58.5	59.2
110°	82.0	65.2	57.1	57.8	58.5	59.1	59.8



TEST NUMBER: P331813-927

CATALOG NUMBER: S122RDIW-S675D970U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	150.0	88.6	58.2	58.8	59.3	59.9	60.4
115°	233.4	155.5	110.5	98.4	86.3	74.1	62.1
117.5°	460.8	442.0	412.6	372.8	333.0	293.3	253.4
120°	560.9	562.9	552.5	529.9	507.2	484.4	461.8
122.5°	594.2	595.4	593.8	589.4	585.0	580.6	576.2
125°	643.2	644.4	645.2	645.7	646.2	646.7	647.2
127.5°	689.0	690.7	691.6	691.7	691.8	691.9	692.0
130°	717.9	719.7	720.6	720.3	720.2	720.0	719.9
132.5°	745.5	747.1	747.8	747.6	747.4	747.3	747.1
135°	785.4	787.1	787.8	787.5	787.1	786.8	786.5
137.5°	822.4	824.1	824.7	824.1	823.5	822.9	822.4
140°	846.3	847.8	848.1	847.3	846.4	845.6	844.8
142.5°	868.3	869.7	869.9	869.1	868.2	867.4	866.6
145°	899.0	900.2	900.4	899.5	898.7	897.9	897.0
147.5°	925.7	926.5	926.6	925.9	925.2	924.5	923.8
150°	942.4	943.4	943.5	942.7	941.8	941.0	940.2
152.5°	957.5	958.5	958.5	957.4	956.3	955.2	954.1
155°	977.9	979.0	978.8	977.5	976.1	974.8	973.4
157.5°	995.4	996.5	996.4	995.1	993.8	992.4	991.2
160°	1005.2	1006.2	1006.2	1005.0	1003.8	1002.7	1001.5
162.5°	1014.7	1015.9	1015.7	1014.2	1012.8	1011.4	1010.0
165°	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6
167.5°	1035.7	1036.9	1036.7	1035.2	1033.7	1032.2	1030.7
170°	1040.5	1041.7	1041.6	1040.1	1038.6	1037.0	1035.5
172.5°	1044.2	1045.4	1045.2	1043.7	1042.2	1040.7	1039.2
175°	1048.1	1049.3	1049.1	1047.3	1045.7	1044.0	1042.4
177.5°	1048.3	1049.2	1049.2	1047.9	1046.7	1045.5	1044.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1

(END OF REPORT)