

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331507

Luminaire Tested: **S122DIW-S485D970U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331507
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D970U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6017.0 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36				
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26				
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23				
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17				
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15				
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14				
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12				
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11				
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	1.5
10°-20°	269.0	4.5
20°-30°	390.5	6.5
30°-40°	412.0	6.8
40°-50°	364.8	6.1
50°-60°	291.1	4.8
60°-70°	197.9	3.3
70°-80°	101.5	1.7
80°-90°	27.7	0.5
90°-100°	44.1	0.7
100°-110°	161.5	2.7
110°-120°	431.8	7.2
120°-130°	712.8	11.8
130°-140°	758.0	12.6
140°-150°	704.6	11.7
150°-160°	566.5	9.4
160°-170°	365.0	6.1
170°-180°	125.6	2.1
0°-30°	752.0	12.5
0°-40°	1164.1	19.3
0°-60°	1820.1	30.2
0°-90°	2147.1	35.7
90°-120°	637.4	10.6
90°-150°	2812.8	46.7
90°-180°	3870.0	64.3
0°-180°	6017.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	26	1	26	1	26	12
95°	41	62	41	62	41	38
105°	73	290	73	290	73	76
115°	78	549	78	549	78	196
125°	817	777	817	777	817	707
135°	993	961	993	961	993	765
145°	1132	1115	1132	1115	1132	708
155°	1229	1228	1229	1228	1229	567
165°	1291	1294	1291	1294	1291	364
175°	1316	1323	1316	1323	1316	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	12.9	12.8	13.1	12.7	12.6	12.7	12.5	12.0	12.1	12.2	12.1
90°	25.8	25.4	24.9	24.5	24.1	23.4	22.3	21.2	20.2	19.1	17.4
92.5°	25.8	25.5	25.3	25.0	24.8	24.4	23.8	23.3	22.7	22.2	21.3
95°	41.1	41.3	41.5	41.7	41.9	41.5	40.5	39.4	38.3	37.3	35.8
97.5°	54.8	54.6	54.3	54.1	53.8	53.3	52.4	51.6	50.7	49.9	46.4
100°	64.0	63.6	63.2	62.7	62.3	61.3	59.6	57.9	56.2	54.5	50.9
102.5°	68.6	68.0	67.4	66.8	66.2	64.8	62.6	60.4	58.2	56.0	86.2
105°	72.6	71.8	70.9	70.1	69.2	67.6	65.3	63.0	60.6	58.3	116.3
107.5°	74.7	73.9	73.0	72.2	71.3	72.1	74.5	76.8	79.2	81.6	151.1
110°	75.5	74.6	73.8	72.9	72.1	82.3	103.5	124.7	146.0	167.2	228.6



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	76.3	75.6	74.9	74.2	73.5	111.9	189.4	266.8	344.3	421.8	436.9
115°	78.4	93.6	108.9	124.2	139.5	196.3	294.6	392.9	491.2	589.6	584.3
117.5°	319.9	370.2	420.4	470.6	520.9	557.9	581.7	605.4	629.2	653.0	649.4
120°	582.9	611.5	640.2	668.9	697.5	710.6	708.0	705.5	703.0	700.4	696.6
122.5°	727.4	732.9	738.5	744.0	749.6	751.6	750.1	748.6	747.0	745.5	741.3
125°	817.0	816.3	815.7	815.1	814.4	813.4	811.9	810.4	808.9	807.4	803.4
127.5°	873.5	873.4	873.3	873.2	873.0	871.9	869.7	867.6	865.4	863.2	860.2
130°	908.7	908.9	909.1	909.3	909.6	908.5	906.2	903.8	901.5	899.2	896.8
132.5°	943.1	943.3	943.5	943.7	944.0	943.1	941.1	939.1	937.1	935.1	932.7
135°	992.8	993.2	993.6	994.1	994.5	993.6	991.5	989.4	987.3	985.2	983.2
137.5°	1038.1	1038.8	1039.5	1040.3	1041.0	1040.3	1038.2	1036.1	1034.1	1032.0	1029.8
140°	1066.4	1067.4	1068.5	1069.6	1070.6	1070.2	1068.3	1066.4	1064.5	1062.6	1060.2
142.5°	1093.9	1095.0	1096.0	1097.1	1098.1	1097.8	1096.1	1094.3	1092.6	1090.8	1088.2
145°	1132.3	1133.4	1134.4	1135.5	1136.6	1136.3	1134.9	1133.4	1131.9	1130.4	1126.8
147.5°	1166.1	1167.0	1167.9	1168.8	1169.7	1169.6	1168.5	1167.4	1166.3	1165.2	1161.6
150°	1186.8	1187.8	1188.9	1190.0	1191.0	1190.9	1189.6	1188.4	1187.1	1185.8	1182.4
152.5°	1204.4	1205.8	1207.2	1208.6	1210.0	1210.0	1208.7	1207.5	1206.2	1204.9	1201.7
155°	1228.8	1230.5	1232.2	1233.9	1235.6	1235.8	1234.5	1233.3	1232.0	1230.7	1228.2
157.5°	1251.2	1252.8	1254.5	1256.1	1257.8	1257.9	1256.5	1255.0	1253.6	1252.1	1250.3
160°	1264.2	1265.7	1267.1	1268.6	1270.1	1270.2	1268.9	1267.7	1266.4	1265.1	1263.9
162.5°	1274.9	1276.7	1278.5	1280.3	1282.2	1282.4	1280.9	1279.5	1278.0	1276.6	1275.5
165°	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9	1290.3
167.5°	1301.1	1303.0	1304.9	1306.8	1308.7	1308.9	1307.4	1305.9	1304.4	1303.0	1302.4
170°	1307.2	1309.1	1311.0	1312.9	1314.8	1315.0	1313.5	1312.1	1310.6	1309.1	1308.7
172.5°	1311.8	1313.7	1315.6	1317.5	1319.4	1319.6	1318.1	1316.6	1315.2	1313.7	1313.2
175°	1315.8	1317.9	1320.0	1322.1	1324.3	1324.6	1323.1	1321.6	1320.1	1318.6	1318.2
177.5°	1318.3	1319.8	1321.3	1322.8	1324.4	1324.5	1323.3	1322.2	1321.0	1319.8	1319.6
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	12.1	11.8	11.4	11.6	10.3	9.8	8.1	6.8	6.9	7.1	7.0
90°	15.7	14.0	12.3	10.3	8.0	5.6	3.3	1.0	3.3	5.6	8.0
92.5°	20.5	19.6	18.8	18.5	18.7	18.9	19.1	19.3	19.1	18.9	18.7
95°	34.3	32.8	31.3	34.1	41.1	48.1	55.1	62.1	55.1	48.1	41.1
97.5°	43.0	39.6	36.1	44.3	64.0	83.8	103.5	123.3	103.5	83.8	64.0
100°	47.2	43.6	40.0	52.8	81.9	110.9	140.0	169.1	140.0	110.9	81.9
102.5°	116.4	146.6	176.8	194.9	201.1	207.3	213.4	219.6	213.4	207.3	201.1
105°	174.2	232.2	290.2	316.0	309.6	303.2	296.9	290.5	296.9	303.2	309.6
107.5°	220.6	290.2	359.7	391.9	386.7	381.6	376.5	371.3	376.5	381.6	386.7
110°	290.0	351.3	412.7	441.1	436.7	432.2	427.8	423.3	427.8	432.2	436.7



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	452.1	467.3	482.4	488.0	484.1	480.1	476.2	472.2	476.2	480.1	484.1
115°	578.9	573.6	568.3	563.9	560.3	556.7	553.0	549.4	553.0	556.7	560.3
117.5°	645.7	642.1	638.4	634.6	630.5	626.5	622.5	618.4	622.5	626.5	630.5
120°	692.8	688.9	685.1	681.6	678.4	675.2	672.1	668.9	672.1	675.2	678.4
122.5°	737.2	733.0	728.9	725.1	721.7	718.4	715.0	711.7	715.0	718.4	721.7
125°	799.4	795.3	791.3	787.9	785.1	782.4	779.6	776.8	779.6	782.4	785.1
127.5°	857.2	854.2	851.2	848.1	845.1	842.0	839.0	835.9	839.0	842.0	845.1
130°	894.5	892.1	889.8	886.9	883.5	880.2	876.8	873.4	876.8	880.2	883.5
132.5°	930.4	928.1	925.7	923.1	920.2	917.4	914.5	911.6	914.5	917.4	920.2
135°	981.3	979.4	977.5	974.9	971.5	968.1	964.7	961.3	964.7	968.1	971.5
137.5°	1027.6	1025.5	1023.3	1021.0	1018.7	1016.3	1013.9	1011.5	1013.9	1016.3	1018.7
140°	1057.9	1055.5	1053.2	1051.2	1049.5	1047.8	1046.1	1044.4	1046.1	1047.8	1049.5
142.5°	1085.5	1082.8	1080.1	1078.0	1076.5	1075.0	1073.4	1071.9	1073.4	1075.0	1076.5
145°	1123.2	1119.6	1116.0	1114.3	1114.5	1114.7	1114.9	1115.1	1114.9	1114.7	1114.5
147.5°	1158.0	1154.5	1150.9	1149.5	1150.3	1151.1	1151.9	1152.8	1151.9	1151.1	1150.3
150°	1179.0	1175.6	1172.2	1171.3	1172.8	1174.2	1175.7	1177.2	1175.7	1174.2	1172.8
152.5°	1198.5	1195.2	1192.0	1191.2	1192.9	1194.5	1196.2	1197.9	1196.2	1194.5	1192.9
155°	1225.6	1223.1	1220.5	1220.2	1222.1	1224.0	1225.9	1227.9	1225.9	1224.0	1222.1
157.5°	1248.6	1246.8	1245.0	1244.9	1246.5	1248.1	1249.8	1251.4	1249.8	1248.1	1246.5
160°	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1263.9	1262.6	1261.3
162.5°	1274.4	1273.3	1272.2	1272.3	1273.5	1274.8	1276.1	1277.4	1276.1	1274.8	1273.5
165°	1289.6	1289.0	1288.4	1288.7	1290.0	1291.2	1292.5	1293.8	1292.5	1291.2	1290.0
167.5°	1301.8	1301.2	1300.6	1300.9	1302.2	1303.5	1304.7	1306.0	1304.7	1303.5	1302.2
170°	1308.2	1307.8	1307.4	1307.8	1309.1	1310.4	1311.6	1312.9	1311.6	1310.4	1309.1
172.5°	1312.8	1312.4	1312.0	1312.4	1313.7	1314.9	1316.2	1317.5	1316.2	1314.9	1313.7
175°	1317.8	1317.4	1316.9	1317.5	1319.0	1320.4	1321.9	1323.4	1321.9	1320.4	1319.0
177.5°	1319.4	1319.3	1319.1	1319.6	1320.8	1322.0	1323.2	1324.4	1323.2	1322.0	1320.8
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	7.1	7.2	7.3	7.6	7.7	7.7	7.6	7.8	8.0	7.7	7.8
90°	10.3	12.3	14.0	15.7	17.4	19.1	20.2	21.2	22.3	23.4	24.1
92.5°	18.5	18.8	19.6	20.5	21.3	22.2	22.7	23.3	23.8	24.4	24.8
95°	34.1	31.3	32.8	34.3	35.8	37.3	38.3	39.4	40.5	41.5	41.9
97.5°	44.3	36.1	39.6	43.0	46.4	49.9	50.7	51.6	52.4	53.3	53.8
100°	52.8	40.0	43.6	47.2	50.9	54.5	56.2	57.9	59.6	61.3	62.3
102.5°	194.9	176.8	146.6	116.4	86.2	56.0	58.2	60.4	62.6	64.8	66.2
105°	316.0	290.2	232.2	174.2	116.3	58.3	60.6	63.0	65.3	67.6	69.2
107.5°	391.9	359.7	290.2	220.6	151.1	81.6	79.2	76.8	74.5	72.1	71.3
110°	441.1	412.7	351.3	290.0	228.6	167.2	146.0	124.7	103.5	82.3	72.1



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.0	482.4	467.3	452.1	436.9	421.8	344.3	266.8	189.4	111.9	73.5
115°	563.9	568.3	573.6	578.9	584.3	589.6	491.2	392.9	294.6	196.3	139.5
117.5°	634.6	638.4	642.1	645.7	649.4	653.0	629.2	605.4	581.7	557.9	520.9
120°	681.6	685.1	688.9	692.8	696.6	700.4	703.0	705.5	708.0	710.6	697.5
122.5°	725.1	728.9	733.0	737.2	741.3	745.5	747.0	748.6	750.1	751.6	749.6
125°	787.9	791.3	795.3	799.4	803.4	807.4	808.9	810.4	811.9	813.4	814.4
127.5°	848.1	851.2	854.2	857.2	860.2	863.2	865.4	867.6	869.7	871.9	873.0
130°	886.9	889.8	892.1	894.5	896.8	899.2	901.5	903.8	906.2	908.5	909.6
132.5°	923.1	925.7	928.1	930.4	932.7	935.1	937.1	939.1	941.1	943.1	944.0
135°	974.9	977.5	979.4	981.3	983.2	985.2	987.3	989.4	991.5	993.6	994.5
137.5°	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1	1036.1	1038.2	1040.3	1041.0
140°	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5	1066.4	1068.3	1070.2	1070.6
142.5°	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6	1094.3	1096.1	1097.8	1098.1
145°	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9	1133.4	1134.9	1136.3	1136.6
147.5°	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3	1167.4	1168.5	1169.6	1169.7
150°	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1	1188.4	1189.6	1190.9	1191.0
152.5°	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2	1207.5	1208.7	1210.0	1210.0
155°	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0	1233.3	1234.5	1235.8	1235.6
157.5°	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6	1255.0	1256.5	1257.9	1257.8
160°	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4	1267.7	1268.9	1270.2	1270.1
162.5°	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0	1279.5	1280.9	1282.4	1282.2
165°	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9
167.5°	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4	1305.9	1307.4	1308.9	1308.7
170°	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6	1312.1	1313.5	1315.0	1314.8
172.5°	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2	1316.6	1318.1	1319.6	1319.4
175°	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1	1321.6	1323.1	1324.6	1324.3
177.5°	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0	1322.2	1323.3	1324.5	1324.4
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	7.9	7.7	7.8	7.6	7.8	7.7	7.9	7.8	7.7	8.0	7.8
90°	24.5	24.9	25.4	25.8	25.4	24.9	24.5	24.1	23.4	22.3	21.2
92.5°	25.0	25.3	25.5	25.8	25.5	25.3	25.0	24.8	24.4	23.8	23.3
95°	41.7	41.5	41.3	41.1	41.3	41.5	41.7	41.9	41.5	40.5	39.4
97.5°	54.1	54.3	54.6	54.8	54.6	54.3	54.1	53.8	53.3	52.4	51.6
100°	62.7	63.2	63.6	64.0	63.6	63.2	62.7	62.3	61.3	59.6	57.9
102.5°	66.8	67.4	68.0	68.6	68.0	67.4	66.8	66.2	64.8	62.6	60.4
105°	70.1	70.9	71.8	72.6	71.8	70.9	70.1	69.2	67.6	65.3	63.0
107.5°	72.2	73.0	73.9	74.7	73.9	73.0	72.2	71.3	72.1	74.5	76.8
110°	72.9	73.8	74.6	75.5	74.6	73.8	72.9	72.1	82.3	103.5	124.7



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	74.2	74.9	75.6	76.3	75.6	74.9	74.2	73.5	111.9	189.4	266.8
115°	124.2	108.9	93.6	78.4	93.6	108.9	124.2	139.5	196.3	294.6	392.9
117.5°	470.6	420.4	370.2	319.9	370.2	420.4	470.6	520.9	557.9	581.7	605.4
120°	668.9	640.2	611.5	582.9	611.5	640.2	668.9	697.5	710.6	708.0	705.5
122.5°	744.0	738.5	732.9	727.4	732.9	738.5	744.0	749.6	751.6	750.1	748.6
125°	815.1	815.7	816.3	817.0	816.3	815.7	815.1	814.4	813.4	811.9	810.4
127.5°	873.2	873.3	873.4	873.5	873.4	873.3	873.2	873.0	871.9	869.7	867.6
130°	909.3	909.1	908.9	908.7	908.9	909.1	909.3	909.6	908.5	906.2	903.8
132.5°	943.7	943.5	943.3	943.1	943.3	943.5	943.7	944.0	943.1	941.1	939.1
135°	994.1	993.6	993.2	992.8	993.2	993.6	994.1	994.5	993.6	991.5	989.4
137.5°	1040.3	1039.5	1038.8	1038.1	1038.8	1039.5	1040.3	1041.0	1040.3	1038.2	1036.1
140°	1069.6	1068.5	1067.4	1066.4	1067.4	1068.5	1069.6	1070.6	1070.2	1068.3	1066.4
142.5°	1097.1	1096.0	1095.0	1093.9	1095.0	1096.0	1097.1	1098.1	1097.8	1096.1	1094.3
145°	1135.5	1134.4	1133.4	1132.3	1133.4	1134.4	1135.5	1136.6	1136.3	1134.9	1133.4
147.5°	1168.8	1167.9	1167.0	1166.1	1167.0	1167.9	1168.8	1169.7	1169.6	1168.5	1167.4
150°	1190.0	1188.9	1187.8	1186.8	1187.8	1188.9	1190.0	1191.0	1190.9	1189.6	1188.4
152.5°	1208.6	1207.2	1205.8	1204.4	1205.8	1207.2	1208.6	1210.0	1210.0	1208.7	1207.5
155°	1233.9	1232.2	1230.5	1228.8	1230.5	1232.2	1233.9	1235.6	1235.8	1234.5	1233.3
157.5°	1256.1	1254.5	1252.8	1251.2	1252.8	1254.5	1256.1	1257.8	1257.9	1256.5	1255.0
160°	1268.6	1267.1	1265.7	1264.2	1265.7	1267.1	1268.6	1270.1	1270.2	1268.9	1267.7
162.5°	1280.3	1278.5	1276.7	1274.9	1276.7	1278.5	1280.3	1282.2	1282.4	1280.9	1279.5
165°	1295.4	1293.9	1292.4	1290.9	1292.4	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9
167.5°	1306.8	1304.9	1303.0	1301.1	1303.0	1304.9	1306.8	1308.7	1308.9	1307.4	1305.9
170°	1312.9	1311.0	1309.1	1307.2	1309.1	1311.0	1312.9	1314.8	1315.0	1313.5	1312.1
172.5°	1317.5	1315.6	1313.7	1311.8	1313.7	1315.6	1317.5	1319.4	1319.6	1318.1	1316.6
175°	1322.1	1320.0	1317.9	1315.8	1317.9	1320.0	1322.1	1324.3	1324.6	1323.1	1321.6
177.5°	1322.8	1321.3	1319.8	1318.3	1319.8	1321.3	1322.8	1324.4	1324.5	1323.3	1322.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	7.6	7.7	7.7	7.6	7.3	7.2	7.1	7.0	7.1	6.9	6.8
90°	20.2	19.1	17.4	15.7	14.0	12.3	10.3	8.0	5.6	3.3	1.0
92.5°	22.7	22.2	21.3	20.5	19.6	18.8	18.5	18.7	18.9	19.1	19.3
95°	38.3	37.3	35.8	34.3	32.8	31.3	34.1	41.1	48.1	55.1	62.1
97.5°	50.7	49.9	46.4	43.0	39.6	36.1	44.3	64.0	83.8	103.5	123.3
100°	56.2	54.5	50.9	47.2	43.6	40.0	52.8	81.9	110.9	140.0	169.1
102.5°	58.2	56.0	86.2	116.4	146.6	176.8	194.9	201.1	207.3	213.4	219.6
105°	60.6	58.3	116.3	174.2	232.2	290.2	316.0	309.6	303.2	296.9	290.5
107.5°	79.2	81.6	151.1	220.6	290.2	359.7	391.9	386.7	381.6	376.5	371.3
110°	146.0	167.2	228.6	290.0	351.3	412.7	441.1	436.7	432.2	427.8	423.3



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	344.3	421.8	436.9	452.1	467.3	482.4	488.0	484.1	480.1	476.2	472.2
115°	491.2	589.6	584.3	578.9	573.6	568.3	563.9	560.3	556.7	553.0	549.4
117.5°	629.2	653.0	649.4	645.7	642.1	638.4	634.6	630.5	626.5	622.5	618.4
120°	703.0	700.4	696.6	692.8	688.9	685.1	681.6	678.4	675.2	672.1	668.9
122.5°	747.0	745.5	741.3	737.2	733.0	728.9	725.1	721.7	718.4	715.0	711.7
125°	808.9	807.4	803.4	799.4	795.3	791.3	787.9	785.1	782.4	779.6	776.8
127.5°	865.4	863.2	860.2	857.2	854.2	851.2	848.1	845.1	842.0	839.0	835.9
130°	901.5	899.2	896.8	894.5	892.1	889.8	886.9	883.5	880.2	876.8	873.4
132.5°	937.1	935.1	932.7	930.4	928.1	925.7	923.1	920.2	917.4	914.5	911.6
135°	987.3	985.2	983.2	981.3	979.4	977.5	974.9	971.5	968.1	964.7	961.3
137.5°	1034.1	1032.0	1029.8	1027.6	1025.5	1023.3	1021.0	1018.7	1016.3	1013.9	1011.5
140°	1064.5	1062.6	1060.2	1057.9	1055.5	1053.2	1051.2	1049.5	1047.8	1046.1	1044.4
142.5°	1092.6	1090.8	1088.2	1085.5	1082.8	1080.1	1078.0	1076.5	1075.0	1073.4	1071.9
145°	1131.9	1130.4	1126.8	1123.2	1119.6	1116.0	1114.3	1114.5	1114.7	1114.9	1115.1
147.5°	1166.3	1165.2	1161.6	1158.0	1154.5	1150.9	1149.5	1150.3	1151.1	1151.9	1152.8
150°	1187.1	1185.8	1182.4	1179.0	1175.6	1172.2	1171.3	1172.8	1174.2	1175.7	1177.2
152.5°	1206.2	1204.9	1201.7	1198.5	1195.2	1192.0	1191.2	1192.9	1194.5	1196.2	1197.9
155°	1232.0	1230.7	1228.2	1225.6	1223.1	1220.5	1220.2	1222.1	1224.0	1225.9	1227.9
157.5°	1253.6	1252.1	1250.3	1248.6	1246.8	1245.0	1244.9	1246.5	1248.1	1249.8	1251.4
160°	1266.4	1265.1	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1
162.5°	1278.0	1276.6	1275.5	1274.4	1273.3	1272.2	1272.3	1273.5	1274.8	1276.1	1277.4
165°	1292.4	1290.9	1290.3	1289.6	1289.0	1288.4	1288.7	1290.0	1291.2	1292.5	1293.8
167.5°	1304.4	1303.0	1302.4	1301.8	1301.2	1300.6	1300.9	1302.2	1303.5	1304.7	1306.0
170°	1310.6	1309.1	1308.7	1308.2	1307.8	1307.4	1307.8	1309.1	1310.4	1311.6	1312.9
172.5°	1315.2	1313.7	1313.2	1312.8	1312.4	1312.0	1312.4	1313.7	1314.9	1316.2	1317.5
175°	1320.1	1318.6	1318.2	1317.8	1317.4	1316.9	1317.5	1319.0	1320.4	1321.9	1323.4
177.5°	1321.0	1319.8	1319.6	1319.4	1319.3	1319.1	1319.6	1320.8	1322.0	1323.2	1324.4
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.1	9.8	10.3	11.6	11.4	11.8	12.1	12.1	12.2	12.1	12.0
90°	3.3	5.6	8.0	10.3	12.3	14.0	15.7	17.4	19.1	20.2	21.2
92.5°	19.1	18.9	18.7	18.5	18.8	19.6	20.5	21.3	22.2	22.7	23.3
95°	55.1	48.1	41.1	34.1	31.3	32.8	34.3	35.8	37.3	38.3	39.4
97.5°	103.5	83.8	64.0	44.3	36.1	39.6	43.0	46.4	49.9	50.7	51.6
100°	140.0	110.9	81.9	52.8	40.0	43.6	47.2	50.9	54.5	56.2	57.9
102.5°	213.4	207.3	201.1	194.9	176.8	146.6	116.4	86.2	56.0	58.2	60.4
105°	296.9	303.2	309.6	316.0	290.2	232.2	174.2	116.3	58.3	60.6	63.0
107.5°	376.5	381.6	386.7	391.9	359.7	290.2	220.6	151.1	81.6	79.2	76.8
110°	427.8	432.2	436.7	441.1	412.7	351.3	290.0	228.6	167.2	146.0	124.7



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	476.2	480.1	484.1	488.0	482.4	467.3	452.1	436.9	421.8	344.3	266.8
115°	553.0	556.7	560.3	563.9	568.3	573.6	578.9	584.3	589.6	491.2	392.9
117.5°	622.5	626.5	630.5	634.6	638.4	642.1	645.7	649.4	653.0	629.2	605.4
120°	672.1	675.2	678.4	681.6	685.1	688.9	692.8	696.6	700.4	703.0	705.5
122.5°	715.0	718.4	721.7	725.1	728.9	733.0	737.2	741.3	745.5	747.0	748.6
125°	779.6	782.4	785.1	787.9	791.3	795.3	799.4	803.4	807.4	808.9	810.4
127.5°	839.0	842.0	845.1	848.1	851.2	854.2	857.2	860.2	863.2	865.4	867.6
130°	876.8	880.2	883.5	886.9	889.8	892.1	894.5	896.8	899.2	901.5	903.8
132.5°	914.5	917.4	920.2	923.1	925.7	928.1	930.4	932.7	935.1	937.1	939.1
135°	964.7	968.1	971.5	974.9	977.5	979.4	981.3	983.2	985.2	987.3	989.4
137.5°	1013.9	1016.3	1018.7	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1	1036.1
140°	1046.1	1047.8	1049.5	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5	1066.4
142.5°	1073.4	1075.0	1076.5	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6	1094.3
145°	1114.9	1114.7	1114.5	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9	1133.4
147.5°	1151.9	1151.1	1150.3	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3	1167.4
150°	1175.7	1174.2	1172.8	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1	1188.4
152.5°	1196.2	1194.5	1192.9	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2	1207.5
155°	1225.9	1224.0	1222.1	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0	1233.3
157.5°	1249.8	1248.1	1246.5	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6	1255.0
160°	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4	1267.7
162.5°	1276.1	1274.8	1273.5	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0	1279.5
165°	1292.5	1291.2	1290.0	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4	1293.9
167.5°	1304.7	1303.5	1302.2	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4	1305.9
170°	1311.6	1310.4	1309.1	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6	1312.1
172.5°	1316.2	1314.9	1313.7	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2	1316.6
175°	1321.9	1320.4	1319.0	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1	1321.6
177.5°	1323.2	1322.0	1320.8	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0	1322.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	12.5	12.7	12.6	12.7	13.1	12.8	12.9
90°	22.3	23.4	24.1	24.5	24.9	25.4	25.8
92.5°	23.8	24.4	24.8	25.0	25.3	25.5	25.8
95°	40.5	41.5	41.9	41.7	41.5	41.3	41.1
97.5°	52.4	53.3	53.8	54.1	54.3	54.6	54.8
100°	59.6	61.3	62.3	62.7	63.2	63.6	64.0
102.5°	62.6	64.8	66.2	66.8	67.4	68.0	68.6
105°	65.3	67.6	69.2	70.1	70.9	71.8	72.6
107.5°	74.5	72.1	71.3	72.2	73.0	73.9	74.7
110°	103.5	82.3	72.1	72.9	73.8	74.6	75.5



TEST NUMBER: P331507

CATALOG NUMBER: S122DIW-S485D970U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	189.4	111.9	73.5	74.2	74.9	75.6	76.3
115°	294.6	196.3	139.5	124.2	108.9	93.6	78.4
117.5°	581.7	557.9	520.9	470.6	420.4	370.2	319.9
120°	708.0	710.6	697.5	668.9	640.2	611.5	582.9
122.5°	750.1	751.6	749.6	744.0	738.5	732.9	727.4
125°	811.9	813.4	814.4	815.1	815.7	816.3	817.0
127.5°	869.7	871.9	873.0	873.2	873.3	873.4	873.5
130°	906.2	908.5	909.6	909.3	909.1	908.9	908.7
132.5°	941.1	943.1	944.0	943.7	943.5	943.3	943.1
135°	991.5	993.6	994.5	994.1	993.6	993.2	992.8
137.5°	1038.2	1040.3	1041.0	1040.3	1039.5	1038.8	1038.1
140°	1068.3	1070.2	1070.6	1069.6	1068.5	1067.4	1066.4
142.5°	1096.1	1097.8	1098.1	1097.1	1096.0	1095.0	1093.9
145°	1134.9	1136.3	1136.6	1135.5	1134.4	1133.4	1132.3
147.5°	1168.5	1169.6	1169.7	1168.8	1167.9	1167.0	1166.1
150°	1189.6	1190.9	1191.0	1190.0	1188.9	1187.8	1186.8
152.5°	1208.7	1210.0	1210.0	1208.6	1207.2	1205.8	1204.4
155°	1234.5	1235.8	1235.6	1233.9	1232.2	1230.5	1228.8
157.5°	1256.5	1257.9	1257.8	1256.1	1254.5	1252.8	1251.2
160°	1268.9	1270.2	1270.1	1268.6	1267.1	1265.7	1264.2
162.5°	1280.9	1282.4	1282.2	1280.3	1278.5	1276.7	1274.9
165°	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9
167.5°	1307.4	1308.9	1308.7	1306.8	1304.9	1303.0	1301.1
170°	1313.5	1315.0	1314.8	1312.9	1311.0	1309.1	1307.2
172.5°	1318.1	1319.6	1319.4	1317.5	1315.6	1313.7	1311.8
175°	1323.1	1324.6	1324.3	1322.1	1320.0	1317.9	1315.8
177.5°	1323.3	1324.5	1324.4	1322.8	1321.3	1319.8	1318.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)