

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331553

Luminaire Tested: **S122DIW-S675D1440U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331553
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8466.0 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	1.2
10°-20°	280.9	3.3
20°-30°	412.9	4.9
30°-40°	479.6	5.7
40°-50°	479.1	5.7
50°-60°	417.8	4.9
60°-70°	308.9	3.6
70°-80°	175.0	2.1
80°-90°	51.9	0.6
90°-100°	65.6	0.8
100°-110°	240.4	2.8
110°-120°	642.7	7.6
120°-130°	1060.9	12.5
130°-140°	1128.3	13.3
140°-150°	1048.7	12.4
150°-160°	843.1	10.0
160°-170°	543.3	6.4
170°-180°	187.0	2.2
0°-30°	793.6	9.4
0°-40°	1273.2	15.0
0°-60°	2170.1	25.6
0°-90°	2705.9	32.0
90°-120°	948.7	11.2
90°-150°	4186.6	49.5
90°-180°	5760.0	68.0
0°-180°	8466.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	1	17	28	35	38	6
95°	92	49	56	62	61	113
105°	432	451	87	102	108	462
115°	818	843	878	250	117	805
125°	1156	1175	1202	1211	1216	1031
135°	1431	1453	1466	1480	1478	1105
145°	1660	1660	1682	1692	1685	1038
155°	1828	1816	1832	1839	1829	842
165°	1926	1918	1921	1930	1921	544
175°	1970	1961	1963	1971	1958	187
180°	1966	1966	1966	1966	1966	



TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	15.0	15.3	15.6	16.0	16.3	16.6	16.7	16.8	17.0	17.1	16.9
90°	1.4	4.9	8.4	11.9	15.3	18.3	20.9	23.4	25.9	28.4	30.0
92.5°	28.7	28.4	28.1	27.8	27.5	27.9	29.2	30.5	31.7	33.0	33.8
95°	92.4	82.0	71.6	61.2	50.7	46.6	48.8	51.0	53.3	55.5	57.0
97.5°	183.5	154.1	124.7	95.3	65.9	53.8	58.9	64.0	69.1	74.2	75.5
100°	251.7	208.4	165.1	121.8	78.5	59.6	64.9	70.3	75.7	81.1	83.6
102.5°	326.8	317.7	308.5	299.3	290.2	263.1	218.2	173.2	128.3	83.3	86.6
105°	432.4	441.8	451.3	460.8	470.3	431.9	345.6	259.3	173.0	86.8	90.2
107.5°	552.7	560.3	568.0	575.6	583.3	535.4	431.9	328.4	224.9	121.5	117.9
110°	630.1	636.7	643.3	650.0	656.6	614.2	522.9	431.6	340.2	248.9	217.3



TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	702.9	708.7	714.6	720.5	726.4	718.0	695.5	672.9	650.3	627.8	512.5
115°	817.8	823.2	828.5	833.9	839.3	845.9	853.8	861.7	869.6	877.5	731.2
117.5°	920.5	926.5	932.5	938.5	944.5	950.2	955.6	961.1	966.5	972.0	936.6
120°	995.6	1000.3	1005.0	1009.8	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3
122.5°	1059.3	1064.3	1069.3	1074.3	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9
125°	1156.3	1160.4	1164.5	1168.6	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0
127.5°	1244.2	1248.7	1253.3	1257.8	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1
130°	1299.9	1305.0	1310.0	1315.1	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8
132.5°	1356.8	1361.1	1365.4	1369.7	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8
135°	1430.8	1435.8	1440.9	1445.9	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5
137.5°	1505.6	1509.1	1512.7	1516.2	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1
140°	1554.5	1557.0	1559.6	1562.1	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4
142.5°	1595.5	1597.7	1600.0	1602.3	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2
145°	1659.8	1659.4	1659.1	1658.8	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7
147.5°	1715.8	1714.6	1713.4	1712.2	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9
150°	1752.2	1750.0	1747.8	1745.6	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9
152.5°	1782.9	1780.5	1778.0	1775.5	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3
155°	1827.6	1824.7	1821.9	1819.0	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7
157.5°	1862.6	1860.2	1857.8	1855.4	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9
160°	1883.0	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9
162.5°	1901.2	1899.4	1897.5	1895.6	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3
165°	1925.7	1923.8	1921.9	1920.0	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7
167.5°	1943.9	1942.0	1940.1	1938.2	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6
170°	1954.2	1952.3	1950.4	1948.5	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7
172.5°	1961.0	1959.1	1957.2	1955.3	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5
175°	1969.8	1967.6	1965.4	1963.2	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9
177.5°	1971.2	1969.5	1967.7	1965.9	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	16.7	16.4	16.2	16.1	16.0	16.0	15.9	15.8
90°	31.6	33.2	34.8	35.9	36.5	37.1	37.8	38.4
92.5°	34.6	35.5	36.3	36.9	37.3	37.6	38.0	38.4
95°	58.6	60.2	61.8	62.4	62.1	61.8	61.5	61.2
97.5°	76.8	78.0	79.3	80.1	80.5	80.9	81.3	81.6
100°	86.1	88.7	91.2	92.8	93.4	94.0	94.7	95.3
102.5°	89.9	93.2	96.5	98.6	99.5	100.3	101.2	102.1
105°	93.7	97.2	100.7	103.0	104.3	105.6	106.8	108.1
107.5°	114.4	110.8	107.3	106.2	107.4	108.7	110.0	111.2
110°	185.7	154.1	122.5	107.3	108.6	109.8	111.1	112.4



TEST NUMBER: P331553

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	397.2	281.9	166.6	109.4	110.5	111.5	112.5	113.5
115°	584.9	438.5	292.2	207.6	184.9	162.1	139.4	116.6
117.5°	901.2	865.8	830.4	775.3	700.5	625.7	550.9	476.2
120°	1050.1	1053.9	1057.7	1038.2	995.6	952.9	910.2	867.6
122.5°	1114.2	1116.5	1118.7	1115.7	1107.4	1099.2	1090.9	1082.6
125°	1206.2	1208.4	1210.6	1212.2	1213.2	1214.1	1215.1	1216.0
127.5°	1291.3	1294.5	1297.7	1299.5	1299.6	1299.8	1300.0	1300.2
130°	1345.3	1348.8	1352.2	1353.8	1353.5	1353.2	1352.9	1352.5
132.5°	1397.7	1400.7	1403.7	1405.0	1404.7	1404.4	1404.1	1403.7
135°	1472.6	1475.8	1479.0	1480.2	1479.6	1479.0	1478.3	1477.7
137.5°	1542.2	1545.3	1548.4	1549.4	1548.3	1547.3	1546.2	1545.1
140°	1587.2	1590.1	1592.9	1593.5	1592.0	1590.4	1588.8	1587.2
142.5°	1628.8	1631.4	1634.0	1634.5	1632.9	1631.3	1629.8	1628.2
145°	1686.9	1689.1	1691.4	1691.7	1690.1	1688.5	1686.9	1685.4
147.5°	1737.6	1739.2	1740.9	1741.0	1739.7	1738.4	1737.0	1735.7
150°	1768.8	1770.7	1772.6	1772.7	1771.2	1769.6	1768.0	1766.4
152.5°	1797.2	1799.1	1801.0	1800.9	1798.8	1796.8	1794.7	1792.6
155°	1835.6	1837.5	1839.4	1839.1	1836.6	1834.1	1831.5	1829.0
157.5°	1868.0	1870.1	1872.3	1872.1	1869.7	1867.2	1864.7	1862.3
160°	1886.8	1888.7	1890.6	1890.5	1888.3	1886.0	1883.8	1881.6
162.5°	1904.4	1906.6	1908.7	1908.4	1905.7	1903.0	1900.3	1897.6
165°	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4
167.5°	1943.8	1946.0	1948.2	1947.9	1945.1	1942.2	1939.4	1936.5
170°	1952.9	1955.1	1957.3	1957.0	1954.2	1951.3	1948.5	1945.6
172.5°	1959.7	1961.9	1964.1	1963.8	1961.0	1958.1	1955.3	1952.4
175°	1967.1	1969.3	1971.5	1971.1	1967.9	1964.7	1961.6	1958.4
177.5°	1967.9	1969.7	1971.5	1971.2	1968.9	1966.7	1964.4	1962.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5

(END OF REPORT)