

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331554

Luminaire Tested: **S122DIW-S675D1440U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331554
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7703.5 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	1.3
10°-20°	280.9	3.6
20°-30°	412.9	5.4
30°-40°	479.6	6.2
40°-50°	479.1	6.2
50°-60°	417.8	5.4
60°-70°	308.9	4.0
70°-80°	175.0	2.3
80°-90°	54.2	0.7
90°-100°	113.2	1.5
100°-110°	351.6	4.6
110°-120°	601.0	7.8
120°-130°	790.3	10.3
130°-140°	887.0	11.5
140°-150°	869.7	11.3
150°-160°	729.5	9.5
160°-170°	483.8	6.3
170°-180°	169.1	2.2
0°-30°	793.6	10.3
0°-40°	1273.2	16.5
0°-60°	2170.1	28.2
0°-90°	2708.2	35.2
90°-120°	1065.7	13.8
90°-150°	3612.8	46.9
90°-180°	4995.0	64.8
0°-180°	7703.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	2	20	53	50	51	6
95°	78	93	96	96	94	90
105°	324	329	332	334	335	342
115°	603	611	609	607	603	596
125°	877	890	886	882	880	784
135°	1135	1151	1155	1153	1149	877
145°	1378	1388	1398	1399	1393	860
155°	1575	1580	1584	1591	1588	725
165°	1714	1713	1713	1722	1716	483
175°	1783	1779	1776	1785	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	15.0	15.4	15.9	16.3	16.8	17.5	18.7	19.8	20.9	22.0	21.3
90°	1.5	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1
92.5°	26.8	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1
95°	78.4	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5
97.5°	143.2	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2
100°	191.5	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0
102.5°	242.1	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8
105°	324.1	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3
107.5°	406.7	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6
110°	459.8	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	517.7	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7
115°	603.0	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7
117.5°	688.1	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9
120°	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7
122.5°	796.6	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8
125°	877.4	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4
127.5°	956.1	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6
130°	1005.5	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5
132.5°	1061.0	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1
135°	1135.2	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5
137.5°	1213.3	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5
140°	1260.3	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4
142.5°	1308.6	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5
145°	1377.9	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8
147.5°	1439.7	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2
150°	1481.9	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0
152.5°	1519.3	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9
155°	1575.4	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1
157.5°	1623.3	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3
160°	1652.3	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8
162.5°	1678.8	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2
165°	1714.1	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9
167.5°	1743.6	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2
170°	1759.3	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6
172.5°	1770.2	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5
175°	1783.4	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3
177.5°	1788.9	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	20.6	20.0	19.3	18.9	18.8	18.6	18.5	18.4
90°	51.4	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.2	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.0	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.0	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	413.9	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331554

CATALOG NUMBER: S122DIW-S675D1440U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	523.9	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.4	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	690.1	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	801.0	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	884.4	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	965.4	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.8	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1074.7	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1154.1	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.2	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1327.8	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.2	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1459.9	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1587.8	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1633.6	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1660.8	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1685.5	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1717.3	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1743.5	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1758.0	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1768.8	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1780.6	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)