

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331526

Luminaire Tested: **S122DIW-S675D435U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331526
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4433.8 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66								
1	102	98	94	91	96	92	89	86	82	80	77	72	71	69	64	62	61	57								
2	93	86	80	75	88	81	76	72	73	69	65	64	61	59	57	55	53	49								
3	86	76	69	63	80	72	66	61	65	60	55	58	54	50	51	48	45	42								
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37								
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32								
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29								
7	62	50	42	37	59	48	41	35	43	37	33	39	34	30	35	31	28	26								
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23								
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21								
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	2.9
10°-20°	367.8	8.3
20°-30°	533.7	12.0
30°-40°	563.2	12.7
40°-50°	498.7	11.2
50°-60°	398.0	9.0
60°-70°	270.5	6.1
70°-80°	138.7	3.1
80°-90°	35.6	0.8
90°-100°	34.0	0.8
100°-110°	105.7	2.4
110°-120°	180.6	4.1
120°-130°	237.5	5.4
130°-140°	266.6	6.0
140°-150°	261.4	5.9
150°-160°	219.2	4.9
160°-170°	145.4	3.3
170°-180°	50.8	1.1
0°-30°	1028.0	23.2
0°-40°	1591.2	35.9
0°-60°	2487.8	56.1
0°-90°	2932.6	66.1
90°-120°	320.3	7.2
90°-150°	1085.7	24.5
90°-180°	1501.0	33.9
0°-180°	4433.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	15	0	15	0	15	8
95°	28	24	28	24	28	31
105°	101	97	101	97	101	106
115°	181	181	181	181	181	179
125°	265	264	265	264	265	236
135°	345	341	345	341	345	266
145°	419	414	419	414	419	261
155°	477	473	477	473	477	220
165°	516	515	516	515	516	145
175°	534	536	534	536	534	51
180°	537	537	537	537	537	



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	13.7	13.7	14.1	13.6	13.6	14.0	14.1	13.7	14.2	14.6	14.6
90°	15.4	15.3	15.2	15.1	15.0	15.1	15.3	15.5	15.7	15.9	13.6
92.5°	14.7	14.7	14.6	14.6	14.6	14.6	14.5	14.5	14.4	14.4	13.9
95°	28.1	28.3	28.5	28.7	28.9	29.0	29.0	29.0	29.0	29.0	28.8
97.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.4
100°	62.1	62.2	62.3	62.4	62.5	62.5	62.5	62.5	62.5	62.5	62.2
102.5°	77.3	77.4	77.5	77.6	77.7	77.7	77.6	77.5	77.5	77.4	77.0
105°	100.6	100.6	100.6	100.6	100.6	100.5	100.3	100.1	99.9	99.7	99.5
107.5°	122.5	123.0	123.4	123.9	124.4	124.6	124.5	124.4	124.3	124.2	124.2
110°	139.5	139.8	140.1	140.4	140.7	140.9	140.9	140.9	140.9	140.9	140.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.9	156.1	156.3	156.5	156.7	157.0	157.2	157.5	157.7	157.9	158.0
115°	181.2	181.5	181.8	182.1	182.4	182.6	182.7	182.8	182.9	183.0	183.2
117.5°	205.4	205.7	206.0	206.3	206.6	206.9	207.1	207.4	207.6	207.9	208.4
120°	222.5	222.8	223.1	223.4	223.7	223.8	223.8	223.8	223.8	223.8	224.6
122.5°	239.1	239.3	239.6	239.8	240.0	240.2	240.5	240.7	241.0	241.2	241.8
125°	264.6	264.7	264.8	264.9	265.0	265.2	265.5	265.8	266.1	266.4	266.7
127.5°	287.8	288.1	288.4	288.7	289.1	289.4	289.8	290.1	290.5	290.9	291.2
130°	304.5	304.9	305.3	305.7	306.1	306.4	306.6	306.8	307.0	307.2	307.4
132.5°	320.4	320.7	321.0	321.4	321.7	322.1	322.5	323.0	323.4	323.8	323.8
135°	345.2	345.5	345.8	346.1	346.4	346.6	346.7	346.8	346.9	347.0	346.8
137.5°	367.7	368.1	368.5	368.9	369.3	369.6	369.6	369.7	369.8	369.9	369.6
140°	383.3	383.7	384.1	384.5	384.9	385.1	385.1	385.1	385.1	385.1	384.6
142.5°	397.4	397.8	398.2	398.6	399.0	399.2	399.1	399.0	399.0	398.9	398.5
145°	418.6	419.0	419.4	419.8	420.2	420.4	420.3	420.2	420.1	420.0	419.4
147.5°	437.6	437.9	438.3	438.7	439.1	439.2	439.0	438.7	438.5	438.3	437.9
150°	449.9	450.2	450.5	450.8	451.1	451.1	450.8	450.5	450.2	449.9	449.5
152.5°	461.5	461.9	462.2	462.6	463.0	463.0	462.6	462.2	461.9	461.5	461.0
155°	477.1	477.4	477.7	478.0	478.3	478.2	477.7	477.2	476.7	476.2	475.9
157.5°	490.5	491.0	491.4	491.9	492.4	492.3	491.6	490.9	490.3	489.6	489.4
160°	498.8	499.2	499.6	500.0	500.4	500.3	499.7	499.1	498.5	497.9	497.8
162.5°	506.1	506.5	507.0	507.5	508.0	507.9	507.2	506.5	505.8	505.2	505.1
165°	515.6	516.1	516.6	517.1	517.6	517.5	516.8	516.1	515.4	514.7	514.7
167.5°	523.4	523.9	524.4	524.9	525.5	525.4	524.7	524.0	523.3	522.6	522.6
170°	527.4	528.0	528.6	529.2	529.8	529.7	529.0	528.3	527.6	526.9	527.0
172.5°	530.6	531.2	531.8	532.4	533.0	533.0	532.3	531.6	530.9	530.2	530.3
175°	534.2	534.8	535.4	536.0	536.6	536.5	535.8	535.1	534.4	533.7	533.9
177.5°	535.8	536.3	536.8	537.2	537.7	537.7	537.2	536.8	536.3	535.8	535.9
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	14.5	14.1	13.7	14.1	12.7	12.4	10.5	9.1	8.9	8.7	8.2
90°	11.4	9.2	7.0	5.3	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	13.4	12.8	12.3	11.6	10.7	9.8	9.0	8.1	9.0	9.8	10.7
95°	28.6	28.4	28.2	27.6	26.6	25.6	24.6	23.6	24.6	25.6	26.6
97.5°	48.0	47.6	47.2	46.6	45.7	44.8	43.9	43.0	43.9	44.8	45.7
100°	61.9	61.6	61.3	60.8	60.0	59.1	58.3	57.5	58.3	59.1	60.0
102.5°	76.6	76.2	75.9	75.3	74.7	74.0	73.4	72.8	73.4	74.0	74.7
105°	99.3	99.1	98.9	98.6	98.3	98.0	97.7	97.4	97.7	98.0	98.3
107.5°	124.2	124.2	124.2	124.0	123.6	123.1	122.7	122.2	122.7	123.1	123.6
110°	140.9	140.9	140.9	140.6	140.0	139.4	138.8	138.2	138.8	139.4	140.0



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	158.1	158.2	158.3	158.0	157.4	156.8	156.2	155.6	156.2	156.8	157.4
115°	183.4	183.6	183.8	183.6	183.0	182.4	181.8	181.2	181.8	182.4	183.0
117.5°	209.0	209.6	210.1	210.0	209.2	208.4	207.6	206.8	207.6	208.4	209.2
120°	225.4	226.2	227.0	227.0	226.2	225.4	224.6	223.8	224.6	225.4	226.2
122.5°	242.3	242.9	243.5	243.3	242.3	241.3	240.4	239.4	240.4	241.3	242.3
125°	267.0	267.3	267.6	267.3	266.4	265.5	264.6	263.7	264.6	265.5	266.4
127.5°	291.6	292.0	292.3	291.9	290.8	289.6	288.5	287.3	288.5	289.6	290.8
130°	307.6	307.8	308.0	307.4	306.1	304.8	303.5	302.2	303.5	304.8	306.1
132.5°	323.8	323.7	323.7	323.1	322.1	321.0	319.9	318.9	319.9	321.0	322.1
135°	346.6	346.4	346.2	345.6	344.5	343.4	342.3	341.2	342.3	343.4	344.5
137.5°	369.4	369.1	368.8	368.2	367.3	366.4	365.5	364.6	365.5	366.4	367.3
140°	384.1	383.6	383.1	382.4	381.5	380.6	379.7	378.8	379.7	380.6	381.5
142.5°	398.2	397.8	397.5	396.9	396.0	395.1	394.2	393.3	394.2	395.1	396.0
145°	418.8	418.2	417.6	416.9	416.2	415.5	414.8	414.1	414.8	415.5	416.2
147.5°	437.5	437.1	436.7	436.1	435.2	434.4	433.5	432.7	433.5	434.4	435.2
150°	449.1	448.7	448.3	447.8	447.2	446.6	446.0	445.4	446.0	446.6	447.2
152.5°	460.5	460.0	459.6	459.0	458.4	457.8	457.2	456.6	457.2	457.8	458.4
155°	475.6	475.3	475.0	474.7	474.4	474.0	473.7	473.4	473.7	474.0	474.4
157.5°	489.2	489.0	488.8	488.7	488.5	488.3	488.1	487.9	488.1	488.3	488.5
160°	497.7	497.6	497.5	497.4	497.2	497.0	496.8	496.6	496.8	497.0	497.2
162.5°	505.0	504.9	504.8	504.7	504.6	504.6	504.6	504.5	504.6	504.6	504.6
165°	514.7	514.7	514.7	514.7	514.8	514.9	515.0	515.1	515.0	514.9	514.8
167.5°	522.6	522.6	522.6	522.8	523.1	523.4	523.7	524.0	523.7	523.4	523.1
170°	527.1	527.2	527.3	527.5	527.8	528.1	528.4	528.7	528.4	528.1	527.8
172.5°	530.4	530.5	530.6	530.8	531.1	531.4	531.7	532.0	531.7	531.4	531.1
175°	534.1	534.3	534.5	534.8	535.1	535.4	535.7	536.0	535.7	535.4	535.1
177.5°	536.1	536.3	536.4	536.6	536.9	537.1	537.4	537.6	537.4	537.1	536.9
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	8.0	7.9	8.0	8.4	8.4	8.5	8.0	8.0	8.0	7.1	7.1
90°	5.3	7.0	9.2	11.4	13.6	15.9	15.7	15.5	15.3	15.1	15.0
92.5°	11.6	12.3	12.8	13.4	13.9	14.4	14.4	14.5	14.5	14.6	14.6
95°	27.6	28.2	28.4	28.6	28.8	29.0	29.0	29.0	29.0	29.0	28.9
97.5°	46.6	47.2	47.6	48.0	48.4	48.7	48.7	48.7	48.7	48.7	48.7
100°	60.8	61.3	61.6	61.9	62.2	62.5	62.5	62.5	62.5	62.5	62.5
102.5°	75.3	75.9	76.2	76.6	77.0	77.4	77.5	77.5	77.6	77.7	77.7
105°	98.6	98.9	99.1	99.3	99.5	99.7	99.9	100.1	100.3	100.5	100.6
107.5°	124.0	124.2	124.2	124.2	124.2	124.2	124.3	124.4	124.5	124.6	124.4
110°	140.6	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.7



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	158.0	158.3	158.2	158.1	158.0	157.9	157.7	157.5	157.2	157.0	156.7
115°	183.6	183.8	183.6	183.4	183.2	183.0	182.9	182.8	182.7	182.6	182.4
117.5°	210.0	210.1	209.6	209.0	208.4	207.9	207.6	207.4	207.1	206.9	206.6
120°	227.0	227.0	226.2	225.4	224.6	223.8	223.8	223.8	223.8	223.8	223.7
122.5°	243.3	243.5	242.9	242.3	241.8	241.2	241.0	240.7	240.5	240.2	240.0
125°	267.3	267.6	267.3	267.0	266.7	266.4	266.1	265.8	265.5	265.2	265.0
127.5°	291.9	292.3	292.0	291.6	291.2	290.9	290.5	290.1	289.8	289.4	289.1
130°	307.4	308.0	307.8	307.6	307.4	307.2	307.0	306.8	306.6	306.4	306.1
132.5°	323.1	323.7	323.7	323.8	323.8	323.8	323.4	323.0	322.5	322.1	321.7
135°	345.6	346.2	346.4	346.6	346.8	347.0	346.9	346.8	346.7	346.6	346.4
137.5°	368.2	368.8	369.1	369.4	369.6	369.9	369.8	369.7	369.6	369.6	369.3
140°	382.4	383.1	383.6	384.1	384.6	385.1	385.1	385.1	385.1	385.1	384.9
142.5°	396.9	397.5	397.8	398.2	398.5	398.9	399.0	399.0	399.1	399.2	399.0
145°	416.9	417.6	418.2	418.8	419.4	420.0	420.1	420.2	420.3	420.4	420.2
147.5°	436.1	436.7	437.1	437.5	437.9	438.3	438.5	438.7	439.0	439.2	439.1
150°	447.8	448.3	448.7	449.1	449.5	449.9	450.2	450.5	450.8	451.1	451.1
152.5°	459.0	459.6	460.0	460.5	461.0	461.5	461.9	462.2	462.6	463.0	463.0
155°	474.7	475.0	475.3	475.6	475.9	476.2	476.7	477.2	477.7	478.2	478.3
157.5°	488.7	488.8	489.0	489.2	489.4	489.6	490.3	490.9	491.6	492.3	492.4
160°	497.4	497.5	497.6	497.7	497.8	497.9	498.5	499.1	499.7	500.3	500.4
162.5°	504.7	504.8	504.9	505.0	505.1	505.2	505.8	506.5	507.2	507.9	508.0
165°	514.7	514.7	514.7	514.7	514.7	514.7	515.4	516.1	516.8	517.5	517.6
167.5°	522.8	522.6	522.6	522.6	522.6	522.6	523.3	524.0	524.7	525.4	525.5
170°	527.5	527.3	527.2	527.1	527.0	526.9	527.6	528.3	529.0	529.7	529.8
172.5°	530.8	530.6	530.5	530.4	530.3	530.2	530.9	531.6	532.3	533.0	533.0
175°	534.8	534.5	534.3	534.1	533.9	533.7	534.4	535.1	535.8	536.5	536.6
177.5°	536.6	536.4	536.3	536.1	535.9	535.8	536.3	536.8	537.2	537.7	537.7
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	7.1	6.7	6.7	6.3	6.7	6.7	7.1	7.1	7.1	8.0	8.0
90°	15.1	15.2	15.3	15.4	15.3	15.2	15.1	15.0	15.1	15.3	15.5
92.5°	14.6	14.6	14.7	14.7	14.7	14.6	14.6	14.6	14.6	14.5	14.5
95°	28.7	28.5	28.3	28.1	28.3	28.5	28.7	28.9	29.0	29.0	29.0
97.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7
100°	62.4	62.3	62.2	62.1	62.2	62.3	62.4	62.5	62.5	62.5	62.5
102.5°	77.6	77.5	77.4	77.3	77.4	77.5	77.6	77.7	77.7	77.6	77.5
105°	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.5	100.3	100.1
107.5°	123.9	123.4	123.0	122.5	123.0	123.4	123.9	124.4	124.6	124.5	124.4
110°	140.4	140.1	139.8	139.5	139.8	140.1	140.4	140.7	140.9	140.9	140.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	156.5	156.3	156.1	155.9	156.1	156.3	156.5	156.7	157.0	157.2	157.5
115°	182.1	181.8	181.5	181.2	181.5	181.8	182.1	182.4	182.6	182.7	182.8
117.5°	206.3	206.0	205.7	205.4	205.7	206.0	206.3	206.6	206.9	207.1	207.4
120°	223.4	223.1	222.8	222.5	222.8	223.1	223.4	223.7	223.8	223.8	223.8
122.5°	239.8	239.6	239.3	239.1	239.3	239.6	239.8	240.0	240.2	240.5	240.7
125°	264.9	264.8	264.7	264.6	264.7	264.8	264.9	265.0	265.2	265.5	265.8
127.5°	288.7	288.4	288.1	287.8	288.1	288.4	288.7	289.1	289.4	289.8	290.1
130°	305.7	305.3	304.9	304.5	304.9	305.3	305.7	306.1	306.4	306.6	306.8
132.5°	321.4	321.0	320.7	320.4	320.7	321.0	321.4	321.7	322.1	322.5	323.0
135°	346.1	345.8	345.5	345.2	345.5	345.8	346.1	346.4	346.6	346.7	346.8
137.5°	368.9	368.5	368.1	367.7	368.1	368.5	368.9	369.3	369.6	369.6	369.7
140°	384.5	384.1	383.7	383.3	383.7	384.1	384.5	384.9	385.1	385.1	385.1
142.5°	398.6	398.2	397.8	397.4	397.8	398.2	398.6	399.0	399.2	399.1	399.0
145°	419.8	419.4	419.0	418.6	419.0	419.4	419.8	420.2	420.4	420.3	420.2
147.5°	438.7	438.3	437.9	437.6	437.9	438.3	438.7	439.1	439.2	439.0	438.7
150°	450.8	450.5	450.2	449.9	450.2	450.5	450.8	451.1	451.1	450.8	450.5
152.5°	462.6	462.2	461.9	461.5	461.9	462.2	462.6	463.0	463.0	462.6	462.2
155°	478.0	477.7	477.4	477.1	477.4	477.7	478.0	478.3	478.2	477.7	477.2
157.5°	491.9	491.4	491.0	490.5	491.0	491.4	491.9	492.4	492.3	491.6	490.9
160°	500.0	499.6	499.2	498.8	499.2	499.6	500.0	500.4	500.3	499.7	499.1
162.5°	507.5	507.0	506.5	506.1	506.5	507.0	507.5	508.0	507.9	507.2	506.5
165°	517.1	516.6	516.1	515.6	516.1	516.6	517.1	517.6	517.5	516.8	516.1
167.5°	524.9	524.4	523.9	523.4	523.9	524.4	524.9	525.5	525.4	524.7	524.0
170°	529.2	528.6	528.0	527.4	528.0	528.6	529.2	529.8	529.7	529.0	528.3
172.5°	532.4	531.8	531.2	530.6	531.2	531.8	532.4	533.0	533.0	532.3	531.6
175°	536.0	535.4	534.8	534.2	534.8	535.4	536.0	536.6	536.5	535.8	535.1
177.5°	537.2	536.8	536.3	535.8	536.3	536.8	537.2	537.7	537.7	537.2	536.8
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	8.0	8.5	8.4	8.4	8.0	7.9	8.0	8.2	8.7	8.9	9.1
90°	15.7	15.9	13.6	11.4	9.2	7.0	5.3	4.1	2.9	1.7	0.5
92.5°	14.4	14.4	13.9	13.4	12.8	12.3	11.6	10.7	9.8	9.0	8.1
95°	29.0	29.0	28.8	28.6	28.4	28.2	27.6	26.6	25.6	24.6	23.6
97.5°	48.7	48.7	48.4	48.0	47.6	47.2	46.6	45.7	44.8	43.9	43.0
100°	62.5	62.5	62.2	61.9	61.6	61.3	60.8	60.0	59.1	58.3	57.5
102.5°	77.5	77.4	77.0	76.6	76.2	75.9	75.3	74.7	74.0	73.4	72.8
105°	99.9	99.7	99.5	99.3	99.1	98.9	98.6	98.3	98.0	97.7	97.4
107.5°	124.3	124.2	124.2	124.2	124.2	124.2	124.0	123.6	123.1	122.7	122.2
110°	140.9	140.9	140.9	140.9	140.9	140.9	140.6	140.0	139.4	138.8	138.2



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	157.7	157.9	158.0	158.1	158.2	158.3	158.0	157.4	156.8	156.2	155.6
115°	182.9	183.0	183.2	183.4	183.6	183.8	183.6	183.0	182.4	181.8	181.2
117.5°	207.6	207.9	208.4	209.0	209.6	210.1	210.0	209.2	208.4	207.6	206.8
120°	223.8	223.8	224.6	225.4	226.2	227.0	227.0	226.2	225.4	224.6	223.8
122.5°	241.0	241.2	241.8	242.3	242.9	243.5	243.3	242.3	241.3	240.4	239.4
125°	266.1	266.4	266.7	267.0	267.3	267.6	267.3	266.4	265.5	264.6	263.7
127.5°	290.5	290.9	291.2	291.6	292.0	292.3	291.9	290.8	289.6	288.5	287.3
130°	307.0	307.2	307.4	307.6	307.8	308.0	307.4	306.1	304.8	303.5	302.2
132.5°	323.4	323.8	323.8	323.8	323.7	323.7	323.1	322.1	321.0	319.9	318.9
135°	346.9	347.0	346.8	346.6	346.4	346.2	345.6	344.5	343.4	342.3	341.2
137.5°	369.8	369.9	369.6	369.4	369.1	368.8	368.2	367.3	366.4	365.5	364.6
140°	385.1	385.1	384.6	384.1	383.6	383.1	382.4	381.5	380.6	379.7	378.8
142.5°	399.0	398.9	398.5	398.2	397.8	397.5	396.9	396.0	395.1	394.2	393.3
145°	420.1	420.0	419.4	418.8	418.2	417.6	416.9	416.2	415.5	414.8	414.1
147.5°	438.5	438.3	437.9	437.5	437.1	436.7	436.1	435.2	434.4	433.5	432.7
150°	450.2	449.9	449.5	449.1	448.7	448.3	447.8	447.2	446.6	446.0	445.4
152.5°	461.9	461.5	461.0	460.5	460.0	459.6	459.0	458.4	457.8	457.2	456.6
155°	476.7	476.2	475.9	475.6	475.3	475.0	474.7	474.4	474.0	473.7	473.4
157.5°	490.3	489.6	489.4	489.2	489.0	488.8	488.7	488.5	488.3	488.1	487.9
160°	498.5	497.9	497.8	497.7	497.6	497.5	497.4	497.2	497.0	496.8	496.6
162.5°	505.8	505.2	505.1	505.0	504.9	504.8	504.7	504.6	504.6	504.6	504.5
165°	515.4	514.7	514.7	514.7	514.7	514.7	514.7	514.8	514.9	515.0	515.1
167.5°	523.3	522.6	522.6	522.6	522.6	522.6	522.8	523.1	523.4	523.7	524.0
170°	527.6	526.9	527.0	527.1	527.2	527.3	527.5	527.8	528.1	528.4	528.7
172.5°	530.9	530.2	530.3	530.4	530.5	530.6	530.8	531.1	531.4	531.7	532.0
175°	534.4	533.7	533.9	534.1	534.3	534.5	534.8	535.1	535.4	535.7	536.0
177.5°	536.3	535.8	535.9	536.1	536.3	536.4	536.6	536.9	537.1	537.4	537.6
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.5	12.4	12.7	14.1	13.7	14.1	14.5	14.6	14.6	14.2	13.7
90°	1.7	2.9	4.1	5.3	7.0	9.2	11.4	13.6	15.9	15.7	15.5
92.5°	9.0	9.8	10.7	11.6	12.3	12.8	13.4	13.9	14.4	14.4	14.5
95°	24.6	25.6	26.6	27.6	28.2	28.4	28.6	28.8	29.0	29.0	29.0
97.5°	43.9	44.8	45.7	46.6	47.2	47.6	48.0	48.4	48.7	48.7	48.7
100°	58.3	59.1	60.0	60.8	61.3	61.6	61.9	62.2	62.5	62.5	62.5
102.5°	73.4	74.0	74.7	75.3	75.9	76.2	76.6	77.0	77.4	77.5	77.5
105°	97.7	98.0	98.3	98.6	98.9	99.1	99.3	99.5	99.7	99.9	100.1
107.5°	122.7	123.1	123.6	124.0	124.2	124.2	124.2	124.2	124.2	124.3	124.4
110°	138.8	139.4	140.0	140.6	140.9	140.9	140.9	140.9	140.9	140.9	140.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	156.2	156.8	157.4	158.0	158.3	158.2	158.1	158.0	157.9	157.7	157.5
115°	181.8	182.4	183.0	183.6	183.8	183.6	183.4	183.2	183.0	182.9	182.8
117.5°	207.6	208.4	209.2	210.0	210.1	209.6	209.0	208.4	207.9	207.6	207.4
120°	224.6	225.4	226.2	227.0	227.0	226.2	225.4	224.6	223.8	223.8	223.8
122.5°	240.4	241.3	242.3	243.3	243.5	242.9	242.3	241.8	241.2	241.0	240.7
125°	264.6	265.5	266.4	267.3	267.6	267.3	267.0	266.7	266.4	266.1	265.8
127.5°	288.5	289.6	290.8	291.9	292.3	292.0	291.6	291.2	290.9	290.5	290.1
130°	303.5	304.8	306.1	307.4	308.0	307.8	307.6	307.4	307.2	307.0	306.8
132.5°	319.9	321.0	322.1	323.1	323.7	323.7	323.8	323.8	323.8	323.4	323.0
135°	342.3	343.4	344.5	345.6	346.2	346.4	346.6	346.8	347.0	346.9	346.8
137.5°	365.5	366.4	367.3	368.2	368.8	369.1	369.4	369.6	369.9	369.8	369.7
140°	379.7	380.6	381.5	382.4	383.1	383.6	384.1	384.6	385.1	385.1	385.1
142.5°	394.2	395.1	396.0	396.9	397.5	397.8	398.2	398.5	398.9	399.0	399.0
145°	414.8	415.5	416.2	416.9	417.6	418.2	418.8	419.4	420.0	420.1	420.2
147.5°	433.5	434.4	435.2	436.1	436.7	437.1	437.5	437.9	438.3	438.5	438.7
150°	446.0	446.6	447.2	447.8	448.3	448.7	449.1	449.5	449.9	450.2	450.5
152.5°	457.2	457.8	458.4	459.0	459.6	460.0	460.5	461.0	461.5	461.9	462.2
155°	473.7	474.0	474.4	474.7	475.0	475.3	475.6	475.9	476.2	476.7	477.2
157.5°	488.1	488.3	488.5	488.7	488.8	489.0	489.2	489.4	489.6	490.3	490.9
160°	496.8	497.0	497.2	497.4	497.5	497.6	497.7	497.8	497.9	498.5	499.1
162.5°	504.6	504.6	504.6	504.7	504.8	504.9	505.0	505.1	505.2	505.8	506.5
165°	515.0	514.9	514.8	514.7	514.7	514.7	514.7	514.7	514.7	515.4	516.1
167.5°	523.7	523.4	523.1	522.8	522.6	522.6	522.6	522.6	522.6	523.3	524.0
170°	528.4	528.1	527.8	527.5	527.3	527.2	527.1	527.0	526.9	527.6	528.3
172.5°	531.7	531.4	531.1	530.8	530.6	530.5	530.4	530.3	530.2	530.9	531.6
175°	535.7	535.4	535.1	534.8	534.5	534.3	534.1	533.9	533.7	534.4	535.1
177.5°	537.4	537.1	536.9	536.6	536.4	536.3	536.1	535.9	535.8	536.3	536.8
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	14.1	14.0	13.6	13.6	14.1	13.7	13.7
90°	15.3	15.1	15.0	15.1	15.2	15.3	15.4
92.5°	14.5	14.6	14.6	14.6	14.6	14.7	14.7
95°	29.0	29.0	28.9	28.7	28.5	28.3	28.1
97.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7
100°	62.5	62.5	62.5	62.4	62.3	62.2	62.1
102.5°	77.6	77.7	77.7	77.6	77.5	77.4	77.3
105°	100.3	100.5	100.6	100.6	100.6	100.6	100.6
107.5°	124.5	124.6	124.4	123.9	123.4	123.0	122.5
110°	140.9	140.9	140.7	140.4	140.1	139.8	139.5



TEST NUMBER: P331526

CATALOG NUMBER: S122DIW-S675D435U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	157.2	157.0	156.7	156.5	156.3	156.1	155.9
115°	182.7	182.6	182.4	182.1	181.8	181.5	181.2
117.5°	207.1	206.9	206.6	206.3	206.0	205.7	205.4
120°	223.8	223.8	223.7	223.4	223.1	222.8	222.5
122.5°	240.5	240.2	240.0	239.8	239.6	239.3	239.1
125°	265.5	265.2	265.0	264.9	264.8	264.7	264.6
127.5°	289.8	289.4	289.1	288.7	288.4	288.1	287.8
130°	306.6	306.4	306.1	305.7	305.3	304.9	304.5
132.5°	322.5	322.1	321.7	321.4	321.0	320.7	320.4
135°	346.7	346.6	346.4	346.1	345.8	345.5	345.2
137.5°	369.6	369.6	369.3	368.9	368.5	368.1	367.7
140°	385.1	385.1	384.9	384.5	384.1	383.7	383.3
142.5°	399.1	399.2	399.0	398.6	398.2	397.8	397.4
145°	420.3	420.4	420.2	419.8	419.4	419.0	418.6
147.5°	439.0	439.2	439.1	438.7	438.3	437.9	437.6
150°	450.8	451.1	451.1	450.8	450.5	450.2	449.9
152.5°	462.6	463.0	463.0	462.6	462.2	461.9	461.5
155°	477.7	478.2	478.3	478.0	477.7	477.4	477.1
157.5°	491.6	492.3	492.4	491.9	491.4	491.0	490.5
160°	499.7	500.3	500.4	500.0	499.6	499.2	498.8
162.5°	507.2	507.9	508.0	507.5	507.0	506.5	506.1
165°	516.8	517.5	517.6	517.1	516.6	516.1	515.6
167.5°	524.7	525.4	525.5	524.9	524.4	523.9	523.4
170°	529.0	529.7	529.8	529.2	528.6	528.0	527.4
172.5°	532.3	533.0	533.0	532.4	531.8	531.2	530.6
175°	535.8	536.5	536.6	536.0	535.4	534.8	534.2
177.5°	537.2	537.7	537.7	537.2	536.8	536.3	535.8
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9

(END OF REPORT)