

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331603-830

Luminaire Tested: **S122DIW-S1005D1240U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331603-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8820.0 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30344	30344	30344	30344
5°	34020	30543	27067	30543
10°	38984	30293	23423	30293
15°	43127	29737	20694	29737
20°	42471	29141	18866	29141
25°	38297	28349	17706	28349
30°	31646	27082	16861	27082
35°	23065	25754	16259	25754
40°	18421	24190	15924	24190
45°	16098	22379	15470	22379
50°	15131	20627	15169	20627
55°	13948	18849	14762	18849
60°	12784	16956	14134	16956
65°	11645	15259	13521	15259
70°	10570	13605	12619	13605
75°	9370	11759	11179	11759
80°	8061	9735	9000	9735
85°	7225	7225	5354	7225



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.0	2.0
10°-20°	520.4	5.9
20°-30°	755.2	8.6
30°-40°	796.9	9.0
40°-50°	705.6	8.0
50°-60°	563.1	6.4
60°-70°	382.7	4.3
70°-80°	196.2	2.2
80°-90°	51.2	0.6
90°-100°	53.1	0.6
100°-110°	194.9	2.2
110°-120°	521.0	5.9
120°-130°	860.1	9.8
130°-140°	914.7	10.4
140°-150°	850.1	9.6
150°-160°	683.5	7.7
160°-170°	440.5	5.0
170°-180°	151.6	1.7
0°-30°	1454.6	16.5
0°-40°	2251.5	25.5
0°-60°	3520.2	39.9
0°-90°	4150.4	47.1
90°-120°	769.1	8.7
90°-150°	3394.0	38.5
90°-180°	4670.0	52.9
0°-180°	8820.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1879	1879	1879	1879	1879	
5°	2099	1884	1670	1884	2099	210
15°	2580	1779	1238	1779	2580	712
25°	2150	1591	994	1591	2150	972
35°	1170	1307	825	1307	1170	761
45°	705	980	678	980	705	554
55°	496	670	524	670	496	444
65°	305	399	354	399	305	303
75°	150	188	179	188	150	161
85°	39	39	29	39	39	43
90°	31	1	31	1	31	16
95°	50	75	50	75	50	46
105°	88	350	88	350	88	91
115°	94	663	94	663	94	237
125°	986	937	986	937	986	853
135°	1198	1160	1198	1160	1198	923
145°	1366	1346	1366	1346	1366	854
155°	1483	1482	1483	1482	1483	684
165°	1558	1561	1558	1561	1558	440
175°	1588	1597	1588	1597	1588	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1966.1	1966.7	1967.8	1958.6	1957.5	1957.5	1949.4	1942.5	1934.4	1923.4	1924.6
5°	2099.0	2107.0	2109.9	2101.2	2088.2	2086.8	2074.5	2054.3	2035.5	2020.3	2009.5
7.5°	2257.7	2260.9	2253.8	2242.4	2232.7	2215.4	2192.5	2170.1	2138.8	2110.1	2088.7
10°	2377.8	2382.2	2369.9	2353.3	2339.6	2319.4	2286.1	2252.2	2211.0	2171.3	2139.5
12.5°	2469.2	2479.8	2464.1	2461.9	2438.5	2410.6	2371.1	2353.9	2295.9	2240.6	2206.6
15°	2580.1	2579.4	2580.9	2567.1	2549.8	2545.4	2503.6	2458.1	2376.4	2343.9	2287.6
17.5°	2548.1	2559.0	2564.1	2563.9	2563.5	2560.8	2547.3	2518.6	2477.7	2425.0	2359.9
20°	2471.8	2486.2	2488.4	2505.0	2514.4	2526.7	2531.8	2523.8	2498.5	2454.5	2398.1
22.5°	2353.9	2358.0	2364.7	2390.6	2410.9	2441.8	2457.8	2484.4	2474.8	2453.2	2406.2
25°	2149.7	2142.4	2167.7	2180.7	2227.6	2276.7	2312.2	2351.2	2385.9	2406.8	2393.0
27.5°	1904.3	1893.5	1931.4	1965.9	2004.0	2057.2	2112.3	2177.5	2231.7	2299.4	2322.7
30°	1697.4	1703.9	1740.0	1776.9	1834.7	1909.8	1971.9	2043.4	2120.7	2196.6	2249.3
32.5°	1474.4	1499.4	1522.2	1578.7	1629.6	1713.4	1804.3	1893.8	1990.2	2076.4	2158.0
35°	1170.2	1199.0	1230.9	1272.0	1343.5	1426.5	1515.4	1636.1	1767.6	1885.3	1982.1
37.5°	985.0	980.3	998.5	1028.3	1086.2	1153.3	1255.6	1374.7	1529.5	1667.8	1804.3
40°	874.0	871.1	884.1	911.5	955.6	1004.8	1094.3	1199.0	1342.7	1511.8	1674.3
42.5°	797.8	799.5	806.7	826.0	856.2	896.6	963.7	1052.8	1184.5	1343.7	1518.3
45°	705.0	710.0	718.0	727.4	744.7	778.0	815.5	879.1	983.1	1116.0	1287.9
47.5°	638.2	638.4	646.5	654.7	665.0	683.7	714.4	754.2	827.6	935.9	1083.6
50°	602.4	597.4	603.1	609.6	620.5	633.5	653.7	691.3	740.4	827.7	951.3
52.5°	558.5	558.6	563.8	566.3	576.0	589.0	607.5	633.5	678.0	746.3	847.8
55°	495.5	499.1	502.0	506.3	515.0	524.4	538.9	556.2	590.9	642.2	717.3
57.5°	436.3	437.4	440.4	448.6	454.0	462.7	476.5	492.2	514.7	552.7	609.2
60°	395.9	395.9	401.6	405.2	412.5	421.1	432.0	447.1	467.3	498.4	543.9
62.5°	358.8	358.3	360.6	366.5	372.0	380.1	390.9	403.8	422.8	450.4	487.9
65°	304.8	303.4	307.7	309.2	314.9	322.9	331.6	345.3	360.4	380.7	413.9
67.5°	252.8	254.6	256.8	259.6	262.8	271.2	276.9	286.6	299.4	316.2	338.7
70°	223.9	223.9	223.9	226.1	230.5	234.8	240.5	248.5	260.8	275.2	295.4
72.5°	191.5	193.9	196.1	194.9	200.4	202.9	209.9	214.4	226.1	235.4	253.3
75°	150.2	150.2	150.2	153.8	156.0	158.2	162.5	166.8	172.7	184.2	193.6
77.5°	112.1	111.8	112.5	113.4	115.7	118.3	119.6	123.5	128.8	134.2	142.1
80°	86.7	88.1	88.9	90.3	90.3	91.7	92.5	97.6	101.1	104.7	109.8
82.5°	67.0	67.3	67.5	67.8	68.3	69.2	71.1	72.7	74.0	77.0	80.9
85°	39.0	38.3	38.3	39.7	39.0	39.0	40.4	41.8	41.8	42.6	44.8
87.5°	21.2	21.1	21.6	20.9	20.8	21.2	21.0	20.2	20.5	20.8	20.9
90°	31.1	30.6	30.1	29.6	29.1	28.2	26.9	25.6	24.3	23.1	21.0
92.5°	31.1	30.8	30.5	30.2	29.9	29.4	28.7	28.1	27.4	26.8	25.7
95°	49.6	49.9	50.0	50.3	50.6	50.0	48.8	47.5	46.3	45.0	43.2
97.5°	66.2	65.9	65.6	65.2	64.9	64.3	63.2	62.2	61.2	60.2	56.1
100°	77.3	76.7	76.3	75.7	75.2	73.9	71.8	69.8	67.8	65.7	61.4
102.5°	82.8	82.1	81.3	80.6	79.9	78.2	75.6	72.9	70.2	67.6	104.0
105°	87.7	86.6	85.6	84.5	83.5	81.6	78.8	76.0	73.1	70.3	140.3
107.5°	90.2	89.2	88.1	87.1	86.1	87.0	89.8	92.7	95.6	98.5	182.4
110°	91.0	90.1	89.1	88.0	87.0	99.2	124.9	150.5	176.2	201.8	275.8



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	92.0	91.1	90.4	89.5	88.7	135.1	228.6	322.0	415.5	508.9	527.3
115°	94.5	113.0	131.5	149.9	168.3	236.9	355.5	474.1	592.8	711.4	705.0
117.5°	386.0	446.7	507.3	567.9	628.5	673.2	701.8	730.6	759.2	788.0	783.5
120°	703.3	737.9	772.5	807.1	841.7	857.4	854.3	851.3	848.2	845.1	840.6
122.5°	877.6	884.4	891.1	897.8	904.5	906.9	905.1	903.2	901.4	899.6	894.6
125°	985.8	985.1	984.3	983.4	982.7	981.5	979.7	977.9	976.1	974.3	969.4
127.5°	1054.0	1053.9	1053.8	1053.6	1053.5	1052.1	1049.4	1046.8	1044.2	1041.6	1037.9
130°	1096.5	1096.7	1097.0	1097.2	1097.5	1096.2	1093.4	1090.6	1087.8	1085.0	1082.1
132.5°	1138.0	1138.2	1138.5	1138.8	1139.0	1137.9	1135.5	1133.1	1130.7	1128.3	1125.5
135°	1198.0	1198.4	1199.0	1199.5	1200.0	1199.0	1196.4	1193.8	1191.3	1188.7	1186.4
137.5°	1252.5	1253.5	1254.3	1255.2	1256.0	1255.3	1252.7	1250.2	1247.7	1245.2	1242.6
140°	1286.8	1288.0	1289.3	1290.5	1291.8	1291.4	1289.0	1286.8	1284.4	1282.1	1279.3
142.5°	1319.9	1321.2	1322.5	1323.8	1325.0	1324.6	1322.6	1320.4	1318.3	1316.3	1313.0
145°	1366.3	1367.5	1368.9	1370.1	1371.4	1371.1	1369.3	1367.5	1365.7	1364.0	1359.6
147.5°	1407.1	1408.2	1409.2	1410.3	1411.4	1411.3	1409.9	1408.6	1407.3	1405.9	1401.7
150°	1432.0	1433.2	1434.5	1435.9	1437.1	1437.0	1435.5	1433.9	1432.4	1430.9	1426.7
152.5°	1453.2	1454.9	1456.6	1458.3	1460.0	1460.1	1458.5	1457.0	1455.5	1453.9	1450.0
155°	1482.7	1484.8	1486.9	1488.8	1490.9	1491.2	1489.7	1488.1	1486.6	1485.1	1482.0
157.5°	1509.7	1511.7	1513.7	1515.7	1517.7	1517.9	1516.1	1514.4	1512.6	1510.9	1508.7
160°	1525.4	1527.2	1529.0	1530.8	1532.6	1532.7	1531.2	1529.7	1528.0	1526.5	1525.0
162.5°	1538.3	1540.5	1542.7	1544.9	1547.1	1547.4	1545.6	1543.9	1542.1	1540.4	1539.1
165°	1557.6	1559.4	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6	1556.9
167.5°	1569.9	1572.2	1574.5	1576.8	1579.1	1579.3	1577.5	1575.7	1574.0	1572.2	1571.5
170°	1577.3	1579.6	1581.9	1584.2	1586.5	1586.8	1585.0	1583.2	1581.4	1579.6	1579.0
172.5°	1582.8	1585.1	1587.4	1589.7	1592.0	1592.2	1590.4	1588.7	1586.9	1585.1	1584.6
175°	1587.6	1590.2	1592.8	1595.3	1597.9	1598.3	1596.5	1594.7	1592.9	1591.1	1590.6
177.5°	1590.6	1592.5	1594.3	1596.2	1598.0	1598.3	1596.8	1595.3	1593.9	1592.5	1592.2
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1928.6	1924.0	1921.1	1910.7	1901.4	1892.2	1889.3	1890.5	1877.7	1865.6	1860.4
5°	2003.8	1989.2	1975.6	1956.1	1933.0	1907.6	1894.6	1884.5	1859.3	1831.8	1815.9
7.5°	2071.0	2050.4	2023.9	1987.3	1953.6	1913.8	1888.6	1866.1	1829.2	1790.5	1766.8
10°	2112.0	2083.9	2049.9	2005.2	1964.0	1915.6	1881.6	1847.7	1804.3	1758.1	1729.2
12.5°	2147.3	2109.3	2075.9	2018.5	1969.7	1909.2	1869.0	1821.1	1775.5	1720.5	1692.2
15°	2231.3	2161.2	2097.6	2032.6	1972.6	1888.1	1843.3	1779.0	1719.1	1651.2	1618.7
17.5°	2296.1	2217.3	2117.2	2034.7	1964.7	1871.1	1805.3	1728.3	1657.5	1579.9	1535.7
20°	2333.1	2242.8	2135.1	2036.9	1953.1	1846.3	1774.7	1696.0	1613.0	1525.5	1477.9
22.5°	2355.0	2260.1	2153.7	2028.3	1930.0	1826.0	1736.0	1649.7	1565.6	1471.2	1421.3
25°	2362.0	2275.3	2162.7	2021.1	1901.1	1783.4	1675.1	1591.3	1489.4	1401.3	1328.3
27.5°	2327.6	2265.5	2157.1	2007.4	1867.7	1730.1	1609.3	1514.4	1406.9	1311.3	1237.9
30°	2285.4	2249.3	2143.8	1993.6	1841.2	1693.1	1560.2	1452.6	1345.7	1248.9	1173.7
32.5°	2220.2	2212.3	2119.6	1974.0	1812.9	1646.3	1508.8	1400.0	1281.6	1186.5	1114.8
35°	2091.9	2126.5	2068.0	1930.0	1759.5	1579.7	1430.9	1306.6	1183.9	1092.9	1025.7
37.5°	1920.0	2006.0	1990.7	1865.8	1687.6	1507.2	1342.9	1213.1	1096.1	1004.2	938.3
40°	1801.5	1911.3	1927.1	1816.7	1636.8	1451.1	1277.1	1147.7	1033.6	949.9	883.4
42.5°	1674.3	1802.6	1846.3	1757.7	1581.3	1392.2	1218.1	1084.2	971.2	889.8	830.9
45°	1461.2	1631.0	1709.8	1659.2	1488.7	1295.1	1116.0	980.1	877.6	801.1	755.5
47.5°	1262.1	1447.6	1553.4	1535.5	1385.7	1194.0	1016.9	886.6	786.7	725.7	684.9
50°	1121.1	1311.7	1439.5	1445.4	1311.7	1121.7	944.1	821.2	729.5	672.5	639.2
52.5°	998.5	1180.5	1319.9	1350.6	1229.1	1046.6	878.7	756.6	675.8	623.4	593.6
55°	838.6	992.5	1147.1	1203.3	1105.9	932.6	777.2	669.6	593.7	557.6	531.6
57.5°	697.2	825.5	968.2	1030.5	970.3	822.0	676.4	582.9	521.4	489.7	469.8
60°	622.6	723.8	850.9	925.3	873.3	741.1	614.0	525.1	474.6	446.4	427.6
62.5°	553.3	642.9	750.4	818.4	790.0	665.4	551.6	473.2	429.5	403.0	389.5
65°	456.5	527.3	610.4	673.2	654.4	559.8	466.7	399.4	364.8	343.8	333.0
67.5°	375.9	427.1	484.7	539.7	524.5	457.5	382.7	330.4	304.5	286.4	279.9
70°	325.1	364.0	415.4	459.4	447.1	392.2	333.0	288.2	265.8	250.6	244.1
72.5°	276.5	308.6	347.7	383.7	375.4	329.8	280.4	246.6	229.4	215.4	210.1
75°	208.8	233.3	257.1	281.0	278.8	243.5	214.5	188.5	174.8	164.0	161.8
77.5°	154.1	167.9	184.1	198.2	194.3	174.1	151.4	136.5	126.4	119.1	118.0
80°	117.7	125.6	137.2	147.3	142.3	133.7	115.6	104.7	97.6	90.3	87.4
82.5°	85.4	93.3	100.3	105.8	101.9	93.8	82.7	75.3	71.0	66.0	64.8
85°	44.8	49.1	52.0	53.4	52.0	46.9	41.8	39.0	35.4	33.3	32.5
87.5°	21.1	20.7	20.3	21.0	18.7	18.1	15.3	12.9	12.9	12.9	12.3
90°	18.9	16.9	14.9	12.4	9.6	6.8	4.0	1.1	4.0	6.8	9.6
92.5°	24.7	23.7	22.6	22.2	22.5	22.8	23.0	23.3	23.0	22.8	22.5
95°	41.4	39.6	37.8	41.1	49.6	58.1	66.4	74.9	66.4	58.1	49.6
97.5°	51.8	47.7	43.5	53.4	77.3	101.0	124.9	148.7	124.9	101.0	77.3
100°	57.0	52.7	48.3	63.7	98.8	133.8	169.0	204.1	169.0	133.8	98.8
102.5°	140.4	176.8	213.3	235.3	242.7	250.1	257.5	264.9	257.5	250.1	242.7
105°	210.2	280.2	350.2	381.3	373.5	365.9	358.2	350.5	358.2	365.9	373.5
107.5°	266.3	350.2	434.0	472.9	466.7	460.4	454.2	448.1	454.2	460.4	466.7
110°	349.9	424.0	497.9	532.3	526.9	521.5	516.1	510.8	516.1	521.5	526.9





TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	545.5	563.8	582.1	588.9	584.1	579.3	574.6	569.8	574.6	579.3	584.1
115°	698.6	692.2	685.8	680.4	676.0	671.7	667.3	663.0	667.3	671.7	676.0
117.5°	779.1	774.7	770.3	765.7	760.8	755.9	751.1	746.2	751.1	755.9	760.8
120°	835.9	831.3	826.7	822.5	818.6	814.7	811.0	807.1	811.0	814.7	818.6
122.5°	889.5	884.5	879.5	875.0	870.9	866.9	862.8	858.8	862.8	866.9	870.9
125°	964.5	959.7	954.8	950.6	947.3	944.1	940.7	937.4	940.7	944.1	947.3
127.5°	1034.3	1030.7	1027.1	1023.4	1019.7	1016.0	1012.3	1008.6	1012.3	1016.0	1019.7
130°	1079.3	1076.5	1073.7	1070.3	1066.1	1062.1	1057.9	1053.9	1057.9	1062.1	1066.1
132.5°	1122.7	1119.8	1117.0	1113.9	1110.4	1106.9	1103.4	1099.9	1103.4	1106.9	1110.4
135°	1184.1	1181.8	1179.5	1176.3	1172.1	1168.1	1163.9	1159.9	1163.9	1168.1	1172.1
137.5°	1240.0	1237.4	1234.7	1232.0	1229.2	1226.2	1223.4	1220.5	1223.4	1226.2	1229.2
140°	1276.5	1273.7	1270.8	1268.4	1266.3	1264.3	1262.3	1260.2	1262.3	1264.3	1266.3
142.5°	1309.8	1306.6	1303.3	1300.8	1298.9	1297.1	1295.2	1293.5	1295.2	1297.1	1298.9
145°	1355.3	1350.9	1346.5	1344.5	1344.7	1345.0	1345.3	1345.5	1345.3	1345.0	1344.7
147.5°	1397.3	1393.0	1388.7	1387.0	1388.0	1389.0	1390.0	1390.9	1390.0	1389.0	1388.0
150°	1422.7	1418.5	1414.5	1413.2	1415.0	1416.9	1418.7	1420.5	1418.7	1416.9	1415.0
152.5°	1446.1	1442.2	1438.3	1437.4	1439.4	1441.3	1443.4	1445.4	1443.4	1441.3	1439.4
155°	1478.8	1475.8	1472.7	1472.3	1474.6	1477.0	1479.2	1481.6	1479.2	1477.0	1474.6
157.5°	1506.6	1504.4	1502.2	1502.1	1504.1	1506.0	1508.0	1510.0	1508.0	1506.0	1504.1
160°	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1525.0	1523.4	1521.9
162.5°	1537.7	1536.3	1535.0	1535.1	1536.7	1538.2	1539.7	1541.3	1539.7	1538.2	1536.7
165°	1556.1	1555.4	1554.6	1555.0	1556.5	1558.0	1559.6	1561.1	1559.6	1558.0	1556.5
167.5°	1570.7	1570.1	1569.3	1569.7	1571.3	1572.8	1574.3	1575.9	1574.3	1572.8	1571.3
170°	1578.6	1578.0	1577.5	1578.0	1579.6	1581.1	1582.6	1584.2	1582.6	1581.1	1579.6
172.5°	1584.0	1583.6	1583.1	1583.6	1585.1	1586.7	1588.2	1589.7	1588.2	1586.7	1585.1
175°	1590.1	1589.6	1589.0	1589.7	1591.5	1593.3	1595.1	1596.9	1595.1	1593.3	1591.5
177.5°	1592.0	1591.9	1591.7	1592.2	1593.7	1595.2	1596.6	1598.0	1596.6	1595.2	1593.7
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1854.6	1851.2	1839.0	1832.7	1822.3	1812.4	1806.1	1809.0	1811.3	1810.2	1808.4
5°	1801.5	1787.7	1766.8	1748.7	1735.7	1711.9	1701.8	1696.8	1692.4	1687.3	1682.2
7.5°	1738.1	1716.6	1686.5	1660.8	1636.4	1606.8	1590.0	1579.9	1569.4	1558.0	1547.9
10°	1693.1	1662.7	1631.0	1594.9	1566.0	1539.3	1515.4	1499.5	1485.1	1471.4	1461.2
12.5°	1645.8	1610.8	1571.5	1522.1	1490.3	1452.0	1448.4	1420.4	1397.8	1389.3	1377.4
15°	1570.3	1521.2	1471.4	1412.9	1387.6	1352.9	1331.2	1309.6	1290.1	1276.3	1272.7
17.5°	1484.7	1421.1	1371.5	1329.5	1288.1	1252.5	1232.6	1215.2	1199.2	1180.8	1178.4
20°	1419.4	1364.4	1310.3	1273.5	1230.9	1194.7	1170.2	1152.8	1139.1	1128.2	1118.9
22.5°	1357.5	1297.4	1247.8	1207.6	1165.5	1136.3	1117.0	1100.2	1088.8	1076.9	1068.0
25°	1258.3	1211.4	1157.2	1111.6	1076.9	1058.2	1042.3	1027.8	1020.7	1012.7	1002.6
27.5°	1171.5	1119.3	1068.6	1033.3	1002.9	986.3	975.0	965.2	958.4	953.8	948.0
30°	1110.2	1057.4	1017.8	983.1	957.8	941.2	934.0	928.2	920.2	917.4	914.5
32.5°	1051.2	1003.7	969.8	939.7	915.6	904.7	898.1	893.0	886.7	883.8	878.1
35°	967.9	928.2	894.9	878.4	858.8	849.4	844.4	837.2	831.4	828.5	827.7
37.5°	889.5	855.0	833.1	811.7	803.5	797.8	790.8	785.9	784.2	783.7	783.0
40°	838.6	810.4	791.0	773.6	770.0	761.3	755.5	751.2	751.2	752.0	751.2
42.5°	792.4	767.1	749.9	734.9	730.7	725.5	719.7	719.4	720.6	723.0	720.6
45°	722.4	704.3	692.0	684.8	676.8	671.8	671.0	673.2	673.9	674.7	676.8
47.5°	657.9	645.9	634.8	626.8	623.4	622.5	621.6	625.4	628.9	630.2	633.5
50°	619.7	606.1	596.6	591.5	588.7	587.2	588.7	593.0	595.9	599.6	601.7
52.5°	577.0	567.3	560.8	556.9	555.7	556.7	556.9	561.8	566.5	567.8	568.7
55°	517.9	510.7	509.3	502.8	505.6	504.9	508.5	511.4	515.8	520.1	520.8
57.5°	458.9	453.2	449.3	449.9	450.7	453.9	456.9	462.0	466.7	471.3	471.6
60°	419.7	416.8	414.6	414.6	416.0	420.4	424.0	429.0	432.0	434.8	437.0
62.5°	383.8	381.0	378.8	379.9	383.7	386.3	390.5	393.2	396.2	399.0	400.0
65°	327.3	325.7	327.9	329.4	330.1	333.8	338.7	340.9	343.8	345.3	350.3
67.5°	275.0	275.3	275.0	277.1	281.3	282.1	286.9	292.0	292.6	295.3	298.6
70°	239.8	241.3	242.7	244.1	247.8	249.2	252.8	255.0	257.9	260.0	262.2
72.5°	207.5	207.7	209.2	208.9	211.9	215.1	218.1	220.3	223.2	225.9	228.1
75°	159.7	159.7	161.1	161.8	165.4	169.0	168.3	169.8	172.7	175.5	177.0
77.5°	116.6	115.0	116.6	117.3	118.5	121.5	122.1	124.1	127.4	126.4	128.0
80°	88.9	86.7	88.9	89.5	89.5	93.2	93.2	94.6	96.8	94.6	96.8
82.5°	63.4	62.4	64.0	64.2	65.3	65.4	66.6	66.9	69.1	68.1	69.1
85°	31.8	31.1	31.8	31.1	31.8	32.5	32.5	31.8	31.8	33.3	31.1
87.5°	12.3	12.3	12.1	12.4	12.3	12.2	11.8	12.1	12.3	11.4	11.6
90°	12.4	14.9	16.9	18.9	21.0	23.1	24.3	25.6	26.9	28.2	29.1
92.5°	22.2	22.6	23.7	24.7	25.7	26.8	27.4	28.1	28.7	29.4	29.9
95°	41.1	37.8	39.6	41.4	43.2	45.0	46.3	47.5	48.8	50.0	50.6
97.5°	53.4	43.5	47.7	51.8	56.1	60.2	61.2	62.2	63.2	64.3	64.9
100°	63.7	48.3	52.7	57.0	61.4	65.7	67.8	69.8	71.8	73.9	75.2
102.5°	235.3	213.3	176.8	140.4	104.0	67.6	70.2	72.9	75.6	78.2	79.9
105°	381.3	350.2	280.2	210.2	140.3	70.3	73.1	76.0	78.8	81.6	83.5
107.5°	472.9	434.0	350.2	266.3	182.4	98.5	95.6	92.7	89.8	87.0	86.1
110°	532.3	497.9	424.0	349.9	275.8	201.8	176.2	150.5	124.9	99.2	87.0



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.9	582.1	563.8	545.5	527.3	508.9	415.5	322.0	228.6	135.1	88.7
115°	680.4	685.8	692.2	698.6	705.0	711.4	592.8	474.1	355.5	236.9	168.3
117.5°	765.7	770.3	774.7	779.1	783.5	788.0	759.2	730.6	701.8	673.2	628.5
120°	822.5	826.7	831.3	835.9	840.6	845.1	848.2	851.3	854.3	857.4	841.7
122.5°	875.0	879.5	884.5	889.5	894.6	899.6	901.4	903.2	905.1	906.9	904.5
125°	950.6	954.8	959.7	964.5	969.4	974.3	976.1	977.9	979.7	981.5	982.7
127.5°	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2	1046.8	1049.4	1052.1	1053.5
130°	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8	1090.6	1093.4	1096.2	1097.5
132.5°	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7	1133.1	1135.5	1137.9	1139.0
135°	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3	1193.8	1196.4	1199.0	1200.0
137.5°	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7	1250.2	1252.7	1255.3	1256.0
140°	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4	1286.8	1289.0	1291.4	1291.8
142.5°	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3	1320.4	1322.6	1324.6	1325.0
145°	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7	1367.5	1369.3	1371.1	1371.4
147.5°	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3	1408.6	1409.9	1411.3	1411.4
150°	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4	1433.9	1435.5	1437.0	1437.1
152.5°	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5	1457.0	1458.5	1460.1	1460.0
155°	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6	1488.1	1489.7	1491.2	1490.9
157.5°	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6	1514.4	1516.1	1517.9	1517.7
160°	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0	1529.7	1531.2	1532.7	1532.6
162.5°	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1	1543.9	1545.6	1547.4	1547.1
165°	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4	1561.2	1563.0	1564.8	1564.8
167.5°	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0	1575.7	1577.5	1579.3	1579.1
170°	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4	1583.2	1585.0	1586.8	1586.5
172.5°	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9	1588.7	1590.4	1592.2	1592.0
175°	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9	1594.7	1596.5	1598.3	1597.9
177.5°	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9	1595.3	1596.8	1598.3	1598.0
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1802.6	1801.5	1801.5	1796.3	1801.5	1801.5	1802.6	1808.4	1810.2	1811.3	1809.0
5°	1672.2	1670.0	1666.4	1670.0	1666.4	1670.0	1672.2	1682.2	1687.3	1692.4	1696.8
7.5°	1543.1	1534.5	1533.2	1524.7	1533.2	1534.5	1543.1	1547.9	1558.0	1569.4	1579.9
10°	1449.0	1443.2	1442.5	1428.7	1442.5	1443.2	1449.0	1461.2	1471.4	1485.1	1499.5
12.5°	1377.3	1363.5	1366.2	1358.2	1366.2	1363.5	1377.3	1377.4	1389.3	1397.8	1420.4
15°	1253.2	1253.2	1250.4	1238.0	1250.4	1253.2	1253.2	1272.7	1276.3	1290.1	1309.6
17.5°	1164.1	1162.6	1155.7	1159.1	1155.7	1162.6	1164.1	1178.4	1180.8	1199.2	1215.2
20°	1110.9	1106.6	1098.0	1098.0	1098.0	1106.6	1110.9	1118.9	1128.2	1139.1	1152.8
22.5°	1060.6	1060.4	1051.1	1054.0	1051.1	1060.4	1060.6	1068.0	1076.9	1088.8	1100.2
25°	1001.8	996.1	991.7	993.9	991.7	996.1	1001.8	1002.6	1012.7	1020.7	1027.8
27.5°	946.1	942.9	942.6	936.7	942.6	942.9	946.1	948.0	953.8	958.4	965.2
30°	913.7	906.5	908.0	904.4	908.0	906.5	913.7	914.5	917.4	920.2	928.2
32.5°	876.8	874.1	872.7	869.7	872.7	874.1	876.8	878.1	883.8	886.7	893.0
35°	826.3	827.1	823.4	824.9	823.4	827.1	826.3	827.7	828.5	831.4	837.2
37.5°	782.3	784.6	782.9	783.3	782.9	784.6	782.3	783.0	783.7	784.2	785.9
40°	753.4	753.4	753.4	755.5	753.4	753.4	753.4	751.2	752.0	751.2	751.2
42.5°	725.7	724.5	723.3	723.2	723.3	724.5	725.7	720.6	723.0	720.6	719.4
45°	678.3	680.4	681.2	677.5	681.2	680.4	678.3	676.8	674.7	673.9	673.2
47.5°	635.4	635.7	635.4	638.6	635.4	635.7	635.4	633.5	630.2	628.9	625.4
50°	605.3	603.9	605.3	603.9	605.3	603.9	605.3	601.7	599.6	595.9	593.0
52.5°	573.5	573.8	573.0	572.7	573.0	573.8	573.5	568.7	567.8	566.5	561.8
55°	523.7	525.1	524.4	524.4	524.4	525.1	523.7	520.8	520.1	515.8	511.4
57.5°	472.1	473.4	474.4	471.3	474.4	473.4	472.1	471.6	471.3	466.7	462.0
60°	436.3	439.9	439.1	437.7	439.1	439.9	436.3	437.0	434.8	432.0	429.0
62.5°	403.3	404.6	404.5	404.3	404.5	404.6	403.3	400.0	399.0	396.2	393.2
65°	352.5	353.9	351.8	353.9	351.8	353.9	352.5	350.3	345.3	343.8	340.9
67.5°	297.7	298.2	299.7	300.8	299.7	298.2	297.7	298.6	295.3	292.6	292.0
70°	263.6	263.0	265.1	267.3	265.1	263.0	263.6	262.2	260.0	257.9	255.0
72.5°	227.8	229.4	228.7	230.3	228.7	229.4	227.8	228.1	225.9	223.2	220.3
75°	175.5	177.7	177.0	179.2	177.0	177.7	175.5	177.0	175.5	172.7	169.8
77.5°	126.9	127.1	126.9	128.0	126.9	127.1	126.9	128.0	126.4	127.4	124.1
80°	96.8	95.4	93.9	96.8	93.9	95.4	96.8	96.8	94.6	96.8	94.6
82.5°	67.3	68.1	66.7	66.7	66.7	68.1	67.3	69.1	68.1	69.1	66.9
85°	31.1	30.3	28.9	28.9	28.9	30.3	31.1	31.1	33.3	31.8	31.8
87.5°	11.7	11.2	11.3	10.8	11.3	11.2	11.7	11.6	11.4	12.3	12.1
90°	29.6	30.1	30.6	31.1	30.6	30.1	29.6	29.1	28.2	26.9	25.6
92.5°	30.2	30.5	30.8	31.1	30.8	30.5	30.2	29.9	29.4	28.7	28.1
95°	50.3	50.0	49.9	49.6	49.9	50.0	50.3	50.6	50.0	48.8	47.5
97.5°	65.2	65.6	65.9	66.2	65.9	65.6	65.2	64.9	64.3	63.2	62.2
100°	75.7	76.3	76.7	77.3	76.7	76.3	75.7	75.2	73.9	71.8	69.8
102.5°	80.6	81.3	82.1	82.8	82.1	81.3	80.6	79.9	78.2	75.6	72.9
105°	84.5	85.6	86.6	87.7	86.6	85.6	84.5	83.5	81.6	78.8	76.0
107.5°	87.1	88.1	89.2	90.2	89.2	88.1	87.1	86.1	87.0	89.8	92.7
110°	88.0	89.1	90.1	91.0	90.1	89.1	88.0	87.0	99.2	124.9	150.5



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	89.5	90.4	91.1	92.0	91.1	90.4	89.5	88.7	135.1	228.6	322.0
115°	149.9	131.5	113.0	94.5	113.0	131.5	149.9	168.3	236.9	355.5	474.1
117.5°	567.9	507.3	446.7	386.0	446.7	507.3	567.9	628.5	673.2	701.8	730.6
120°	807.1	772.5	737.9	703.3	737.9	772.5	807.1	841.7	857.4	854.3	851.3
122.5°	897.8	891.1	884.4	877.6	884.4	891.1	897.8	904.5	906.9	905.1	903.2
125°	983.4	984.3	985.1	985.8	985.1	984.3	983.4	982.7	981.5	979.7	977.9
127.5°	1053.6	1053.8	1053.9	1054.0	1053.9	1053.8	1053.6	1053.5	1052.1	1049.4	1046.8
130°	1097.2	1097.0	1096.7	1096.5	1096.7	1097.0	1097.2	1097.5	1096.2	1093.4	1090.6
132.5°	1138.8	1138.5	1138.2	1138.0	1138.2	1138.5	1138.8	1139.0	1137.9	1135.5	1133.1
135°	1199.5	1199.0	1198.4	1198.0	1198.4	1199.0	1199.5	1200.0	1199.0	1196.4	1193.8
137.5°	1255.2	1254.3	1253.5	1252.5	1253.5	1254.3	1255.2	1256.0	1255.3	1252.7	1250.2
140°	1290.5	1289.3	1288.0	1286.8	1288.0	1289.3	1290.5	1291.8	1291.4	1289.0	1286.8
142.5°	1323.8	1322.5	1321.2	1319.9	1321.2	1322.5	1323.8	1325.0	1324.6	1322.6	1320.4
145°	1370.1	1368.9	1367.5	1366.3	1367.5	1368.9	1370.1	1371.4	1371.1	1369.3	1367.5
147.5°	1410.3	1409.2	1408.2	1407.1	1408.2	1409.2	1410.3	1411.4	1411.3	1409.9	1408.6
150°	1435.9	1434.5	1433.2	1432.0	1433.2	1434.5	1435.9	1437.1	1437.0	1435.5	1433.9
152.5°	1458.3	1456.6	1454.9	1453.2	1454.9	1456.6	1458.3	1460.0	1460.1	1458.5	1457.0
155°	1488.8	1486.9	1484.8	1482.7	1484.8	1486.9	1488.8	1490.9	1491.2	1489.7	1488.1
157.5°	1515.7	1513.7	1511.7	1509.7	1511.7	1513.7	1515.7	1517.7	1517.9	1516.1	1514.4
160°	1530.8	1529.0	1527.2	1525.4	1527.2	1529.0	1530.8	1532.6	1532.7	1531.2	1529.7
162.5°	1544.9	1542.7	1540.5	1538.3	1540.5	1542.7	1544.9	1547.1	1547.4	1545.6	1543.9
165°	1563.0	1561.2	1559.4	1557.6	1559.4	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2
167.5°	1576.8	1574.5	1572.2	1569.9	1572.2	1574.5	1576.8	1579.1	1579.3	1577.5	1575.7
170°	1584.2	1581.9	1579.6	1577.3	1579.6	1581.9	1584.2	1586.5	1586.8	1585.0	1583.2
172.5°	1589.7	1587.4	1585.1	1582.8	1585.1	1587.4	1589.7	1592.0	1592.2	1590.4	1588.7
175°	1595.3	1592.8	1590.2	1587.6	1590.2	1592.8	1595.3	1597.9	1598.3	1596.5	1594.7
177.5°	1596.2	1594.3	1592.5	1590.6	1592.5	1594.3	1596.2	1598.0	1598.3	1596.8	1595.3
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1806.1	1812.4	1822.3	1832.7	1839.0	1851.2	1854.6	1860.4	1865.6	1877.7	1890.5
5°	1701.8	1711.9	1735.7	1748.7	1766.8	1787.7	1801.5	1815.9	1831.8	1859.3	1884.5
7.5°	1590.0	1606.8	1636.4	1660.8	1686.5	1716.6	1738.1	1766.8	1790.5	1829.2	1866.1
10°	1515.4	1539.3	1566.0	1594.9	1631.0	1662.7	1693.1	1729.2	1758.1	1804.3	1847.7
12.5°	1448.4	1452.0	1490.3	1522.1	1571.5	1610.8	1645.8	1692.2	1720.5	1775.5	1821.1
15°	1331.2	1352.9	1387.6	1412.9	1471.4	1521.2	1570.3	1618.7	1651.2	1719.1	1779.0
17.5°	1232.6	1252.5	1288.1	1329.5	1371.5	1421.1	1484.7	1535.7	1579.9	1657.5	1728.3
20°	1170.2	1194.7	1230.9	1273.5	1310.3	1364.4	1419.4	1477.9	1525.5	1613.0	1696.0
22.5°	1117.0	1136.3	1165.5	1207.6	1247.8	1297.4	1357.5	1421.3	1471.2	1565.6	1649.7
25°	1042.3	1058.2	1076.9	1111.6	1157.2	1211.4	1258.3	1328.3	1401.3	1489.4	1591.3
27.5°	975.0	986.3	1002.9	1033.3	1068.6	1119.3	1171.5	1237.9	1311.3	1406.9	1514.4
30°	934.0	941.2	957.8	983.1	1017.8	1057.4	1110.2	1173.7	1248.9	1345.7	1452.6
32.5°	898.1	904.7	915.6	939.7	969.8	1003.7	1051.2	1114.8	1186.5	1281.6	1400.0
35°	844.4	849.4	858.8	878.4	894.9	928.2	967.9	1025.7	1092.9	1183.9	1306.6
37.5°	790.8	797.8	803.5	811.7	833.1	855.0	889.5	938.3	1004.2	1096.1	1213.1
40°	755.5	761.3	770.0	773.6	791.0	810.4	838.6	883.4	949.9	1033.6	1147.7
42.5°	719.7	725.5	730.7	734.9	749.9	767.1	792.4	830.9	889.8	971.2	1084.2
45°	671.0	671.8	676.8	684.8	692.0	704.3	722.4	755.5	801.1	877.6	980.1
47.5°	621.6	622.5	623.4	626.8	634.8	645.9	657.9	684.9	725.7	786.7	886.6
50°	588.7	587.2	588.7	591.5	596.6	606.1	619.7	639.2	672.5	729.5	821.2
52.5°	556.9	556.7	555.7	556.9	560.8	567.3	577.0	593.6	623.4	675.8	756.6
55°	508.5	504.9	505.6	502.8	509.3	510.7	517.9	531.6	557.6	593.7	669.6
57.5°	456.9	453.9	450.7	449.9	449.3	453.2	458.9	469.8	489.7	521.4	582.9
60°	424.0	420.4	416.0	414.6	414.6	416.8	419.7	427.6	446.4	474.6	525.1
62.5°	390.5	386.3	383.7	379.9	378.8	381.0	383.8	389.5	403.0	429.5	473.2
65°	338.7	333.8	330.1	329.4	327.9	325.7	327.3	333.0	343.8	364.8	399.4
67.5°	286.9	282.1	281.3	277.1	275.0	275.3	275.0	279.9	286.4	304.5	330.4
70°	252.8	249.2	247.8	244.1	242.7	241.3	239.8	244.1	250.6	265.8	288.2
72.5°	218.1	215.1	211.9	208.9	209.2	207.7	207.5	210.1	215.4	229.4	246.6
75°	168.3	169.0	165.4	161.8	161.1	159.7	159.7	161.8	164.0	174.8	188.5
77.5°	122.1	121.5	118.5	117.3	116.6	115.0	116.6	118.0	119.1	126.4	136.5
80°	93.2	93.2	89.5	89.5	88.9	86.7	88.9	87.4	90.3	97.6	104.7
82.5°	66.6	65.4	65.3	64.2	64.0	62.4	63.4	64.8	66.0	71.0	75.3
85°	32.5	32.5	31.8	31.1	31.8	31.1	31.8	32.5	33.3	35.4	39.0
87.5°	11.8	12.2	12.3	12.4	12.1	12.3	12.3	12.3	12.9	12.9	12.9
90°	24.3	23.1	21.0	18.9	16.9	14.9	12.4	9.6	6.8	4.0	1.1
92.5°	27.4	26.8	25.7	24.7	23.7	22.6	22.2	22.5	22.8	23.0	23.3
95°	46.3	45.0	43.2	41.4	39.6	37.8	41.1	49.6	58.1	66.4	74.9
97.5°	61.2	60.2	56.1	51.8	47.7	43.5	53.4	77.3	101.0	124.9	148.7
100°	67.8	65.7	61.4	57.0	52.7	48.3	63.7	98.8	133.8	169.0	204.1
102.5°	70.2	67.6	104.0	140.4	176.8	213.3	235.3	242.7	250.1	257.5	264.9
105°	73.1	70.3	140.3	210.2	280.2	350.2	381.3	373.5	365.9	358.2	350.5
107.5°	95.6	98.5	182.4	266.3	350.2	434.0	472.9	466.7	460.4	454.2	448.1
110°	176.2	201.8	275.8	349.9	424.0	497.9	532.3	526.9	521.5	516.1	510.8



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.5	508.9	527.3	545.5	563.8	582.1	588.9	584.1	579.3	574.6	569.8
115°	592.8	711.4	705.0	698.6	692.2	685.8	680.4	676.0	671.7	667.3	663.0
117.5°	759.2	788.0	783.5	779.1	774.7	770.3	765.7	760.8	755.9	751.1	746.2
120°	848.2	845.1	840.6	835.9	831.3	826.7	822.5	818.6	814.7	811.0	807.1
122.5°	901.4	899.6	894.6	889.5	884.5	879.5	875.0	870.9	866.9	862.8	858.8
125°	976.1	974.3	969.4	964.5	959.7	954.8	950.6	947.3	944.1	940.7	937.4
127.5°	1044.2	1041.6	1037.9	1034.3	1030.7	1027.1	1023.4	1019.7	1016.0	1012.3	1008.6
130°	1087.8	1085.0	1082.1	1079.3	1076.5	1073.7	1070.3	1066.1	1062.1	1057.9	1053.9
132.5°	1130.7	1128.3	1125.5	1122.7	1119.8	1117.0	1113.9	1110.4	1106.9	1103.4	1099.9
135°	1191.3	1188.7	1186.4	1184.1	1181.8	1179.5	1176.3	1172.1	1168.1	1163.9	1159.9
137.5°	1247.7	1245.2	1242.6	1240.0	1237.4	1234.7	1232.0	1229.2	1226.2	1223.4	1220.5
140°	1284.4	1282.1	1279.3	1276.5	1273.7	1270.8	1268.4	1266.3	1264.3	1262.3	1260.2
142.5°	1318.3	1316.3	1313.0	1309.8	1306.6	1303.3	1300.8	1298.9	1297.1	1295.2	1293.5
145°	1365.7	1364.0	1359.6	1355.3	1350.9	1346.5	1344.5	1344.7	1345.0	1345.3	1345.5
147.5°	1407.3	1405.9	1401.7	1397.3	1393.0	1388.7	1387.0	1388.0	1389.0	1390.0	1390.9
150°	1432.4	1430.9	1426.7	1422.7	1418.5	1414.5	1413.2	1415.0	1416.9	1418.7	1420.5
152.5°	1455.5	1453.9	1450.0	1446.1	1442.2	1438.3	1437.4	1439.4	1441.3	1443.4	1445.4
155°	1486.6	1485.1	1482.0	1478.8	1475.8	1472.7	1472.3	1474.6	1477.0	1479.2	1481.6
157.5°	1512.6	1510.9	1508.7	1506.6	1504.4	1502.2	1502.1	1504.1	1506.0	1508.0	1510.0
160°	1528.0	1526.5	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5
162.5°	1542.1	1540.4	1539.1	1537.7	1536.3	1535.0	1535.1	1536.7	1538.2	1539.7	1541.3
165°	1559.4	1557.6	1556.9	1556.1	1555.4	1554.6	1555.0	1556.5	1558.0	1559.6	1561.1
167.5°	1574.0	1572.2	1571.5	1570.7	1570.1	1569.3	1569.7	1571.3	1572.8	1574.3	1575.9
170°	1581.4	1579.6	1579.0	1578.6	1578.0	1577.5	1578.0	1579.6	1581.1	1582.6	1584.2
172.5°	1586.9	1585.1	1584.6	1584.0	1583.6	1583.1	1583.6	1585.1	1586.7	1588.2	1589.7
175°	1592.9	1591.1	1590.6	1590.1	1589.6	1589.0	1589.7	1591.5	1593.3	1595.1	1596.9
177.5°	1593.9	1592.5	1592.2	1592.0	1591.9	1591.7	1592.2	1593.7	1595.2	1596.6	1598.0
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1889.3	1892.2	1901.4	1910.7	1921.1	1924.0	1928.6	1924.6	1923.4	1934.4	1942.5
5°	1894.6	1907.6	1933.0	1956.1	1975.6	1989.2	2003.8	2009.5	2020.3	2035.5	2054.3
7.5°	1888.6	1913.8	1953.6	1987.3	2023.9	2050.4	2071.0	2088.7	2110.1	2138.8	2170.1
10°	1881.6	1915.6	1964.0	2005.2	2049.9	2083.9	2112.0	2139.5	2171.3	2211.0	2252.2
12.5°	1869.0	1909.2	1969.7	2018.5	2075.9	2109.3	2147.3	2206.6	2240.6	2295.9	2353.9
15°	1843.3	1888.1	1972.6	2032.6	2097.6	2161.2	2231.3	2287.6	2343.9	2376.4	2458.1
17.5°	1805.3	1871.1	1964.7	2034.7	2117.2	2217.3	2296.1	2359.9	2425.0	2477.7	2518.6
20°	1774.7	1846.3	1953.1	2036.9	2135.1	2242.8	2333.1	2398.1	2454.5	2498.5	2523.8
22.5°	1736.0	1826.0	1930.0	2028.3	2153.7	2260.1	2355.0	2406.2	2453.2	2474.8	2484.4
25°	1675.1	1783.4	1901.1	2021.1	2162.7	2275.3	2362.0	2393.0	2406.8	2385.9	2351.2
27.5°	1609.3	1730.1	1867.7	2007.4	2157.1	2265.5	2327.6	2322.7	2299.4	2231.7	2177.5
30°	1560.2	1693.1	1841.2	1993.6	2143.8	2249.3	2285.4	2249.3	2196.6	2120.7	2043.4
32.5°	1508.8	1646.3	1812.9	1974.0	2119.6	2212.3	2220.2	2158.0	2076.4	1990.2	1893.8
35°	1430.9	1579.7	1759.5	1930.0	2068.0	2126.5	2091.9	1982.1	1885.3	1767.6	1636.1
37.5°	1342.9	1507.2	1687.6	1865.8	1990.7	2006.0	1920.0	1804.3	1667.8	1529.5	1374.7
40°	1277.1	1451.1	1636.8	1816.7	1927.1	1911.3	1801.5	1674.3	1511.8	1342.7	1199.0
42.5°	1218.1	1392.2	1581.3	1757.7	1846.3	1802.6	1674.3	1518.3	1343.7	1184.5	1052.8
45°	1116.0	1295.1	1488.7	1659.2	1709.8	1631.0	1461.2	1287.9	1116.0	983.1	879.1
47.5°	1016.9	1194.0	1385.7	1535.5	1553.4	1447.6	1262.1	1083.6	935.9	827.6	754.2
50°	944.1	1121.7	1311.7	1445.4	1439.5	1311.7	1121.1	951.3	827.7	740.4	691.3
52.5°	878.7	1046.6	1229.1	1350.6	1319.9	1180.5	998.5	847.8	746.3	678.0	633.5
55°	777.2	932.6	1105.9	1203.3	1147.1	992.5	838.6	717.3	642.2	590.9	556.2
57.5°	676.4	822.0	970.3	1030.5	968.2	825.5	697.2	609.2	552.7	514.7	492.2
60°	614.0	741.1	873.3	925.3	850.9	723.8	622.6	543.9	498.4	467.3	447.1
62.5°	551.6	665.4	790.0	818.4	750.4	642.9	553.3	487.9	450.4	422.8	403.8
65°	466.7	559.8	654.4	673.2	610.4	527.3	456.5	413.9	380.7	360.4	345.3
67.5°	382.7	457.5	524.5	539.7	484.7	427.1	375.9	338.7	316.2	299.4	286.6
70°	333.0	392.2	447.1	459.4	415.4	364.0	325.1	295.4	275.2	260.8	248.5
72.5°	280.4	329.8	375.4	383.7	347.7	308.6	276.5	253.3	235.4	226.1	214.4
75°	214.5	243.5	278.8	281.0	257.1	233.3	208.8	193.6	184.2	172.7	166.8
77.5°	151.4	174.1	194.3	198.2	184.1	167.9	154.1	142.1	134.2	128.8	123.5
80°	115.6	133.7	142.3	147.3	137.2	125.6	117.7	109.8	104.7	101.1	97.6
82.5°	82.7	93.8	101.9	105.8	100.3	93.3	85.4	80.9	77.0	74.0	72.7
85°	41.8	46.9	52.0	53.4	52.0	49.1	44.8	44.8	42.6	41.8	41.8
87.5°	15.3	18.1	18.7	21.0	20.3	20.7	21.1	20.9	20.8	20.5	20.2
90°	4.0	6.8	9.6	12.4	14.9	16.9	18.9	21.0	23.1	24.3	25.6
92.5°	23.0	22.8	22.5	22.2	22.6	23.7	24.7	25.7	26.8	27.4	28.1
95°	66.4	58.1	49.6	41.1	37.8	39.6	41.4	43.2	45.0	46.3	47.5
97.5°	124.9	101.0	77.3	53.4	43.5	47.7	51.8	56.1	60.2	61.2	62.2
100°	169.0	133.8	98.8	63.7	48.3	52.7	57.0	61.4	65.7	67.8	69.8
102.5°	257.5	250.1	242.7	235.3	213.3	176.8	140.4	104.0	67.6	70.2	72.9
105°	358.2	365.9	373.5	381.3	350.2	280.2	210.2	140.3	70.3	73.1	76.0
107.5°	454.2	460.4	466.7	472.9	434.0	350.2	266.3	182.4	98.5	95.6	92.7
110°	516.1	521.5	526.9	532.3	497.9	424.0	349.9	275.8	201.8	176.2	150.5





TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	574.6	579.3	584.1	588.9	582.1	563.8	545.5	527.3	508.9	415.5	322.0
115°	667.3	671.7	676.0	680.4	685.8	692.2	698.6	705.0	711.4	592.8	474.1
117.5°	751.1	755.9	760.8	765.7	770.3	774.7	779.1	783.5	788.0	759.2	730.6
120°	811.0	814.7	818.6	822.5	826.7	831.3	835.9	840.6	845.1	848.2	851.3
122.5°	862.8	866.9	870.9	875.0	879.5	884.5	889.5	894.6	899.6	901.4	903.2
125°	940.7	944.1	947.3	950.6	954.8	959.7	964.5	969.4	974.3	976.1	977.9
127.5°	1012.3	1016.0	1019.7	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2	1046.8
130°	1057.9	1062.1	1066.1	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8	1090.6
132.5°	1103.4	1106.9	1110.4	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7	1133.1
135°	1163.9	1168.1	1172.1	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3	1193.8
137.5°	1223.4	1226.2	1229.2	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7	1250.2
140°	1262.3	1264.3	1266.3	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4	1286.8
142.5°	1295.2	1297.1	1298.9	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3	1320.4
145°	1345.3	1345.0	1344.7	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7	1367.5
147.5°	1390.0	1389.0	1388.0	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3	1408.6
150°	1418.7	1416.9	1415.0	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4	1433.9
152.5°	1443.4	1441.3	1439.4	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5	1457.0
155°	1479.2	1477.0	1474.6	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6	1488.1
157.5°	1508.0	1506.0	1504.1	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6	1514.4
160°	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0	1529.7
162.5°	1539.7	1538.2	1536.7	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1	1543.9
165°	1559.6	1558.0	1556.5	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4	1561.2
167.5°	1574.3	1572.8	1571.3	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0	1575.7
170°	1582.6	1581.1	1579.6	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4	1583.2
172.5°	1588.2	1586.7	1585.1	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9	1588.7
175°	1595.1	1593.3	1591.5	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9	1594.7
177.5°	1596.6	1595.2	1593.7	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9	1595.3
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1949.4	1957.5	1957.5	1958.6	1967.8	1966.7	1966.1
5°	2074.5	2086.8	2088.2	2101.2	2109.9	2107.0	2099.0
7.5°	2192.5	2215.4	2232.7	2242.4	2253.8	2260.9	2257.7
10°	2286.1	2319.4	2339.6	2353.3	2369.9	2382.2	2377.8
12.5°	2371.1	2410.6	2438.5	2461.9	2464.1	2479.8	2469.2
15°	2503.6	2545.4	2549.8	2567.1	2580.9	2579.4	2580.1
17.5°	2547.3	2560.8	2563.5	2563.9	2564.1	2559.0	2548.1
20°	2531.8	2526.7	2514.4	2505.0	2488.4	2486.2	2471.8
22.5°	2457.8	2441.8	2410.9	2390.6	2364.7	2358.0	2353.9
25°	2312.2	2276.7	2227.6	2180.7	2167.7	2142.4	2149.7
27.5°	2112.3	2057.2	2004.0	1965.9	1931.4	1893.5	1904.3
30°	1971.9	1909.8	1834.7	1776.9	1740.0	1703.9	1697.4
32.5°	1804.3	1713.4	1629.6	1578.7	1522.2	1499.4	1474.4
35°	1515.4	1426.5	1343.5	1272.0	1230.9	1199.0	1170.2
37.5°	1255.6	1153.3	1086.2	1028.3	998.5	980.3	985.0
40°	1094.3	1004.8	955.6	911.5	884.1	871.1	874.0
42.5°	963.7	896.6	856.2	826.0	806.7	799.5	797.8
45°	815.5	778.0	744.7	727.4	718.0	710.0	705.0
47.5°	714.4	683.7	665.0	654.7	646.5	638.4	638.2
50°	653.7	633.5	620.5	609.6	603.1	597.4	602.4
52.5°	607.5	589.0	576.0	566.3	563.8	558.6	558.5
55°	538.9	524.4	515.0	506.3	502.0	499.1	495.5
57.5°	476.5	462.7	454.0	448.6	440.4	437.4	436.3
60°	432.0	421.1	412.5	405.2	401.6	395.9	395.9
62.5°	390.9	380.1	372.0	366.5	360.6	358.3	358.8
65°	331.6	322.9	314.9	309.2	307.7	303.4	304.8
67.5°	276.9	271.2	262.8	259.6	256.8	254.6	252.8
70°	240.5	234.8	230.5	226.1	223.9	223.9	223.9
72.5°	209.9	202.9	200.4	194.9	196.1	193.9	191.5
75°	162.5	158.2	156.0	153.8	150.2	150.2	150.2
77.5°	119.6	118.3	115.7	113.4	112.5	111.8	112.1
80°	92.5	91.7	90.3	90.3	88.9	88.1	86.7
82.5°	71.1	69.2	68.3	67.8	67.5	67.3	67.0
85°	40.4	39.0	39.0	39.7	38.3	38.3	39.0
87.5°	21.0	21.2	20.8	20.9	21.6	21.1	21.2
90°	26.9	28.2	29.1	29.6	30.1	30.6	31.1
92.5°	28.7	29.4	29.9	30.2	30.5	30.8	31.1
95°	48.8	50.0	50.6	50.3	50.0	49.9	49.6
97.5°	63.2	64.3	64.9	65.2	65.6	65.9	66.2
100°	71.8	73.9	75.2	75.7	76.3	76.7	77.3
102.5°	75.6	78.2	79.9	80.6	81.3	82.1	82.8
105°	78.8	81.6	83.5	84.5	85.6	86.6	87.7
107.5°	89.8	87.0	86.1	87.1	88.1	89.2	90.2
110°	124.9	99.2	87.0	88.0	89.1	90.1	91.0



TEST NUMBER: P331603-830

CATALOG NUMBER: S122DIW-S1005D1240U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	228.6	135.1	88.7	89.5	90.4	91.1	92.0
115°	355.5	236.9	168.3	149.9	131.5	113.0	94.5
117.5°	701.8	673.2	628.5	567.9	507.3	446.7	386.0
120°	854.3	857.4	841.7	807.1	772.5	737.9	703.3
122.5°	905.1	906.9	904.5	897.8	891.1	884.4	877.6
125°	979.7	981.5	982.7	983.4	984.3	985.1	985.8
127.5°	1049.4	1052.1	1053.5	1053.6	1053.8	1053.9	1054.0
130°	1093.4	1096.2	1097.5	1097.2	1097.0	1096.7	1096.5
132.5°	1135.5	1137.9	1139.0	1138.8	1138.5	1138.2	1138.0
135°	1196.4	1199.0	1200.0	1199.5	1199.0	1198.4	1198.0
137.5°	1252.7	1255.3	1256.0	1255.2	1254.3	1253.5	1252.5
140°	1289.0	1291.4	1291.8	1290.5	1289.3	1288.0	1286.8
142.5°	1322.6	1324.6	1325.0	1323.8	1322.5	1321.2	1319.9
145°	1369.3	1371.1	1371.4	1370.1	1368.9	1367.5	1366.3
147.5°	1409.9	1411.3	1411.4	1410.3	1409.2	1408.2	1407.1
150°	1435.5	1437.0	1437.1	1435.9	1434.5	1433.2	1432.0
152.5°	1458.5	1460.1	1460.0	1458.3	1456.6	1454.9	1453.2
155°	1489.7	1491.2	1490.9	1488.8	1486.9	1484.8	1482.7
157.5°	1516.1	1517.9	1517.7	1515.7	1513.7	1511.7	1509.7
160°	1531.2	1532.7	1532.6	1530.8	1529.0	1527.2	1525.4
162.5°	1545.6	1547.4	1547.1	1544.9	1542.7	1540.5	1538.3
165°	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6
167.5°	1577.5	1579.3	1579.1	1576.8	1574.5	1572.2	1569.9
170°	1585.0	1586.8	1586.5	1584.2	1581.9	1579.6	1577.3
172.5°	1590.4	1592.2	1592.0	1589.7	1587.4	1585.1	1582.8
175°	1596.5	1598.3	1597.9	1595.3	1592.8	1590.2	1587.6
177.5°	1596.8	1598.3	1598.0	1596.2	1594.3	1592.5	1590.6
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4

(END OF REPORT)